

# Surface Mount Bandpass Filter

## BPF-BD1800+

50Ω 1600 to 2000 MHz

### The Big Deal

- Wide bandwidth
- Rejection upto  $2x F_c$
- Miniature shielded package



Generic photo used for illustration purposes only  
CASE STYLE: TV2849

### Product Overview

The BPF-BD1800+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 1600-2000 MHz. This filter is built with high Q capacitors and air-coil inductors for superior performance. It has repeatable performance across lots and consistent performance across temperature.

### Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications such as radio astronomy.
Good rejection	Rejection upto $2x F_c$ . This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Shielded case	Reduced interference with and from the surrounding components.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

## BPF-BD1800+

50Ω 1600 to 2000 MHz



Generic photo used for illustration purposes only  
CASE STYLE: TV2849


### Features

- Wide bandwidth
- Rejection upto  $2 \times F_c$
- Miniature shielded package


### Applications

- Radio telescope applications
- Public cellular networks
- International mobile telecommunication
- Weather instruments / Radar / Satellite
- Transmitters / Receivers
- Harmonic rejection / Industrial applications

### Functional Schematic



### Typical Frequency Response



### Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	1800	—	MHz	
	Insertion Loss	F1-F2	1600 - 2000	—	1.7	3.0	dB
	VSWR	F1-F2	1600 - 2000	—	1.67	2.0	:1
Stop Band, Lower	Rejection	DC-F3	DC - 1000	50	60	—	dB
		F3-F4	1000 - 1400	20	25	—	dB
Stop Band, Upper	Rejection	F5-F6	2200 - 2400	20	25	—	dB
		F6-F7	2400 - 4000	35	45	—	dB

### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W





Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	101.08	191.20	1600	4.14
100	104.21	979.89	1620	3.78
300	88.33	669.45	1640	3.57
500	83.33	261.65	1660	3.42
1000	64.18	88.70	1680	3.31
1400	29.23	43.77	1700	3.24
1454	20.64	30.71	1720	3.19
1546	3.19	2.72	1740	3.16
1600	1.24	1.10	1760	3.15
1800	1.11	1.08	1780	3.15
2000	1.60	1.08	1800	3.16
2080	3.11	1.51	1820	3.18
2154	20.10	12.18	1840	3.21
2194	30.78	19.54	1860	3.25
2200	32.26	20.48	1880	3.30
2400	62.00	39.98	1900	3.36
3000	52.47	47.46	1920	3.46
3300	49.70	47.44	1940	3.59
3500	49.42	46.39	1960	3.75
4000	53.22	50.64	2000	4.17

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A  
ECO-011411  
BPF-BD1800+  
EDU3591  
URJ  
220113  
Page 2 of 3

## Pad Connections

INPUT	2
OUTPUT	11
GROUND	1, 3-10, 12-18

## Demo Board MCL P/N: TB-1108+ Suggested PCB Layout (PL-640)




### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Outline Drawing



## Outline Dimensions ( inch / mm)

A	B	C	D	E	F	G	H	J	K
.433	1.299	.350	.197	.079	.140	.040	.100	.060	.157
11.00	33.00	8.89	5.00	2.02	3.56	1.02	2.54	1.52	4.00
L	M	N	P	Q	R	S	Wt.		
.098	.058	1.179	.080	.177	1.339	.473	grams		
2.50	1.48	29.95	2.03	4.51	34.02	12.02	4		

Note: Please refer to case style drawing for details

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*


FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	103.28	98.06	111.41	0.05	0.05	0.05	0.06	0.05	0.06
50	93.75	99.34	95.48	0.04	0.04	0.04	0.05	0.04	0.04
100	98.67	94.82	102.58	0.03	0.03	0.03	0.03	0.03	0.04
170	92.89	96.12	94.58	0.02	0.02	0.03	0.02	0.03	0.03
240	91.46	90.81	89.63	0.01	0.03	0.03	0.02	0.03	0.04
310	90.47	90.12	87.28	0.02	0.03	0.04	0.02	0.04	0.05
380	89.11	86.46	89.81	0.03	0.05	0.06	0.03	0.05	0.06
450	84.27	86.07	86.43	0.03	0.06	0.07	0.04	0.06	0.07
520	83.38	81.88	84.26	0.05	0.08	0.09	0.06	0.08	0.09
590	81.35	81.33	80.70	0.06	0.10	0.11	0.07	0.10	0.11
660	80.16	79.28	78.64	0.08	0.12	0.13	0.09	0.12	0.13
730	76.88	77.36	77.53	0.09	0.14	0.15	0.10	0.14	0.15
800	73.73	73.62	73.68	0.11	0.16	0.17	0.12	0.16	0.17
870	70.36	70.38	70.59	0.13	0.18	0.19	0.14	0.18	0.19
940	68.21	68.98	68.72	0.15	0.21	0.22	0.15	0.19	0.21
1000	64.90	66.29	65.37	0.17	0.23	0.24	0.17	0.21	0.23
1080	59.82	59.93	59.87	0.19	0.25	0.26	0.18	0.23	0.25
1150	54.85	55.22	54.86	0.21	0.27	0.29	0.20	0.25	0.27
1220	49.02	49.13	48.88	0.23	0.29	0.30	0.21	0.26	0.28
1290	42.54	42.49	42.29	0.25	0.31	0.34	0.24	0.30	0.32
1360	34.72	34.54	34.34	0.27	0.34	0.38	0.26	0.33	0.36
1400	29.45	29.23	28.99	0.31	0.39	0.44	0.30	0.38	0.42
1454	20.94	20.62	20.37	0.44	0.55	0.61	0.43	0.54	0.60
1546	3.27	3.17	3.16	5.73	6.62	7.06	5.85	6.76	7.21
1600	1.07	1.24	1.33	24.64	24.52	24.26	27.25	26.61	26.02
1710	0.92	1.08	1.17	22.56	23.39	23.99	21.75	22.62	23.07
1780	0.91	1.09	1.18	30.07	29.80	28.93	29.64	29.30	28.44
1800	0.92	1.11	1.20	31.26	29.30	28.09	30.92	29.06	27.91
1920	1.16	1.37	1.47	18.04	18.38	18.83	18.18	18.54	19.05
1990	1.28	1.54	1.67	29.74	30.18	29.68	33.43	35.67	34.29
2000	1.33	1.60	1.74	30.31	28.30	27.89	33.50	29.58	28.94
2080	2.50	3.11	3.45	12.86	11.96	11.50	14.26	13.57	13.10
2100	4.33	5.47	6.05	6.73	6.03	5.75	7.54	6.87	6.57
2154	18.33	20.14	20.82	1.21	1.32	1.37	1.36	1.45	1.52
2194	29.23	30.84	31.39	0.75	0.87	0.91	0.81	0.91	0.96
2200	30.73	32.31	32.85	0.71	0.83	0.87	0.77	0.87	0.92
2400	66.11	63.92	65.32	0.32	0.41	0.44	0.32	0.40	0.44
2550	61.30	61.64	60.99	0.24	0.32	0.37	0.24	0.33	0.37
2620	58.29	61.74	62.62	0.23	0.30	0.36	0.22	0.31	0.36
2690	56.18	63.03	59.37	0.21	0.29	0.34	0.21	0.31	0.35
2760	54.58	54.80	52.17	0.21	0.28	0.34	0.21	0.30	0.35
2830	53.75	54.24	56.25	0.20	0.29	0.36	0.21	0.30	0.37
2900	53.88	52.30	54.52	0.22	0.30	0.36	0.21	0.31	0.36
2970	53.28	57.34	51.66	0.20	0.30	0.35	0.20	0.33	0.37
3040	52.86	53.42	49.65	0.22	0.31	0.37	0.22	0.32	0.38
3110	50.92	64.56	48.29	0.21	0.31	0.41	0.23	0.33	0.42
3180	55.21	52.71	55.44	0.22	0.32	0.37	0.23	0.34	0.40
3250	46.85	52.95	44.64	0.26	0.33	0.42	0.29	0.35	0.43
3320	54.70	51.28	53.12	0.24	0.37	0.38	0.26	0.39	0.41
3390	44.40	57.41	69.23	0.28	0.37	0.41	0.30	0.37	0.43
3460	51.46	47.27	54.57	0.35	0.39	0.40	0.32	0.40	0.42
3530	51.08	52.89	50.85	0.25	0.39	0.40	0.28	0.41	0.41
3600	49.92	47.41	47.39	0.26	0.39	0.40	0.29	0.40	0.43
3670	46.61	53.27	48.13	0.29	0.37	0.39	0.33	0.36	0.45
3740	52.24	50.21	48.44	0.27	0.38	0.39	0.30	0.38	0.43
3810	47.71	46.55	48.76	0.28	0.40	0.37	0.30	0.43	0.39
3880	50.51	53.94	50.96	0.27	0.35	0.35	0.27	0.36	0.37
3950	49.89	48.01	53.00	0.25	0.36	0.37	0.26	0.36	0.37
3970	49.34	48.43	50.54	0.26	0.35	0.35	0.27	0.35	0.37
4000	57.22	54.22	52.79	0.23	0.33	0.33	0.24	0.33	0.35

## Typical Performance Data


FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1600	4.20	4.14	4.10
1610	3.98	3.94	3.91
1620	3.82	3.78	3.76
1630	3.70	3.67	3.65
1640	3.59	3.57	3.56
1650	3.51	3.49	3.48
1660	3.44	3.42	3.41
1670	3.38	3.37	3.36
1680	3.33	3.32	3.31
1690	3.28	3.27	3.27
1700	3.25	3.24	3.23
1710	3.22	3.21	3.21
1720	3.20	3.19	3.19
1730	3.18	3.18	3.17
1740	3.17	3.17	3.16
1750	3.16	3.16	3.15
1760	3.15	3.15	3.15
1770	3.15	3.15	3.15
1780	3.15	3.15	3.15
1790	3.15	3.16	3.15
1800	3.16	3.16	3.16
1810	3.17	3.17	3.17
1820	3.18	3.18	3.18
1830	3.19	3.20	3.20
1840	3.21	3.21	3.21
1850	3.23	3.23	3.23
1860	3.24	3.25	3.25
1870	3.26	3.27	3.28
1880	3.29	3.30	3.30
1890	3.31	3.33	3.33
1900	3.35	3.36	3.37
1910	3.39	3.41	3.42
1920	3.43	3.46	3.47
1930	3.49	3.52	3.54
1940	3.55	3.59	3.61
1950	3.63	3.67	3.68
1960	3.71	3.75	3.77
1970	3.80	3.84	3.86
1980	3.89	3.94	3.96
1990	4.00	4.05	4.07
2000	4.12	4.18	4.20

## Typical Performance Curves


**INSERTION LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm




**INSERTION LOSS vs. TEMPERATURE (Zoomed)**  
INPUT POWER = 0 dBm




**INPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm



**OUTPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm



**GROUP DELAY vs. TEMPERATURE**  
INPUT POWER = 0 dBm






# Case Style


# TV



## TV2849

### Outline Dimensions



### SUGGESTED LAYOUT FOR P.C. PATTERN



 METALLIZATION  
 SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M
TV2849	.433 (11.00)	1.299 (33.00)	.350 (8.89)	.197 (5.00)	.079 (2.02)	.140 (3.56)	.040 (1.02)	.100 (2.54)	.060 (1.52)	.157 (4.00)	.098 (2.50)	.058 (1.48)

CASE#	N	P	Q	R	S	WT. GRAMS
TV2849	1.179 (29.95)	.080 (2.03)	.177 (4.51)	1.339 (34.02)	.473 (12.02)	4

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm$  --; 3 Pl.  $\pm$  .030

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5  $\mu$  inch Gold over 120-240  $\mu$  inch Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.



ISO 9001 ISO 14001 CERTIFIED




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M174627	NEW RELEASE	JUN 19	ES	VC

SUGGESTED MOUNTING CONFIGURATION FOR TV2849 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	ES	14 JUN 19
TOLERANCES ON:	TM	14 JUN 19
2 PL DECIMALS ±	APPROVED	14 JUN 19
3 PL DECIMALS ± .005	KKK	
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, TV2849, BPF, TB-1108+, 50 Ohm

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-640	OR
FILE:	98PL640	SCALE:	SHEET:
		3:1	1 OF 1





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215