

Surface Mount Bandpass Filter

BPF-E16+

50Ω 2 to 30 MHz

The Big Deal

- Low insertion loss (1 dB typical)
- Good VSWR (1.4:1 typical)
- High rejection
- Fast roll-off



CASE STYLE: HR1176

Product Overview

The BPF-E16+ is a 50Ω band pass filter in a shielded package (size of 1.20" x 1.20" x 0.370") fabricated using SMT technology. These units offer good matching within the pass band and high rejection. This unit has miniature high Q capacitors and wire welded inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Sharp shape factor	Sharp shape factor helps in adjacent channel rejection and increased selectivity.
Good VSWR, 1.4:1 typical in passband	The BPF-E16+ has very good return loss which provides good matching when used with other devices.
More than 40dB rejection up to 500MHz	This enables the filter to attenuate spurious signals and reject harmonics for broad band of frequency.
Shielded case	Reduced interference with and from the surrounding components.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

BPF-E16+

50Ω 2 to 30 MHz



CASE STYLE: HR1176

Features

- Excellent VSWR, 1.4:1 typical in passband
- High rejection
- Sharp insertion loss roll off
- Shielded case
- Aqueous washable

Applications

- Harmonic rejection
- Transmitters / receivers
- Lab use

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	16	—	MHz
	Insertion Loss	F1-F2	2-30	1.5	3.0	dB
	VSWR	F1-F2	2-30	1.4	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1.4	20	40	dB
	VSWR	DC-F3	DC-1.4	—	21	:1
Stop Band, Upper	Insertion Loss	F4-F5	35-500	20	32	dB
	VSWR	F4-F5	35-500	—	22	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
0.10	89.63	868.59	2	1325.56
1.20	72.57	44.55	4	269.01
1.40	41.88	21.46	6	146.43
1.50	23.78	11.03	8	108.69
1.55	12.95	4.88	10	91.88
1.60	4.84	1.10	11	87.19
1.70	2.58	1.49	12	84.03
2.00	1.25	1.09	13	81.77
3.00	0.70	1.18	14	80.25
16.00	0.49	1.13	15	79.26
25.00	0.81	1.23	16	78.69
30.00	1.47	1.09	17	78.29
31.00	2.29	1.44	18	78.21
31.50	4.11	2.65	20	80.84
32.00	7.86	5.47	22	84.77
33.00	17.29	13.29	24	89.39
35.00	32.63	21.73	25	94.14
40.00	54.55	33.42	26	100.52
200.00	91.51	144.77	28	116.42
500.00	93.56	54.29	30	156.93

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M160153
BPF-E16+
EDR-8470/3U
RAV/URJ/NY
161230
Page 2 of 3

Pad Connections



INPUT	18
OUTPUT	9
GROUND	1-8, 10-17, 19-,20

Demo Board MCL P/N: TB-573+
Suggested PCB Layout (PL-329)




NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030"±.003". COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F	G
1.200	1.200	.370	.196	.202	.071	.079
30.48	30.48	9.40	4.98	5.13	1.80	2.01
H	J	K	L	M	wt	
.202	.091	.079	1.240	1.240	grams	
5.13	2.31	2.01	31.50	31.50	8.5	

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Surface Mount Band Pass Filter

BPF-E16+

Typical Performance Data







FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.1	91.24	93.70	90.14	0.03	0.04	0.03	0.03	0.04	0.03
0.2	96.02	102.00	96.95	0.02	0.03	0.03	0.03	0.02	0.02
0.3	94.26	87.86	98.30	0.01	0.01	0.01	0.01	0.02	0.01
0.4	96.30	99.00	100.33	0.01	0.02	0.02	0.02	0.02	0.02
0.5	99.65	93.80	97.07	0.03	0.03	0.02	0.01	0.03	0.01
0.6	95.70	94.82	97.75	0.03	0.03	0.04	0.02	0.02	0.03
0.7	113.23	101.70	101.08	0.04	0.04	0.06	0.02	0.04	0.02
0.8	99.58	94.80	104.71	0.07	0.06	0.07	0.04	0.06	0.05
0.9	90.46	98.68	91.43	0.07	0.08	0.10	0.07	0.06	0.07
1.0	90.65	88.69	89.00	0.10	0.13	0.13	0.08	0.11	0.10
1.1	79.47	80.37	78.73	0.14	0.17	0.18	0.12	0.16	0.17
1.2	67.41	67.43	67.16	0.22	0.25	0.28	0.19	0.22	0.24
1.3	52.59	52.51	52.73	0.37	0.39	0.43	0.30	0.34	0.37
1.4	36.35	36.23	36.47	0.66	0.72	0.78	0.52	0.58	0.62
1.5	16.95	16.84	17.21	2.15	2.35	2.47	1.41	1.54	1.61
1.6	3.47	3.64	3.91	12.64	12.74	13.04	9.00	9.06	8.98
1.7	1.95	2.07	2.22	22.70	23.44	23.14	19.02	19.25	18.94
1.8	1.53	1.61	1.71	19.25	19.37	19.37	19.66	19.87	19.87
1.9	1.27	1.34	1.42	21.05	21.26	21.17	24.07	24.44	24.39
2.0	1.09	1.16	1.23	23.81	23.99	24.09	25.87	25.80	25.96
3.0	0.69	0.73	0.75	21.31	21.01	21.02	21.13	20.81	20.77
4.0	0.52	0.56	0.57	18.73	18.83	18.87	19.07	19.26	19.36
5.0	0.44	0.48	0.48	18.30	18.05	17.92	18.70	18.37	18.22
6.0	0.47	0.51	0.51	15.08	14.96	14.89	15.07	14.95	14.85
7.0	0.38	0.41	0.42	18.35	18.29	18.14	18.39	18.34	18.23
8.0	0.33	0.35	0.35	28.05	27.80	27.24	29.43	29.55	29.17
9.0	0.32	0.34	0.34	28.12	28.02	28.21	29.40	29.28	29.72
10.0	0.32	0.35	0.34	23.61	23.73	24.02	23.78	23.85	24.12
15.0	0.35	0.38	0.37	31.26	31.05	30.66	30.98	31.31	31.29
20.0	0.48	0.49	0.51	26.22	26.39	26.38	26.28	26.28	26.15
21.0	0.50	0.52	0.54	27.29	27.29	27.47	27.19	27.42	27.75
22.0	0.54	0.56	0.58	23.66	23.36	23.23	23.69	23.65	23.70
23.0	0.60	0.61	0.64	21.64	21.34	21.17	21.80	21.63	21.53
24.0	0.64	0.65	0.67	23.03	22.93	22.71	23.29	23.22	22.97
25.0	0.67	0.69	0.72	32.56	33.58	33.28	34.19	34.65	33.72
26.0	0.75	0.77	0.80	26.01	25.47	25.49	25.95	25.60	25.73
27.0	0.88	0.90	0.94	19.75	19.58	19.46	19.80	19.70	19.65
28.0	1.00	1.02	1.06	20.54	20.70	20.54	20.84	21.09	20.94
29.0	1.14	1.16	1.22	29.19	29.77	29.90	42.06	40.90	40.02
30.0	1.46	1.51	1.59	28.99	32.54	35.44	23.59	23.60	23.45
31.0	3.02	3.39	3.61	9.71	8.43	8.15	9.02	7.87	7.58
32.0	10.34	11.16	11.47	2.01	1.81	1.83	1.92	1.76	1.78
33.0	19.37	20.15	20.45	0.84	0.81	0.84	0.81	0.81	0.85
34.0	27.06	27.71	27.96	0.55	0.55	0.57	0.54	0.56	0.60
35.0	33.45	34.01	34.21	0.45	0.44	0.46	0.42	0.45	0.48
36.0	38.78	39.30	39.51	0.38	0.38	0.39	0.36	0.39	0.41
37.0	43.24	43.71	43.88	0.33	0.33	0.35	0.33	0.36	0.37
38.0	46.96	47.50	47.53	0.31	0.31	0.32	0.29	0.32	0.34
39.0	50.20	50.69	50.71	0.27	0.28	0.29	0.26	0.29	0.30
40.0	53.01	53.14	53.25	0.26	0.27	0.28	0.25	0.28	0.29
50.0	68.13	67.48	67.57	0.20	0.20	0.22	0.19	0.22	0.22
100.0	85.31	87.28	86.53	0.16	0.17	0.18	0.09	0.13	0.15
200.0	93.46	87.59	98.26	0.15	0.17	0.18	0.07	0.13	0.16
300.0	87.15	87.33	88.16	0.15	0.18	0.20	0.07	0.15	0.17
400.0	91.43	88.43	96.35	0.17	0.21	0.23	0.09	0.19	0.24
500.0	90.16	89.63	91.84	0.18	0.23	0.26	0.22	0.38	0.47



Typical Performance Data


FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
2.0	1242.09	1238.89	1241.22
3.0	466.35	466.01	466.36
3.5	336.61	336.51	336.67
4.0	264.66	264.45	264.84
4.5	219.93	219.69	220.06
5.0	186.21	186.31	186.34
5.5	161.37	161.17	161.12
6.0	143.61	143.61	143.68
6.5	130.93	131.19	131.29
7.0	121.92	122.00	122.04
7.5	114.55	114.71	114.86
8.0	108.12	108.61	108.53
8.5	103.14	103.38	103.34
9.0	98.66	98.71	98.95
9.5	94.95	95.00	95.02
10.0	91.27	91.70	91.81
10.5	88.93	89.00	89.21
11.0	86.73	87.06	87.05
11.5	85.12	85.38	85.49
12.0	84.17	84.19	84.09
12.5	82.64	82.79	82.71
13.0	81.89	81.97	81.93
13.5	81.11	81.32	81.35
14.0	80.03	80.48	80.46
14.5	79.84	80.01	80.06
15.0	79.45	79.60	79.92
15.5	79.06	79.12	79.20
16.0	78.90	79.00	79.08
16.5	78.73	78.91	78.95
17.0	78.79	78.94	78.95
17.5	78.80	79.04	79.12
18.0	78.96	79.18	79.30
18.5	79.52	79.81	79.80
19.0	79.85	80.03	80.30
19.5	80.55	80.85	81.07
20.0	81.09	81.44	81.75
20.5	82.22	82.56	82.65
21.0	83.26	83.55	83.60
21.5	84.05	84.51	84.62
22.0	85.05	85.39	85.50
22.5	86.19	86.46	86.72
23.0	87.78	87.97	88.14
23.5	89.16	89.60	89.76
24.0	91.23	91.86	91.99
24.5	93.60	94.20	94.39
25.0	96.40	96.98	97.10
25.5	99.13	100.02	100.27
26.0	102.20	103.05	103.21
26.5	105.32	106.12	106.54
27.0	108.98	109.81	110.29
27.5	113.71	114.85	115.40
28.0	119.88	121.38	121.84
28.5	127.88	129.61	130.26
29.0	137.36	139.53	140.36
29.5	150.01	153.09	154.00
30.0	168.85	173.53	174.99

Typical Performance Curves




Surface Mount Band Pass Filter BPF-E16+

Typical Performance Curves




Outline Dimensions


HR1176



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAM
HR1176	1.200 (30.48)	1.200 (30.48)	.370 (9.40)	.196 (4.98)	.202 (5.13)	.071 (1.80)	.079 (2.01)	.202 (5.13)	.091 (2.31)	.079 (2.01)	1.240 (31.50)	1.240 (31.50)	8.5

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F80



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	40	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M126151	NEW RELEASE	APR 10	RB	KG

**SUGGESTED MOUNTING CONFIGURATION FOR
HR1176 CASE STYLE "20FL01" PIN CODE**



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .003". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN RB	27 APR 10
TOLERANCES ON:	CHECKED MD	27 APR 10
2 PL DECIMALS ±	APPROVED KR	27 APR 10
3 PL DECIMALS ± .005"		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, 20FL01, HR1176, BPF-E,
TB-573S+, 50Ω

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-329	OR
FILE:	98PL329	SCALE:	SHEET:
ASHEETA1.DWG REV:A	DATE:01/12/95	2:1	1 OF 1

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215