


Surface Mount Bandpass Filter

BPF-F184+

50Ω 154.32 to 214.32 MHz



Generic photo used for illustration purposes only
CASE STYLE: HP1156

The Big Deal

- Broad bandwidth
- High Rejection
- Good VSWR
- Miniature shielded package

Product Overview

BPF-F184+ is a 50Ω bandpass filter in a shielded package fabricated using SMT technology. This bandpass filter covers from 154.32 to 214.32 MHz. This is broad filter and finds extensive application in television networks.

Key Features

Feature	Advantages
Low insertion loss	Broad bandwidth and it can be used in television networks.
Good rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band
Shielded package	The small surface mount package enables the BPF-F184+ to used in compact design

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

BPF-F184+

50Ω 154.32 to 214.32 MHz



Generic photo used for illustration purposes only
CASE STYLE: HP1156

Features


- Broad bandwidth
- High rejection
- Miniature shielded package

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	184	—	MHz	
	Insertion Loss	F1-F2	154.32 - 214.32	—	1.90	3.00	dB
	VSWR	F1-F2	154.32 - 214.32	—	1.43	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 139	20	30	—	dB
	VSWR	DC-F3	DC - 139	—	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	242 - 2800	20	27	—	dB
	VSWR	F4-F5	242 - 2800	—	20	—	:1

Applications

- Digital television networks
- Biomedical telemetry devise
- Wireless microphone
- Test and measurement




Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	2 W

Permanent damage may occur if any of these limits are exceeded.





Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1.00	77.68	1737.18	154.32	30.64
50.00	44.73	289.53	155.00	28.90
100.00	41.04	144.77	156.00	26.81
139.00	30.13	32.18	158.00	23.67
140.00	26.26	28.49	160.00	21.41
141.00	22.71	24.48	164.00	18.31
142.00	19.38	20.45	168.00	16.42
145.00	10.40	8.81	173.00	15.12
149.00	3.20	2.02	178.00	14.40
154.32	1.68	1.08	184.00	13.82
184.00	1.26	1.15	188.00	13.57
214.32	1.78	1.28	193.00	13.52
225.00	3.38	2.45	198.00	13.88
233.00	12.82	15.53	202.00	14.50
238.00	20.82	29.96	205.00	15.13
242.00	27.56	40.41	208.00	15.87
244.00	31.21	45.72	210.00	16.44
500.00	75.22	115.81	212.00	17.13
1800.00	66.26	82.73	214.00	17.99
2800.00	53.53	29.46	214.32	18.17

Typical Frequency Response



+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B
M174392
BPF-F184+
EDU1489
URJ
190909
Page 2 of 3

Pad Connections



INPUT	2
OUTPUT	11
GROUND	1,3,4,5,6,7,8,10,12,13,14,15,16,17
NO CONNECTION	9,18

Demo Board MCL P/N: TB-695+
Suggested PCB Layout (PL-418)



- NOTES:**
- TRACE WIDTH IS SHOWN FOR OAK-602, WITH DIELECTRIC THICKNESS $.022 \pm .0015"$, COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	H	J
.730	1.360	.350	.100	.100	.180	.140	.140	.305
18.54	34.54	8.89	2.54	2.54	4.57	3.56	3.56	7.75
K	L	M	N	P	Q	R	Wt.	
.150	.225	.120	.275	1.400	.110	.770	grams	
3.81	5.72	3.05	6.99	35.56	2.79	19.56	6.0	

Note: Please refer to case style drawing for details

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Band Pass Filter

BPF-F184+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.30	88.82	87.12	86.58	0.01	0.01	0.01	0.31	0.39	0.44
1.00	77.23	77.68	77.44	0.00	0.00	0.01	0.31	0.39	0.45
15.00	54.97	54.93	54.97	0.02	0.02	0.03	0.51	0.60	0.66
60.00	43.09	43.19	43.23	0.06	0.07	0.08	0.80	0.91	0.97
122.00	69.46	67.28	66.13	0.19	0.21	0.24	0.61	0.70	0.75
135.00	52.17	51.47	50.88	0.33	0.38	0.42	0.68	0.80	0.86
139.00	30.87	30.13	29.68	0.46	0.54	0.59	0.89	1.05	1.14
141.00	23.29	22.71	22.34	0.60	0.71	0.78	1.14	1.34	1.47
142.00	19.91	19.38	19.03	0.72	0.85	0.93	1.34	1.59	1.73
144.00	13.63	13.21	12.92	1.19	1.42	1.56	2.11	2.49	2.72
147.00	5.92	5.81	5.71	3.80	4.39	4.77	5.91	6.78	7.36
149.00	3.10	3.20	3.23	8.48	9.45	10.09	13.14	14.76	15.88
151.00	2.00	2.18	2.27	15.56	17.22	18.32	28.57	37.44	38.84
153.00	1.62	1.81	1.90	22.97	26.01	27.78	22.45	22.84	22.94
154.32	1.49	1.68	1.77	26.78	28.47	28.15	21.98	22.56	23.00
158.00	1.30	1.48	1.58	25.16	23.11	21.84	33.56	35.71	39.96
166.00	1.23	1.38	1.46	16.33	16.54	16.56	16.93	17.12	17.17
171.00	1.17	1.31	1.39	17.29	17.87	18.19	16.20	16.51	16.70
173.00	1.14	1.28	1.36	18.71	19.45	19.89	16.84	17.20	17.45
176.00	1.10	1.25	1.33	22.52	23.58	24.16	18.80	19.26	19.64
182.00	1.08	1.24	1.33	32.27	27.71	25.72	27.94	29.77	31.76
184.00	1.10	1.26	1.35	25.20	23.35	22.28	29.73	31.65	33.49
186.00	1.12	1.29	1.38	21.66	20.61	19.95	26.47	27.01	27.36
187.00	1.13	1.30	1.39	20.45	19.61	19.08	24.70	24.98	25.18
196.00	1.24	1.41	1.51	17.00	16.77	16.78	18.04	17.90	18.04
201.00	1.26	1.44	1.54	19.08	18.78	18.96	18.58	18.20	18.33
207.00	1.31	1.51	1.62	24.48	22.95	22.74	22.83	21.77	21.72
211.00	1.42	1.63	1.75	21.21	20.34	19.94	25.69	24.92	24.55
214.00	1.53	1.76	1.89	18.75	18.39	18.20	24.73	25.35	25.21
214.32	1.49	1.49	1.49	18.68	18.68	18.68	24.42	24.42	24.42
216.00	1.62	1.85	1.99	18.34	18.21	18.19	24.57	25.88	26.10
220.00	1.82	2.10	2.26	22.86	22.62	22.95	36.82	41.32	35.59
223.00	2.22	2.58	2.81	17.25	15.99	15.21	19.16	18.32	17.54
224.00	2.50	2.91	3.17	13.44	12.56	11.94	15.37	14.91	14.38
226.00	3.49	4.01	4.36	7.99	7.54	7.19	10.06	10.03	9.81
228.00	5.23	5.86	6.29	4.62	4.42	4.25	6.75	6.95	6.93
229.00	6.37	7.04	7.50	3.51	3.39	3.29	5.64	5.92	5.96
233.00	12.10	12.82	13.32	1.32	1.35	1.36	3.40	3.79	3.96
237.00	18.48	19.20	19.69	0.68	0.73	0.76	2.68	3.05	3.24
238.00	20.11	20.82	21.32	0.60	0.65	0.68	2.58	2.94	3.13
240.00	23.41	24.13	24.64	0.49	0.54	0.57	2.43	2.77	2.96
242.00	26.82	27.56	28.08	0.42	0.46	0.50	2.32	2.64	2.83
274.00	45.24	45.65	45.90	0.17	0.20	0.23	1.72	1.94	2.07
350.00	59.83	60.44	60.79	0.12	0.15	0.18	5.76	7.30	8.36
375.00	74.07	75.05	76.50	0.12	0.15	0.17	7.07	7.02	6.84
470.00	53.46	53.20	52.98	0.16	0.20	0.24	0.93	1.07	1.14
495.00	72.51	73.15	73.60	0.13	0.16	0.19	0.82	0.94	1.01
625.00	64.32	64.36	64.30	0.14	0.17	0.20	0.52	0.61	0.66
725.00	102.06	96.54	95.70	0.14	0.18	0.20	0.41	0.50	0.54
775.00	77.57	78.09	77.54	0.13	0.17	0.19	0.36	0.45	0.50
1050.00	86.42	89.34	89.12	0.12	0.16	0.18	0.25	0.35	0.38
1200.00	93.38	99.13	93.79	0.11	0.16	0.18	0.23	0.33	0.36
1400.00	76.75	76.57	76.63	0.10	0.16	0.19	0.23	0.32	0.36
1500.00	79.87	80.11	79.78	0.09	0.17	0.19	0.23	0.32	0.36
1850.00	66.52	66.70	67.18	0.10	0.20	0.23	0.25	0.34	0.37
2100.00	59.17	57.07	55.70	0.12	0.24	0.28	0.26	0.36	0.38
2225.00	58.03	58.40	58.22	0.14	0.26	0.31	0.27	0.36	0.39
2350.00	60.01	59.66	58.70	0.18	0.31	0.35	0.26	0.36	0.40
2550.00	53.03	52.30	51.90	0.38	0.53	0.58	0.31	0.43	0.45
2800.00	53.75	53.53	52.29	0.39	0.54	0.59	0.29	0.42	0.45









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

Band Pass Filter**BPF-F184+***Typical Performance Data*

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
154.32	31.32	30.64	30.22
155.00	29.48	28.90	28.54
156.00	27.28	26.81	26.51
157.00	25.49	25.09	24.85
158.00	24.01	23.67	23.46
159.00	22.75	22.46	22.28
160.00	21.67	21.41	21.25
161.00	20.71	20.49	20.35
162.00	19.87	19.68	19.56
163.00	19.11	18.96	18.86
164.00	18.44	18.31	18.23
165.00	17.85	17.74	17.68
166.00	17.33	17.25	17.19
167.00	16.87	16.81	16.77
168.00	16.47	16.42	16.39
169.00	16.12	16.09	16.07
170.00	15.81	15.79	15.78
171.00	15.55	15.54	15.54
172.00	15.33	15.32	15.33
173.00	15.12	15.12	15.13
174.00	14.95	14.94	14.95
175.00	14.79	14.79	14.80
176.00	14.66	14.65	14.65
177.00	14.53	14.52	14.53
178.00	14.41	14.40	14.41
179.00	14.30	14.29	14.29
180.00	14.20	14.19	14.19
181.00	14.10	14.09	14.09
182.00	14.01	14.00	14.00
183.00	13.92	13.91	13.91
184.00	13.84	13.82	13.82
186.00	13.69	13.68	13.68
187.00	13.63	13.62	13.62
188.00	13.57	13.57	13.58
189.00	13.53	13.53	13.54
190.00	13.51	13.51	13.52
191.00	13.48	13.49	13.51
193.00	13.49	13.52	13.54
194.00	13.53	13.55	13.58
195.00	13.57	13.61	13.65
196.00	13.64	13.68	13.72
197.00	13.72	13.77	13.82
198.00	13.83	13.88	13.94
199.00	13.95	14.01	14.07
200.00	14.10	14.16	14.22
201.00	14.25	14.32	14.39
202.00	14.43	14.50	14.57
203.00	14.62	14.69	14.78
204.00	14.83	14.91	14.98
205.00	15.05	15.13	15.21
206.00	15.28	15.37	15.45
207.00	15.52	15.61	15.70
208.00	15.78	15.87	15.95
209.00	16.05	16.15	16.25
210.00	16.34	16.44	16.54
211.00	16.65	16.77	16.87
212.00	17.00	17.13	17.24
213.00	17.38	17.53	17.66
214.00	17.83	17.99	18.13
214.32	17.97	17.97	17.97


Typical Performance Curves



Band Pass Filter


BPF-F184+

Typical Performance Curves



Outline Dimensions

HP1156



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HP1156	.730 (18.54)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.140 (3.56)	.305 (7.75)	.150 (3.81)	.225 (5.72)	.120 (3.05)

CASE#	N	P	Q	R	WT.GRAM
HP1156	.275 (6.99)	1.400 (35.56)	.110 (2.79)	.770 (19.56)	6.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5μinch (.08-.13microns) Gold over 120-240μinch (3.05-6.10microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F89

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	32	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M145648	NEW RELEASE	MAR 14	DDR	MD

SUGGESTED MOUNTING CONFIGURATION FOR
HP1156 CASE STYLE "18FL01" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR OAK-602, WITH DIELECTRIC THICKNESS $.022 \pm .0015$ ". COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DDR 14 MAR 14
TOLERANCES ON:	CHECKED	MD 14 MAR 14
2 PL DECIMALS ±	APPROVED	MD 14 MAR 14
3 PL DECIMALS ± .005"		
ANGLES ±		
FRACTIONS ±		





Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 18FL01, HP1156, BPF
TB-695+, 50 Ohm

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-418	REV: OR
FILE: 98PL418	SCALE: 3:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 Inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D