


Surface Mount Bandpass Filter

BPF-F200+

50Ω 195 to 205 MHz



Generic photo used for illustration purposes only
CASE STYLE: HP1156

The Big Deal

- Narrow bandwidth
- High Rejection
- Good VSWR
- Shielded package

Product Overview

BPF-F200+ is a 50Ω bandpass filter in a shielded package fabricated using SMT technology. This bandpass filter covers from 195 to 205 MHz. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability, It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Narrow bandwidth filter	Narrow bandwidth with fast roll-off, this will attenuate frequencies closer to the passband with good rejection value of > 40 dB which increases selectivity on the adjacent channel
Good rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band.
Shielded package	The small surface mount package enables the BPF-F200+ to used in compact design

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

BPF-F200+

50Ω 195 to 205 MHz



Generic photo used for illustration purposes only
CASE STYLE: HP1156

Features

- Narrow bandwidth
- Sharper cut-off
- Shielded package

Applications

- Radio test equipment
- Receiver \ Transmitter
- SATCOM
- Harmonic rejection

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	200	—	MHz
	Insertion Loss	F1-F2	195-205	7	8	dB
	VSWR	F1-F2	195-205	1.58	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-177	50	60	dB
	VSWR	F3-F4	177-182	40	45	dB
	VSWR	DC-F4	DC-182	—	20	:1
Stop Band, Upper	Insertion Loss	F5-F6	225-1600	45	55	dB
	VSWR	F5-F6	225-1600	—	20	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W Max.

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	105.61	148.16	195.0	96.93
150	90.19	139.13	195.5	93.40
177	69.25	36.70	196.0	90.42
182	52.25	20.61	196.5	87.93
185	40.60	12.80	197.0	85.83
187	31.68	8.44	197.5	84.08
189	21.70	4.74	198.0	82.65
195	5.72	1.11	198.5	81.49
200	4.88	1.15	199.0	80.61
205	5.60	1.04	199.5	79.96
210	15.03	4.14	200.0	79.53
211	18.96	5.86	200.5	79.29
212	22.90	7.80	201.0	79.25
214	30.22	12.06	201.5	79.40
216	36.66	16.69	202.0	79.76
225	57.95	41.36	202.5	80.32
500	104.50	626.76	203.0	81.10
1000	83.33	242.72	203.5	82.17
1575	54.83	118.68	204.0	83.56
1600	61.79	126.21	205.0	87.36

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M174392
BPF-F200+
EDU2929
URJ
190909
Page 2 of 3

Typical Performance Data


FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	99.21	105.61	104.62	0.11	0.12	0.13	0.10	0.11	0.12
5	103.08	101.71	98.53	0.16	0.18	0.20	0.15	0.17	0.19
10	115.10	98.68	100.81	0.20	0.22	0.24	0.19	0.22	0.24
50	101.39	96.66	106.27	0.17	0.19	0.21	0.16	0.18	0.20
100	93.61	96.90	89.99	0.10	0.11	0.12	0.09	0.11	0.11
150	112.02	90.19	98.88	0.10	0.12	0.14	0.09	0.11	0.12
177	70.74	69.25	68.19	0.37	0.47	0.55	0.31	0.39	0.46
180	60.70	59.32	58.02	0.51	0.65	0.76	0.42	0.54	0.63
181	57.20	55.86	54.52	0.58	0.74	0.87	0.47	0.61	0.71
182	53.68	52.25	50.94	0.66	0.84	0.99	0.54	0.69	0.81
183	50.00	48.55	47.19	0.76	0.97	1.15	0.62	0.79	0.94
185	42.11	40.60	39.13	1.06	1.36	1.62	0.86	1.10	1.31
186	37.84	36.28	34.74	1.28	1.65	1.98	1.03	1.33	1.61
187	33.30	31.68	30.10	1.59	2.07	2.51	1.28	1.67	2.03
188	28.46	26.82	25.22	2.05	2.69	3.31	1.66	2.19	2.70
189	23.31	21.70	20.18	2.78	3.72	4.65	2.28	3.04	3.82
190	17.96	16.56	15.32	4.08	5.59	7.13	3.40	4.63	5.90
192	8.89	8.85	8.77	12.14	16.16	19.39	10.43	13.23	15.46
193	6.68	7.14	7.39	21.47	23.89	23.98	17.91	19.75	21.33
194	5.61	6.25	6.61	26.92	24.99	24.31	24.99	25.98	28.53
195	5.04	5.72	6.13	26.90	25.47	24.78	34.05	39.46	36.94
198	4.32	5.02	5.48	22.80	23.03	23.17	21.68	22.13	23.06
200	4.16	4.88	5.37	21.95	23.18	23.99	22.58	25.46	29.66
202	4.16	4.94	5.50	24.65	24.83	25.11	35.89	34.25	31.61
205	4.61	5.60	6.40	25.12	34.33	30.50	22.71	25.67	29.46
208	6.77	8.78	10.60	13.33	10.47	8.52	16.19	14.07	11.98
210	12.15	15.03	17.43	4.90	4.28	3.79	6.51	5.80	5.15
212	20.21	22.90	25.13	2.26	2.24	2.15	2.99	2.95	2.79
213	24.20	26.67	28.75	1.71	1.77	1.74	2.23	2.28	2.20
214	27.96	30.22	32.15	1.36	1.44	1.45	1.74	1.82	1.80
215	31.48	33.55	35.34	1.13	1.22	1.23	1.41	1.50	1.50
220	45.90	47.34	48.66	0.57	0.65	0.68	0.65	0.73	0.76
225	56.75	57.95	58.87	0.36	0.42	0.45	0.39	0.45	0.48
230	65.44	66.30	67.22	0.25	0.30	0.33	0.26	0.31	0.34
240	79.11	79.34	80.31	0.15	0.19	0.21	0.15	0.19	0.20
245	86.63	85.48	87.43	0.12	0.16	0.17	0.12	0.15	0.17
250	89.06	89.27	91.43	0.10	0.13	0.15	0.09	0.13	0.14
300	111.17	96.95	98.54	0.02	0.05	0.06	0.02	0.04	0.05
350	100.85	100.99	103.85	0.01	0.03	0.04	0.00	0.03	0.04
400	95.89	101.83	105.13	0.00	0.03	0.04	0.01	0.02	0.03
450	109.56	102.64	101.03	0.01	0.02	0.03	0.01	0.01	0.02
500	100.53	104.50	111.80	0.01	0.03	0.04	0.01	0.02	0.03
550	112.08	101.83	98.45	0.01	0.03	0.04	0.01	0.02	0.03
600	98.04	94.75	110.08	0.02	0.03	0.04	0.02	0.02	0.03
650	94.26	101.87	102.72	0.01	0.04	0.05	0.01	0.03	0.04
700	98.97	100.08	109.06	0.01	0.04	0.06	0.01	0.03	0.05
750	101.69	100.21	95.64	0.01	0.04	0.06	0.01	0.03	0.04
800	93.30	99.31	96.69	0.00	0.05	0.07	0.01	0.04	0.06
850	92.42	92.00	99.38	0.00	0.05	0.07	0.00	0.05	0.06
900	93.45	95.15	94.68	0.00	0.06	0.08	0.00	0.05	0.07
950	91.59	91.12	91.94	0.01	0.07	0.09	0.01	0.06	0.08
1000	84.56	83.33	83.19	0.01	0.07	0.10	0.01	0.07	0.09
1050	85.40	86.38	89.49	0.01	0.08	0.11	0.02	0.07	0.10
1100	110.10	95.08	90.63	0.02	0.09	0.11	0.02	0.08	0.11
1150	77.78	78.98	78.02	0.02	0.09	0.11	0.03	0.09	0.11
1200	78.22	77.86	78.92	0.02	0.10	0.12	0.04	0.10	0.12
1300	67.63	78.63	77.16	0.03	0.11	0.14	0.05	0.11	0.14
1500	83.87	83.82	82.83	0.05	0.14	0.17	0.07	0.14	0.17
1575	58.58	54.83	57.95	0.06	0.15	0.18	0.07	0.15	0.18
1600	63.05	61.79	63.33	0.05	0.14	0.17	0.07	0.14	0.18

Typical Performance Data


FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
190.0	80.31	87.85	93.68
190.5	90.96	97.20	101.53
191.0	100.86	105.08	107.57
191.5	108.99	110.83	111.31
192.0	114.71	114.11	112.69
192.5	117.63	114.82	111.82
193.0	117.77	113.17	109.14
193.5	115.38	109.78	105.39
194.0	111.18	105.45	101.27
194.5	106.19	101.00	97.32
195.0	101.31	96.93	93.88
195.5	96.97	93.40	90.89
196.0	93.31	90.42	88.38
196.5	90.26	87.93	86.25
197.0	87.72	85.83	84.50
197.5	85.59	84.08	83.03
198.0	83.84	82.65	81.86
198.5	82.39	81.49	80.93
199.0	81.25	80.61	80.24
199.5	80.37	79.96	79.76
200.0	79.74	79.53	79.51
200.5	79.33	79.29	79.42
201.0	79.12	79.25	79.54
201.5	79.10	79.40	79.86
202.0	79.29	79.76	80.39
202.5	79.63	80.32	81.17
203.0	80.19	81.10	82.18
203.5	81.00	82.17	83.50
204.0	82.08	83.56	85.13
204.5	83.52	85.29	87.11
205.0	85.31	87.36	89.33
205.5	87.53	89.76	91.74
206.0	90.16	92.35	94.03
206.5	93.09	94.86	95.89
207.0	96.05	96.93	96.82
207.5	98.61	98.03	96.47
208.0	100.24	97.80	94.61
208.5	100.41	95.93	91.15
209.0	98.79	92.40	86.22
209.5	95.28	87.29	80.13
210.0	90.03	80.97	73.33

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm




INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm



Outline Dimensions

HP1156



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HP1156	.730 (18.54)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.140 (3.56)	.305 (7.75)	.150 (3.81)	.225 (5.72)	.120 (3.05)

CASE#	N	P	Q	R	WT.GRAM
HP1156	.275 (6.99)	1.400 (35.56)	.110 (2.79)	.770 (19.56)	6.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13microns) Gold over 120-240 μ inch (3.05-6.10microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F89

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	32	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M145648	NEW RELEASE	MAR 14	DDR	MD

**SUGGESTED MOUNTING CONFIGURATION FOR
HP1156 CASE STYLE "18FL01" PIN CODE**



NOTES:

- TRACE WIDTH IS SHOWN FOR OAK-602, WITH DIELECTRIC THICKNESS $.022 \pm .0015$ ". COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005" ANGLES ± FRACTIONS ±	DRAWN	DDR 14 MAR 14
	CHECKED	MD 14 MAR 14
	APPROVED	MD 14 MAR 14





Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

**PL, 18FL01, HP1156, BPF
TB-695+, 50 Ohm**

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-418	REV: OR
FILE: 98PL418	SCALE: 3:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 Inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215