

LTCC

# Bandpass Filter

50Ω 2400 to 2500 MHz

## Features

- High Rejection.
- Miniature size 0603
- Low cost
- Aqueous washable


## Applications

- ISM Band
- WLAN
- Bluetooth
- Zigbee

### Block Diagram



### Top View



### Pad Connections

Input	1
Output	3
Ground	2,4

## BPJC-252R+



Generic photo used for illustration purposes only

CASE STYLE: JC0603C-1

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 3000

## Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency		—	—	2450	—	MHz
	Insertion Loss	F1-F2	2400 – 2500	—	2.3	3.2	dB
	VSWR	F1-F2	2400 – 2500	—	1.4	2	:1
Stop Band, Lower	Rejection		695 – 880	25	46	—	dB
			1910	20	26	—	dB
Stop Band, Upper	Rejection		3200	35	38	—	dB
			4800 - 5000	20	29	—	dB
			7200 - 7500	20	43	—	dB

1. Tested on Evaluation Board TB-1023+.

### Maximum Ratings



Operating Temperature	-40°C to +85°C
Storage Temperature*	-40°C to +85°C
RF Power Input**	0.5W at 25°C

\* Refer to product storage temperature after installation  
Suggestion for T&R unused product storage condition:  
+5 ~ +35 °C, Humidity 45-75%RH, 12 month Max

\*\*Derate linearly to 0.25W at 85°C.

## Typical Performance Data at 25°C


Frequency (GHz)	Insertion Loss (dB)	VSWR (:1)
0.50	48.37	2136.92
0.70	46.33	677.41
0.88	45.53	2146.38
1.50	50.11	725.50
1.90	27.37	204.87
2.00	22.95	167.73
2.40	2.81	1.80
2.44	2.23	1.30
2.50	2.11	1.42
3.00	23.70	55.93
3.20	36.29	85.70
4.00	30.90	407.47
4.80	29.18	315.18
4.90	29.11	315.66
5.00	29.05	243.46
6.00	30.18	73.23
7.20	42.31	137.13
7.50	45.22	505.84
8.00	37.15	2458.98




# Bandpass Filter

# BPJC-252R+

## Outline Drawing



## Demo Board MCL P/N: TB-1023+ Suggested PCB Layout (PL-563)



## Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.063	.031	.024	.018	.028	.006	.012	.100	.071
1.60	0.79	0.61	0.46	0.71	0.15	0.30	2.54	1.80
K	L	M	N	P	Q	R	wt	
.032	.028	.012	.049	.026	.016	.014	grams	
0.81	0.71	0.30	1.24	0.66	0.41	0.36	0.005	

## Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
500	48.37	418.72	2136.92
600	47.13	666.70	373.60
700	46.33	677.41	407.40
800	45.76	3108.80	269.56
900	45.55	3194.05	1688.03
1000	45.77	4322.72	541.95
1100	46.54	1731.85	325.99
1200	48.32	1001.83	1052.26
1300	52.44	446.65	2201.81
1400	69.45	409.70	313.73
1500	50.11	293.05	725.50
1600	42.00	264.79	28019.30
1700	36.45	197.82	243.02
1800	31.74	169.41	330.50
1900	27.37	123.54	204.87
2000	22.95	85.71	167.73
2100	18.29	48.07	66.46
2200	13.06	21.82	23.67
2300	7.23	7.03	6.97
2400	2.81	1.80	1.73
2410	2.65	1.65	1.58
2420	2.45	1.47	1.41
2430	2.35	1.38	1.32
2440	2.23	1.30	1.25
2450	2.18	1.28	1.24
2460	2.13	1.29	1.26
2470	2.11	1.31	1.29
2480	2.10	1.36	1.33
2490	2.10	1.39	1.36
2500	2.11	1.42	1.39
2600	2.67	1.54	1.30
2700	6.40	4.85	4.46
2800	12.43	14.83	14.56
2900	18.24	31.12	32.15
3000	23.70	50.58	55.93
3100	29.38	70.16	73.85
3200	36.29	85.70	82.41
3300	45.18	100.50	106.89
3400	41.72	110.13	126.42
3500	37.33	125.35	156.15
3600	34.90	134.61	158.91
3700	33.34	143.11	139.12
3800	32.30	139.26	147.29
3900	31.49	140.06	217.77
4000	30.90	138.26	407.47
4100	30.41	138.85	439.33
4200	30.08	132.86	458.97
4300	29.84	131.41	282.30
4400	29.61	125.89	296.43
4500	29.44	122.21	360.73
4600	29.32	119.10	334.41
4700	29.22	112.04	572.00
4800	29.18	105.09	315.18
4900	29.11	100.60	315.66
5000	29.05	97.16	243.46
5100	29.00	93.73	229.25
5200	28.95	89.56	305.62
5300	28.96	86.23	237.52
5400	28.99	80.97	230.19
5500	29.08	76.65	131.76
5600	29.22	71.79	102.71
5700	29.38	68.29	91.53
5800	29.57	64.75	86.01
5900	29.85	62.75	81.97
6000	30.18	61.54	73.23
6200	31.06	60.74	67.96
6400	32.29	61.10	71.28
6600	33.92	65.76	70.56
6800	36.00	75.76	75.46
7000	38.74	92.44	88.69
7200	42.31	115.67	137.13
7400	45.52	159.11	233.85
7600	43.68	245.45	1222.97
7800	40.03	506.19	289.55
8000	37.15	2458.98	185.75









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)


**IF/RF MICROWAVE COMPONENTS**

## Typical Performance Curves




## Outline Dimensions

JC0603C-1



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
JC0603C-1	.063 (1.60)	.031 (0.80)	.024 (0.60)	.018 (0.45)	.028 (0.70)	.006 (0.15)	.012 (0.30)	.100 (2.54)	.071 (1.80)	.032 (0.80)	.028 (0.70)

CASE #	M*	N	P	Q	R	WT. GRAMS
JC0603C-1	.012 (0.30)	.049 (1.24)	.026 (0.65)	.016 (0.40)	.014 (0.35)	.005

Dimensions are in inches (mm). Tolerances: 3 Pl.  $\pm .004$

### Notes:

1. Open style, ceramic base.
2. Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- 3.\* - Line width should be designed to match 50 OHMS characteristic impedance, depending on PCB material & thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F74


## DEVICE ORIENTATION IN T&R



**ILLUSTRATION 1**

### Applicable Case Styles


GE0805C-1  
 GE0805C-1AP  
 JV1210C-1  
 GU2939



**ILLUSTRATION 2**

### Applicable Case Styles

JV1210C  
 JV1210C-2  
 JV1210C-3  
 JV1210C-4  
 JV1210C-5  
 JV1210C-6  
 JV1210C-11



**ILLUSTRATION 3**

### Applicable Case Styles

JC0603C-8  
 JV1210C-7  
 JV1210C-8  
 JV1210C-9  
 JV1210C-10  
 JV1210C-13  
 GE0805C-13

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000
				2000
			4000	

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M168200	NEW RELEASE	05/31/18	NP	SL

**SUGGESTED MOUNTING CONFIGURATION  
FOR JC0603C-1 CASE STYLE, "04FL01" PIN CODE**



**NOTES:**

1. TRACE WIDTH IS SHOWN FOR FR4, GRADE IT-180TC (ITEQ CORP.) WITH DIELECTRIC THICKNESS  $.016 \pm .0015$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	NP	05/30/18
CHECKED	GF	05/30/18
APPROVED	SL	05/31/18


**Mini-Circuits**<sup>®</sup> 13 Neptune Avenue  
Brooklyn NY 11235

**PL, 04FL01, JC0603C-1, TB-1023+**


**Mini-Circuits**<sup>®</sup>  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.  
 ASHETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-563	OR
FILE:	98PL563	SCALE: 10:1	SHEET: 1 OF 1

# Evaluation Board and Circuit




TB-1023+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: FR4 or equivalent,  
Dielectric Constant=4.5, Thickness=.016 inch.

 **Mini-Circuits®**





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A