

Surface Mount Bandpass Filter

CBP-1034C+

50Ω 978 to 1090 MHz



Generic photo used for illustration purposes only
CASE STYLE: MP1766

The Big Deal

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package

Product Overview

CBP-1034C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aviation, mobile radio, broadband and fixed wireless.

Key Features

Feature	Advantages
High Selectivity	The CBP-1034C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1034C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount

Bandpass Filter

50Ω

978 to 1090 MHz

CBP-1034C+




Features

- Low Insertion loss
- High selectivity
- Miniature shielded package


Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	—	1034	—	MHz
	Insertion Loss	F1-F2	978-1090	—	0.6	2	dB
	VSWR	F1-F2	978-1090	—	1.2	—	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-790	20	30	—	dB
	VSWR	DC-F3	DC-790	—	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	1400-2000	20	30	—	dB
	VSWR	F4-F5	1400-2000	—	20	—	:1





Electrical Specifications at 25°C

Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	5W

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	94.35	1737.18	978	4.06
660	63.48	64.35	984	3.96
790	31.74	43.44	989	3.89
850	15.91	26.33	992	3.85
875	8.62	11.93	996	3.79
890	4.76	5.72	1000	3.75
905	2.22	2.75	1008	3.68
920	1.14	1.65	1015	3.64
978	0.64	1.13	1020	3.60
1034	0.58	1.09	1025	3.58
1090	0.59	1.09	1030	3.55
1145	1.75	2.60	1034	3.54
1170	3.95	5.49	1040	3.51
1190	6.49	10.13	1045	3.50
1230	12.09	25.19	1050	3.48
1330	24.12	48.26	1055	3.48
1550	50.44	48.26	1060	3.48
1600	75.91	48.26	1070	3.50
1900	55.39	48.26	1080	3.54
2000	61.65	46.96	1090	3.60



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


 **Mini-Circuits®**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13


**Demo Board MCL P/N: TB-684+
Suggested PCB Layout (PL-373)**

**NOTES:**

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing**Outline Dimensions (inch)**

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z		
.790	.541	.790	.499	.384	.203	.080	.069	.630	.630	.145		
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68	wt, grams	4.6

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Band Pass Filter

CBP-1034C+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
	1	101.90	94.35	97.78	0.00	0.00	0.00	0.00	0.00
75	106.40	97.87	96.71	0.01	0.01	0.01	0.01	0.01	0.01
150	97.51	98.25	97.78	0.01	0.02	0.02	0.01	0.02	0.02
175	105.01	94.12	100.77	0.01	0.03	0.03	0.01	0.03	0.03
200	92.62	95.18	89.67	0.01	0.03	0.04	0.01	0.03	0.04
300	82.95	85.16	86.22	0.04	0.07	0.07	0.04	0.07	0.07
400	77.75	77.59	77.74	0.08	0.11	0.12	0.07	0.11	0.11
500	73.11	72.92	73.46	0.13	0.17	0.18	0.12	0.16	0.17
550	73.08	73.01	72.86	0.16	0.20	0.21	0.14	0.19	0.20
600	78.84	78.62	80.51	0.19	0.24	0.24	0.17	0.23	0.23
650	66.56	66.16	66.38	0.22	0.27	0.28	0.21	0.26	0.27
700	52.91	52.76	52.68	0.26	0.31	0.32	0.24	0.30	0.31
755	40.19	40.02	39.86	0.30	0.36	0.37	0.29	0.35	0.37
790	31.95	31.74	31.58	0.34	0.40	0.42	0.32	0.40	0.41
810	26.96	26.76	26.58	0.37	0.44	0.46	0.35	0.43	0.46
835	20.36	20.14	19.95	0.45	0.54	0.56	0.44	0.53	0.56
855	14.67	14.45	14.25	0.62	0.74	0.79	0.62	0.74	0.79
875	8.80	8.62	8.44	1.25	1.46	1.56	1.26	1.46	1.56
890	4.85	4.76	4.64	2.72	3.07	3.26	2.73	3.07	3.26
900	2.89	2.88	2.83	4.68	5.18	5.44	4.69	5.18	5.44
905	2.18	2.22	2.19	6.04	6.61	6.91	6.05	6.61	6.91
915	1.28	1.38	1.39	9.46	10.18	10.52	9.46	10.16	10.49
925	0.85	0.98	1.01	13.56	14.40	14.75	13.52	14.33	14.66
950	0.55	0.69	0.73	23.09	23.96	24.02	22.56	23.42	23.42
968	0.51	0.65	0.68	25.02	25.45	25.38	24.08	24.61	24.53
978	0.50	0.64	0.67	24.68	24.92	24.93	23.72	24.08	24.10
988	0.49	0.62	0.66	24.25	24.39	24.51	23.32	23.59	23.72
998	0.48	0.61	0.64	24.11	24.24	24.48	23.22	23.46	23.70
1010	0.47	0.60	0.63	24.57	24.76	25.14	23.72	23.99	24.35
1034	0.45	0.58	0.61	28.07	28.50	29.42	27.27	27.68	28.51
1060	0.43	0.57	0.60	33.83	34.15	35.41	34.98	35.54	37.39
1090	0.45	0.59	0.63	26.89	26.49	26.33	27.43	27.09	26.95
1105	0.50	0.66	0.70	20.12	19.70	19.42	20.26	19.83	19.56
1135	1.03	1.25	1.33	9.66	9.41	9.20	9.68	9.42	9.21
1155	2.16	2.46	2.60	5.30	5.18	5.06	5.30	5.18	5.06
1175	4.17	4.54	4.70	2.74	2.74	2.69	2.73	2.72	2.68
1180	4.78	5.16	5.33	2.32	2.34	2.31	2.31	2.33	2.29
1210	8.90	9.30	9.47	0.96	1.04	1.04	0.93	1.01	1.02
1230	11.70	12.09	12.25	0.62	0.71	0.72	0.59	0.69	0.70
1260	15.68	16.04	16.18	0.41	0.50	0.52	0.38	0.48	0.49
1290	19.34	19.67	19.78	0.34	0.42	0.44	0.31	0.40	0.42
1370	28.01	28.29	28.36	0.31	0.38	0.39	0.27	0.35	0.36
1400	31.06	31.33	31.40	0.31	0.38	0.39	0.28	0.36	0.37
1480	39.53	39.77	39.84	0.31	0.38	0.39	0.28	0.35	0.36
1510	43.17	43.42	43.48	0.32	0.39	0.39	0.28	0.36	0.36
1550	50.23	50.44	50.62	0.32	0.39	0.39	0.29	0.36	0.37
1580	58.10	58.84	59.30	0.32	0.38	0.39	0.29	0.36	0.37
1600	73.53	75.91	77.90	0.32	0.38	0.39	0.29	0.36	0.37
1630	59.96	59.55	59.25	0.32	0.38	0.39	0.29	0.36	0.37
1670	53.85	53.77	53.61	0.31	0.38	0.39	0.29	0.36	0.37
1700	52.37	52.38	52.41	0.31	0.37	0.38	0.29	0.36	0.37
1720	51.93	51.93	51.87	0.31	0.38	0.38	0.29	0.36	0.37
1750	51.29	51.29	51.30	0.30	0.38	0.38	0.29	0.36	0.37
1810	52.12	52.08	51.85	0.30	0.37	0.38	0.29	0.36	0.37
1860	54.30	54.48	54.35	0.29	0.37	0.38	0.29	0.36	0.37
1900	55.27	55.39	55.66	0.29	0.37	0.38	0.28	0.36	0.37
1940	58.63	58.70	58.77	0.29	0.37	0.38	0.28	0.36	0.37
1960	59.92	59.71	59.92	0.29	0.37	0.38	0.28	0.36	0.38
1980	59.76	60.06	59.86	0.28	0.37	0.39	0.29	0.37	0.38
2000	61.48	61.65	60.87	0.28	0.37	0.39	0.29	0.37	0.39



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

CBP-1034C+

130408

Page 1 of 2

Band Pass Filter**CBP-1034C+***Typical Performance Data*

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@ -40°C	@ +25°C	@ +85°C
978	4.09	4.06	4.05
980	4.05	4.02	4.02
982	4.02	3.99	3.98
984	3.98	3.96	3.95
985	3.96	3.94	3.93
986	3.95	3.93	3.92
988	3.92	3.90	3.89
990	3.89	3.87	3.86
992	3.87	3.85	3.84
994	3.85	3.82	3.82
996	3.82	3.79	3.79
998	3.79	3.77	3.77
1000	3.77	3.75	3.75
1002	3.75	3.73	3.73
1004	3.73	3.71	3.71
1006	3.71	3.69	3.69
1008	3.70	3.68	3.68
1010	3.68	3.67	3.67
1012	3.67	3.66	3.65
1014	3.65	3.64	3.63
1016	3.65	3.63	3.63
1018	3.63	3.61	3.61
1020	3.62	3.60	3.60
1022	3.60	3.59	3.59
1024	3.60	3.58	3.59
1026	3.59	3.57	3.57
1028	3.58	3.57	3.57
1029	3.57	3.56	3.56
1030	3.57	3.55	3.55
1032	3.56	3.55	3.55
1034	3.55	3.54	3.54
1036	3.54	3.53	3.53
1038	3.53	3.52	3.52
1040	3.52	3.51	3.51
1042	3.51	3.50	3.50
1044	3.50	3.50	3.50
1046	3.50	3.49	3.49
1048	3.49	3.49	3.48
1050	3.49	3.48	3.48
1052	3.49	3.48	3.48
1054	3.49	3.49	3.49
1056	3.49	3.48	3.48
1058	3.49	3.49	3.49
1060	3.49	3.48	3.48
1062	3.49	3.49	3.49
1064	3.50	3.49	3.50
1066	3.50	3.49	3.50
1068	3.50	3.50	3.50
1070	3.50	3.50	3.51
1072	3.51	3.51	3.51
1073	3.51	3.52	3.52
1074	3.52	3.51	3.52
1076	3.52	3.53	3.53
1078	3.54	3.53	3.54
1080	3.54	3.54	3.55
1082	3.55	3.55	3.56
1084	3.55	3.56	3.57
1085	3.56	3.57	3.58
1088	3.58	3.58	3.59
1090	3.60	3.60	3.61



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
Mouser Electronics The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS









REV. OR
CBP-1034C+
130408
Page 2 of 2

Band Pass Filter

CBP-1034C+

Typical Performance Curves



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

CBP-1034C+


130408

Page 1 of 2

Band Pass Filter

CBP-1034C+

Typical Performance Curves




Case Style


MP

Outline Dimensions

MP1766



PCB Land Pattern



METALLIZATION
 SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site


The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



RF/IIF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111

DEVICE ORIENTATION IN T&R



Applicable Case styles:

Applicable Case styles:RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV	ECN No.	DESCRIPTION			DATE
OR	M137721	NEW RELEASE			JUN 12

SUGGESTED MOUNTING CONFIGURATION FOR
MP1766 CASE STYLE "13FL01" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS $.022'' \pm .0015''$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON:
2 PL DECIMALS $\pm .005''$
3 PL DECIMALS $\pm .005''$
ANGLES \pm
FRACTIONS \pm

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 13FL01, MP1766, BPF,
TB-684+, 50 Ohm


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-373	REV: OR
FILE: 98PL373	SCALE: 4:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

INDEX



TB-684+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A