

Precision Fixed Attenuator BW-SXXW2+Series

50Ω 2W DC to 18000 MHz

The Big Deal

- Wideband, DC to 18 GHz
- Outstanding attenuation flatness
- Excellent VSWR, 1.11 typ up to 18 GHz



CASE STYLE: FF658

Product Overview

The BW-SXXW2+ series of precision fixed attenuators achieves wide frequency range with excellent flatness of attenuation. Available in a variety of attention values for different requirements, these units support a broad range of system and testing applications. Precise performance, excellent VSWR (1.11:1 typ.) and passivated stainless steel construction make these models ideal solutions for systems requiring precise attenuation across very wide frequency range.

Key Features

Feature	Advantages
Wideband, DC to 18 GHz	Ideal for an exceptionally wide variety of applications.
Excellent VSWR, 1.11 typ. up to 18 GHz	Efficient power utilization with low power reflected back to source.
Outstanding attenuation flatness	Provides precise, consistent attenuation across the entire frequency band, ideal for broadband and multi-band usage.
Passivated stainless steel connectors	Rugged construction withstands harsh environmental conditions for high reliability and long life of use.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Precision Fixed Attenuator

BW-S0.5W2+

50Ω 2W 0.5dB DC to 18000 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Input Power ¹	2W max

Permanent damage may occur if any of these limits are exceeded.
1. Derates linearly to 10% at 125°C

Features

- DC to 18 GHz
- precise attenuation
- excellent VSWR, 1.11:1 typ. up to 18 GHz
- passivated stainless steel connectors

Applications

- test instrument
- lab use



Generic photo used for illustration purposes only


CASE STYLE: FF658

Connectors _____ Model _____
SMA Female-SMA Male BW-S0.5W2+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch/mm)

B	D	E	F	wt
.36	.85	.312	.312	grams
9.14	21.59	7.92	7.92	4.3


Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		DC	—	18	MHz
Attenuation	10-6000	0.2	0.4	0.8	dB
	6000-12400	0.2	0.5	0.8	
	12400-18000	0.2	0.6	0.8	
Input VSWR	10-6000	—	1.01	1.15	:1
	6000-12400	—	1.09	1.25	
	12400-18000	—	1.11	1.35	
Output VSWR	10-6000	—	1.02	1.15	:1
	6000-12400	—	1.07	1.25	
	12400-18000	—	1.12	1.35	


Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)	
		SMA-M	SMA-F
10	0.34	1.02	1.02
100	0.35	1.02	1.02
2000	0.39	1.04	1.01
4000	0.41	1.04	1.00
6000	0.45	1.02	1.04
8000	0.48	1.02	1.07
10000	0.51	1.02	1.09
12500	0.57	1.03	1.11
14000	0.59	1.05	1.02
16000	0.66	1.15	1.08
18000	0.72	1.19	1.10


Electrical Schematic



BW-S0.5W2+ ATTENUATION



BW-S0.5W2+ VSWR



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT VSWR			OUTPUT VSWR		
(MHz)	(dB)			(:1)			(:1)		
	@-55°C	@25°C	@+100°C	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C
10	0.34	0.34	0.34	1.02	1.02	1.02	1.02	1.02	1.02
100	0.35	0.35	0.35	1.02	1.02	1.02	1.02	1.02	1.02
500	0.37	0.37	0.37	1.03	1.03	1.03	1.02	1.02	1.02
1000	0.37	0.37	0.38	1.03	1.03	1.03	1.02	1.02	1.02
1500	0.38	0.38	0.38	1.03	1.03	1.03	1.02	1.02	1.02
2000	0.39	0.39	0.39	1.04	1.04	1.04	1.01	1.01	1.01
2500	0.39	0.39	0.40	1.04	1.04	1.04	1.01	1.01	1.01
3000	0.40	0.40	0.40	1.04	1.04	1.04	1.00	1.00	1.00
3500	0.41	0.41	0.41	1.04	1.04	1.04	1.00	1.00	1.00
4000	0.41	0.41	0.42	1.05	1.04	1.04	1.00	1.00	1.00
4500	0.42	0.42	0.43	1.05	1.04	1.04	1.00	1.01	1.01
5000	0.43	0.43	0.44	1.04	1.04	1.03	1.02	1.02	1.02
5500	0.44	0.44	0.44	1.03	1.03	1.02	1.03	1.03	1.03
6000	0.44	0.45	0.45	1.02	1.02	1.02	1.04	1.04	1.04
6500	0.45	0.45	0.46	1.02	1.01	1.01	1.05	1.05	1.05
7000	0.46	0.46	0.47	1.03	1.02	1.02	1.06	1.05	1.06
7500	0.47	0.47	0.48	1.03	1.02	1.02	1.07	1.06	1.07
8000	0.48	0.48	0.48	1.03	1.02	1.02	1.08	1.07	1.08
8500	0.48	0.48	0.49	1.03	1.03	1.03	1.08	1.08	1.08
9000	0.50	0.50	0.50	1.03	1.03	1.03	1.08	1.08	1.08
9500	0.50	0.50	0.51	1.03	1.02	1.02	1.09	1.08	1.08
10000	0.51	0.51	0.52	1.03	1.02	1.01	1.10	1.09	1.09
10500	0.52	0.52	0.53	1.03	1.02	1.01	1.11	1.10	1.09
11000	0.54	0.53	0.54	1.03	1.02	1.02	1.10	1.10	1.09
11500	0.55	0.54	0.55	1.04	1.03	1.03	1.10	1.10	1.10
12000	0.56	0.56	0.57	1.03	1.03	1.03	1.10	1.11	1.10
12500	0.57	0.57	0.58	1.03	1.03	1.03	1.10	1.11	1.11
13000	0.57	0.57	0.58	1.01	1.02	1.02	1.08	1.09	1.09
13500	0.58	0.58	0.59	1.03	1.02	1.03	1.04	1.06	1.05
14000	0.59	0.59	0.60	1.06	1.05	1.06	1.00	1.02	1.01
14500	0.61	0.61	0.62	1.10	1.09	1.09	1.03	1.03	1.03
15000	0.63	0.62	0.63	1.13	1.12	1.12	1.05	1.05	1.05
15500	0.64	0.64	0.65	1.14	1.14	1.15	1.06	1.07	1.07
16000	0.66	0.66	0.67	1.15	1.15	1.15	1.07	1.08	1.08
17000	0.68	0.68	0.70	1.15	1.15	1.15	1.06	1.07	1.07
18000	0.72	0.72	0.73	1.19	1.19	1.19	1.10	1.10	1.10



Typical Performance Curves




Case Style

FF

Outline Dimensions

FF658
FF659



CASE #.	A	B	C	D	E	F	WT GRAMS
FF658	--	.36 (9.14)	--	.85 (21.59)	.312 (7.92)	.312 (7.92)	4.3
FF659	--		--	.99 (25.15)			5.1

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

1. Case material: Stainless steel.

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From Mini-CIRCUITS At: www.minicircuits.com



RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I