



### FEATURES

- RoHS compliant
- Wideband coverage, DC to 3000 MHz
- Extra rugged construction with strain relief for longer life
- Stainless steel N-Male connectors for long mating-cycle life
- Useful over temperature range, -55°C to +105°C
- Triple shield cable for excellent shielding effectiveness
- Flexible for easy connection & bend radius
- 6 month guarantee\*

### APPLICATIONS

- High volume production test stations
- Research & development labs
- Environmental & temperature test chambers
- Replacement for OEM test port cables
- Field RF testing
- Cellular infrastructure site testing

### PRODUCT OVERVIEW

Mini-Circuits CBL-NM-75+ series 75Ω test cables provide extra rugged yet flexible construction, performance qualified up to 20,000 flex cycles for test applications from DC to 3000 MHz, backed by our 6-month product guarantee. Connectors are N-type (M) to N-type (M). Inner conductor is solid silver-plated, copper clad steel, and shield is silver-plated copper braid with aluminum-polymide tape interlayer. Available in a variety of lengths.

### KEY FEATURES

Feature	Advantages
Wideband, DC to 3000 MHz	Wide frequency range covers many applications.
High Power Handling: <ul style="list-style-type: none"> <li>• 338W @ 0.5 GHz</li> <li>• 98W @ 3 GHz</li> </ul>	High power handling makes CBL test cables suitable for applications with a wide range of requirements.
Good Return Loss and Low Insertion Loss	Well matched for 75Ω systems across the entire frequency band.
Extra rugged, triple shield cable construction	CBL-FM-75+ test cables provide outstanding durability, flexibility, and shielding effectiveness.
Passivated stainless steel N-Male connectors	Long connector mating cycle life.
Superior stability of Insertion Loss and Return Loss	Reliable performance in almost any test layout configuration.



Generic photo used for illustration purposes only

Model No.	CBL-4NM-75+
Case Style	ND1920-4
Connectors	N-Male

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

#### Product Guarantee\*

Mini-Circuits\* will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.



# Test Cable

## CBL-4NM-75+

Mini-Circuits

75Ω 4FT DC to 3000 MHz N-Male

### ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency range		DC		3000	MHz
Length <sup>1</sup>		4			FT
Insertion Loss	DC - 500	—	0.26	0.5	dB
	500 - 1000	—	0.43	0.7	
	1000 - 2000	—	0.62	1.0	
	2000 - 3000	—	0.80	1.2	
Return Loss	DC - 500	26	41	—	dB
	500 - 1000	26	42	—	
	1000 - 2000	24	34	—	
	2000 - 3000	24	31	—	

1. Custom sizes available, consult factory.

### ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
Power Handling at 25°C, Sea Level	338W Max. at 0.5 GHz 210W Max. at 1 GHz 143W Max. at 2 GHz 98W Max. at 3 GHz

Permanent damage may occur if any of these limits are exceeded.






### CABLE CONSTRUCTION



### OUTLINE DRAWING



### OUTLINE DIMENSIONS (Inch mm)

A		B	C	D	E	T		wt
Feet	Meters	.81	.750	.81	.750	Feet	Meters	grams
4	1.22	20.57	19.05	20.57	19.05	0.12	0.04	147



# Test Cable



## CBL-4NM-75+

Mini-Circuits

75Ω 4FT DC to 3000 MHz N-Male

### TYPICAL PERFORMANCE DATA

Frequenc (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		N-Male	N-Male
40	0.10	36.99	36.70
70	0.13	42.43	42.26
100	0.16	41.47	39.54
400	0.31	43.47	43.47
700	0.42	44.36	43.12
1000	0.50	36.26	35.99
1300	0.58	32.30	33.33
1600	0.63	35.50	36.38
1800	0.68	32.38	33.76
2000	0.72	30.30	29.50
2200	0.74	35.16	33.77
2400	0.77	32.84	28.83
2600	0.82	27.57	27.26
2800	0.84	31.07	31.96
3000	0.84	30.02	26.89



#### NOTES



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10	0.06	41.22	41.44
20	0.06	38.24	38.37
30	0.08	37.01	37.02
40	0.10	36.99	36.70
50	0.10	37.64	37.55
60	0.12	39.32	39.06
70	0.13	42.43	42.26
80	0.14	46.58	44.85
90	0.15	44.81	42.55
100	0.16	41.47	39.54
200	0.23	49.66	48.74
300	0.27	41.27	40.41
400	0.31	43.47	43.47
500	0.35	38.88	41.08
600	0.38	40.78	45.18
700	0.42	44.36	43.12
800	0.44	48.70	56.02
900	0.47	47.28	46.03
1000	0.50	36.26	35.99
1100	0.53	34.96	34.94
1200	0.55	31.52	32.22
1300	0.58	32.30	33.33
1400	0.60	36.75	38.75
1500	0.62	45.98	42.96
1600	0.63	35.50	36.38
1700	0.66	32.64	34.27
1800	0.68	32.38	33.76
1900	0.70	31.65	31.59
2000	0.72	30.30	29.50
2100	0.73	31.95	30.49
2200	0.74	35.16	33.77
2300	0.76	50.10	31.81
2400	0.77	32.84	28.83
2500	0.80	28.96	27.02
2600	0.82	27.57	27.26
2700	0.85	29.24	30.38
2800	0.84	31.07	31.96
2900	0.84	34.04	28.77
3000	0.84	30.02	26.89

## Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 105°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -105°C
Mechanical Flexing	20,000 cycles During each cycle, cable flexed from 90° through 0° to -90° and back with a Radii of 3 inches	- - -