

Surface Mount

Bandpass Filter

CBP-1950C+

50Ω 1920 to 1980 MHz



Generic photo used for illustration purposes only
CASE STYLE: MP1766

The Big Deal

- Narrow bandwidth
- Excellent Rejection
- High power handling
- Miniature shielded package

Product Overview

CBP-1950C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in public cellular networks and CDMA handsets applications

Key Features

Feature	Advantages
High Selectivity	The CBP-1950C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1950C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount

Bandpass Filter

50Ω

1920 to 1980 MHz

CBP-1950C+




Features

- Narrow bandwidth
- Excellent rejection
- High selectivity
- High power handling
- Miniature shielded package


Applications

- Public cellular network
- Wireless local loop (WLL)
- WCDMA handsets

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications





Electrical Specifications at 25°C						
	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.
Pass Band	Center Frequency	—	—	—	1950	—
	Insertion Loss	F1-F2	1920-1980	—	1.00	2.50
	VSWR	F1-F2	1920-1980	—	1.33	2.32
Stop Band, Lower	Insertion Loss	DC-F3	DC-1740	20	32	—
	VSWR	DC-F3	DC-1740	—	20	—
Stop Band, Upper	Insertion Loss	F4-F5	2190-4300	20	27	—
	VSWR	F4-F5	2190-4300	—	20	—

Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10W

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	103.07	347.44	1920	4.52
700	92.01	347.44	1923	4.47
1200	75.56	133.63	1926	4.42
1740	34.02	45.72	1929	4.38
1754	30.51	42.38	1932	4.34
1790	20.22	28.03	1935	4.30
1818	10.49	11.93	1938	4.28
1840	3.31	3.00	1941	4.26
1880	1.13	1.29	1944	4.24
1920	0.93	1.22	1947	4.23
1950	0.92	1.30	1950	4.21
1980	0.85	1.08	1953	4.21
2030	1.17	1.38	1956	4.22
2055	3.64	3.92	1959	4.23
2100	13.46	23.81	1962	4.23
2134	20.00	44.55	1965	4.25
2190	28.31	66.82	1968	4.26
2204	30.05	69.49	1970	4.27
2550	65.91	91.43	1975	4.30
4300	38.17	40.41	1980	4.33



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13


**Demo Board MCL P/N: TB-684+
Suggested PCB Layout (PL-373)**

**NOTES:**

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS $.022'' \pm .0015''$, COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SODERMASK

Outline Drawing**Outline Dimensions (inch)**

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z		
.790	.541	.790	.499	.384	.203	.080	.069	.630	.145			
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68		
											wt, grams	4.6

Note: Please refer to case style drawing for details.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Band Pass Filter

CBP-1950C+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C
	1	99.55	103.07	106.57	0.05	0.05	0.05	0.05	0.05
200	109.13	103.56	96.87	0.01	0.03	0.03	0.01	0.03	0.03
500	92.56	98.61	97.78	0.00	0.03	0.04	0.00	0.04	0.05
860	83.43	82.74	85.99	0.02	0.07	0.09	0.03	0.09	0.11
1040	79.12	77.35	76.53	0.04	0.10	0.12	0.06	0.12	0.14
1160	76.20	76.13	76.00	0.06	0.12	0.14	0.08	0.14	0.17
1360	72.18	71.35	71.31	0.09	0.16	0.18	0.12	0.19	0.22
1420	73.16	72.46	71.93	0.10	0.17	0.20	0.13	0.20	0.24
1500	78.27	78.20	77.56	0.12	0.19	0.22	0.16	0.23	0.26
1540	65.85	67.16	65.50	0.14	0.21	0.24	0.17	0.25	0.28
1590	72.61	73.08	73.22	0.15	0.23	0.25	0.19	0.27	0.31
1646	55.99	55.79	55.62	0.17	0.26	0.29	0.21	0.30	0.34
1714	40.62	40.14	40.11	0.23	0.32	0.37	0.28	0.38	0.44
1740	34.55	34.02	33.95	0.27	0.38	0.43	0.32	0.44	0.50
1756	30.51	29.98	29.88	0.30	0.42	0.48	0.36	0.49	0.57
1760	29.46	28.93	28.83	0.31	0.43	0.50	0.37	0.51	0.59
1768	27.31	26.76	26.66	0.33	0.47	0.54	0.40	0.55	0.64
1790	20.81	20.22	20.14	0.45	0.62	0.72	0.53	0.74	0.86
1796	18.87	18.28	18.20	0.50	0.70	0.81	0.61	0.84	0.97
1798	18.20	17.61	17.54	0.53	0.73	0.84	0.63	0.87	1.01
1829	6.88	6.49	6.69	2.14	2.76	2.92	2.44	3.19	3.40
1839	3.62	3.54	3.83	4.62	5.59	5.61	5.20	6.42	6.46
1846	2.12	2.25	2.55	7.98	9.11	8.81	9.09	10.64	10.23
1859	1.09	1.36	1.56	15.87	16.46	16.28	19.82	19.73	18.97
1870	0.98	1.22	1.35	15.47	16.85	18.50	16.38	17.18	18.36
1874	0.95	1.18	1.31	15.28	16.98	18.90	15.81	16.91	18.14
1893	0.78	1.01	1.14	19.95	24.05	27.16	19.90	21.95	22.16
1903	0.69	0.94	1.08	30.90	46.41	34.02	29.30	27.49	24.80
1908	0.68	0.93	1.07	40.76	29.31	27.54	33.61	25.98	24.01
1920	0.68	0.93	1.05	21.05	20.20	20.89	20.86	19.94	20.51
1942	0.73	0.93	1.03	15.83	17.01	18.94	15.76	17.01	19.19
1950	0.72	0.92	1.01	15.86	17.60	20.03	15.79	17.62	20.52
1980	0.63	0.85	0.98	23.28	28.52	26.23	23.34	32.16	33.79
1984	0.62	0.85	0.99	25.59	30.00	25.13	25.84	39.09	29.62
1998	0.61	0.86	1.01	36.48	27.79	23.31	46.01	30.28	24.78
2005	0.62	0.87	1.02	36.93	28.43	24.87	36.48	29.33	25.53
2010	0.63	0.89	1.04	37.42	30.87	27.92	32.94	29.66	26.88
2014	0.64	0.91	1.06	35.62	32.89	31.14	30.27	28.71	26.73
2030	0.80	1.17	1.42	17.87	15.99	14.65	17.19	15.33	13.94
2062	3.84	4.97	5.78	3.59	3.16	2.87	3.57	3.12	2.83
2092	10.48	11.72	12.57	0.83	0.91	0.93	0.85	0.93	0.96
2100	12.26	13.46	14.28	0.61	0.73	0.77	0.64	0.75	0.79
2130	18.30	19.31	19.99	0.28	0.41	0.47	0.31	0.44	0.51
2132	18.66	19.66	20.34	0.27	0.40	0.46	0.31	0.44	0.50
2158	23.01	23.87	24.46	0.19	0.31	0.37	0.23	0.35	0.41
2190	27.57	28.31	28.83	0.15	0.26	0.31	0.19	0.30	0.36
2212	30.33	31.00	31.48	0.14	0.24	0.29	0.17	0.28	0.33
2350	43.33	43.99	44.17	0.12	0.21	0.24	0.14	0.23	0.27
2490	59.98	59.18	61.58	0.11	0.19	0.22	0.13	0.21	0.25
2560	69.13	65.07	73.68	0.10	0.19	0.22	0.12	0.21	0.24
2610	59.47	59.14	59.11	0.09	0.18	0.22	0.12	0.20	0.24
2660	60.86	59.61	59.08	0.09	0.18	0.21	0.11	0.20	0.23
2900	54.35	53.07	53.36	0.07	0.17	0.21	0.09	0.19	0.22
3120	46.01	46.29	45.07	0.07	0.18	0.23	0.08	0.18	0.23
3420	47.67	48.68	47.69	0.08	0.22	0.25	0.11	0.23	0.27
3500	44.05	44.05	43.73	0.07	0.20	0.27	0.11	0.24	0.29
3680	42.07	42.88	46.11	0.12	0.27	0.31	0.19	0.32	0.37
3780	42.55	41.48	41.81	0.10	0.25	0.32	0.17	0.32	0.39
4200	39.60	39.59	39.16	0.22	0.38	0.46	0.34	0.53	0.63
4300	38.47	38.17	38.47	0.25	0.43	0.51	0.34	0.56	0.68



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. OR

CBP-1950C+

140215

Page 1 of 2

Band Pass Filter**CBP-1950C+***Typical Performance Data*

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@ -40°C	@ +25°C	@ +85°C
1920	4.58	4.52	4.53
1921	4.56	4.50	4.51
1922	4.54	4.49	4.50
1923	4.52	4.47	4.48
1924	4.50	4.46	4.46
1925	4.49	4.44	4.46
1926	4.46	4.42	4.44
1927	4.45	4.41	4.44
1928	4.43	4.40	4.42
1929	4.41	4.38	4.40
1930	4.39	4.37	4.40
1931	4.38	4.36	4.39
1932	4.37	4.34	4.38
1933	4.34	4.33	4.36
1935	4.32	4.30	4.34
1936	4.31	4.30	4.34
1937	4.29	4.29	4.33
1938	4.28	4.28	4.32
1939	4.27	4.28	4.32
1940	4.26	4.26	4.31
1941	4.25	4.26	4.30
1942	4.24	4.25	4.30
1943	4.23	4.24	4.29
1944	4.22	4.24	4.29
1945	4.21	4.23	4.28
1946	4.21	4.23	4.28
1947	4.20	4.23	4.28
1948	4.19	4.22	4.27
1949	4.19	4.22	4.27
1950	4.18	4.21	4.26
1951	4.18	4.22	4.27
1952	4.18	4.21	4.27
1953	4.17	4.21	4.27
1954	4.17	4.21	4.27
1955	4.18	4.22	4.27
1956	4.18	4.22	4.27
1957	4.18	4.22	4.27
1958	4.18	4.22	4.28
1959	4.18	4.23	4.28
1960	4.18	4.22	4.28
1961	4.19	4.24	4.29
1962	4.19	4.23	4.28
1963	4.19	4.24	4.29
1964	4.20	4.24	4.29
1965	4.20	4.25	4.29
1966	4.21	4.25	4.30
1967	4.21	4.26	4.30
1968	4.22	4.26	4.30
1969	4.22	4.27	4.31
1970	4.23	4.27	4.31
1971	4.23	4.28	4.32
1972	4.24	4.28	4.32
1973	4.25	4.29	4.33
1974	4.26	4.30	4.33
1975	4.26	4.30	4.34
1976	4.27	4.31	4.35
1977	4.27	4.31	4.35
1978	4.28	4.32	4.35
1979	4.29	4.33	4.36
1980	4.30	4.33	4.36



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com







IF/RF MICROWAVE COMPONENTS

REV. OR
CBP-1950C+
140215
Page 2 of 2

Band Pass Filter

CBP-1950C+

Typical Performance Curves



 **Mini-Circuits®**

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


minicircuits.com

REV. OR
CBP-1950C+
140215
Page 1 of 2

Band Pass Filter

CBP-1950C+

Typical Performance Curves



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com



IF/RF MICROWAVE COMPONENTS

Case Style


MP

Outline Dimensions

MP1766



PCB Land Pattern



METALLIZATION
SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site


The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



RF/IIF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111

DEVICE ORIENTATION IN T&R



Applicable Case styles:

Applicable Case styles:RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION			DATE
	M137721	NEW RELEASE			JUN 12
					DDR
					KG

SUGGESTED MOUNTING CONFIGURATION FOR
MP1766 CASE STYLE "13FL01" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS $.022'' \pm .0015''$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON:
2 PL DECIMALS $\pm .005''$
3 PL DECIMALS $\pm .005''$
ANGLES \pm
FRACTIONS \pm

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 13FL01, MP1766, BPF,
TB-684+, 50 Ohm


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-373	OR
FILE:	98PL373	SCALE:	4:1
		SHEET:	1 OF 1

Evaluation Board and Circuit

INDEX



TB-684+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A