

# Surface Mount Bandpass Filter

## CBP-1250C+

50Ω 1215 to 1285 MHz

### The Big Deal

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package



Generic photo used for illustration purposes only  
CASE STYLE: MP1766

### Product Overview

CBP-1250C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aviation, mobile radio, broadband and fixed wireless.

### Key Features

| Feature             | Advantages   |
|---------------------|--|
| High Selectivity    | The CBP-1250C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.   |
| Low Passband VSWR   | This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple. |
| Rugged construction | The CBP-1250C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.                       |

#### Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

## CBP-1250C+

50Ω 1215 to 1285 MHz



Generic photo used for illustration purposes only  
CASE STYLE: MP1766


### Features

- Low Insertion loss
- High selectivity
- Miniature shielded package


### Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

### Functional Schematic



### Typical Frequency Response



### Electrical Specifications at 25°C

| Parameter        | F#               | Frequency (MHz) | Min.      | Typ. | Max. | Unit |
|------------------|------------------|-----------------|-----------|------|------|------|
| Pass Band        | Center Frequency | —               | —         | 1250 | —    | MHz  |
|                  | Insertion Loss   | F1-F2           | 1215-1285 | —    | 0.8  | 2 dB |
|                  | VSWR             | F1-F2           | 1215-1285 | —    | 1.2  | — :1 |
| Stop Band, Lower | Insertion Loss   | DC-F3           | DC-1055   | 20   | 30   | dB   |
|                  | VSWR             | DC-F3           | DC-1055   | —    | 20   | — :1 |
| Stop Band, Upper | Insertion Loss   | F4-F5           | 1510-2500 | 20   | 30   | dB   |
|                  | VSWR             | F4-F5           | 1510-2500 | —    | 20   | — :1 |

### Maximum Ratings





|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input        | 5W             |

Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (nsec) |
|-----------------|---------------------|-----------|-----------------|--------------------|
| 1               | 103.53              | 1737.18   | 1215            | 5.23               |
| 970             | 51.48               | 49.64     | 1218            | 5.18               |
| 1055            | 31.64               | 36.20     | 1223            | 5.07               |
| 1115            | 15.08               | 19.76     | 1226            | 5.01               |
| 1136            | 8.79                | 10.31     | 1230            | 4.96               |
| 1150            | 5.18                | 5.52      | 1234            | 4.90               |
| 1168            | 2.33                | 2.58      | 1237            | 4.86               |
| 1187            | 1.28                | 1.60      | 1240            | 4.84               |
| 1215            | 0.92                | 1.23      | 1245            | 4.80               |
| 1226            | 0.87                | 1.16      | 1250            | 4.76               |
| 1250            | 0.81                | 1.02      | 1255            | 4.75               |
| 1275            | 0.82                | 1.08      | 1258            | 4.74               |
| 1285            | 0.83                | 1.08      | 1261            | 4.73               |
| 1331            | 2.26                | 2.69      | 1265            | 4.74               |
| 1350            | 5.07                | 6.26      | 1268            | 4.75               |
| 1390            | 13.22               | 24.83     | 1272            | 4.76               |
| 1510            | 31.48               | 49.64     | 1276            | 4.78               |
| 1725            | 59.97               | 46.96     | 1280            | 4.82               |
| 2100            | 52.89               | 44.55     | 1283            | 4.86               |
| 2500            | 46.78               | 39.49     | 1285            | 4.89               |

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B  
M174392  
CBP-1250C+  
EDU1782  
URJ  
200811  
Page 2 of 3

## Pad Connections

|        |                          |
|--------|--------------------------|
| INPUT  | 1                        |
| OUTPUT | 10                       |
| GROUND | 2,3,4,5,6,7,8,9,11,12,13 |

**Demo Board MCL P/N: TB-684+**  
**Suggested PCB Layout (PL-373)**




### NOTES:


- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Outline Drawing



## PCB Land Pattern



## Outline Dimensions (inch)

| A     | B     | C     | D     | E    | F    | G    | H    | J     | K     | L    | M     | N    |
|-------|-------|-------|-------|------|------|------|------|-------|-------|------|-------|------|
| .750  | .750  | .210  | .139  | .157 | .215 | .160 | .218 | .157  | .100  | .060 | .069  | .149 |
| 19.05 | 19.05 | 5.33  | 3.53  | 3.99 | 5.46 | 4.06 | 5.54 | 3.99  | 2.54  | 1.52 | 1.75  | 3.78 |
| P     | Q     | R     | S     | T    | U    | V    | W    | X     | Y     | Z    | wt.   |      |
| .790  | .541  | .790  | .499  | .384 | .203 | .080 | .069 | .630  | .630  | .145 | grams |      |
| 20.07 | 13.74 | 20.07 | 12.67 | 9.75 | 5.16 | 2.03 | 1.75 | 16.00 | 16.00 | 3.68 | 4.6   |      |

*Note: Please refer to case style drawing for details*

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Band Pass Filter

# CBP-1250C+

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS |        |        | INPUT RETURN LOSS |        |        | OUTPUT RETURN LOSS |        |        |
|----------------|----------------|--------|--------|-------------------|--------|--------|--------------------|--------|--------|
|                | (dB)           |        |        | (dB)              |        |        | (dB)               |        |        |
|                | @-40°C         | @+25°C | @+85°C | @-40°C            | @+25°C | @+85°C | @-40°C             | @+25°C | @+85°C |
| 1              | 105.25         | 103.53 | 98.10  | 0.00              | 0.00   | 0.00   | 0.00               | 0.00   | 0.00   |
| 250            | 97.73          | 100.77 | 99.47  | 0.01              | 0.03   | 0.04   | 0.01               | 0.03   | 0.03   |
| 475            | 82.30          | 81.27  | 82.15  | 0.05              | 0.08   | 0.09   | 0.05               | 0.08   | 0.08   |
| 650            | 76.63          | 75.58  | 75.74  | 0.10              | 0.15   | 0.16   | 0.11               | 0.15   | 0.15   |
| 800            | 74.86          | 75.07  | 74.52  | 0.17              | 0.23   | 0.24   | 0.18               | 0.23   | 0.24   |
| 900            | 71.42          | 70.13  | 70.24  | 0.23              | 0.29   | 0.31   | 0.24               | 0.30   | 0.30   |
| 915            | 65.56          | 65.15  | 64.94  | 0.24              | 0.30   | 0.32   | 0.25               | 0.31   | 0.31   |
| 930            | 61.29          | 60.94  | 60.72  | 0.25              | 0.31   | 0.34   | 0.26               | 0.32   | 0.32   |
| 955            | 55.15          | 54.76  | 54.67  | 0.27              | 0.33   | 0.36   | 0.28               | 0.34   | 0.34   |
| 975            | 50.62          | 50.33  | 50.15  | 0.28              | 0.35   | 0.38   | 0.30               | 0.36   | 0.36   |
| 1000           | 44.99          | 44.66  | 44.48  | 0.31              | 0.38   | 0.41   | 0.33               | 0.39   | 0.40   |
| 1020           | 40.41          | 40.05  | 39.86  | 0.33              | 0.41   | 0.44   | 0.35               | 0.42   | 0.43   |
| 1055           | 32.05          | 31.64  | 31.42  | 0.38              | 0.48   | 0.51   | 0.40               | 0.49   | 0.50   |
| 1060           | 30.80          | 30.38  | 30.16  | 0.40              | 0.49   | 0.52   | 0.41               | 0.50   | 0.51   |
| 1080           | 25.61          | 25.15  | 24.90  | 0.45              | 0.56   | 0.60   | 0.47               | 0.57   | 0.59   |
| 1095           | 21.48          | 20.98  | 20.71  | 0.51              | 0.65   | 0.69   | 0.53               | 0.65   | 0.69   |
| 1100           | 20.06          | 19.54  | 19.26  | 0.54              | 0.69   | 0.74   | 0.56               | 0.69   | 0.73   |
| 1115           | 15.63          | 15.08  | 14.78  | 0.69              | 0.88   | 0.95   | 0.71               | 0.90   | 0.96   |
| 1120           | 14.13          | 13.57  | 13.27  | 0.78              | 0.99   | 1.07   | 0.80               | 1.01   | 1.08   |
| 1125           | 12.61          | 12.05  | 11.75  | 0.90              | 1.14   | 1.24   | 0.92               | 1.16   | 1.25   |
| 1138           | 8.73           | 8.23   | 7.96   | 1.44              | 1.84   | 2.00   | 1.47               | 1.86   | 2.02   |
| 1150           | 5.54           | 5.18   | 4.99   | 2.55              | 3.18   | 3.44   | 2.58               | 3.22   | 3.50   |
| 1155           | 4.44           | 4.16   | 4.01   | 3.28              | 4.03   | 4.34   | 3.32               | 4.09   | 4.41   |
| 1162           | 3.18           | 3.03   | 2.94   | 4.62              | 5.55   | 5.92   | 4.66               | 5.62   | 6.03   |
| 1170           | 2.17           | 2.15   | 2.12   | 6.56              | 7.66   | 8.10   | 6.62               | 7.77   | 8.25   |
| 1200           | 0.86           | 1.04   | 1.09   | 15.00             | 16.18  | 16.59  | 15.12              | 16.46  | 16.97  |
| 1215           | 0.73           | 0.92   | 0.97   | 18.64             | 19.72  | 20.10  | 18.71              | 20.03  | 20.56  |
| 1230           | 0.66           | 0.85   | 0.91   | 22.86             | 23.99  | 24.39  | 22.73              | 24.35  | 25.09  |
| 1250           | 0.61           | 0.81   | 0.87   | 37.99             | 39.12  | 36.20  | 32.41              | 38.49  | 45.32  |
| 1275           | 0.62           | 0.82   | 0.88   | 26.49             | 28.26  | 29.21  | 27.28              | 29.61  | 30.87  |
| 1285           | 0.63           | 0.83   | 0.89   | 25.54             | 28.24  | 30.09  | 27.90              | 32.86  | 37.04  |
| 1300           | 0.66           | 0.90   | 0.98   | 24.21             | 23.17  | 22.25  | 30.88              | 26.31  | 24.04  |
| 1308           | 0.73           | 1.00   | 1.10   | 19.34             | 17.48  | 16.55  | 21.26              | 18.45  | 17.18  |
| 1329           | 1.55           | 2.07   | 2.29   | 8.27              | 7.40   | 6.99   | 8.50               | 7.57   | 7.13   |
| 1338           | 2.46           | 3.11   | 3.38   | 5.41              | 4.90   | 4.65   | 5.54               | 5.00   | 4.73   |
| 1344           | 3.30           | 4.02   | 4.32   | 4.02              | 3.70   | 3.53   | 4.12               | 3.78   | 3.59   |
| 1385           | 11.49          | 12.22  | 12.51  | 0.69              | 0.79   | 0.81   | 0.71               | 0.81   | 0.82   |
| 1405           | 15.45          | 16.09  | 16.34  | 0.42              | 0.54   | 0.57   | 0.44               | 0.55   | 0.57   |
| 1430           | 19.87          | 20.41  | 20.63  | 0.31              | 0.42   | 0.45   | 0.32               | 0.43   | 0.45   |
| 1500           | 29.89          | 30.26  | 30.42  | 0.25              | 0.35   | 0.38   | 0.27               | 0.36   | 0.37   |
| 1510           | 31.13          | 31.48  | 31.63  | 0.25              | 0.35   | 0.38   | 0.27               | 0.35   | 0.37   |
| 1585           | 40.01          | 40.31  | 40.44  | 0.26              | 0.35   | 0.38   | 0.28               | 0.35   | 0.36   |
| 1630           | 45.22          | 45.51  | 45.59  | 0.27              | 0.35   | 0.38   | 0.28               | 0.35   | 0.36   |
| 1670           | 50.38          | 50.75  | 50.88  | 0.28              | 0.36   | 0.38   | 0.29               | 0.36   | 0.36   |
| 1700           | 55.07          | 55.52  | 55.80  | 0.28              | 0.36   | 0.38   | 0.29               | 0.36   | 0.37   |
| 1725           | 59.54          | 59.97  | 60.45  | 0.28              | 0.37   | 0.39   | 0.30               | 0.37   | 0.37   |
| 1750           | 71.41          | 72.67  | 72.82  | 0.29              | 0.37   | 0.39   | 0.30               | 0.37   | 0.37   |
| 1775           | 71.36          | 69.32  | 68.84  | 0.29              | 0.37   | 0.39   | 0.30               | 0.37   | 0.37   |
| 1825           | 58.94          | 58.43  | 58.05  | 0.29              | 0.37   | 0.39   | 0.30               | 0.37   | 0.37   |
| 1875           | 55.87          | 55.77  | 55.63  | 0.30              | 0.38   | 0.39   | 0.31               | 0.37   | 0.38   |
| 1975           | 53.57          | 53.24  | 52.98  | 0.30              | 0.38   | 0.40   | 0.31               | 0.38   | 0.38   |
| 2000           | 54.57          | 54.33  | 54.22  | 0.30              | 0.38   | 0.40   | 0.31               | 0.38   | 0.38   |
| 2050           | 51.41          | 51.63  | 52.00  | 0.31              | 0.39   | 0.40   | 0.32               | 0.39   | 0.39   |
| 2175           | 53.13          | 53.02  | 53.24  | 0.30              | 0.39   | 0.40   | 0.31               | 0.39   | 0.39   |
| 2225           | 53.66          | 53.27  | 52.73  | 0.30              | 0.39   | 0.40   | 0.31               | 0.39   | 0.40   |
| 2300           | 52.68          | 52.44  | 52.22  | 0.30              | 0.40   | 0.41   | 0.31               | 0.40   | 0.41   |
| 2350           | 51.66          | 51.56  | 51.15  | 0.30              | 0.41   | 0.41   | 0.32               | 0.41   | 0.42   |
| 2400           | 50.47          | 50.11  | 50.06  | 0.30              | 0.41   | 0.43   | 0.32               | 0.42   | 0.43   |
| 2450           | 49.93          | 49.52  | 48.68  | 0.31              | 0.42   | 0.44   | 0.33               | 0.44   | 0.46   |
| 2500           | 46.92          | 46.78  | 46.58  | 0.32              | 0.44   | 0.46   | 0.35               | 0.46   | 0.48   |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

REV. OR  
 CBP-1250C+  
 130409  
 Page 1 of 2

**Band Pass Filter****CBP-1250C+***Typical Performance Data*

| FREQ.<br><br>(MHz) | GROUP DELAY |        |        |
|--------------------|-------------|--------|--------|
|                    | (nsec)      |        |        |
|                    | @-40°C      | @+25°C | @+85°C |
| 1215               | 5.31        | 5.23   | 5.21   |
| 1216               | 5.28        | 5.20   | 5.18   |
| 1217               | 5.25        | 5.19   | 5.15   |
| 1218               | 5.24        | 5.18   | 5.15   |
| 1219               | 5.21        | 5.15   | 5.12   |
| 1220               | 5.18        | 5.12   | 5.09   |
| 1221               | 5.17        | 5.11   | 5.09   |
| 1222               | 5.13        | 5.07   | 5.06   |
| 1223               | 5.12        | 5.07   | 5.05   |
| 1224               | 5.10        | 5.05   | 5.03   |
| 1225               | 5.07        | 5.02   | 5.01   |
| 1226               | 5.07        | 5.01   | 4.99   |
| 1227               | 5.05        | 5.00   | 4.98   |
| 1228               | 5.03        | 4.98   | 4.96   |
| 1229               | 5.02        | 4.97   | 4.95   |
| 1230               | 5.00        | 4.96   | 4.94   |
| 1231               | 4.99        | 4.94   | 4.92   |
| 1232               | 4.98        | 4.93   | 4.92   |
| 1233               | 4.96        | 4.92   | 4.91   |
| 1234               | 4.94        | 4.90   | 4.88   |
| 1235               | 4.93        | 4.89   | 4.87   |
| 1236               | 4.92        | 4.88   | 4.87   |
| 1237               | 4.91        | 4.86   | 4.86   |
| 1239               | 4.88        | 4.85   | 4.84   |
| 1240               | 4.87        | 4.84   | 4.82   |
| 1241               | 4.86        | 4.83   | 4.82   |
| 1242               | 4.86        | 4.82   | 4.82   |
| 1243               | 4.84        | 4.81   | 4.81   |
| 1244               | 4.84        | 4.81   | 4.80   |
| 1245               | 4.83        | 4.80   | 4.79   |
| 1246               | 4.82        | 4.78   | 4.78   |
| 1247               | 4.81        | 4.78   | 4.78   |
| 1248               | 4.80        | 4.77   | 4.77   |
| 1250               | 4.78        | 4.76   | 4.75   |
| 1251               | 4.77        | 4.75   | 4.75   |
| 1255               | 4.76        | 4.75   | 4.74   |
| 1256               | 4.75        | 4.74   | 4.74   |
| 1257               | 4.75        | 4.75   | 4.75   |
| 1258               | 4.75        | 4.74   | 4.74   |
| 1260               | 4.75        | 4.74   | 4.74   |
| 1261               | 4.75        | 4.73   | 4.73   |
| 1262               | 4.75        | 4.75   | 4.74   |
| 1263               | 4.74        | 4.74   | 4.74   |
| 1265               | 4.74        | 4.74   | 4.74   |
| 1266               | 4.75        | 4.75   | 4.75   |
| 1269               | 4.75        | 4.75   | 4.76   |
| 1270               | 4.76        | 4.76   | 4.77   |
| 1272               | 4.75        | 4.76   | 4.78   |
| 1273               | 4.76        | 4.77   | 4.79   |
| 1274               | 4.76        | 4.77   | 4.79   |
| 1275               | 4.76        | 4.78   | 4.80   |
| 1276               | 4.77        | 4.78   | 4.80   |
| 1278               | 4.78        | 4.79   | 4.81   |
| 1279               | 4.79        | 4.81   | 4.83   |
| 1280               | 4.79        | 4.82   | 4.84   |
| 1281               | 4.81        | 4.84   | 4.86   |
| 1282               | 4.82        | 4.85   | 4.87   |
| 1283               | 4.82        | 4.86   | 4.88   |
| 1284               | 4.83        | 4.87   | 4.90   |
| 1285               | 4.85        | 4.89   | 4.92   |









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS


## Typical Performance Curves



# Band Pass Filter


# CBP-1250C+

## Typical Performance Curves




## Outline Dimensions

MP1766



## PCB Land Pattern



| CASE#  | A               | B               | C              | D              | E              | F              | G              | H              | J              | K              | L              | M              | N              |
|--------|-----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| MP1766 | .750<br>(19.05) | .750<br>(19.05) | .210<br>(5.33) | .139<br>(3.53) | .157<br>(3.99) | .215<br>(5.46) | .160<br>(4.06) | .218<br>(5.54) | .157<br>(3.99) | .100<br>(2.54) | .060<br>(1.52) | .069<br>(1.75) | .149<br>(3.78) |

| CASE#  | P               | Q               | R               | S               | T              | U              | V              | W              | X               | Y               | Z              | WT.GRAMS |
|--------|-----------------|-----------------|-----------------|-----------------|----------------|----------------|----------------|----------------|-----------------|-----------------|----------------|----------|
| MP1766 | .790<br>(20.07) | .541<br>(13.74) | .790<br>(20.07) | .499<br>(12.67) | .384<br>(9.75) | .203<br>(5.16) | .080<br>(2.03) | .069<br>(1.75) | .630<br>(16.00) | .630<br>(16.00) | .145<br>(3.68) | 4.6      |

Dimensions are in inches (mm). Tolerances: 2PL.  $\pm .03$ ; 3PL.  $\pm .015$

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F111



Applicable Case styles:

Applicable Case styles:RS1539

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel |
|----------------|-------------------------|-------------------|------------------|
| 32             | 24                      | 13                | 250              |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


| REV OR | ECN No. | DESCRIPTION | DATE   | DR  | AUTH |
|--------|---------|-------------|--------|-----|------|
|        | M137721 | NEW RELEASE | JUN 12 | DDR | KG   |
|        |         |             |        |     |      |
|        |         |             |        |     |      |

**SUGGESTED MOUNTING CONFIGURATION FOR  
MP1766 CASE STYLE "13FL01" PIN CODE**



**NOTES:**

- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

| UNLESS OTHERWISE SPECIFIED  | INITIALS |     | DATE      |
|---|----------|-----|-----------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .005"<br>ANGLES ±<br>FRACTIONS ± | DRAWN    | DDR | 22 JUN 12 |
|   | CHECKED  | MD  | 22 JUN 12 |
|   | APPROVED | GM  | 22 JUN 12 |


 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

**PL, 13FL01, MP1766, BPF,  
TB-684+, 50 Ohm**


 Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERE TO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

|                  |                     |                          |            |
|------------------|---------------------|--------------------------|------------|
| SIZE<br>A        | CODE IDENT<br>15542 | DRAWING NO:<br>98-PL-373 | REV:<br>OR |
| FILE:<br>98PL373 | SCALE:<br>4:1       | SHEET:<br>1 OF 1         |            |

# Evaluation Board and Circuit




TB-684+



Schematic Diagram

**Notes:**

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent  
Dielectric Constant=2.50±.04, Thickness=.022 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition   | Reference/Spec  |
|----------------------------|---|---|
| Operating Temperature      | -40° to 85°C<br>Ambient Environment                               | Individual Model Data Sheet                           |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                             | Individual Model Data Sheet                           |
| Humidity                   | 90 to 95% RH, 96 hours, 40°C                                      | MIL-STD-202, Method 103B, Condition B, Except 50°C    |
| Thermal Shock              | -55° to 100°C, 100 cycles   | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat         | Sn-Pb Eutectic Process: 225°C peak<br>Pb-Free Process, 245°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1         |
| Solderability              | 10X Magnification   | J-STD-002, Para 4.2.5, Test S, 95% Coverage           |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)    | MIL-STD-202, Method 204, Condition D                  |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A                  |