

# Surface Mount Bandpass Filter

## CBP-1490A+

50Ω 1465 to 1515 MHz

### The Big Deal

- High selectivity
- Good Return loss
- Miniature shielded package



Generic photo used for illustration purposes only  
CASE STYLE: KV1514

### Product Overview

CBP-1490A+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection and power handling for use in aeronautical, test and measurement applications.

### Key Features

Feature	Advantages
High Selectivity	The CBP-1490A+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over a passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1490A+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

## CBP-1490A+

50Ω 1465 to 1515 MHz



Generic photo used for illustration purposes only  
CASE STYLE: KV1514

### Features

- High selectivity
- Good return loss
- Miniature shielded package

### Applications

- Aeronautical
- Digital audio broadcasting
- Test and measurement

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1490	-	MHz
	Insertion Loss	F1-F2	1465-1515	3.0	4.5	dB
	VSWR	F1-F2	1465-1515	1.3	2.3	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1430	20.0	30.0	dB
	VSWR	DC-F3	DC-1430	2.0	2.0	:1
Stop Band, Upper	Insertion Loss	F4-F5	1550-3300	20.0	29.5	dB
	VSWR	F4-F5	1550-3300	-	20.0	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	4 W max.

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic







### Typical Frequency Response



### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	107.36	356.22	1465	23.75
50	93.32	405.86	1468	21.52
350	108.05	474.84	1470	20.51
750	89.67	298.94	1473	19.45
1100	77.42	168.32	1475	18.89
1430	33.06	24.76	1477	18.40
1433	30.54	22.25	1480	17.77
1443	20.72	13.12	1483	17.32
1460	3.42	1.16	1485	17.12
1465	2.76	1.30	1487	17.01
1490	2.06	1.22	1490	16.97
1515	2.73	1.36	1492	17.00
1518	3.20	1.51	1495	17.10
1540	20.69	15.42	1498	17.27
1550	29.34	26.88	1500	17.43
1551	30.12	28.00	1502	17.64
1555	33.12	32.77	1505	18.11
2000	64.03	100.47	1508	18.83
2800	50.60	56.83	1510	19.48
3300	49.31	32.57	1515	21.75

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



#### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Pad Connections


INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13,14,15,16

**Demo Board MCL P/N: TB-578+**  
**Suggested PCB Layout (PL-331)**



- NOTE: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .060"±.004"; COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
  - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## Outline Drawing



## Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L
.550	1.040	.225	.160	.120	.077	.070	.160	.590	1.080	.100
13.97	26.24	5.72	4.06	3.05	1.96	1.78	4.06	14.99	27.43	2.54
M	N	P	Q	R	S	T	U	V	Wt.	
.140	.230	.180	.195	.115	.780	.290	.110	.100	grams	
3.56	5.84	4.57	4.95	2.92	19.81	7.37	2.79	2.54	4.8	

Note: Please refer to case style drawing for details.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)









## Typical Performance Data

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	101.48	107.36	100.46	0.05	0.05	0.05	0.05	0.05	0.05
20	106.16	99.57	99.79	0.04	0.05	0.04	0.05	0.05	0.05
225	97.07	98.56	99.75	0.02	0.03	0.03	0.02	0.04	0.04
350	132.85	108.05	98.93	0.01	0.03	0.03	0.01	0.04	0.04
500	98.76	104.94	94.81	0.01	0.03	0.04	0.00	0.04	0.04
725	91.39	91.33	89.28	0.01	0.05	0.06	0.01	0.05	0.07
950	79.85	80.98	79.59	0.02	0.07	0.08	0.02	0.08	0.10
1100	76.86	77.42	77.38	0.03	0.09	0.11	0.04	0.10	0.13
1250	72.22	72.69	72.52	0.07	0.14	0.16	0.07	0.15	0.18
1382	57.86	58.14	58.37	0.20	0.29	0.34	0.19	0.29	0.34
1430	32.42	33.06	33.99	0.54	0.72	0.83	0.54	0.70	0.78
1433	29.84	30.54	31.57	0.61	0.80	0.92	0.61	0.78	0.86
1434	28.93	29.67	30.73	0.63	0.83	0.95	0.64	0.81	0.90
1442	20.77	21.82	23.25	1.01	1.25	1.37	1.04	1.23	1.30
1443	19.62	20.72	22.21	1.09	1.33	1.46	1.13	1.33	1.38
1445	17.20	18.43	20.05	1.32	1.56	1.66	1.37	1.55	1.58
1452	8.03	9.72	11.83	3.96	3.72	3.29	4.21	3.81	3.23
1458	3.17	4.15	5.58	15.96	13.13	9.18	20.29	14.29	9.42
1459	2.93	3.72	4.92	17.05	16.12	11.19	21.66	18.31	11.64
1460	2.77	3.42	4.39	16.38	18.85	13.64	18.93	22.63	14.47
1461	2.66	3.20	3.98	15.30	19.88	16.57	16.69	23.30	18.15
1463	2.51	2.93	3.44	14.06	18.32	22.97	14.72	19.07	28.27
1465	2.37	2.76	3.14	14.25	17.48	24.20	14.80	17.58	24.26
1471	1.98	2.38	2.68	21.78	24.27	28.53	26.31	23.91	22.48
1476	1.87	2.22	2.47	18.70	22.35	28.45	19.48	21.86	23.55
1479	1.88	2.18	2.41	15.84	18.88	23.20	15.89	18.29	21.32
1480	1.88	2.17	2.39	15.32	18.28	22.41	15.28	17.64	20.77
1481	1.88	2.17	2.37	14.98	17.90	21.93	14.86	17.20	20.36
1482	1.88	2.15	2.36	14.81	17.72	21.74	14.63	16.93	20.10
1490	1.77	2.06	2.27	18.79	23.37	31.08	18.11	19.97	21.52
1492	1.74	2.05	2.26	21.89	28.22	33.20	20.84	21.76	21.52
1496	1.71	2.05	2.27	30.42	28.37	23.31	26.97	22.55	19.71
1497	1.72	2.05	2.28	28.31	25.72	21.90	25.99	21.87	19.17
1502	1.81	2.13	2.35	19.09	19.32	18.36	18.58	18.31	17.41
1507	1.99	2.26	2.43	15.81	17.70	18.47	15.62	16.97	17.79
1508	2.03	2.29	2.45	15.39	17.61	18.83	15.30	16.91	18.09
1510	2.15	2.37	2.51	14.60	17.47	19.81	14.77	16.92	18.88
1514	2.50	2.63	2.69	12.63	16.39	21.88	13.41	16.67	20.59
1515	2.63	2.73	2.76	11.97	15.77	21.90	12.84	16.30	20.81
1517	3.00	3.01	2.95	10.47	14.08	20.46	11.33	14.90	20.28
1525	6.81	6.31	5.50	4.32	5.75	7.85	4.39	5.89	8.14
1529	10.29	9.73	8.69	2.62	3.38	4.32	2.53	3.35	4.41
1533	14.22	13.74	12.74	1.71	2.16	2.59	1.57	2.07	2.61
1538	19.12	18.76	17.94	1.12	1.41	1.62	0.98	1.31	1.60
1539	20.06	19.73	18.94	1.04	1.31	1.50	0.90	1.21	1.47
1550	29.49	29.34	28.84	0.55	0.72	0.81	0.45	0.65	0.77
1565	39.87	39.83	39.52	0.30	0.43	0.49	0.24	0.39	0.47
1600	58.34	58.42	58.25	0.13	0.23	0.27	0.11	0.22	0.27
1640	86.64	88.79	83.82	0.09	0.17	0.20	0.07	0.17	0.21
1696	71.33	71.89	70.47	0.07	0.14	0.17	0.07	0.15	0.19
1755	67.09	67.44	66.22	0.07	0.14	0.17	0.07	0.15	0.19
1850	68.62	68.96	67.53	0.08	0.15	0.18	0.08	0.16	0.19
1995	63.99	64.09	63.68	0.09	0.16	0.19	0.09	0.17	0.20
2185	62.66	62.79	62.44	0.11	0.19	0.22	0.12	0.19	0.23
2475	51.52	52.69	50.01	0.16	0.25	0.29	0.15	0.25	0.28
2645	51.26	51.53	49.03	0.17	0.28	0.33	0.15	0.26	0.31
2800	50.16	50.60	49.05	0.20	0.34	0.42	0.16	0.31	0.38
2905	53.17	55.32	50.98	0.23	0.40	0.50	0.20	0.37	0.44
3080	50.66	51.45	50.38	0.28	0.49	0.62	0.22	0.44	0.56
3300	48.99	49.31	49.57	0.30	0.54	0.67	0.28	0.53	0.68


*Typical Performance Data*

FREQ.	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1465	22.84	23.75	25.01
1466	22.09	22.91	24.20
1467	21.46	22.16	23.38
1468	20.96	21.52	22.63
1469	20.54	20.98	21.94
1470	20.19	20.51	21.33
1471	19.88	20.12	20.80
1472	19.59	19.77	20.34
1473	19.32	19.45	19.94
1474	19.05	19.17	19.58
1475	18.79	18.89	19.26
1476	18.53	18.65	18.98
1477	18.27	18.40	18.72
1478	18.04	18.18	18.48
1479	17.80	17.96	18.26
1480	17.59	17.77	18.06
1481	17.41	17.60	17.89
1482	17.25	17.44	17.72
1483	17.13	17.32	17.59
1484	17.03	17.21	17.47
1485	16.96	17.12	17.36
1486	16.91	17.05	17.27
1487	16.89	17.01	17.19
1488	16.89	16.98	17.14
1489	16.91	16.97	17.09
1490	16.95	16.97	17.06
1491	17.01	16.99	17.03
1492	17.06	17.00	17.01
1493	17.13	17.03	17.01
1494	17.19	17.06	17.00
1495	17.26	17.10	17.00
1496	17.34	17.15	17.02
1497	17.42	17.21	17.05
1498	17.50	17.27	17.09
1499	17.59	17.34	17.14
1500	17.69	17.43	17.21
1501	17.80	17.52	17.29
1502	17.92	17.64	17.38
1503	18.07	17.78	17.51
1504	18.23	17.94	17.64
1505	18.42	18.11	17.81
1506	18.65	18.33	18.00
1507	18.89	18.56	18.20
1508	19.17	18.83	18.44
1509	19.49	19.13	18.72
1510	19.85	19.48	19.03
1511	20.23	19.86	19.36
1512	20.67	20.28	19.75
1513	21.12	20.74	20.17
1514	21.60	21.23	20.64
1515	22.08	21.75	21.15


## Typical Performance Curves



## Typical Performance Curves



### Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
KV1514	.550 (13.97)	1.040 (26.24)	.225 (5.72)	.160 (4.06)	.120 (3.05)	.077 (1.96)	.070 (1.78)	.160 (4.06)	.590 (14.99)	1.080 (27.43)	.100 (2.54)	.140 (3.56)

CASE#	N	P	Q	R	S	T	U	V	WT, GRAMS
KV1514	.230 (5.84)	.180 (4.57)	.195 (4.95)	.115 (2.92)	.780 (19.81)	.290 (7.37)	.110 (2.79)	.100 (2.54)	4.8

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

#### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F106

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M126876	NEW RELEASE	04/21/10	MMG	RD

**SUGGESTED MOUNTING CONFIGURATION FOR  
KU1513/KV1514 CASE STYLE, "16FL02" PIN CODE**



- NOTE: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .060" ± .004"; COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN MMG	04/08/10
TOLERANCES ON:	CHECKED IL	04/21/10
2 PL DECIMALS ±	APPROVED RD	04/21/10
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		


**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

**PL, 16FL02, KU1513/KV1514, TB-578+**


Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-331	REV: OR
FILE: 98PL331	SCALE: 4:1	SHEET: 1 OF 1	

# Evaluation Board and Circuit




TB-578+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.060 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A