

Surface Mount Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω 1027 to 1033 MHz

CBP12-1030BE+





Generic photo used for illustration purposes only
CASE STYLE: UP2912

Features

- Excellent roll-off
- Excellent rejection
- Good passband IL
- Cavity filter standard specs in compact profile

Applications

- Traffic Alert and Collision Avoidance System (TCAS)
- Military IFF

Functional Schematic**Typical Frequency Response****+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications





Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	-	1030	-	MHz
	Insertion Loss	F1-F2	1027 - 1033	-	1.75	2.5	dB
	VSWR	F1-F2	1027 - 1033	-	1.5	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 950	70	80	-	dB
		F3-F4	950 - 1008	20	30	-	dB
Stop Band, Upper	Insertion Loss	F5-F6	1052 - 1100	20	30	-	dB
		F6-F7	1100 - 1800	60	67	-	dB
		F7-F8	1800 - 2000	-	40	-	dB

Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10 W max. at 25°C

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	107.75	169.12	1020	64.52
10	108.16	287.78	1021	69.93
100	100.39	386.63	1022	68.72
950	87.28	267.91	1023	63.53
1000	46.05	86.67	1024	58.11
1008	34.15	52.19	1025	54.11
1014	21.86	25.67	1026	51.41
1027	1.67	1.12	1027	49.55
1029	1.60	1.19	1028	48.28
1030	1.58	1.19	1029	47.52
1032	1.58	1.15	1030	47.28
1033	1.62	1.18	1031	47.56
1038	2.88	1.62	1032	48.25
1046	21.86	32.63	1033	49.27
1052	32.91	75.15	1034	50.86
1100	72.91	388.69	1035	53.46
1200	91.70	370.21	1036	57.79
1500	76.17	261.41	1037	63.65
1800	70.39	203.10	1038	68.65
2000	65.32	149.47	1039	68.45

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.


Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections


INPUT	1
OUTPUT	17
GROUND	2-16, 18-26

**Demo Board MCL P/N: TB-1137+
Suggested PCB Layout (PL-686)**

**NOTES:**

- COPLANAR WAVEGUIDE PARAMETER ARE SHOWN FOR ROGERS(R04350B), WITH DIELECTRIC THICKNESS .023"±.002". COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing**Outline Dimensions (inch mm)**

A	B	C	D	E	F	G	H	J	K	L
.800	2.100	.580	.095	1.910	.160	.210	.075	.115	.155	1.680
20.32	53.34	14.73	2.41	48.51	4.06	5.33	1.91	2.92	3.94	42.67
M	N	P	Q	R	S	T	U	V	Wt.	
1.755	1.870	1.950	2.140	.840	.650	.570	.555	1.783	grams	
44.58	47.50	49.53	54.36	21.34	16.51	14.48	14.10	45.29		40

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface mount Band Pass Filter

CBP12-1030BE+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
	1	102.38	99.84	99.42	0.10	0.10	0.10	0.10	0.10
10	98.47	103.65	99.76	0.06	0.06	0.06	0.06	0.06	0.06
100	102.17	96.64	94.74	0.04	0.04	0.05	0.04	0.05	0.05
150	97.36	101.78	115.20	0.03	0.04	0.04	0.03	0.04	0.04
200	98.05	103.57	98.03	0.02	0.03	0.04	0.02	0.03	0.04
220	98.26	97.74	94.95	0.02	0.03	0.03	0.02	0.03	0.04
250	105.61	102.22	100.22	0.01	0.03	0.04	0.02	0.03	0.04
300	99.99	94.27	104.74	0.01	0.02	0.03	0.01	0.03	0.03
320	99.41	96.81	103.17	0.01	0.02	0.03	0.01	0.03	0.03
350	106.15	99.89	116.69	0.01	0.02	0.03	0.01	0.02	0.03
400	111.62	98.68	103.31	0.00	0.02	0.03	0.01	0.02	0.03
420	95.65	95.65	113.96	0.00	0.02	0.03	0.01	0.02	0.03
600	99.08	97.99	95.38	0.01	0.02	0.03	0.01	0.02	0.03
700	89.38	88.16	94.18	0.01	0.02	0.04	0.00	0.03	0.04
800	86.28	94.55	91.70	0.00	0.03	0.05	0.00	0.03	0.05
950	76.68	78.06	74.63	0.02	0.06	0.08	0.02	0.06	0.08
990	59.10	58.83	55.55	0.09	0.13	0.16	0.09	0.13	0.17
1000	47.63	47.31	46.33	0.14	0.19	0.23	0.15	0.20	0.24
1008	35.26	34.89	34.42	0.26	0.33	0.37	0.28	0.35	0.40
1014	23.01	22.55	22.21	0.55	0.66	0.74	0.58	0.73	0.83
1018	12.10	11.69	11.38	1.50	1.79	2.01	1.65	2.03	2.32
1020	6.24	6.08	5.93	3.81	4.41	4.90	4.24	5.06	5.75
1021	3.98	4.03	4.02	6.64	7.40	8.08	7.56	8.73	9.81
1027	1.45	1.66	1.81	23.92	25.34	25.67	19.29	19.88	19.85
1028	1.41	1.62	1.77	22.23	22.58	22.31	19.25	19.68	19.53
1029	1.38	1.60	1.74	20.16	20.51	20.34	19.05	19.58	19.46
1030	1.37	1.58	1.73	19.12	19.77	19.78	19.37	20.28	20.34
1031	1.36	1.57	1.72	19.13	20.09	20.29	20.75	22.42	22.87
1032	1.36	1.57	1.72	19.89	20.99	21.27	23.64	27.09	28.78
1033	1.37	1.59	1.75	20.81	21.51	21.61	27.65	32.71	35.28
1038	2.36	2.71	2.98	12.67	12.86	12.77	11.31	11.09	10.81
1039	3.56	3.98	4.30	7.30	7.39	7.36	6.77	6.68	6.55
1040	5.52	6.00	6.37	4.16	4.27	4.30	3.91	3.92	3.88
1043	13.55	14.01	14.37	1.02	1.15	1.21	0.98	1.07	1.12
1046	20.96	21.33	21.64	0.43	0.53	0.58	0.42	0.50	0.54
1050	28.89	29.18	29.44	0.20	0.28	0.32	0.20	0.27	0.30
1052	32.23	32.49	32.73	0.15	0.22	0.26	0.15	0.21	0.25
1100	71.35	71.60	70.29	0.01	0.03	0.06	0.00	0.04	0.06
1120	86.32	84.58	76.02	0.01	0.03	0.06	0.01	0.03	0.05
1140	77.75	79.94	87.20	0.02	0.03	0.05	0.01	0.04	0.06
1160	81.03	83.56	83.61	0.02	0.02	0.05	0.01	0.03	0.05
1180	78.98	79.85	84.70	0.02	0.03	0.05	0.01	0.03	0.05
1200	81.10	80.84	74.80	0.01	0.04	0.06	0.01	0.04	0.06
1240	78.78	78.77	73.29	0.01	0.03	0.06	0.00	0.04	0.06
1260	77.39	76.95	73.20	0.01	0.04	0.06	0.00	0.04	0.06
1280	76.05	77.99	73.47	0.01	0.03	0.06	0.01	0.04	0.06
1300	75.43	78.14	74.44	0.01	0.03	0.06	0.00	0.04	0.06
1320	75.16	77.91	76.16	0.01	0.03	0.06	0.00	0.04	0.06
1340	75.41	78.51	76.34	0.00	0.04	0.07	0.00	0.04	0.07
1360	75.14	77.99	77.66	0.00	0.04	0.07	0.01	0.05	0.07
1380	74.27	74.87	78.10	0.01	0.04	0.07	0.00	0.05	0.07
1400	74.89	74.83	77.24	0.00	0.04	0.07	0.00	0.05	0.07
1500	69.41	70.31	71.76	0.01	0.05	0.08	0.00	0.05	0.07
1550	66.84	67.47	65.07	0.01	0.06	0.09	0.01	0.05	0.08
1600	63.34	63.86	65.81	0.00	0.04	0.07	0.01	0.06	0.08
1650	66.42	66.17	71.98	0.01	0.06	0.09	0.02	0.06	0.09
1800	58.20	58.17	67.65	0.01	0.06	0.10	0.03	0.08	0.10
1900	62.67	65.55	62.60	0.01	0.06	0.09	0.03	0.08	0.10
1950	65.07	66.83	66.46	0.02	0.07	0.11	0.03	0.08	0.11
2000	62.95	64.91	62.52	0.02	0.08	0.11	0.03	0.09	0.13



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



Surface mount Band Pass Filter CBP12-1030BE+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1022.0	72.62	70.43	69.25
1022.3	71.69	69.39	68.10
1022.5	70.42	68.12	66.80
1022.8	68.88	66.66	65.35
1023.0	67.23	65.11	63.85
1023.3	65.50	63.54	62.33
1023.5	63.75	61.97	60.85
1023.8	62.05	60.45	59.43
1024.0	60.47	59.06	58.15
1024.3	58.98	57.75	56.94
1024.5	57.65	56.60	55.88
1024.8	56.44	55.51	54.88
1025.0	55.37	54.55	54.00
1025.3	54.42	53.69	53.20
1025.5	53.59	52.93	52.51
1025.8	52.83	52.24	51.88
1026.0	52.19	51.64	51.32
1026.3	51.59	51.08	50.78
1026.5	51.05	50.57	50.30
1026.8	50.58	50.11	49.87
1027.0	50.15	49.72	49.48
1027.3	49.77	49.35	49.12
1027.5	49.40	49.00	48.79
1027.8	49.05	48.70	48.48
1028.0	48.76	48.41	48.20
1028.3	48.47	48.14	47.95
1028.5	48.23	47.90	47.73
1028.8	48.02	47.75	47.57
1029.0	47.83	47.57	47.40
1029.3	47.69	47.43	47.31
1029.5	47.53	47.31	47.21
1029.8	47.45	47.24	47.14
1030.0	47.38	47.20	47.13
1030.3	47.35	47.19	47.13
1030.5	47.35	47.22	47.20
1030.8	47.37	47.28	47.24
1031.0	47.42	47.34	47.34
1031.3	47.53	47.46	47.48
1031.5	47.67	47.61	47.61
1031.8	47.82	47.79	47.83
1032.0	48.02	47.98	48.03
1032.3	48.22	48.18	48.24
1032.5	48.45	48.44	48.50
1032.8	48.73	48.73	48.78
1033.0	49.06	49.04	49.11
1033.3	49.40	49.38	49.47
1033.5	49.78	49.76	49.84
1033.8	50.20	50.18	50.28
1034.0	50.66	50.63	50.74
1034.3	51.19	51.19	51.30
1034.5	51.78	51.79	51.91



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS








REV. OR
CBP12-1030BE+
200914
Page 2 of 2

Surface mount Band Pass Filter

CBP12-1030BE+

Typical Performance Curves





Case Style



UP

Outline Dimensions

UP2912



SUGGESTED PCB LAND PATTERN



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
UP2912	.800 (20.32)	2.100 (53.34)	.580 (14.73)	.095 (2.41)	1.910 (48.51)	.160 (4.06)	.210 (5.33)	.075 (1.91)	.115 (2.92)	.155 (3.94)	1.680 (42.67)	1.755 (44.58)	1.870 (47.50)

CASE#	P	Q	R	S	T	U	V	WT.GRAM
UP2912	1.950 (49.53)	2.140 (54.36)	.840 (21.34)	.650 (16.51)	.570 (14.48)	.555 (14.10)	1.783 (45.29)	40

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13microns) Gold over 120-240 μ inch (3.05-6.10microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


RF/MICROWAVE COMPONENTS

THIRD ANGLE PROJECTION



REVIEWS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	NPO-000681	NEW RELEASE	JUL 20	AP	VC

SUGGESTED MOUNTING CONFIGURATION
FOR UP2912 CASE STYLE



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS(R04350B), WITH DIELECTRIC THICKNESS $.023\pm.002$ ". COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	AP	25 JUL 20
TOLERANCES ON: 2 PL DECIMALS \pm .005" 3 PL DECIMALS \pm .005" ANGLES \pm FRACTIONS \pm	CHECKED	MD	25 JUL 20
	APPROVED	KN	25 JUL 20



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, UP2912, TB-1137+, 50 Ohm

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-686	OR
FILE:	98PL686	SCALE: 3:1	SHEET: 1 OF 1



Environmental Specifications ENV115

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
---------------	---------------------------	----------------

Operating Temperature
-40° to 85° C
Ambient Environment
Individual Model Data Sheet

Storage Temperature
-55° to 100° C
Ambient Environment
Individual Model Data Sheet

Thermal Shock
-55° to 100°C, 100 cycles
MIL-STD-202, Method 107, Condition A-3, except
+100°C

Solder Reflow Heat
Sn-Pb Eutectic Process: 225°C peak
Pb-Free Process: 245°C peak
J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1

Solderability
10X Magnification
J-STD-002, Para 4.2.5, Test S, 95% Coverage