

## Surface Mount

# Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω DC to 6 GHz

## The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



## Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA in greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

50Ω 2000 to 2500 MHz

## CBP-2250A+



Generic photo used for illustration purposes only  
CASE STYLE: KU1513

### Features

- Low insertion loss
- Better rejection
- Miniature shielded package

### Applications

- Amateur radio
- Space operation
- ISM

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	2250	-	MHz
	Insertion Loss	F1-F2	2000-2500	1.1	2.0	dB
	VSWR	F1-F2	2000-2500	1.6	2.1	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1630	20.0	31.0	dB
	VSWR	DC-F3	DC-1630	20.0	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	2900-6000	20.0	31.0	dB
	VSWR	F4-F5	2900-6000	20.0	-	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	2 W Max.

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	109.86	408.42	2000	2.21
750	84.77	238.23	2025	2.12
1630	33.42	51.25	2050	2.04
1695	20.93	31.81	2075	1.96
1740	10.73	13.36	2100	1.90
1775	3.84	3.71	2125	1.85
2000	0.76	1.14	2150	1.80
2200	0.76	1.39	2175	1.77
2250	0.71	1.31	2200	1.75
2300	0.69	1.25	2225	1.74
2500	0.85	1.37	2250	1.72
2630	3.26	3.76	2275	1.72
2700	10.31	18.35	2300	1.72
2800	20.37	59.73	2325	1.72
2900	28.51	87.45	2350	1.73
2930	30.67	91.69	2375	1.75
3500	62.12	78.51	2400	1.76
4000	69.58	51.50	2425	1.79
5450	32.34	56.51	2450	1.82
6000	46.17	51.46	2500	1.94

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13,14,15,16


**Demo Board MCL P/N: TB-578+**  
**Suggested PCB Layout (PL-331)**



- NOTE: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS  $.060" \pm .004"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## Outline Drawing



## Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L
.550	1.040	.185	.160	.120	.077	.070	.160	.590	1.080	.100
13.97	26.24	4.70	4.06	3.05	1.96	1.78	4.06	14.99	27.43	2.54
M	N	P	Q	R	S	T	U	V	Wt.	
.140	.230	.180	.195	.115	.780	.290	.110	.100	grams	
3.56	5.84	4.57	4.95	2.92	19.81	7.36	2.79	2.54	2.6	

Note: Please refer to case style drawing for details.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






Typical Performance Data

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	99.57	97.70	101.54	0.04	0.05	0.04	0.05	0.05	0.05
5	101.12	104.99	97.82	0.05	0.05	0.04	0.04	0.05	0.05
25	101.66	97.85	103.80	0.04	0.04	0.04	0.04	0.04	0.04
50	107.84	102.32	96.35	0.03	0.04	0.03	0.03	0.03	0.03
100	98.36	95.03	103.08	0.02	0.02	0.02	0.02	0.03	0.02
250	105.37	97.05	114.98	0.00	0.01	0.01	0.01	0.03	0.03
500	90.60	91.55	91.31	0.01	0.02	0.02	0.08	0.12	0.12
750	85.29	83.94	82.18	0.01	0.05	0.05	0.18	0.24	0.25
1000	74.86	75.93	74.38	0.04	0.09	0.09	0.22	0.30	0.31
1250	71.68	71.69	71.42	0.09	0.14	0.15	0.16	0.24	0.27
1500	53.22	53.14	53.06	0.16	0.23	0.24	0.13	0.23	0.26
1550	46.62	46.41	46.48	0.19	0.26	0.28	0.16	0.26	0.29
1600	38.56	38.45	38.29	0.21	0.29	0.31	0.21	0.32	0.36
1630	33.55	33.42	33.22	0.24	0.33	0.35	0.27	0.39	0.43
1650	29.97	29.82	29.62	0.27	0.36	0.39	0.32	0.45	0.49
1700	20.00	19.83	19.57	0.43	0.55	0.60	0.63	0.78	0.85
1725	14.38	14.21	13.94	0.68	0.83	0.92	1.05	1.25	1.36
1750	8.54	8.42	8.17	1.51	1.75	1.94	2.25	2.57	2.82
1780	3.17	3.21	3.16	5.18	5.65	6.05	7.01	7.70	8.32
1800	1.74	1.86	1.91	9.18	9.69	10.01	11.61	12.42	12.87
2000	0.59	0.73	0.79	22.38	23.48	23.45	20.74	21.34	20.99
2250	0.55	0.69	0.75	17.34	17.21	17.57	18.75	18.81	19.48
2500	0.66	0.83	0.89	16.08	16.06	16.35	15.98	15.99	16.28
2600	1.31	1.58	1.75	10.07	9.81	9.45	10.36	10.09	9.75
2635	3.24	3.63	3.89	4.19	4.11	3.97	4.60	4.57	4.45
2750	15.25	15.63	15.88	0.34	0.44	0.46	0.57	0.72	0.77
2800	20.05	20.37	20.59	0.19	0.29	0.31	0.37	0.52	0.57
2850	24.34	24.63	24.83	0.13	0.23	0.25	0.26	0.41	0.47
2900	28.18	28.42	28.63	0.09	0.20	0.22	0.20	0.35	0.40
2950	31.95	32.20	32.38	0.07	0.18	0.20	0.18	0.32	0.37
3000	35.01	35.16	35.44	0.06	0.17	0.19	0.14	0.28	0.32
3200	45.96	46.20	46.02	0.03	0.15	0.18	0.06	0.20	0.25
3250	49.28	49.37	49.05	0.03	0.14	0.18	0.06	0.19	0.23
3300	49.38	49.40	49.44	0.02	0.14	0.18	0.04	0.18	0.22
3350	48.95	50.28	51.27	0.06	0.20	0.23	0.04	0.18	0.22
3400	60.75	59.64	60.77	0.01	0.13	0.17	0.03	0.17	0.21
3450	61.68	62.05	63.37	0.00	0.13	0.18	0.02	0.16	0.20
3500	64.70	63.21	63.70	0.00	0.13	0.19	0.02	0.15	0.19
3600	60.64	60.57	61.39	0.00	0.14	0.18	0.01	0.15	0.18
3650	62.81	62.45	64.36	0.01	0.14	0.19	0.00	0.14	0.17
3750	65.08	75.98	65.08	0.05	0.16	0.26	0.00	0.13	0.15
3800	72.35	74.07	74.96	0.02	0.17	0.23	0.00	0.13	0.16
3900	84.68	85.68	93.51	0.03	0.19	0.25	0.01	0.12	0.14
4000	71.02	70.48	70.18	0.09	0.24	0.32	0.01	0.12	0.14
4100	47.29	48.20	46.91	0.70	1.02	1.18	0.01	0.12	0.13
4200	41.69	41.99	42.37	0.80	0.95	0.98	0.02	0.10	0.12
4300	40.05	40.03	39.85	0.69	0.92	1.08	0.02	0.11	0.13
4400	31.59	32.00	32.31	9.86	10.83	10.38	0.04	0.10	0.11
4500	38.54	38.76	39.06	0.84	1.00	1.06	0.04	0.09	0.11
4600	42.38	42.06	43.16	0.32	0.51	0.57	0.05	0.09	0.10
4700	41.66	42.16	42.32	0.25	0.40	0.51	0.05	0.08	0.10
4800	41.38	41.27	42.45	0.17	0.34	0.40	0.05	0.09	0.11
4900	41.70	41.49	41.03	0.20	0.35	0.41	0.03	0.10	0.12
5000	42.91	44.65	43.19	0.13	0.30	0.35	0.06	0.09	0.15
5100	40.28	39.63	40.75	0.16	0.32	0.34	0.04	0.12	0.16
5200	43.55	40.26	43.47	0.15	0.32	0.33	0.02	0.21	0.18
5500	37.41	38.90	39.61	0.11	0.26	0.30	0.13	0.25	0.27
5750	51.87	50.66	53.99	0.10	0.27	0.32	0.08	0.09	0.13
5800	52.26	55.40	55.91	0.09	0.26	0.30	0.08	0.11	0.15
6000	46.95	45.86	45.65	0.08	0.28	0.34	0.08	0.25	0.31


Typical Performance Data

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
2000	2.22	2.21	2.19
2010	2.18	2.17	2.16
2020	2.15	2.14	2.13
2030	2.12	2.11	2.09
2040	2.08	2.07	2.06
2050	2.05	2.04	2.02
2060	2.02	2.01	2.00
2070	1.99	1.98	1.97
2080	1.96	1.95	1.94
2090	1.94	1.92	1.91
2100	1.91	1.90	1.88
2110	1.89	1.88	1.86
2120	1.87	1.86	1.85
2130	1.85	1.84	1.83
2140	1.83	1.82	1.81
2150	1.82	1.80	1.79
2160	1.80	1.79	1.78
2170	1.79	1.77	1.77
2180	1.78	1.77	1.76
2190	1.77	1.76	1.75
2200	1.76	1.75	1.74
2210	1.76	1.75	1.74
2220	1.75	1.74	1.73
2230	1.75	1.73	1.73
2240	1.74	1.73	1.72
2250	1.73	1.72	1.72
2260	1.73	1.72	1.71
2270	1.73	1.72	1.71
2280	1.73	1.72	1.71
2290	1.72	1.71	1.71
2300	1.72	1.72	1.71
2310	1.72	1.72	1.71
2320	1.72	1.72	1.71
2330	1.73	1.72	1.71
2340	1.73	1.72	1.72
2350	1.74	1.73	1.72
2360	1.74	1.73	1.73
2370	1.75	1.74	1.73
2380	1.76	1.75	1.74
2390	1.77	1.76	1.75
2400	1.78	1.76	1.76
2410	1.79	1.78	1.77
2420	1.80	1.78	1.78
2430	1.81	1.80	1.79
2440	1.82	1.81	1.80
2450	1.83	1.82	1.82
2460	1.85	1.84	1.83
2470	1.86	1.86	1.85
2480	1.89	1.88	1.88
2490	1.91	1.91	1.91
2500	1.95	1.94	1.95

## Typical Performance Curves



### Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
KU1513	.550 (13.97)	1.040 (26.24)	.185 (4.70)	.160 (4.06)	.120 (3.05)	.077 (1.96)	.070 (1.78)	.160 (4.06)	.590 (14.99)	1.080 (27.43)	.100 (2.54)	.140 (3.56)

CASE#	N	P	Q	R	S	T	U	V	WT, GRAMS
KU1513	.230 (5.84)	.180 (4.57)	.195 (4.95)	.115 (2.92)	.780 (19.81)	.290 (7.36)	.110 (2.79)	.100 (2.54)	2.6

Dimensions are in inches (mm). Tolerances: 2PL.  $\pm .03$ ; 3PL.  $\pm .015$

#### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.

**Mini-Circuits**<sup>®</sup>

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F106

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified






REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M126876	NEW RELEASE	04/21/10	MMG	RD

**SUGGESTED MOUNTING CONFIGURATION FOR  
KU1513/KV1514 CASE STYLE, "16FL02" PIN CODE**



- NOTE: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .060"  $\pm$  .004"; COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN MMG	04/08/10
TOLERANCES ON:	CHECKED IL	04/21/10
2 PL DECIMALS $\pm$	APPROVED RD	04/21/10
3 PL DECIMALS $\pm$ .005		
ANGLES $\pm$		
FRACTIONS $\pm$		



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235


PL, 16FL02, KU1513/KV1514, TB-578+

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-331	OR
FILE:	98PL331	SCALE: 4:1	SHEET: 1 OF 1

# Evaluation Board and Circuit




TB-578+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.060 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A