

Surface Mount

# Diplexer

## DPLB-8510A04+

75Ω 5 to 1220 MHz  
(5-85, 102-1220 MHz)



CASE STYLE: NU1620

### The Big Deal

- Very Low insertion loss, 0.9dB typ.
- High rejection
- Very good return loss, 24dB typ.
- 75Ω Impedance
- Used for DOCSIS 3.1 standard

### Product Overview

DPLB-8510A04+ is a Low cost diplexer with the lowpass port at 5-85 MHz and highpass port at 102-1220 MHz. Good return loss combined with high out of channel rejection makes it an ideal part in cable TV and multiband radio systems.

### Key Features

Feature	Advantages
Low passband insertion loss	Passband insertion loss of 0.9dB typical ensures low signal loss through both the channels.
Good Stopband rejection	Co-channel rejection of 48dB typical ensures unwanted spurious are eliminated.
Excellent return loss at 5-85 and 102-1220 MHz	This makes signal transmission with very less reflection and well-matched with the adjacent component used in the system.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Diplexer

# DPLB-8510A04+

75Ω 5 to 1220 MHz (5-85, 102-1220 MHz)

## Maximum Ratings

Operating Temperature -40° to 85°C

Storage Temperature -55°C to 100°C


RF Power Input 30dBm Max.

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

## Pin Connections

HIGH PASS PORT	7
LOW PASS PORT	9
COMMON PORT	18
GROUND	1-6,8,10-17,19,20

## Outline Drawing




## Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
-	-	Max	Min	-	-	-	-	-	-
1.181	1.181	.280	.205	.197	.394	.591	.787	.984	.066
30.00	30.00	7.11	5.21	5.00	10.00	15.00	20.00	25.00	1.68
L	M	N	P	Q	R	S	T		Wt.
.111	.079	.071	1.221	1.221	.079	.091	.280		grams
2.82	2.01	1.80	31.01	31.01	2.01	2.31	7.11		3.6

## Demo Board MCL P/N: TB-786+ Suggested PCB Layout (PL-435)

SUGGESTED MOUNTING CONFIGURATION FOR NU1620,  
NV1998, NZ2001, PA2002 CASE STYLE "20DP01" PIN CODE



### NOTES:

- TRACE WIDTH IS SHOWN FOR OAK-502 WITH DIELECTRIC THICKNESS .031±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

## Features

- Low insertion loss
- 75Ω Impedance
- Good return loss
- High rejection

## Applications

- Cable TV systems (DOCSIS 3.1 standard)
- Multiband radio systems



**CAUTION NOTE:** Open units are not recommended for use with Aqueous wash systems. Please evaluate your wash process before use.



CASE STYLE: NU1620

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Electrical Specifications at 25°C







Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	Low Pass	5-85	-	0.7	1.0	dB
		High Pass	102-1220	-	1.0	1.3	
	Return Loss	Low Pass	5-85	20	24	-	dB
		High Pass	102-1220	20	24	-	
Common		5-85 102-1220	20	24	-		
Stop Band Isolation	Low Pass	102-1220	41	48	-	dB	
	High Pass	5-85	41	48	-		
Cross over Isolation	LP-HP	85-102	-	9	-	dB	
Group Delay Variation	Low Pass	83-84	-	2.3	-	ns	
		84-85	-	2.8	-		
	High Pass	102-107 109-113	-	13	-		

## Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
1.0	0.05	76.90	50.71	50.56	0.02
5.0	0.07	63.29	41.83	42.55	0.02
83.0	0.65	54.34	29.87	32.74	1.23
84.0	0.69	50.99	31.37	37.87	1.42
85.0	0.74	47.69	34.10	48.55	1.68
88.0	1.01	29.66	25.22	21.64	3.66
89.4	1.30	20.31	19.14	16.20	4.89
90.0	1.50	17.15	17.07	14.07	4.80
92.0	2.69	10.19	11.81	8.22	3.79
93.0	3.60	8.15	10.03	6.29	3.98
97.4	13.03	3.36	13.75	2.11	15.65
98.4	20.94	1.89	22.03	1.07	32.20
99.6	30.27	1.39	28.93	0.73	31.26
100.0	33.50	1.30	29.99	0.68	29.55
102.0	57.10	1.02	34.17	0.54	29.04
107.0	48.16	0.73	33.87	0.42	41.25
109.0	50.10	0.67	31.07	0.40	47.63
113.0	54.90	0.58	28.85	0.37	40.25
500.0	49.90	0.25	30.76	0.01	28.52
750.0	50.33	0.29	33.25	0.04	37.98
950.0	49.81	0.34	39.31	0.13	33.33
1220.0	49.51	0.45	27.92	0.30	25.85

## Functional Schematic





Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data



FREQUENCY (MHz)	INSERTION LOSS (dB)		Cross over isolation (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Lowpass port	Highpass port		Common port	Lowpass port	Highpass port
1.0	0.05	76.90	77.49	50.71	50.56	0.02
3.0	0.07	68.03	67.30	45.01	45.40	0.02
5.0	0.07	63.29	63.56	41.83	42.55	0.02
6.0	0.08	61.71	61.97	40.72	41.61	0.02
7.0	0.08	60.31	61.25	39.85	40.98	0.02
8.0	0.08	59.45	59.66	39.01	40.05	0.02
10.0	0.09	57.64	58.30	37.39	38.98	0.02
12.0	0.09	56.61	56.41	36.07	38.07	0.02
15.0	0.10	54.89	55.48	34.56	36.92	0.02
20.0	0.11	53.57	53.88	32.56	35.34	0.03
25.0	0.12	53.25	53.72	31.14	34.00	0.04
30.0	0.13	54.06	54.35	30.13	32.91	0.06
80.0	0.55	51.08	50.77	29.09	28.19	0.90
82.0	0.61	54.85	53.07	29.18	30.32	1.09
83.0	0.65	54.34	52.81	29.87	32.74	1.23
84.0	0.69	50.99	51.94	31.37	37.87	1.42
85.0	0.74	47.69	52.09	34.10	48.55	1.68
87.0	0.89	37.06	41.34	31.13	26.39	2.71
88.0	1.01	29.66	32.17	25.22	21.64	3.66
89.0	1.19	22.73	25.09	20.67	17.68	4.68
89.0	1.19	22.73	25.09	20.67	17.68	4.68
90.0	1.50	17.15	20.02	17.07	14.07	4.80
91.0	1.98	13.10	16.77	14.15	10.84	4.13
92.0	2.69	10.19	14.72	11.81	8.22	3.79
93.0	3.60	8.15	13.33	10.03	6.29	3.98
94.0	4.61	6.96	12.22	8.71	5.12	4.49
95.0	5.42	6.95	11.10	7.67	4.88	5.07
96.0	6.23	8.53	10.25	7.27	5.49	6.18
97.0	10.16	4.81	12.85	10.81	3.11	11.55
98.0	17.77	2.26	19.47	18.74	1.32	23.84
99.0	25.62	1.58	26.55	26.23	0.85	39.86
100.0	33.50	1.30	33.58	29.99	0.68	29.55
101.0	42.83	1.14	40.80	31.87	0.59	28.45
102.0	57.10	1.02	47.19	34.17	0.54	29.04
103.0	51.22	0.94	48.66	37.33	0.50	30.44
104.0	48.13	0.87	47.90	39.91	0.47	32.32
105.0	47.39	0.82	47.78	38.70	0.45	34.75
106.0	47.63	0.77	48.03	36.06	0.43	37.68
107.0	48.16	0.73	48.61	33.87	0.42	41.25
108.0	49.32	0.70	49.46	32.21	0.41	45.39
109.0	50.10	0.67	50.34	31.07	0.40	47.63
110.0	51.24	0.64	51.35	30.18	0.39	45.95
113.0	54.90	0.58	54.00	28.85	0.37	40.25
120.0	56.34	0.48	55.79	29.00	0.34	37.65
150.0	52.86	0.31	52.82	41.67	0.26	41.03
250.0	53.83	0.23	54.54	34.47	0.12	34.30
300.0	51.42	0.23	51.70	32.49	0.08	30.46
400.0	50.20	0.23	50.43	31.00	0.03	28.20
500.0	49.90	0.25	49.83	30.76	0.01	28.52
600.0	49.50	0.26	49.55	31.12	0.00	30.36
700.0	45.29	0.29	48.45	32.50	0.08	34.51
800.0	50.14	0.30	50.08	35.06	0.05	43.20
900.0	49.70	0.32	49.18	39.36	0.10	37.05
1000.0	50.37	0.35	49.57	36.79	0.16	30.61
1050.0	49.88	0.37	49.13	33.53	0.19	28.64
1100.0	49.80	0.39	49.01	31.24	0.22	27.35
1150.0	49.51	0.41	48.49	29.52	0.25	26.44
1180.0	50.17	0.43	48.83	28.69	0.27	26.36
1200.0	49.81	0.45	47.54	28.10	0.29	25.96
1220.0	49.51	0.45	47.91	27.92	0.30	25.85

## Typical Performance Curves



## Outline Dimensions

NU1620



CASE#	A	B	C		D	E	F	G	H	J	K	L	M
			Max	Min									
NU1620	1.181 (30.00)	1.181 (30.00)	.280 (7.11)	.205 (5.21)	.197 (5.00)	.394 (10.00)	.591 (15.00)	.787 (20.00)	.984 (25.00)	.066 (1.68)	.089 (2.26)	.111 (2.82)	.079 (2.01)

CASE#	N	P	Q	R	S	T	WT.GRAMS
NU1620	.071 (1.80)	1.221 (31.01)	1.221 (31.01)	.079 (2.01)	.091 (2.31)	.280 (7.11)	3.6

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

1. Base: Printed wiring laminate.
2. Termination finish:
  - For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F80



<b>Tape Width, mm</b>	<b>Device Cavity Pitch, mm</b>	<b>Reel Size, inches</b>	<b>Devices per Reel</b>
44	40	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M147697	NEW RELEASE	SEP 14	DDR	MD

SUGGESTED MOUNTING CONFIGURATION FOR NU1620, NV1998, NZ2001, PA2002 CASE STYLE "20DP01" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR OAK-602 WITH DIELECTRIC THICKNESS .031"±.002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DDR	09 SEP 14
TOLERANCES ON:	CHECKED MD	09 SEP 14
2 PL DECIMALS ±	APPROVED KR	09 SEP 14
3 PL DECIMALS ± .005"		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235



PL, 20DP01, NU1620, NV1998, NZ2001, PA2002, TB-786+, 75 OHM

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-435	REV: OR
FILE: 98PL435	SCALE: 3:1	SHEET: 1 OF 1	

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




# Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 75 Ohm N Female connectors.
2. PCB Material: OAK-602 OR Equivalent  
Dielectric Constant=2.50±.04, Thickness=.031 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215