

Plug-in

Diplexer

DPLC-6585A0+

75Ω 5 to 1220 MHz
(5-65, 85-1220 MHz)



Generic photo used for illustration purposes only
CASE STYLE: QB2223

The Big Deal

- Plug-in design
- Field replaceable
- Low insertion loss
- Excellent return loss, 24 dB typ.
- High cross over isolation
- Low group delay variation in passband
- Mirrored version available for ease of routing
- DOCSIS 3.1 standard

Product Overview

DPLC-6585A0+ is a high performance field replaceable plug-in diplexer with the lowpass port at 5-65 MHz and highpass port at 85-1220 MHz. Excellent return loss combined with high out of channel rejection makes it an ideal part in cable TV and multiband radio systems

Key Features

Feature	Advantages
Low passband insertion loss	Ensures low signal loss through both the channels.
Excellent Stopband rejection	Co-channel rejection of 50dB typical ensures unwanted spurious are eliminated.
Excellent return loss at 5-65 and 85-1220 MHz	This makes signal transmission with very less reflection and well-matched with the adjacent component used in the system.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Plug-in Diplexer

DPLC-6585A0+

75Ω 5 to 1220 MHz (5-65, 85-1220 MHz)

Maximum Ratings


Operating Temperature	-40° to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	30 dBm Max.

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

Pin Connections

HIGH PASS PORT	7
LOW PASS PORT	1
COMMON PORT	4
GROUND	2,3,5,6,8,9

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
1.243	1.117	.630	.475	.375	.255	.040	--	.132	.546
31.56	28.36	16.00	12.07	9.53	6.48	1.02	--	3.35	13.87
L	M	N	P	Q	R	S	T	Wt.	
.684	.831	1.111	.143	.559	.974	.417	.415	grams	7
17.37	21.10	28.22	3.63	14.21	24.74	10.58	10.53		

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-897+
Suggested PCB Layout (PL-485)

SUGGESTED MOUNTING CONFIGURATION FOR QB2223 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR IT180, WITH DIELECTRIC THICKNESS .059"±.005", COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features


- Low insertion loss
- 75Ω Impedance
- Excellent return loss 24 dB typ.
- Low group delay variation
- High cross over isolation
- High rejection

Applications

- Cable TV systems (DOCSIS 3.1 standard)
- Multiband radio systems



CAUTION NOTE: Not designed for reflow process.



Generic photo used for illustration purposes only
CASE STYLE: QB2223

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C







Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	Low Pass	5-65	-	1.0	1.5	dB
		High Pass	85-1220	-	1.0	1.5	
	Return Loss	Low Pass	5-65	20	24	-	dB
		High Pass	85-1220	20	24	-	
		Common	5-65	20	24	-	
			85-1220	20	24	-	
Stop Band Isolation	Low Pass	85-1220	43	50	-	dB	
	High Pass	5-65	50	55	-		
	Cross over	65-85	35	40	-		
Group Delay Variation	Low Pass	62-63.5	-	7	10	ns	
		63.5-65	-	10	13		
	High Pass	112-116	-	1	2		
		120-124	-	1	1.5		

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
5.0	0.07	79.31	45.56	50.67	0.04
10.0	0.09	72.60	39.84	62.37	0.03
35.0	0.19	61.34	29.64	29.35	0.11
62.0	0.89	63.24	32.21	26.57	0.43
63.5	1.04	62.55	38.21	28.10	0.46
65.0	1.25	73.25	35.44	30.13	0.50
68.0	2.51	47.09	13.81	11.93	0.58
69.0	3.86	40.41	9.14	7.48	0.61
70.5	7.91	29.79	4.70	3.39	0.70
72.0	14.32	21.59	2.82	1.74	0.84
72.5	16.81	19.35	2.52	1.48	0.92
73.0	19.46	17.29	2.34	1.29	1.02
73.5	22.26	15.38	2.24	1.15	1.14
74.5	28.41	11.94	2.28	0.96	1.53
75.0	31.84	10.41	2.43	0.90	1.80
77.0	49.43	5.56	4.09	0.74	3.84
78.0	60.88	3.97	5.70	0.69	5.57
80.0	60.63	2.17	10.36	0.61	10.42
85.0	61.78	1.02	25.27	0.52	28.79
112.0	53.78	0.43	34.65	0.42	43.34
116.0	52.99	0.40	35.43	0.41	50.76
120.0	52.22	0.38	35.40	0.41	53.15
124.0	51.97	0.36	34.70	0.41	47.03
250.0	53.63	0.24	27.52	0.33	33.70
500.0	52.90	0.27	28.87	0.29	29.82
750.0	51.48	0.33	26.69	0.34	26.73
900.0	51.33	0.38	28.32	0.41	25.83
1000.0	52.18	0.41	31.23	0.45	26.58
1220.0	52.64	0.54	29.84	0.56	49.59

Functional Schematic





Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)		Cross over isolation (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Lowpass port	Highpass port		Common port	Lowpass port	Highpass port
1.0	0.01	88.53	93.67	51.69	52.76	0.00
5.0	0.04	77.33	78.25	47.68	48.78	0.00
10.0	0.06	74.57	73.35	45.27	47.79	0.01
15.0	0.07	75.14	71.78	42.83	46.75	0.01
20.0	0.09	76.33	74.28	40.04	42.18	0.02
25.0	0.11	70.97	70.11	37.40	38.41	0.04
35.0	0.17	61.18	60.29	34.31	34.49	0.09
40.0	0.22	59.56	59.00	34.88	34.96	0.13
45.0	0.28	58.84	58.73	38.55	37.39	0.18
50.0	0.36	59.02	58.58	56.48	41.64	0.24
60.0	0.74	61.62	61.03	26.29	26.19	0.43
65.0	1.29	59.59	58.14	30.96	29.11	0.55
70.0	8.37	32.04	42.96	3.66	3.15	0.77
70.5	10.20	28.93	42.48	3.07	2.54	0.81
71.0	12.20	26.06	42.09	2.65	2.10	0.86
72.0	16.60	21.03	42.25	2.18	1.55	1.00
72.5	19.00	18.77	42.49	2.07	1.38	1.10
73.0	21.53	16.64	43.01	2.02	1.24	1.23
74.0	27.08	12.75	44.55	2.14	1.06	1.63
74.5	30.18	11.00	45.51	2.32	0.99	1.94
75.0	33.60	9.37	46.91	2.60	0.94	2.34
76.0	41.67	6.61	51.16	3.56	0.85	3.54
77.0	52.18	4.54	58.52	5.14	0.78	5.41
78.0	58.29	3.15	67.82	7.36	0.72	7.98
79.0	57.58	2.29	60.17	10.07	0.68	11.21
80.0	57.28	1.79	57.76	13.04	0.64	15.01
82.0	58.61	1.29	58.92	18.69	0.58	24.84
84.0	61.33	1.06	62.74	22.03	0.54	49.25
85.0	62.23	0.99	65.48	22.77	0.53	37.94
86.0	62.40	0.92	66.87	23.21	0.52	33.37
87.0	62.22	0.87	65.37	23.52	0.50	31.48
88.0	62.11	0.83	64.96	23.82	0.49	30.56
90.0	61.33	0.75	63.03	24.41	0.48	29.92
92.0	61.09	0.70	61.41	24.96	0.47	29.75
94.0	61.90	0.65	60.87	25.35	0.46	29.50
95.0	61.47	0.63	59.76	25.50	0.46	29.37
96.0	61.21	0.61	59.97	25.65	0.45	29.08
97.0	60.33	0.60	59.71	25.69	0.45	28.88
98.0	60.06	0.58	58.72	25.73	0.45	28.64
100.0	58.96	0.55	57.32	25.71	0.44	28.09
110.0	53.72	0.47	53.26	24.94	0.44	26.43
120.0	51.40	0.41	51.16	24.44	0.44	26.27
125.0	51.03	0.39	50.68	24.37	0.44	26.56
150.0	50.68	0.34	49.96	24.82	0.44	29.78
175.0	51.36	0.31	51.20	25.48	0.44	33.87
200.0	51.97	0.30	51.68	26.03	0.43	35.67
250.0	53.08	0.29	53.15	27.16	0.42	33.76
300.0	54.07	0.30	53.94	27.95	0.40	31.96
350.0	54.54	0.31	53.97	28.97	0.39	30.89
500.0	53.24	0.36	52.24	28.71	0.36	28.70
600.0	52.62	0.41	51.50	26.60	0.36	27.26
700.0	51.65	0.45	51.20	25.10	0.38	25.68
800.0	52.12	0.50	51.02	24.54	0.41	24.45
900.0	52.74	0.54	52.09	25.33	0.46	24.11
1000.0	54.20	0.58	51.65	26.53	0.54	24.47
1100.0	55.22	0.63	54.69	25.90	0.61	26.46
1105.0	55.39	0.63	54.83	25.80	0.62	26.57
1110.0	55.64	0.64	54.92	25.71	0.62	26.68
1115.0	55.39	0.64	54.92	25.62	0.63	26.81
1220.0	55.90	0.72	56.61	22.29	0.72	27.56

Typical Performance Curves



Outline Dimensions

QB2223



CASE#	A	B	C	D	E	F	G	H	J	K
QB2223	1.243 (31.56)	1.117 (28.36)	.630 (16.00)	.475 (12.07)	.375 (9.53)	.255 (6.48)	.040 (1.02)	.070 (1.78)	.132 (3.35)	.546 (13.87)

CASE#	L	M	N	P	Q	R	S	T	WT.GRAMS
QB2223	.684 (17.37)	.831 (21.10)	1.111 (28.22)	.143 (3.63)	.559 (14.21)	.974 (24.74)	.417 (10.58)	.415 (10.53)	7

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .015$; 3 Pl. $\pm .030$

Notes:

1. Cover material: Fortan PPS
2. Pin material: Brass alloy [C3604]
3. Pin finish: Gold flash
4. Tolerance on pin diameter $\pm .001$
5. Base: Printed wiring laminate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M156280	NEW RELEASE	MAY 16	SSA	MD

SUGGESTED MOUNTING CONFIGURATION FOR
QB2223 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR IT180, WITH DIELECTRIC THICKNESS .059"±.005". COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	SSA	05 MAY 16
TOLERANCES ON:	MD	05 MAY 16
2 PL DECIMALS ±	MD	05 MAY 16
3 PL DECIMALS ± .005"		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, QB2223, DPLC,
75 Ohm

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-485	OR
FILE:	98PL485	SCALE:	SHEET:
		3:1	1 OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. PCB Material: FR4, GADE IT-180TC OR Equivalent
Dielectric Constant=4.7, Thickness=.059 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C