

MMIC

Power Splitter/Combiner Die

EPQ-133-D+

2 Way-90° 50Ω 6 to 14 GHz

The Big Deal

- Wideband, 6 to 14 GHz
- Good Isolation and Return Loss
- Highly repeatable performance (GaAs based design)
- No external termination required
- High Power handling (>30 dBm)



Product Overview

Mini-Circuits' EPQ-133-D+ is a wideband 6-14 GHz , 90° hybrid die . It splits an input signal into two output signals with quadrature phase shift between them. It provides low loss, wideband in a small layout size and handles high power with good VSWR.

Key Features

| Feature | Advantages |
|-----------------------------------|--|
| Low Phase and Amplitude Unbalance | 3.4 deg. and 0.5 dB unbalance make this 90° hybrid applicable for use in higher level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers. |
| High Power Handling | Capable of operating up to 32 dBm, MMIC structure of EPQ-133-D+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths. |
| Unpackaged Die | Enables user to integrate it directly into hybrids. |



MMIC

Power Splitter/Combiner Die

EPQ-133-D+

2 Way-90° 50Ω 6 to 14 GHz

Features

- Low insertion loss, 0.6 dB typ. at 8-10 GHz
- Good isolation, 20 dB typ. at 8-10 GHz
- High Power

Applications

- Balanced amplifiers
- Modulators
- Electronic variable attenuator
- Phase shifter




+RoHS Compliant
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

General Description

Mini-Circuits' EPQ-133-D+ is a wideband 6-14 GHz , 90° hybrid die . It splits an input signal into two output signals with quadrature phase shift between them. It provides low loss, wideband in a small layout size and handles high power with good VSWR.

Simplified Schematic and Pad Description



| Pad# | Function |
|------|---------------|
| 1 | Sum Port |
| 2 | Port 1 (0°) |
| 3 | Port 2 (+90°) |

Note: 1. Bond Pad material - Gold
 2. Bottom of Die - Gold plated

Bonding Pad Position



Dimensions in μm , Typical

| L1 | L2 | L3 | H1 | H2 | H3 | H4 | Thickness | Bond Pad Size |
|----|------|------|----|-----|------|------|-----------|---------------|
| 84 | 2566 | 2650 | 42 | 948 | 1078 | 1120 | 100 | 80 x 175 |



Electrical Specifications¹ at 25°C, 50Ω

| Parameter | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|--|-----------------|------|------|-------|--------|
| Frequency Range | | 6000 | | 14000 | MHz |
| Insertion Loss, (Avg. of Mainline & Coupled) above 3dB | 6000 - 8000 | | 0.6 | | dB |
| | 8000 - 10000 | | 0.6 | | |
| | 10000 - 12000 | | 0.8 | | |
| | 12000 - 14000 | | 1.0 | | |
| Isolation | 6000 - 8000 | | 20 | | dB |
| | 8000 - 10000 | | 20 | | |
| | 10000 - 12000 | | 18 | | |
| | 12000 - 14000 | | 16 | | |
| Amplitude Unbalance | 6000 - 8000 | | 0.5 | | dB |
| | 8000 - 10000 | | 0.5 | | |
| | 10000 - 12000 | | 0.6 | | |
| | 12000 - 14000 | | 0.4 | | |
| Phase Unbalance (Deviation from 90°) | 6000 - 8000 | | 2.9 | | Degree |
| | 8000 - 10000 | | 3.4 | | |
| | 10000 - 12000 | | 4.1 | | |
| | 12000 - 14000 | | 4.4 | | |
| Input VSWR | 6000 - 8000 | | 1.2 | | :1 |
| | 8000 - 10000 | | 1.2 | | |
| | 10000 - 12000 | | 1.4 | | |
| | 12000 - 14000 | | 1.6 | | |
| Output VSWR (0°&90°) | 6000 - 8000 | | 1.2 | | :1 |
| | 8000 - 10000 | | 1.1 | | |
| | 10000 - 12000 | | 1.3 | | |
| | 12000 - 14000 | | 1.5 | | |


1. Measured on Mini-Circuits Die Characterization Test Board. Die packaged in 4x4 mm, 24-lead MCLP package and soldered in TB-961-133+.

Maximum Ratings

| Parameter | Ratings |
|--|---------------|
| Operating Temperature | -45°C to 85°C |
| Power Input (as a splitter) ¹ | 32 dBm |
| Internal Dissipation ¹ | 30 dBm |

Permanent damage may occur if any of these limits are exceeded.

Assembly Diagram



Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The Die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total Die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic Die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the Die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

| Additional Detailed Technical Information <i>additional information is available on our dash board.</i> | | |
|---|---|--|
| Performance Data | Data Table | |
| | Swept Graphs | |
| | S-Parameter (S3P Files) Data Set with and without port extension(.zip file) | |
| Case Style | Die | |
| Die Ordering and packaging information (Note 5) | Quantity, Package Small, Gel - Pak: 5,10, 50, KGD* Medium†, Partial wafer: 350 Max. Large†, Full wafer | Model No. EPQ-133-DG+ EPQ-133-DP+ EPQ-133-DF+ |
| | †Available upon request contact sales representative Refer to AN-60-067 | |
| Environmental Ratings | ENV-80 | |

*Known Good Dice ("KGD") means that the dice are taken from PCM good wafer and are visually inspected. While this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits."

ESD Rating**

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard, 4x4mm, 24-lead MCLP package.

Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, Die preparation, Die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



2 Way-90° Power Splitter/Combiner Die EPQ-133-D+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10 dBm @Temperature = +25°C






| FREQ. (GHz) | TOTAL LOSS ⁽¹⁾ (dB) | | AMP. UNBAL. (dB) | PHASE UNBAL. (deg.) | ISOLATION (dB) 1-2 | VSWR (:1) | | |
|----------------|-----------------------------------|------|------------------------|---------------------------|--------------------------|--------------|------|------|
| | S-1 | S-2 | | | | S | 1 | 2 |
| 3.0 | 1.25 | 7.30 | 6.05 | 90.51 | 25.98 | 1.09 | 1.08 | 1.02 |
| 3.5 | 1.54 | 6.37 | 4.83 | 90.61 | 24.21 | 1.10 | 1.06 | 1.04 |
| 4.0 | 1.84 | 5.65 | 3.80 | 90.69 | 22.53 | 1.13 | 1.02 | 1.09 |
| 4.5 | 2.14 | 5.08 | 2.93 | 90.73 | 21.57 | 1.16 | 1.05 | 1.13 |
| 5.0 | 2.43 | 4.64 | 2.21 | 90.72 | 20.92 | 1.20 | 1.09 | 1.16 |
| 5.5 | 2.71 | 4.29 | 1.59 | 90.80 | 20.18 | 1.24 | 1.10 | 1.19 |
| 6.0 | 2.96 | 4.01 | 1.05 | 90.86 | 19.89 | 1.26 | 1.16 | 1.20 |
| 6.5 | 3.18 | 3.81 | 0.63 | 90.91 | 19.90 | 1.27 | 1.18 | 1.21 |
| 7.0 | 3.38 | 3.63 | 0.25 | 90.99 | 19.62 | 1.27 | 1.17 | 1.23 |
| 7.5 | 3.53 | 3.50 | 0.04 | 91.08 | 19.75 | 1.24 | 1.19 | 1.24 |
| 8.0 | 3.64 | 3.38 | 0.26 | 91.35 | 20.31 | 1.17 | 1.17 | 1.22 |
| 8.5 | 3.73 | 3.29 | 0.44 | 91.67 | 20.32 | 1.13 | 1.16 | 1.20 |
| 9.0 | 3.81 | 3.23 | 0.58 | 91.98 | 20.02 | 1.13 | 1.16 | 1.16 |
| 9.5 | 3.86 | 3.17 | 0.70 | 92.43 | 19.91 | 1.12 | 1.12 | 1.10 |
| 10.0 | 3.92 | 3.15 | 0.77 | 92.54 | 19.17 | 1.18 | 1.12 | 1.02 |
| 10.5 | 4.00 | 3.17 | 0.83 | 92.57 | 17.85 | 1.31 | 1.11 | 1.09 |
| 11.0 | 4.10 | 3.33 | 0.78 | 92.80 | 16.48 | 1.46 | 1.19 | 1.19 |
| 11.5 | 4.17 | 3.49 | 0.68 | 92.61 | 15.80 | 1.58 | 1.29 | 1.23 |
| 12.0 | 4.24 | 3.72 | 0.52 | 92.45 | 15.04 | 1.72 | 1.40 | 1.24 |
| 12.5 | 4.26 | 4.00 | 0.26 | 92.30 | 14.45 | 1.86 | 1.58 | 1.18 |
| 13.0 | 4.08 | 4.15 | 0.06 | 92.48 | 14.41 | 1.81 | 1.56 | 1.08 |
| 13.5 | 3.75 | 4.19 | 0.44 | 92.68 | 15.86 | 1.52 | 1.53 | 1.17 |
| 14.0 | 3.54 | 4.45 | 0.91 | 93.75 | 16.08 | 1.49 | 1.46 | 1.31 |
| 14.5 | 3.32 | 4.66 | 1.34 | 94.49 | 17.23 | 1.35 | 1.39 | 1.47 |
| 15.0 | 3.12 | 5.01 | 1.88 | 95.38 | 17.68 | 1.30 | 1.29 | 1.55 |
| 15.5 | 2.95 | 5.38 | 2.43 | 96.32 | 18.54 | 1.22 | 1.26 | 1.57 |
| 16.0 | 2.76 | 5.80 | 3.04 | 96.73 | 18.98 | 1.17 | 1.19 | 1.50 |

¹Total Loss = Insertion Loss + 3dB Splitter Loss

Note: Data tested in industry standard, 4x4mm, 24-lead MCLP package



Typical Performance Curves



Note: Data tested in industry standard, 4x4mm, 24-lead MCLP package

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|--------------------------------------|
| Operating Temperature | -40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment | Refer to Individual Model Data Sheet |
| Storage Environment (Die) | -65° to 150°C | Individual Model Data Sheet |
| Storage Environment(Packaging) | -40° to 70°C and 40 to 60% humidity (In Factory Shipped Package) | |