

MMIC


# Power Splitter/Combiner Die

EP2RCW-D+

2 Way-0° 50Ω DC to 8 GHz

## The Big Deal

- Ultra-Wide Bandwidth, DC to 8 GHz
- High Isolation, 21 dB typ. at 4 GHz
- High Power Handling, 0.6W as a splitter/combiner



## Product Overview

Mini-Circuits' EP2RCW-D+ is a MMIC 2-way 0° splitter/combiner Die designed for wideband operation from DC to 8 GHz supporting many applications requiring high performance across a wide frequency range including all the LTE bands through WiMax an WiFi, as well as instrumentation and more. This model provides excellent power handling up to 0.6W (as a splitter/combiner) with low insertion loss, good isolation, and low phase and amplitude unbalance. Manufactured using GaAs IPD technology, the EP2RCW-D+ provides a high level of ESD protection and excellent repeatability.

## Key Features

Feature	Advantages
Wideband, DC to 8 GHz	One power splitter can be used in all the LTE bands through WiMAX and WiFi, saving component count. Also ideal for wideband applications such as military and instrumentation.
Excellent power handling <ul style="list-style-type: none"><li>• 0.6W as a splitter</li><li>• 0.6W internal dissipation as a combiner</li></ul>	In power combiner applications, half the power is dissipated internally. EP2RCW-D+ is designed to handle 0.6W internal dissipation as a combiner allowing reliable operation without excessive temperature rise.
Unpackaged Die	Enables user to integrate it directly into hybrids.



MMIC

# Power Splitter/Combiner Die

## EP2RCW-D+

2 Way-0° 50Ω DC to 8 GHz

### Product Features


- Wide bandwidth, DC to 8 GHz
- Excellent isolation, 21 dB typ. up to 4 GHz
- Excellent amplitude unbalance, 0.1 dB typ. up to 8 GHz
- Good phase unbalance, 0.1 deg. typ. at 4 GHz
- High ESD level
- Patent pending

### Typical Applications

- WIMAX
- ISM
- Instrumentation
- Radar
- WLAN
- Satellite communications
- LTE

### General Description


Mini-Circuits' EP2RCW-D+ is a MMIC 2-way 0° splitter/combiner Die designed for wideband operation from DC to 8 GHz supporting many applications requiring high performance across a wide frequency range including all the LTE bands through WiMax an WiFi, as well as instrumentation and more. This model provides excellent power handling up to 0.6W (as a splitter/combiner) with low insertion loss, good isolation, and low phase and amplitude unbalance. Manufactured using GaAs IPD technology, the EP2RCW-D+ provides a high level of ESD protection and excellent repeatability.



**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

**Ordering Information: Refer to Last Page**


### Simplified Schematic and Pad Description



Pad#	Function
1	Sum Port (RF IN)
4	Port 1 (RF OUT 1)
7	Port 2 (RF OUT 2)
2,3,5,6,8,9	Ground

Note: 1. Bond Pad material - Gold  
2. Bottom of Die is ground - Gold plated

### Bonding Pad Position



L1	L2	L3	L4	L5	H1	H2	H3	H4	H5	H6	Thickness	Die Size	Pad Size	Pad Size 2,3,5,6,8,9	Pad Size 7&4
89	2851	3001	3151	3500	88	1370	1520	1670	3412	3500	100	3500x3500	92x117	92x92	117x92



Electrical Specifications at 25°C<sup>1</sup>

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range		DC		8	GHz
Insertion Loss, above 3.0 dB	DC - 0.4	—	5.4	—	dB
	0.4 - 0.7	—	5.4	—	
	0.7 - 7.5	—	4.5	—	
	7.5 - 8.0	—	3.7	—	
Isolation	DC - 0.4	—	16.9	—	dB
	0.4 - 0.7	—	19.3	—	
	0.7 - 7.5	—	22.3	—	
	7.5 - 8.0	—	21.9	—	
Phase Unbalance	DC - 0.4	—	0.1	—	Degree
	0.4 - 0.7	—	0.1	—	
	0.7 - 7.5	—	0.1	—	
	7.5 - 8.0	—	0.2	—	
Amplitude Unbalance	DC - 0.4	—	0.1	—	dB
	0.4 - 0.7	—	0.1	—	
	0.7 - 7.5	—	0.1	—	
	7.5 - 8.0	—	0.1	—	
VSWR (Port S)	DC - 0.4	—	1.1	—	:1
	0.4 - 0.7	—	1.1	—	
	0.7 - 7.5	—	1.6	—	
	7.5 - 8.0	—	1.3	—	
VSWR (Port 1-2)	DC - 0.4	—	1.6	—	:1
	0.4 - 0.7	—	1.8	—	
	0.7 - 7.5	—	1.7	—	
	7.5 - 8.0	—	1.2	—	
Power Handling	As a splitter	DC - 8	—	0.6	W
	As a combiner	DC - 8	—	0.6	


1. Measured on die using MPI Titan series 150 μm pitch as probe

## Maximum Ratings

Parameter	Ratings
Operating Temperature	-55°C to 105°C

Permanent damage may occur if any of these limits are exceeded.

## Assembly Diagram



## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The Die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total Die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic Die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the Die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

<b>Additional Detailed Technical Information</b> <i>additional information is available on our dash board.</i>							
<b>Performance Data</b>	Data Table						
	Swept Graphs						
	S-Parameter (S3P Files) Data Set with and without port extension(.zip file)						
<b>Case Style</b>	Die						
<b>Die Ordering and packaging information</b>	<table> <tr> <td>Quantity, Package</td> <td>Model No.</td> </tr> <tr> <td>Small, Gel - Pak: 5,10</td> <td>EP2RCW-DG+</td> </tr> <tr> <td>Medium†, Partial wafer: 225 Max.</td> <td>EP2RCW-DP+</td> </tr> </table> <p>†Available upon request contact sales representative</p> <p>Refer to <a href="#">AN-60-067</a></p>	Quantity, Package	Model No.	Small, Gel - Pak: 5,10	EP2RCW-DG+	Medium†, Partial wafer: 225 Max.	EP2RCW-DP+
Quantity, Package	Model No.						
Small, Gel - Pak: 5,10	EP2RCW-DG+						
Medium†, Partial wafer: 225 Max.	EP2RCW-DP+						
<b>Environmental Ratings</b>	ENV-80						

**ESD Rating\*\***

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard, 5x5mm, 32-lead MCLP package.

**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, Die preparation, Die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



# 2 Way-0° Power Splitter/Combiner Die EP2RCW-D+

## Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS <sup>(1)</sup>		AMP. UNBAL.	PHASE UNBAL.	ISOLATION	VSWR		
	(dB) S-1	(dB) S-2	(dB)	(deg.)	(dB) 2-1	S	1	2
100	8.43	8.38	0.05	0.01	16.38	1.11	1.57	1.57
200	8.44	8.39	0.05	0.00	16.82	1.11	1.61	1.62
300	8.45	8.40	0.05	0.01	17.43	1.11	1.66	1.67
400	8.45	8.40	0.05	0.01	18.15	1.12	1.71	1.72
500	8.45	8.41	0.05	0.01	18.90	1.13	1.76	1.76
600	8.45	8.40	0.04	0.00	19.65	1.14	1.79	1.80
700	8.45	8.40	0.05	0.01	20.38	1.15	1.82	1.83
800	8.44	8.39	0.05	0.01	21.08	1.16	1.85	1.85
900	8.43	8.39	0.04	0.01	21.74	1.18	1.86	1.87
1000	8.42	8.37	0.04	0.00	22.34	1.20	1.88	1.89
1200	8.39	8.35	0.04	0.02	23.38	1.24	1.90	1.91
1400	8.35	8.31	0.04	0.01	24.17	1.29	1.91	1.92
1600	8.31	8.27	0.04	0.01	24.72	1.35	1.92	1.93
1800	8.26	8.22	0.04	0.02	25.02	1.41	1.91	1.93
2000	8.21	8.17	0.04	0.01	25.06	1.47	1.91	1.92
2200	8.15	8.11	0.04	0.02	24.90	1.54	1.90	1.91
2400	8.09	8.05	0.04	0.02	24.56	1.61	1.89	1.90
2600	8.01	7.98	0.04	0.02	24.10	1.67	1.87	1.88
2800	7.94	7.90	0.03	0.04	23.54	1.72	1.85	1.86
3000	7.86	7.83	0.03	0.07	22.96	1.75	1.82	1.83
3200	7.78	7.75	0.04	0.07	22.36	1.77	1.79	1.80
3400	7.70	7.66	0.04	0.09	21.80	1.78	1.75	1.76
3600	7.60	7.57	0.03	0.12	21.33	1.76	1.71	1.72
3800	7.51	7.47	0.04	0.14	20.96	1.72	1.66	1.68
4000	7.42	7.38	0.04	0.09	20.74	1.67	1.62	1.64
4200	7.33	7.29	0.04	0.09	20.70	1.61	1.58	1.60
4400	7.25	7.20	0.04	0.07	20.82	1.56	1.56	1.57
4600	7.17	7.13	0.04	0.06	21.07	1.52	1.54	1.55
4800	7.11	7.07	0.04	0.08	21.40	1.51	1.53	1.54
5000	7.07	7.03	0.04	0.09	21.74	1.53	1.53	1.54
5200	7.04	7.00	0.03	0.07	22.00	1.58	1.53	1.54
5400	7.02	6.99	0.03	0.07	22.14	1.65	1.54	1.55
5600	7.01	6.98	0.03	0.11	22.14	1.73	1.54	1.55
5800	7.01	6.98	0.03	0.07	22.04	1.81	1.54	1.55
6000	6.99	6.98	0.01	0.12	21.84	1.87	1.54	1.55
6200	6.97	6.95	0.02	0.23	21.58	1.89	1.53	1.54
6400	6.92	6.89	0.03	0.23	21.36	1.87	1.51	1.52
6600	6.86	6.83	0.03	0.23	21.23	1.80	1.48	1.49
6800	6.80	6.76	0.03	0.22	21.20	1.69	1.44	1.45
7000	6.73	6.70	0.04	0.21	21.29	1.55	1.38	1.40
7200	6.67	6.64	0.03	0.21	21.48	1.40	1.32	1.34
7400	6.64	6.61	0.04	0.22	21.72	1.27	1.27	1.28
7600	6.65	6.62	0.04	0.20	21.89	1.21	1.22	1.23
7800	6.70	6.67	0.04	0.19	21.90	1.27	1.18	1.19
8000	6.80	6.76	0.04	0.21	21.70	1.38	1.16	1.17
8200	6.93	6.89	0.04	0.17	21.35	1.49	1.16	1.17
8400	7.08	7.04	0.04	0.19	20.90	1.55	1.16	1.17
8600	7.27	7.23	0.04	0.17	20.42	1.57	1.17	1.18
8800	7.49	7.45	0.04	0.17	19.91	1.55	1.17	1.19
9000	7.75	7.71	0.04	0.17	19.45	1.53	1.18	1.20
9200	8.07	8.02	0.04	0.19	19.22	1.56	1.20	1.21
9400	8.42	8.37	0.05	0.16	19.55	1.55	1.20	1.22
9600	8.93	8.88	0.05	0.13	20.45	1.35	1.20	1.22
9800	10.16	10.11	0.05	0.13	19.28	1.08	1.28	1.29
10000	12.98	12.93	0.05	0.07	15.68	1.90	1.47	1.49

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site








The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
EP2RCW-D+  
10/29/2019  
Page 1 of 1

## Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	