



CERAMIC

# High Pass Filter


## HFCN-1000+

Mini-Circuits

50Ω 1080 to 4000 MHz

### FEATURES

- Low cost
- Small size
- 7 sections
- Temperature stable
- DC block in/out, breakdown voltage, 1kV typ.
- Excellent power handling, 7W
- Hermetically sealed



Generic photo used for illustration purposes only

CASE STYLE: FV1206

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

### APPLICATIONS

- Sub-harmonic rejection
- Transmitters/receivers
- Lab use

### PRODUCT OVERVIEW

The HFCN-1000+ LTCC High Pass Filter is constructed with 12 layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 1080-4000 MHz, these units offer low insertion loss and good rejection.

### KEY FEATURES

Feature	Advantages
Small Size (3.20mm x1.6 mm)	Allows for high layout density of circuit boards, while minimizing affects of parasitics.
Rejection peaks at harmonic frequencies	Provides good rejection of signals at harmonic frequencies, for improved system performance.
Wrap around termination	Provides excellent solderability and easy visual inspection capability.
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.

REV. C  
ECO-023234  
HFCN-1000+  
MCL NY  
241002





CERAMIC

# High Pass Filter

## HFCN-1000+

### ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Stop Band	DC-F1	DC-570	40	—	—	dB
	F1-F2	DC-740	20	—	—	
	Freq. Cut-Off	F3	1000	—	3.0	dB
	VSWR	DC-F2	DC-740	—	20	:1
Pass Band	F4-F7	1080-4000	—	—	2.0	dB
	F5-F6	1150-3700	—	—	1.4	dB
	VSWR	F4-F7	1080-4000	—	1.5	:1


1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required.
2. Measured on Mini-Circuits Characterization Test Board TB-270.

### ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-55°C to +100°C
Storage temperature	-55°C to +100°C
RF Power Input <sup>3</sup>	7W max.at 25°C

3. Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

### TYPICAL FREQUENCY RESPONSE



### FUNCTIONAL SCHEMATIC





CERAMIC

# High Pass Filter


HFCN-1000+

## PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4

PRODUCT MARKING: A5


DEMO BOARD MCL P/N: TB-270  
SUGGESTED PCB LAYOUT (PL-137)




- NOTES:**
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



## OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
H	J	K	L	M	N	P	wt
.087	.024	.122	.024	.087	.012	.071	grams
2.21	0.61	3.10	0.61	2.21	0.30	1.80	.020

TAPE & REEL INFORMATION: F71



CERAMIC



# High Pass Filter

## HFCN-1000+

Mini-Circuits

### TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10.0	89.53	1737.18
50.0	77.22	1737.18
100.0	71.42	1737.18
570.0	50.83	86.86
740.0	30.15	43.44
1070.0	1.65	1.45
1120.0	1.14	1.10
2000.0	0.62	1.64
3060.0	0.33	1.12
4000.0	1.12	2.32



#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55°C	@ +25°C	@ +100°C	@ -55°C	@ +25°C	@ +100°C	@ -55°C	@ +25°C	@ +100°C
10.0	89.76	89.53	92.00	0.01	0.01	0.00	0.02	0.01	0.02
30.0	81.90	82.07	80.56	0.01	0.00	0.00	0.02	0.02	0.03
50.0	77.33	77.22	76.28	0.01	0.01	0.00	0.02	0.02	0.02
70.0	73.95	74.17	73.03	0.02	0.01	0.01	0.01	0.01	0.02
100.0	71.79	71.42	70.55	0.00	0.01	0.02	0.02	0.02	0.04
110.0	70.80	70.11	69.66	0.00	0.01	0.02	0.01	0.02	0.04
180.0	67.11	66.74	65.98	0.01	0.02	0.04	0.01	0.03	0.06
260.0	64.80	64.60	63.60	0.01	0.03	0.06	0.02	0.05	0.09
340.0	64.21	64.25	63.52	0.02	0.06	0.09	0.04	0.08	0.11
410.0	65.28	65.02	64.46	0.04	0.09	0.13	0.06	0.11	0.14
490.0	67.57	66.73	66.88	0.07	0.14	0.19	0.08	0.15	0.20
570.0	51.20	50.83	50.48	0.12	0.20	0.25	0.13	0.20	0.26
580.0	49.78	49.36	49.07	0.13	0.21	0.26	0.14	0.21	0.27
600.0	46.95	46.62	46.31	0.14	0.22	0.28	0.16	0.24	0.30
630.0	42.99	42.70	42.45	0.16	0.25	0.31	0.17	0.25	0.31
660.0	39.39	39.10	38.83	0.19	0.28	0.34	0.20	0.29	0.35
680.0	37.06	36.77	36.52	0.21	0.31	0.37	0.21	0.31	0.37
710.0	33.71	33.41	33.14	0.24	0.34	0.42	0.24	0.34	0.41
740.0	30.45	30.15	29.86	0.29	0.40	0.49	0.27	0.38	0.46
750.0	29.38	29.07	28.78	0.30	0.42	0.51	0.29	0.40	0.49
790.0	25.14	24.83	24.53	0.37	0.50	0.61	0.35	0.48	0.58
830.0	20.95	20.67	20.36	0.47	0.63	0.76	0.46	0.61	0.73
870.0	16.80	16.54	16.25	0.66	0.85	1.01	0.62	0.80	0.95
910.0	12.71	12.47	12.22	1.01	1.26	1.48	0.95	1.17	1.37
950.0	8.78	8.57	8.37	1.75	2.13	2.46	1.63	1.96	2.26
1000.0	4.60	4.51	4.41	3.98	4.71	5.39	3.72	4.35	4.91
1010.0	3.93	3.88	3.81	4.74	5.57	6.36	4.41	5.12	5.77
1040.0	2.39	2.45	2.49	7.92	9.15	10.37	7.27	8.24	9.16
1070.0	1.49	1.65	1.76	12.88	14.73	16.68	11.45	12.61	13.71
1080.0	1.31	1.48	1.61	15.13	17.31	19.71	13.07	14.24	15.31
1100.0	1.06	1.26	1.41	20.88	24.14	27.91	16.33	17.22	17.96
1120.0	0.93	1.14	1.30	25.65	26.46	26.80	18.50	18.67	19.04
1150.0	0.83	1.03	1.17	21.58	20.83	20.51	18.71	18.37	18.28
1160.0	0.80	1.01	1.15	20.14	19.59	19.43	18.23	17.94	17.92
1370.0	0.48	0.64	0.76	23.02	23.74	24.17	23.89	25.47	26.63
1580.0	0.37	0.54	0.65	18.71	18.26	18.07	19.13	18.72	18.46
1790.0	0.42	0.59	0.69	13.62	13.51	13.50	13.79	13.70	13.69
2000.0	0.45	0.62	0.72	12.28	12.29	12.36	12.51	12.53	12.59
2210.0	0.44	0.59	0.70	12.76	12.91	13.07	13.01	13.19	13.31
2430.0	0.34	0.50	0.62	14.49	14.83	14.87	14.84	15.24	15.35
2640.0	0.22	0.40	0.51	17.75	18.26	18.47	18.01	18.68	19.11
2850.0	0.17	0.35	0.46	25.13	25.01	25.03	26.83	28.30	29.55
3060.0	0.12	0.33	0.44	25.79	24.95	24.14	27.55	26.93	26.26
3270.0	0.19	0.40	0.52	18.06	17.75	17.14	17.95	17.82	17.41
3480.0	0.33	0.55	0.67	12.99	12.96	13.24	13.12	13.11	13.27
3700.0	0.54	0.78	0.93	10.39	10.32	10.39	10.49	10.45	10.56
3710.0	0.56	0.79	0.94	10.32	10.26	10.34	10.44	10.38	10.47
3740.0	0.58	0.82	0.97	10.05	10.00	10.10	10.28	10.21	10.33
3770.0	0.60	0.84	1.00	9.80	9.74	9.92	9.94	9.90	10.00
3780.0	0.61	0.86	1.01	9.72	9.67	9.86	9.85	9.81	9.90
3790.0	0.63	0.87	1.03	9.64	9.58	9.77	9.75	9.71	9.80
3800.0	0.64	0.89	1.04	9.54	9.49	9.67	9.68	9.64	9.73
3820.0	0.64	0.89	1.06	9.42	9.35	9.48	9.59	9.52	9.61
3830.0	0.65	0.90	1.06	9.37	9.29	9.40	9.51	9.45	9.54
3850.0	0.67	0.93	1.09	9.21	9.13	9.22	9.29	9.27	9.33
3860.0	0.69	0.95	1.11	9.14	9.06	9.13	9.18	9.15	9.18
3880.0	0.71	0.97	1.14	8.93	8.87	8.94	9.00	8.96	8.98
3890.0	0.72	0.98	1.15	8.88	8.80	8.84	8.97	8.93	8.93
3910.0	0.75	1.02	1.18	8.72	8.62	8.64	8.86	8.81	8.78
3920.0	0.75	1.03	1.19	8.66	8.56	8.54	8.78	8.73	8.70
3950.0	0.78	1.06	1.24	8.41	8.31	8.33	8.43	8.38	8.36
3980.0	0.81	1.09	1.28	8.23	8.15	8.12	8.33	8.25	8.24
4000.0	0.84	1.12	1.31	8.13	8.03	7.99	8.25	8.2	8.14
4260.0	1.21	1.54	1.73	6.83	6.73	6.57	6.93	6.81	6.70
4510.0	1.41	1.77	2.03	5.80	5.68	5.59	5.90	5.79	5.76
5010.0	2.02	2.41	2.70	4.41	4.42	4.37	4.48	4.51	4.46
5260.0	2.34	2.74	3.04	3.94	3.99	3.92	3.93	3.99	3.99
5760.0	3.04	3.36	3.59	3.02	3.26	3.41	3.06	3.29	3.38
6010.0	3.33	3.69	3.96	2.75	2.95	3.13	2.73	2.95	3.07
6500.0	4.09	4.40	4.64	2.27	2.53	2.84	2.35	2.63	2.84
6750.0	4.34	4.66	4.88	2.07	2.42	2.64	2.10	2.47	2.64
7000.0	4.51	4.81	5.19	2.04	2.34	2.47	2.04	2.35	2.47
7500.0	5.31	5.71	5.82	2.13	2.52	2.40	1.77	2.17	2.24




# Ceramic High Pass Filter


## Typical Performance Curves

# HFCN-1000+


Insertion Loss vs Temperature



Input Return Loss vs Temperature



Output Return Loss vs Temperature




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

REV. X1  
 HFCN-1000+  
 5/31/2011  
 Page 1 of 1

### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206	.126 (3.20)	.063 (1.60)	.037 (0.94)	.020 (0.51)	.032 (0.81)	.009 (0.23)	.169 (4.29)	.087 (2.21)	.024 (0.61)	.122 (3.10)	.024 (0.61)	.087 (2.21)	.012 (0.30)	.071 (1.80)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

# Tape & Reel Packaging TR-F71




ILLUSTRATION 1

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS




THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION




- NOTES:**
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" ± .0015".  
 COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF 08/27/03
	CHECKED	AV 08/28/03
	APPROVED	ABD 08/28/03



**Mini-Circuits®**



13 Neptune Avenue  
 Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-137	REV: A
FILE: 98PL137	SCALE: 10:1	SHEET: 1 OF 1	

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A