

Surface Mount Power Splitter/Combiner

JSPQW-100+ JSPQW-100

2 Way-90° 50Ω 40 to 100 MHz



Generic photo used for illustration purposes only

CASE STYLE: BK276

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings


| | |
|-----------------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| Power Input (as a splitter) | 1W max. |

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| | |
|----------------------|-------------------------|
| SUMPORT | 9 |
| PORT 1 (+90°) | 2 |
| PORT 2 (0°) | 6 |
| GROUND | 1,3,4,5,7,8,10,11,12,14 |
| 50 OHM TERM EXTERNAL | 13 |

Outline Drawing




Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G |
|-------|-------|----|------|------|------|------|
| .450 | .803 | -- | .100 | .250 | .102 | .100 |
| 11.43 | 20.40 | -- | 2.54 | 6.35 | 2.59 | 2.54 |

| H | J | K | L | wt |
|------|------|------|-------|-------|
| .047 | .065 | .065 | .470 | grams |
| 1.19 | 1.65 | 1.65 | 11.94 | 3.0 |

Demo Board MCL P/N: TB-212 Suggested PCB Layout (PL-098)



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low insertion loss, 0.2 dB typ.
- good isolation, 24 dB typ.
- excellent phase unbalance 1 deg. typ.
- good VSWR, 1.20:1 typ.
- aqueous washable

Applications

- VHF
- instrumentation
- modulators
- image rejection mixers




Electrical Specifications

| FREQ. RANGE (MHz) | ISOLATION (dB) | | INSERTION LOSS (dB) Avg. of Coupled Outputs ABOVE 3 dB | | PHASE UNBALANCE (Degrees) | AMPLITUDE UNBALANCE (dB) |
|-------------------|----------------|------|---|------|---------------------------|--------------------------|
| | Typ. | Min. | Typ. | Max. | | |
| f_L - f_U | | | | | Max. | Max. |
| 40-100 | 24 | 18 | 0.2 | 0.6 | 3 | 1.2 |


Typical Performance Data

| Frequency (MHz) | Total Loss ¹ (dB) | | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
|-----------------|------------------------------|------|--------------------------|----------------|------------------------|--------|--------|--------|
| | S-1 | S-2 | | | | | | |
| 40.00 | 3.49 | 2.84 | 0.65 | 24.92 | 89.75 | 1.09 | 1.10 | 1.12 |
| 43.00 | 3.34 | 2.99 | 0.35 | 25.05 | 89.81 | 1.09 | 1.10 | 1.13 |
| 46.00 | 3.22 | 3.11 | 0.12 | 25.16 | 89.84 | 1.09 | 1.10 | 1.13 |
| 50.50 | 3.10 | 3.26 | 0.16 | 25.44 | 89.84 | 1.09 | 1.10 | 1.14 |
| 55.00 | 3.02 | 3.36 | 0.34 | 25.72 | 90.00 | 1.09 | 1.10 | 1.14 |
| 59.50 | 2.98 | 3.41 | 0.43 | 26.08 | 90.00 | 1.09 | 1.10 | 1.14 |
| 64.00 | 2.97 | 3.44 | 0.47 | 26.47 | 90.04 | 1.08 | 1.10 | 1.14 |
| 68.50 | 2.98 | 3.42 | 0.45 | 26.94 | 90.17 | 1.08 | 1.09 | 1.14 |
| 73.00 | 3.02 | 3.39 | 0.37 | 27.43 | 90.19 | 1.07 | 1.08 | 1.14 |
| 77.50 | 3.08 | 3.33 | 0.25 | 27.88 | 90.25 | 1.07 | 1.08 | 1.14 |
| 82.00 | 3.15 | 3.25 | 0.10 | 28.30 | 90.38 | 1.07 | 1.07 | 1.15 |
| 88.00 | 3.29 | 3.14 | 0.15 | 28.51 | 90.51 | 1.08 | 1.07 | 1.15 |
| 94.00 | 3.47 | 3.01 | 0.47 | 28.09 | 90.84 | 1.10 | 1.07 | 1.16 |
| 97.00 | 3.57 | 2.94 | 0.64 | 27.59 | 90.94 | 1.12 | 1.08 | 1.17 |
| 100.00 | 3.69 | 2.87 | 0.83 | 26.95 | 91.03 | 1.13 | 1.09 | 1.18 |

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



2 Way-90° Power Splitter/Combiner

JSPQW-100+

Typical Performance Data






| FREQ. (MHz) | TOTAL LOSS ¹ (dB) | | | AMP. UNBAL. (dB) | ISOLATION (dB) 1-2 | PHASE UNBAL. (deg.) | FREQ. (MHz) | VSWR (:1) | | |
|----------------|---------------------------------|------|------|------------------------|--------------------------|---------------------------|----------------|--------------|------|------|
| | S-1 | S-2 | AVG. | | | | | S | 1 | 2 |
| 40.0 | 3.49 | 2.84 | 3.17 | 0.65 | 24.92 | 89.75 | 40.0 | 1.09 | 1.10 | 1.12 |
| 41.5 | 3.41 | 2.92 | 3.17 | 0.49 | 24.98 | 89.80 | 41.5 | 1.09 | 1.10 | 1.12 |
| 43.0 | 3.34 | 2.99 | 3.17 | 0.35 | 25.05 | 89.81 | 43.0 | 1.09 | 1.10 | 1.13 |
| 44.5 | 3.28 | 3.05 | 3.17 | 0.23 | 25.10 | 89.79 | 44.5 | 1.09 | 1.10 | 1.13 |
| 46.0 | 3.22 | 3.11 | 3.17 | 0.12 | 25.16 | 89.84 | 46.0 | 1.09 | 1.10 | 1.13 |
| 47.5 | 3.17 | 3.17 | 3.17 | 0.00 | 25.26 | 89.85 | 47.5 | 1.09 | 1.10 | 1.13 |
| 49.0 | 3.14 | 3.21 | 3.18 | 0.07 | 25.32 | 89.86 | 49.0 | 1.09 | 1.10 | 1.13 |
| 50.5 | 3.10 | 3.26 | 3.18 | 0.16 | 25.44 | 89.84 | 50.5 | 1.09 | 1.10 | 1.14 |
| 52.0 | 3.07 | 3.30 | 3.19 | 0.23 | 25.52 | 89.89 | 52.0 | 1.09 | 1.10 | 1.14 |
| 53.5 | 3.04 | 3.33 | 3.19 | 0.29 | 25.63 | 89.96 | 53.5 | 1.09 | 1.10 | 1.14 |
| 55.0 | 3.02 | 3.36 | 3.19 | 0.34 | 25.72 | 90.00 | 55.0 | 1.09 | 1.10 | 1.14 |
| 56.5 | 3.00 | 3.38 | 3.19 | 0.38 | 25.86 | 89.97 | 56.5 | 1.09 | 1.10 | 1.14 |
| 58.0 | 2.99 | 3.40 | 3.20 | 0.41 | 25.98 | 90.02 | 58.0 | 1.09 | 1.10 | 1.14 |
| 59.5 | 2.98 | 3.41 | 3.20 | 0.43 | 26.08 | 90.00 | 59.5 | 1.09 | 1.10 | 1.14 |
| 61.0 | 2.98 | 3.44 | 3.21 | 0.45 | 26.22 | 90.04 | 61.0 | 1.08 | 1.10 | 1.14 |
| 62.5 | 2.97 | 3.43 | 3.20 | 0.46 | 26.33 | 90.03 | 62.5 | 1.08 | 1.10 | 1.14 |
| 64.0 | 2.97 | 3.44 | 3.21 | 0.47 | 26.47 | 90.04 | 64.0 | 1.08 | 1.10 | 1.14 |
| 65.5 | 2.97 | 3.44 | 3.21 | 0.47 | 26.65 | 90.06 | 65.5 | 1.08 | 1.09 | 1.14 |
| 67.0 | 2.98 | 3.44 | 3.21 | 0.46 | 26.78 | 90.08 | 67.0 | 1.08 | 1.09 | 1.14 |
| 68.5 | 2.98 | 3.42 | 3.20 | 0.45 | 26.94 | 90.17 | 68.5 | 1.08 | 1.09 | 1.14 |
| 70.0 | 2.99 | 3.41 | 3.20 | 0.42 | 27.09 | 90.12 | 70.0 | 1.08 | 1.09 | 1.14 |
| 71.5 | 2.99 | 3.39 | 3.19 | 0.40 | 27.25 | 90.16 | 71.5 | 1.07 | 1.09 | 1.14 |
| 73.0 | 3.02 | 3.39 | 3.21 | 0.37 | 27.43 | 90.19 | 73.0 | 1.07 | 1.08 | 1.14 |
| 74.5 | 3.04 | 3.37 | 3.21 | 0.34 | 27.59 | 90.21 | 74.5 | 1.07 | 1.08 | 1.14 |
| 76.0 | 3.05 | 3.35 | 3.20 | 0.30 | 27.74 | 90.21 | 76.0 | 1.07 | 1.08 | 1.14 |
| 77.5 | 3.08 | 3.33 | 3.21 | 0.25 | 27.88 | 90.25 | 77.5 | 1.07 | 1.08 | 1.14 |
| 79.0 | 3.10 | 3.30 | 3.20 | 0.21 | 28.05 | 90.24 | 79.0 | 1.07 | 1.08 | 1.14 |
| 80.5 | 3.12 | 3.28 | 3.20 | 0.16 | 28.19 | 90.33 | 80.5 | 1.07 | 1.07 | 1.15 |
| 82.0 | 3.15 | 3.25 | 3.20 | 0.10 | 28.30 | 90.38 | 82.0 | 1.07 | 1.07 | 1.15 |
| 83.5 | 3.19 | 3.23 | 3.21 | 0.05 | 28.41 | 90.37 | 83.5 | 1.07 | 1.07 | 1.15 |
| 85.0 | 3.21 | 3.20 | 3.21 | 0.01 | 28.48 | 90.45 | 85.0 | 1.07 | 1.07 | 1.15 |
| 86.5 | 3.26 | 3.16 | 3.21 | 0.09 | 28.53 | 90.47 | 86.5 | 1.08 | 1.07 | 1.15 |
| 88.0 | 3.29 | 3.14 | 3.22 | 0.15 | 28.51 | 90.51 | 88.0 | 1.08 | 1.07 | 1.15 |
| 89.5 | 3.34 | 3.11 | 3.23 | 0.23 | 28.50 | 90.64 | 89.5 | 1.09 | 1.07 | 1.15 |
| 91.0 | 3.38 | 3.07 | 3.23 | 0.31 | 28.41 | 90.67 | 91.0 | 1.09 | 1.07 | 1.16 |
| 92.5 | 3.42 | 3.04 | 3.23 | 0.38 | 28.26 | 90.74 | 92.5 | 1.10 | 1.07 | 1.16 |
| 94.0 | 3.47 | 3.01 | 3.24 | 0.47 | 28.09 | 90.84 | 94.0 | 1.10 | 1.07 | 1.16 |
| 95.5 | 3.52 | 2.98 | 3.25 | 0.54 | 27.88 | 90.80 | 95.5 | 1.11 | 1.08 | 1.17 |
| 97.0 | 3.57 | 2.94 | 3.26 | 0.64 | 27.59 | 90.94 | 97.0 | 1.12 | 1.08 | 1.17 |
| 100.0 | 3.69 | 2.87 | 3.28 | 0.83 | 26.95 | 91.03 | 100.0 | 1.13 | 1.09 | 1.18 |

¹Total Loss = Insertion Loss + 3dB Splitter Loss




2 Way-90° Power Splitter/Combiner

JSPQW-100+


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L | WT. GRAM |
|--------|-----------------|-----------------|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|-------------|
| BK276 | .450 (11.43) | .803 (20.40) | -- -- | .100 (2.54) | .250 (6.35) | .102 (2.59) | .100 (2.54) | .047 (1.19) | .065 (1.65) | .065 (1.65) | .470 (11.94) | 2.0 MAX. |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Copper Nickel alloy.
- Base material: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F5



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel |
|----------------|-------------------------|-------------------|------------------|
| 32 | 16 | 13 | 500 |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|---------------------------------------|----------|-----|------|
| OR | M82501 | NEW RELEASE | 11/15/02 | MMG | HY |
| A | M102713 | MODIFIED NOTES, ADDED "...WITH SMOBC" | 01/16/06 | GT | IL |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR BK276 CASE STYLE, "hm" PIN CONNECTION



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|-------------|----------|
| DIMENSIONS ARE IN INCHES | DRAWN MMG | 10/30/02 |
| TOLERANCES ON: | CHECKED AV | 11/14/02 |
| 2 PL DECIMALS ± | APPROVED HY | 11/15/02 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, hm, BK276, JSPQW-100, TB-212


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|-------|------------|-------------|---------------|
| A | 15542 | 98-PL-098 | A |
| FILE: | 98PL098 | SCALE: 5:1 | SHEET: 1 OF 1 |

Evaluation Board and Circuit




TB-212



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |