



CERAMIC


# High Pass Filter

## HFCN-5500D+

50Ω 6000 to 11500 MHz

### THE BIG DEAL

- Small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Hermetically sealed
- LTCC construction
- Low cost
- Protected by US Patent 7,760,485



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

### APPLICATIONS

- Sub-harmonic rejection
- Transmitters/receivers

### ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Stop Band	Rejection Loss	4000	—	30	dB
		4500	20	—	
	Freq. Cut-Off	5500	—	3.0	dB
		VSWR	4000-4500	—	
Pass Band	Insertion Loss	6000-11500	—	2.0	dB
		6600-10000	—	1.5	
	VSWR	5600-11000	—	1.5	:1

1. DC Resistance to ground is 100 Mohms min.


2. Measured on Mini-Circuits Characterization Test Board TB-285.

### MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-55°C to +100°C
Storage temperature	-55°C to +100°C
RF Power Input <sup>3</sup>	7W max.at 25°C
Max. DC Voltage at pins 1&3	25 VDC

3. Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

### TYPICAL FREQUENCY RESPONSE



### FUNCTIONAL SCHEMATIC



REV. C  
ECO-012367  
HFCN-5500D+  
RAV/CP/AM  
220308






### PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4,5,6

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-285  
SUGGESTED PCB LAYOUT (PL-158)



**NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350 WITH DIELECTRIC THICKNESS:  $.020 \pm .0015$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

### OUTLINE DRAWING



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

### OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F	
.126	.063	.035	.024	.022	.011	
3.20	1.60	0.89	0.61	0.56	0.28	
G	H	J	K			wt
.039	.024	.042	.123			grams
0.99	0.61	1.07	3.12			.020

### TAPE & REEL INFORMATION: F75



CERAMIC

# High Pass Filter


## HFCN-5500D+

Mini-Circuits


### TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	63.32	1737.18
500	41.73	868.59
1000	36.12	434.30
3250	44.07	62.05
4000	32.16	45.72
4500	27.90	34.75
5000	26.03	22.29
5500	3.24	2.44
5600	2.05	1.53
6000	1.39	1.53
6600	1.05	1.22
9000	1.09	1.60
10000	0.79	1.24
11500	1.18	1.64
12000	1.71	2.05

#### HFCN-5500D+ INSERTION LOSS



#### HFCN-5500D+ VSWR



#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Ceramic High Pass Filter

# HFCN-5500D+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
10	63.25	74.58	66.64	0.02	0.02	0.06	0.00	0.01	0.00
20	82.10	64.68	68.24	0.01	0.01	0.04	0.03	0.00	0.03
30	64.12	63.95	64.84	0.00	0.01	0.05	0.02	0.00	0.01
40	63.96	62.49	64.53	0.01	0.01	0.06	0.01	0.00	0.01
50	61.64	62.05	61.62	0.02	0.00	0.02	0.01	0.00	0.01
60	60.30	60.18	59.90	0.02	0.00	0.02	0.01	0.00	0.01
70	59.04	59.01	58.89	0.02	0.00	0.01	0.00	0.00	0.00
80	58.00	57.81	57.41	0.01	0.00	0.01	0.00	0.01	0.00
90	56.82	56.63	56.57	0.01	0.00	0.00	0.00	0.00	0.00
100	55.95	55.66	55.70	0.01	0.00	0.01	0.00	0.01	0.00
200	49.89	49.74	49.54	0.00	0.01	0.00	0.00	0.00	0.00
300	46.30	46.26	46.16	0.00	0.00	0.01	0.02	0.01	0.01
400	43.80	43.84	43.75	0.00	0.01	0.02	0.01	0.01	0.02
500	41.91	41.94	41.93	0.00	0.01	0.02	0.02	0.01	0.02
600	40.38	40.44	40.46	0.00	0.02	0.03	0.02	0.02	0.03
700	39.11	39.16	39.21	0.00	0.02	0.04	0.02	0.02	0.03
800	38.10	38.11	38.16	0.01	0.02	0.04	0.03	0.01	0.03
900	37.22	37.20	37.26	0.01	0.04	0.06	0.03	0.02	0.04
1000	36.45	36.41	36.48	0.01	0.03	0.05	0.04	0.02	0.04
1400	34.26	34.25	34.31	0.03	0.08	0.11	0.05	0.02	0.05
1500	33.88	33.90	33.93	0.02	0.07	0.10	0.06	0.01	0.05
2000	33.11	33.23	33.19	0.06	0.12	0.15	0.05	0.04	0.07
2400	33.88	34.12	34.06	0.10	0.16	0.17	0.01	0.08	0.12
2500	34.36	34.64	34.57	0.10	0.16	0.18	0.00	0.09	0.13
3000	39.51	40.62	40.27	0.15	0.23	0.24	0.07	0.17	0.19
3400	52.76	50.95	54.92	0.22	0.28	0.30	0.18	0.23	0.28
3500	44.17	43.29	45.47	0.23	0.29	0.33	0.21	0.25	0.31
4000	29.31	30.05	28.77	0.27	0.37	0.46	0.32	0.37	0.47
4400	26.73	27.02	26.65	0.29	0.43	0.55	0.41	0.50	0.55
4500	26.65	26.98	26.72	0.32	0.48	0.60	0.43	0.54	0.59
5000	34.00	31.34	29.73	0.48	0.70	0.89	0.71	0.93	1.08
5400	7.92	7.34	6.85	2.12	2.69	3.26	2.05	2.80	3.45
5500	4.64	4.22	3.96	3.96	5.03	5.92	3.72	4.97	6.02
5600	2.54	2.33	2.29	7.36	9.40	10.74	7.00	9.13	10.71
6000	0.71	0.92	1.06	16.49	16.82	17.35	16.55	17.03	17.58
6400	0.51	0.69	0.83	15.99	17.90	19.18	16.53	18.78	20.56
6500	0.46	0.64	0.78	18.01	19.78	21.05	18.70	20.98	22.83
6600	0.43	0.62	0.77	20.79	22.38	23.38	21.90	24.01	25.16
7000	0.36	0.58	0.74	20.87	21.33	21.84	22.08	21.19	19.93
7400	0.47	0.67	0.84	14.14	14.98	15.63	14.51	15.08	14.91
7500	0.50	0.71	0.89	13.36	14.14	14.71	13.87	14.38	14.31
8000	0.53	0.79	1.01	11.45	11.70	11.82	12.30	12.57	12.54
8400	0.53	0.80	1.01	11.28	11.26	11.30	12.21	12.49	12.78
8500	0.51	0.79	1.03	11.21	11.24	11.29	12.16	12.57	12.95
9000	0.40	0.69	0.93	12.90	12.44	12.01	13.13	13.82	14.11
9400	0.28	0.61	0.87	16.38	14.77	13.47	15.81	15.81	15.59
9500	0.28	0.59	0.86	17.28	15.63	13.96	16.49	16.58	15.91
10000	0.33	0.69	1.20	21.59	23.71	19.21	20.44	23.03	20.37
10400	0.50	0.62	0.98	30.02	22.83	21.44	22.78	24.35	23.28
10500	0.73	0.69	0.95	39.82	20.15	18.52	21.02	22.02	20.57
11000	0.39	0.66	1.10	15.49	13.43	11.59	14.46	13.33	12.58
11200	0.36	0.71	1.21	12.78	11.72	10.12	12.02	11.30	10.87
11400	0.43	0.73	1.27	10.49	10.26	8.90	9.91	9.61	9.34
11500	0.56	0.86	1.42	9.28	9.54	8.45	9.20	8.79	8.63

REV. X1

HFCN-5500D+

081019

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE




### INPUT RETURN LOSS vs. TEMPERATURE




### OUTPUT RETURN LOSS vs. TEMPERATURE



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm.01$ ; 3 Pl.  $\pm.005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

### Applicable Case Styles

FV1206-1  
FV1206-3

### Applicable Case Styles

FV1206-4  
FV1206-5  
FV1206-6  
FV1206-7  
FV1206-9

### Applicable Case Styles

FV1206-12  
GE0805C-18  
NL1008C-6  
NL1008C-7  
NL1008C-9  
NL1008C-10

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			1000	
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Mini-Circuits ISO 9001 & ISO 14001 Certified

**Mini-Circuits**<sup>®</sup>


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M92199	NEW RELEASE	05/24/04	AV	ABD
A	M99247	ADD GROUND PTH	06/05	RZ	RZ
A	R60782	ADD GROUND PTH	06/05	RZ	RZ
B	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL


SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-1 CASE STYLE, "pr" PIN CONNECTION.



- NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES  
 TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ±  
 FRACTIONS ±

	INITIALS	DATE
DRAWN	AV	05/03/04
CHECKED	IL	05/24/04
APPROVED	ABD	05/24/04



**Mini-Circuits®** 13 Neptune Avenue  
 Brooklyn NY 11235



PL, pr, FV1206-1, HFCN, TB-285

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-158	REV: B
FILE: 98PL158	SCALE: 12:1	SHEET: 1 OF 1	




# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A