

# Power Splitter/Combiner

## JYPQ-160

2 Way-90° 50Ω 105 to 160 MHz



Generic photo used for illustration purposes only  
CASE STYLE: BJ293

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.

Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

SUM PORT	8
PORT 1 (+90°)	1
PORT 2 (0°)	4
GROUND	2,3,6,7
50 OHM TERM EXTERNAL	5

### Outline Drawing




### PCB Land Pattern



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	
.395	.500	--	.100	.230	.100	.100	
10.03	12.70	--	2.54	5.84	2.54	2.54	
H	J	K	L				wt
.047	.065	.065	.425				grams
1.19	1.65	1.65	10.80				0.80

### Demo Board MCL P/N: TB-216 Suggested PCB Layout (PL-100)



- NOTE:**
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT
  - DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- low insertion loss, 0.25 dB typ.
- good isolation, 24 dB typ.

### Applications

- VHF
- signal processing
- modulators
- image rejection mixers




### Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) Avg. of Coupled Outputs ABOVE 3 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
	Typ.	Min.	Typ.	Max.		
f <sub>L</sub> -f <sub>U</sub>					Max.	Max.
105-160	24	17	0.25	0.6	3	1.5


### Typical Performance Data

Frequency (MHz)	Total Loss <sup>1</sup> (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
105.00	3.71	2.70	1.01	30.06	89.85	1.088	1.101	1.097
110.00	3.60	2.80	0.79	29.77	89.92	1.090	1.104	1.101
120.00	3.42	2.98	0.45	28.89	90.09	1.098	1.112	1.110
125.00	3.36	3.04	0.32	28.26	90.15	1.104	1.117	1.116
127.00	3.34	3.07	0.28	28.00	90.22	1.106	1.119	1.118
131.00	3.31	3.11	0.20	27.40	90.29	1.111	1.124	1.124
135.00	3.29	3.13	0.16	26.76	90.36	1.117	1.130	1.131
139.00	3.29	3.16	0.12	26.05	90.49	1.124	1.137	1.138
141.00	3.29	3.16	0.12	25.70	90.54	1.128	1.140	1.142
145.00	3.29	3.18	0.12	24.96	90.68	1.136	1.148	1.151
151.00	3.33	3.17	0.16	23.79	90.89	1.151	1.163	1.166
155.00	3.37	3.16	0.21	22.98	91.12	1.162	1.174	1.178
160.00	3.45	3.13	0.32	21.94	91.37	1.179	1.191	1.195

1. Total Loss = Insertion Loss + 3dB splitter loss.



### electrical schematic



# 2 Way-90° Power Splitter/Combiner

# JYPQ-160

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2	AVG.				S	1	2
50	6.83	1.17	4.00	5.66	89.37	24.05	1.14	1.13	1.16
55	6.27	1.34	3.81	4.93	89.38	23.64	1.15	1.14	1.17
60	5.78	1.52	3.65	4.26	89.41	23.30	1.15	1.14	1.17
65	5.36	1.70	3.53	3.66	89.45	23.03	1.16	1.14	1.18
70	5.01	1.87	3.44	3.14	89.48	22.83	1.16	1.15	1.18
75	4.69	2.04	3.37	2.65	89.54	22.65	1.16	1.15	1.18
80	4.42	2.20	3.31	2.22	89.59	22.51	1.16	1.15	1.18
85	4.19	2.36	3.27	1.83	89.67	22.40	1.16	1.15	1.18
90	3.98	2.51	3.25	1.47	89.73	22.33	1.16	1.14	1.18
95	3.80	2.65	3.23	1.15	89.82	22.27	1.16	1.14	1.18
100	3.64	2.78	3.21	0.86	89.87	22.26	1.16	1.14	1.18
105	3.51	2.90	3.21	0.61	89.98	22.22	1.15	1.14	1.17
110	3.40	3.02	3.21	0.38	90.05	22.19	1.15	1.14	1.17
115	3.30	3.11	3.20	0.19	90.20	22.17	1.15	1.14	1.17
120	3.22	3.20	3.21	0.02	90.30	22.14	1.15	1.14	1.17
125	3.16	3.28	3.22	0.12	90.41	22.12	1.15	1.14	1.17
130	3.11	3.34	3.22	0.23	90.55	22.07	1.15	1.14	1.16
135	3.08	3.39	3.24	0.31	90.66	22.02	1.15	1.14	1.16
140	3.06	3.42	3.24	0.36	90.80	21.95	1.15	1.14	1.16
145	3.05	3.45	3.25	0.40	90.99	21.85	1.15	1.14	1.16
150	3.06	3.45	3.25	0.39	91.13	21.78	1.15	1.14	1.17
155	3.08	3.45	3.26	0.37	91.33	21.67	1.15	1.15	1.17
160	3.12	3.43	3.27	0.31	91.53	21.55	1.16	1.16	1.17
165	3.17	3.39	3.28	0.22	91.75	21.40	1.16	1.16	1.18
170	3.25	3.34	3.29	0.09	92.00	21.24	1.17	1.17	1.18
175	3.35	3.28	3.31	0.07	92.31	21.03	1.18	1.19	1.19
180	3.48	3.20	3.34	0.28	92.60	20.79	1.19	1.20	1.20
185	3.62	3.11	3.36	0.51	93.00	20.52	1.21	1.22	1.21
190	3.81	3.00	3.40	0.81	93.43	20.20	1.23	1.24	1.23
195	4.02	2.88	3.45	1.14	93.96	19.86	1.25	1.26	1.25
200	4.29	2.74	3.51	1.55	94.54	19.47	1.27	1.28	1.27
205	4.61	2.60	3.61	2.01	95.25	19.04	1.30	1.31	1.30
210	5.00	2.45	3.73	2.55	96.16	18.58	1.33	1.34	1.33
215	5.48	2.29	3.88	3.19	97.27	18.07	1.37	1.38	1.36
220	6.06	2.13	4.10	3.93	98.73	17.55	1.41	1.42	1.40

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2  
JYPQ-160  
100623  
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# 2 Way-90° Power Splitter/Combiner

# JYPQ-160

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2	AVG.				S	1	2
50	6.83	1.12	3.97	5.71	89.49	24.71	1.11	1.12	1.13
55	6.26	1.29	3.78	4.97	89.50	24.26	1.12	1.12	1.13
60	5.77	1.47	3.62	4.30	89.51	23.88	1.12	1.12	1.14
65	5.35	1.64	3.49	3.71	89.53	23.53	1.12	1.13	1.14
70	4.99	1.82	3.40	3.17	89.55	23.23	1.13	1.13	1.14
75	4.67	1.99	3.33	2.68	89.59	22.97	1.14	1.14	1.15
80	4.40	2.15	3.28	2.25	89.62	22.74	1.14	1.14	1.15
85	4.16	2.31	3.23	1.85	89.67	22.55	1.15	1.14	1.16
90	3.95	2.46	3.21	1.49	89.72	22.43	1.15	1.14	1.16
95	3.77	2.60	3.18	1.17	89.78	22.32	1.15	1.14	1.17
100	3.62	2.73	3.17	0.89	89.85	22.29	1.15	1.14	1.17
105	3.48	2.85	3.16	0.63	89.94	22.26	1.15	1.14	1.17
110	3.37	2.96	3.16	0.41	90.00	22.25	1.15	1.14	1.17
115	3.27	3.05	3.16	0.22	90.16	22.28	1.15	1.14	1.17
120	3.18	3.14	3.16	0.04	90.25	22.31	1.15	1.13	1.16
125	3.11	3.21	3.16	0.10	90.37	22.35	1.14	1.13	1.15
130	3.06	3.28	3.17	0.22	90.49	22.36	1.14	1.13	1.15
135	3.02	3.33	3.17	0.31	90.61	22.35	1.13	1.13	1.14
140	2.99	3.36	3.17	0.37	90.73	22.34	1.13	1.13	1.14
145	2.98	3.38	3.18	0.40	90.86	22.29	1.13	1.13	1.14
150	2.98	3.39	3.19	0.41	90.99	22.21	1.13	1.14	1.13
155	3.01	3.40	3.21	0.39	91.17	22.09	1.13	1.14	1.14
160	3.04	3.37	3.20	0.33	91.32	21.93	1.14	1.15	1.14
165	3.09	3.34	3.21	0.25	91.51	21.74	1.14	1.15	1.15
170	3.16	3.29	3.23	0.13	91.72	21.52	1.15	1.16	1.15
175	3.25	3.23	3.24	0.02	91.98	21.25	1.16	1.18	1.17
180	3.37	3.15	3.26	0.22	92.24	20.95	1.18	1.19	1.18
185	3.51	3.06	3.28	0.45	92.60	20.61	1.20	1.21	1.20
190	3.69	2.95	3.32	0.74	92.99	20.25	1.22	1.23	1.22
195	3.89	2.83	3.36	1.06	93.48	19.86	1.24	1.25	1.24
200	4.15	2.69	3.42	1.46	94.03	19.43	1.27	1.28	1.27
205	4.45	2.55	3.50	1.90	94.69	18.98	1.30	1.31	1.29
210	4.82	2.39	3.61	2.43	95.52	18.50	1.33	1.35	1.33
215	5.28	2.24	3.76	3.04	96.54	17.98	1.37	1.38	1.36
220	5.83	2.07	3.95	3.76	97.87	17.45	1.41	1.42	1.40

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

# 2 Way-90° Power Splitter/Combiner

# JYPQ-160

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2	AVG.				S	1	2
50	6.85	1.20	4.02	5.65	89.28	23.57	1.16	1.15	1.19
55	6.30	1.37	3.84	4.93	89.28	23.18	1.18	1.16	1.20
60	5.82	1.55	3.69	4.27	89.31	22.88	1.19	1.16	1.21
65	5.40	1.72	3.56	3.68	89.37	22.68	1.19	1.16	1.22
70	5.05	1.90	3.48	3.15	89.44	22.54	1.19	1.16	1.22
75	4.73	2.07	3.40	2.66	89.52	22.46	1.19	1.16	1.22
80	4.46	2.23	3.35	2.23	89.58	22.40	1.18	1.15	1.21
85	4.22	2.38	3.30	1.84	89.69	22.38	1.18	1.15	1.21
90	4.01	2.53	3.27	1.48	89.78	22.38	1.17	1.14	1.20
95	3.83	2.67	3.25	1.16	89.87	22.38	1.16	1.14	1.19
100	3.67	2.79	3.23	0.88	89.96	22.39	1.16	1.14	1.18
105	3.54	2.91	3.23	0.63	90.06	22.35	1.15	1.14	1.18
110	3.43	3.03	3.23	0.40	90.13	22.29	1.15	1.13	1.17
115	3.34	3.13	3.24	0.21	90.28	22.23	1.15	1.13	1.17
120	3.26	3.21	3.24	0.05	90.38	22.15	1.15	1.14	1.17
125	3.19	3.29	3.24	0.10	90.49	22.04	1.15	1.14	1.17
130	3.15	3.35	3.25	0.20	90.63	21.92	1.15	1.14	1.17
135	3.12	3.40	3.26	0.28	90.76	21.78	1.16	1.14	1.18
140	3.10	3.44	3.27	0.34	90.89	21.66	1.16	1.14	1.18
145	3.10	3.46	3.28	0.36	91.09	21.53	1.17	1.15	1.19
150	3.12	3.47	3.29	0.35	91.26	21.40	1.17	1.15	1.20
155	3.15	3.47	3.31	0.32	91.50	21.26	1.18	1.16	1.20
160	3.19	3.45	3.32	0.26	91.73	21.14	1.18	1.17	1.21
165	3.25	3.41	3.33	0.16	92.00	20.99	1.19	1.18	1.21
170	3.33	3.36	3.34	0.03	92.29	20.86	1.20	1.19	1.22
175	3.43	3.30	3.37	0.13	92.63	20.68	1.21	1.20	1.22
180	3.56	3.22	3.39	0.34	92.99	20.49	1.22	1.22	1.23
185	3.71	3.13	3.42	0.58	93.41	20.26	1.24	1.23	1.24
190	3.90	3.03	3.47	0.87	93.87	20.00	1.25	1.25	1.25
195	4.12	2.91	3.51	1.21	94.42	19.70	1.27	1.27	1.26
200	4.39	2.77	3.58	1.62	95.07	19.34	1.29	1.29	1.28
205	4.72	2.62	3.67	2.10	95.81	18.93	1.31	1.32	1.30
210	5.13	2.47	3.80	2.66	96.79	18.48	1.34	1.35	1.32
215	5.62	2.32	3.97	3.30	97.99	17.99	1.38	1.38	1.36
220	6.23	2.16	4.20	4.07	99.56	17.48	1.42	1.42	1.39

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2  
JYPQ-160  
100623  
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# 2 Way-90° Power Splitter/Combiner


# JYPQ-160

## Typical Performance Curves


### Total Loss




### Average Total Loss vs. TEMPERATURE




### Amplitude Unbalance vs. TEMPERATURE



### Phase Unbalance vs. TEMPERATURE



### Isolation 1-2 vs. TEMPERATURE



REV. X2  
JYPQ-160  
100623  
Page 1 of 2






IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

## Typical Performance Curves




## Outline Dimensions

BJ293  
BJ398



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
BJ293	.395 (10.03)	.500 (12.70)	-- --	.100 (2.54)	.230 (5.84)	.100 (2.54)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.425 (10.80)	.80
BJ398	.305 (7.75)	.390 (9.91)	-- --	.100 (2.54)	.105 (2.67)	.045 (1.14)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.325 (8.26)	.20

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100,200
		13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Note: Please consult individual model data sheet to determine device per reel availability.



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified




THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82549	NEW RELEASE	11/15/02	MMG	HY
A	M102713	MODIFIED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

**SUGGESTED MOUNTING CONFIGURATION  
FOR BJ293 CASE STYLE, "kx" PIN CONNECTION.**



- NOTES:**
- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



SOLID BLUE DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 HATCHED DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES  
 TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ±  
 FRACTIONS ±

	INITIALS	DATE
DRAWN	MMG	11/05/02
CHECKED	AV	11/14/02
APPROVED	HY	11/15/02



**Mini-Circuits®**

13 Neptune Avenue  
 Brooklyn NY 11235


**PL, kx, BJ293, JYPQ, TB-216**

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-100	A
FILE:	98PL100	SCALE: 6:1	SHEET: 1 OF 1

# Evaluation Board and Circuit




TB-216



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215