

# Ceramic Low Pass Filter

## LFCG-1800+

50Ω DC to 1800 MHz



Generic photo used for illustration purposes only  
CASE STYLE: GE0805C-2

### The Big Deal

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W

### Product Overview

Mini-Circuits' LFCG-1800+ is an LTCC low pass filter with a passband from DC to 1800 MHz, supporting a variety of applications. This model provides 1.1 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

### Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 10 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Excellent power handling, 5.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Low Pass Filter

50Ω DC to 1800 MHz

## LFCG-1800+



Generic photo used for illustration purposes only  
CASE STYLE: GE0805C-2

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Features

- Low loss, 1.1 dB typical
- High rejection 50 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (2.0 mm x 1.25 mm)
- Temperature stable
- LTCC construction

### Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications

### Functional Schematic



### Electrical Specifications<sup>1,2</sup> at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	DC-F1	DC-1800	—	1.1	2.2	dB
	Freq. Cut-Off	F2	2030	—	3.0	—	dB
	Return Loss	DC-F1	DC-1800	—	21	—	dB
Stop Band	Rejection Loss	F3-F4	2450-2900	20	40	—	dB
		F4-F5	2900-7000	35	47	—	dB
		F5-F6	7000-10000	—	35	—	dB

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2 Measured on Mini-Circuits Characterization Test Board TB-799+

### Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	5.5W max. @25°C

\*Passband rating, derate linearly to 1W at 125°C ambient  
Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.11	39.81
100	0.15	33.47
1000	0.47	18.17
1400	0.66	21.62
1800	1.26	18.06
2020	3.09	9.64
2030	3.34	9.02
2250	20.08	2.33
2325	30.51	2.01
2450	42.94	1.67
2700	49.22	1.15
3000	55.92	0.78
3700	62.21	0.43
4000	56.80	0.36
5800	54.89	0.21
6000	50.50	0.24
7000	49.20	0.37
8500	39.96	0.47
9300	38.45	0.33
10000	34.38	0.32

### Typical Frequency Response



#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

## Product Marking: LG

**Demo Board MCL P/N: TB-799+**  
**Suggested PCB Layout (PL-429)**




### NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.010" \pm .001"$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

## Outline Drawing



## Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

*Note: Please refer to case style drawing for details*

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

Typical Performance Data






FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.10	0.12	0.14	36.26	38.10	35.39	37.11	38.56	35.90
50	0.11	0.13	0.16	39.74	37.54	36.13	39.26	37.14	35.74
100	0.13	0.15	0.18	36.53	34.85	33.89	35.22	33.67	32.76
250	0.17	0.21	0.25	30.21	31.11	31.82	28.08	28.22	28.21
400	0.20	0.25	0.31	27.56	28.57	29.77	24.66	24.63	24.67
550	0.24	0.30	0.36	24.69	25.50	26.36	22.06	21.97	21.93
700	0.28	0.35	0.43	22.16	22.82	23.43	20.01	19.98	19.96
1000	0.38	0.47	0.57	19.00	19.33	19.65	18.12	18.09	18.04
1200	0.46	0.56	0.67	18.66	18.99	19.34	18.52	18.58	18.58
1400	0.54	0.65	0.79	20.88	21.29	21.78	21.11	21.25	21.26
1460	0.57	0.70	0.85	22.29	22.78	23.34	22.29	22.42	22.38
1650	0.74	0.90	1.10	27.14	26.63	26.24	23.14	22.41	21.70
1740	0.89	1.07	1.30	23.52	23.13	22.93	20.41	19.74	19.10
1750	0.91	1.10	1.33	23.10	22.76	22.61	20.12	19.47	18.85
1800	1.01	1.22	1.48	21.36	21.27	21.39	18.81	18.25	17.68
2020	2.45	3.05	3.88	13.18	12.12	10.93	10.67	9.69	8.68
2030	2.64	3.30	4.21	12.32	11.22	10.05	10.04	9.06	8.10
2250	17.41	19.86	22.64	1.85	1.86	1.94	2.17	2.30	2.52
2325	26.94	30.18	33.91	1.26	1.35	1.49	1.78	1.98	2.23
2450	44.46	43.03	42.13	0.84	0.97	1.14	1.42	1.62	1.87
2700	47.17	48.93	51.06	0.49	0.63	0.81	0.93	1.09	1.27
2900	61.97	59.82	58.25	0.36	0.50	0.68	0.68	0.81	0.96
3000	56.37	55.95	55.76	0.31	0.46	0.63	0.59	0.71	0.83
3250	57.35	58.22	59.36	0.23	0.37	0.53	0.43	0.53	0.62
3400	63.61	66.00	68.02	0.20	0.33	0.49	0.37	0.46	0.54
3550	76.31	72.67	69.15	0.18	0.30	0.45	0.32	0.40	0.47
3700	63.52	62.29	61.60	0.16	0.28	0.41	0.28	0.36	0.43
3850	59.57	58.95	58.65	0.14	0.26	0.38	0.25	0.32	0.39
4000	57.31	57.04	56.74	0.13	0.24	0.35	0.23	0.30	0.37
4150	56.40	56.31	55.99	0.12	0.22	0.33	0.20	0.27	0.35
4300	55.97	55.91	55.97	0.11	0.20	0.30	0.18	0.26	0.34
4450	56.43	56.42	56.79	0.09	0.19	0.29	0.16	0.24	0.32
4600	56.91	56.98	57.02	0.08	0.18	0.27	0.14	0.22	0.31
4750	58.07	58.20	57.71	0.07	0.16	0.25	0.12	0.21	0.31
4900	58.36	58.55	57.40	0.06	0.15	0.24	0.11	0.20	0.31
5050	57.47	58.47	56.96	0.06	0.15	0.24	0.10	0.19	0.31
5200	56.86	57.82	56.72	0.05	0.14	0.23	0.09	0.19	0.32
5350	55.21	56.32	57.12	0.04	0.13	0.23	0.08	0.18	0.32
5500	55.78	55.24	57.01	0.03	0.13	0.23	0.07	0.18	0.33
5650	53.83	52.89	54.93	0.02	0.13	0.23	0.06	0.19	0.34
5800	53.72	53.22	55.15	0.01	0.12	0.23	0.06	0.19	0.35
5950	53.75	53.95	55.11	0.00	0.11	0.24	0.05	0.18	0.36
6100	53.16	53.04	52.46	0.00	0.11	0.25	0.05	0.19	0.38
6250	51.69	51.59	50.20	0.00	0.12	0.27	0.05	0.20	0.40
6400	50.43	50.44	49.21	0.01	0.12	0.28	0.06	0.21	0.42
6550	49.99	49.66	49.38	0.01	0.12	0.30	0.06	0.22	0.43
6600	50.24	49.47	49.88	0.01	0.12	0.30	0.06	0.22	0.43
6850	48.36	47.78	48.50	0.01	0.14	0.34	0.07	0.24	0.46
7000	46.45	46.87	46.93	0.00	0.15	0.36	0.08	0.25	0.48
7150	45.08	46.05	46.16	0.00	0.16	0.38	0.09	0.26	0.49
7300	44.35	45.34	45.01	0.00	0.17	0.41	0.09	0.26	0.50
7450	44.44	45.48	45.07	0.00	0.17	0.43	0.09	0.26	0.50
7600	43.32	44.12	43.76	0.01	0.19	0.47	0.10	0.27	0.51
7750	42.11	42.20	42.80	0.03	0.21	0.49	0.10	0.28	0.51
7900	41.52	41.47	41.57	0.03	0.22	0.52	0.10	0.28	0.51
8050	40.67	41.14	41.07	0.03	0.22	0.54	0.10	0.27	0.50
8200	40.05	40.73	41.03	0.04	0.25	0.57	0.10	0.27	0.49
9000	39.40	38.95	39.28	0.08	0.31	0.66	0.08	0.25	0.42
9300	37.17	37.46	37.51	0.11	0.33	0.71	0.07	0.22	0.39
10000	35.97	36.32	36.59	0.13	0.34	0.69	0.03	0.19	0.31




## Typical Performance Data

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.23	0.27	0.26
30	0.26	0.29	0.29
80	0.28	0.29	0.30
130	0.28	0.29	0.29
180	0.28	0.29	0.29
230	0.28	0.29	0.29
280	0.28	0.29	0.29
330	0.28	0.29	0.29
380	0.29	0.29	0.29
400	0.29	0.29	0.29
480	0.29	0.29	0.30
500	0.29	0.29	0.30
580	0.30	0.30	0.30
630	0.30	0.30	0.31
680	0.30	0.31	0.31
730	0.31	0.31	0.32
780	0.31	0.32	0.32
830	0.32	0.32	0.33
880	0.32	0.33	0.33
930	0.33	0.33	0.34
980	0.34	0.34	0.35
1000	0.34	0.34	0.35
1080	0.35	0.36	0.37
1130	0.36	0.37	0.38
1180	0.38	0.38	0.39
1230	0.39	0.39	0.40
1280	0.40	0.41	0.42
1330	0.42	0.43	0.44
1400	0.44	0.45	0.46
1430	0.46	0.46	0.48
1480	0.48	0.49	0.50
1530	0.50	0.52	0.53
1580	0.53	0.55	0.56
1630	0.57	0.58	0.60
1680	0.61	0.62	0.65
1700	0.62	0.64	0.67
1750	0.67	0.70	0.72
1770	0.70	0.72	0.75
1780	0.71	0.73	0.76
1790	0.72	0.74	0.77
1800	0.73	0.75	0.79


## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
- Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F114

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified




THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148457	NEW RELEASE	10/14/14	GF	MY

SUGGESTED MOUNTING CONFIGURATION  
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE



NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	10/01/14
TOLERANCES ON:	CHECKED IL	10/14/14
2 PL DECIMALS ±	APPROVED MY	10/14/14
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235



PL, 08FL07, GE0805C-4, TB-799+

 Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-429	OR

FILE:	SCALE:	SHEET:
98PL429	15:1	1 OF 1


# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A