



HIGH DIRECTIVITY


# Monolithic Amplifier Die

# MNA-4A-D+

50Ω 0.5 to 4.5 GHz

## THE BIG DEAL

- Choice of supply voltage, +2.8V to +5V
- Internal DC blocking at RF input and output
- High directivity, 19-32 dB typ.
- Output power, up to +19 dBm typ.



**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance.  
 See our website for methodologies and qualifications

## APPLICATIONS

- Buffer amplifier
- Cellular infrastructure
- Communications satellite
- Defense

SEE ORDERING INFORMATION ON THE LAST PAGE

## PRODUCT OVERVIEW

MNA-4A-D+ is a wideband PHEMT based MMIC amplifier die with high active Directivity. MNA integrates the entire matching network and majority of the bias circuit inside the die, reducing the need for complicated external circuits. This approach makes the MNA amplifier die extremely straightforward to use. This design operates on a single +2.8 to +5V supply, is well matched for 50Ω. [MNA series models are available in Die and packaged form.](#)

## KEY FEATURES

Features	Advantages
Excellent Active Directivity (Isolation- Gain) 19-35 dB	Ideal for use as a buffer amplifier minimizing interaction of adjacent circuits
Integrates DC blocks and RF choke	Minimizes external components, component count and circuit area.
Single +2.8 to +5V operation	Amplifier can be used at low voltage such as +3V or standard +5V. +5V operation results in higher P1dB and OIP3.
Unpackaged die	Enables the user to integrate the amplifier directly into hybrids.

REV. B  
 ECO-015286  
 MNA-4A-D+  
 MCL NY  
 221006





HIGH DIRECTIVITY

# Monolithic Amplifier Die

# MNA-4A-D+

50Ω 0.5 to 4.5 GHz

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C

Parameter	Condition (GHz)	Vs=5V			Vs=2.8V	Units
		Min.	Typ.	Max.	Typ.	
Frequency Range		0.5		4.5	0.5-4.5	GHz
Gain	0.5		16.0		14.2	dB
	1.0		17.8		15.4	
	2.0		17.8		14.9	
	2.5		17.0		14.2	
	3.5		13.9		11.6	
	4.5		9.8		8.1	
Input Return Loss	0.5		5.2		5.5	dB
	1.0		14.6		14.5	
	2.0		31.1		26.9	
	2.5		29.8		30.4	
	3.5		15.6		15.4	
	4.5		7.8		8.0	
Output Return Loss	0.5		12.9		12.1	dB
	1.0		25.9		12.7	
	2.0		15.6		11.2	
	2.5		15.0		11.3	
	3.5		17.7		12.6	
	4.5		16.7		11.8	
Output Power at P1dB	0.5		18.7		10.7	dBm
	1.0		18.6		11.8	
	2.0		17.2		12.0	
	2.5		16.8		12.1	
	3.5		15.2		11.9	
	4.5		13.5		10.8	
Output IP3	0.5		30.9		22.8	dBm
	1.0		30.8		23.5	
	2.0		28.5		23.4	
	2.5		27.9		23.2	
	3.5		26.3		22.4	
	4.5		25.0		21.3	
Noise Figure (dB)	0.5		4.9		5.0	dB
	1.0		4.4		4.5	
	2.0		4.5		4.6	
	2.5		4.5		4.6	
	3.5		4.7		4.9	
	4.5		5.5		5.8	
Directivity (Isolation-Gain)	0.5		31.8		35.3	dB
	1.0		26.2		26.2	
	2.0		19.4		20.5	
	2.5		19.0		19.7	
	3.5		20.8		20.7	
	4.5		23.9		23.5	
DC Current			75.1	94.0	70.6	mA
Device Current Variation vs. Temperature <sup>(2)</sup>			35		17	μA/°C
Device Current Variation vs Voltage			0.001 <sup>(3)</sup>		0.003 <sup>(4)</sup>	mA/mV
Thermal resistance at 85°C (Junction to Lead)			50		50	°C/W

1. Measured on Mini-Circuits characterization test board. Die packaged in 3x3 mm MCLP package and soldered on test board TB-186+

2. (Current at 85°C -Current at -45°C)/130

3. (Current at 5.25V-Current at 3.9V)/1.35

4. (Current at 3.9V-Current at 2.66V)/1.24





HIGH DIRECTIVITY

# Monolithic Amplifier Die

# MNA-4A-D+


50Ω 0.5 to 4.5 GHz

### MAXIMUM RATINGS<sup>1,5</sup>

Parameter	Ratings
Operating Temperature	-40°C to 85°C
DC Voltage	7V at DC1 (DC2 connected to DC1 via 33.2Ω) 1V at RF IN & RF OUT
Power Dissipation	500 mW
Input Power	+13 dBm (continuous operation) +24 dBm (5 minutes max)

5. Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.

### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Description
RF IN	RF input pad.
RF-OUT	RF output pad
DC1 & DC2	DC Supply pad. Connect DC2 to DC1 via 33.2Ω resistor

1. Bond Pad material - Gold
2. Bottom of Die - Gold plated



HIGH DIRECTIVITY

# Monolithic Amplifier Die

# MNA-4A-D+

50Ω 0.5 to 4.5 GHz

## CHARACTERIZATION CIRCUIT




Fig 1. Block Diagram of Test Circuit used for characterization. (Die packaged in 3x3 mm MCLP package and soldered on Mini-Circuits Characterization test board TB-186+) Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Component	Size	Value	Units
R1	0805	33.2	Ω
C1	0402	1000	ρF

## RECOMMENDED APPLICATION CIRCUIT




Fig 2. Test Board includes case, connectors, and components soldered to PCB

Component	Value	Units
R1	33.2	Ω
C1	1000	ρF



HIGH DIRECTIVITY

# Monolithic Amplifier Die

# MNA-4A-D+

50Ω 0.5 to 4.5 GHz

### DIE LAYOUT




Fig 3. Die Layout

### BONDING PAD POSITION

(Dimensions in  $\mu\text{m}$ , Typical)




Fig 4. Bonding Pad Positions

### CRITICAL DIMENSIONS

Parameter	Values
Die Thickness, $\mu\text{m}$	100
Die Width, $\mu\text{m}$	970
Die Length, $\mu\text{m}$	1015
Bond Pad Size (RF In, RF Out, DC), $\mu\text{m}$	80 x 80
Bond Pad Size (Ground pad), $\mu\text{m}$	80 x 340




HIGH DIRECTIVITY

# Monolithic Amplifier Die

MNA-4A-D+

50Ω 0.5 to 4.5 GHz

## ASSEMBLY DIAGRAM




Note: Ground bond wires are optional.

## RECOMMENDED WIRE LENGTH, TYPICAL

Wire	Wire Length (mm)	Wire Loop Height (mm)
RF In, RF Out	1.0	0.15
DC	0.5	0.15
Ground	0.5	0.15

## ASSEMBLY PROCEDURE

- Storage**  
Die should be stored in a dry nitrogen purged desiccators or equivalent.
-  **ESD**  
MMIC PHEMT amplifier Die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
- Die Handling and Attachment**  
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
- Wire Bonding**  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the Die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance.





HIGH DIRECTIVITY

# Monolithic Amplifier Die

**MNA-4A-D+**

50Ω 0.5 to 4.5 GHz

**ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.**

<b>Performance Data</b>	Data Table Swept Graphs S-Parameter (S2P Files) Data Set with and without port extension(.zip file)	
<b>Case Style</b>	Die	
<b>Die Ordering and packaging information</b>	Quantity, Package Small, Gel - Pak: 5,10,50,100 KGD* Medium†, Partial wafer: KGD*<1480 Large†, Full Wafer †Available upon request contact sales representative Refer to <a href="#">AN-60-067</a>	Model No. MNA-4A-DG+ MNA-4A-DP+ MNA-4A-DF+
<b>Environmental Ratings</b>	ENV-80	

\*Known Good Die ('KGD') means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical performance specified by Mini-Circuits.

**ESD RATING\*\***

Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\*Tested in \_x\_ xxL MCLP Package

**NOTES**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



*Typical Performance Data*

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.9V, Id = 74.76 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
400	14.00	45.65	3.19	9.61	8.65	1.33	27.25	16.03	5.39
500	15.41	49.95	5.29	13.13	17.76	1.24	27.98	16.84	5.48
600	16.10	50.16	7.33	15.89	19.98	1.16	27.95	16.97	4.86
700	16.49	48.49	9.23	17.74	17.20	1.10	28.17	16.98	4.67
800	16.74	46.14	11.04	18.50	13.40	1.06	28.08	16.99	4.53
1000	17.02	44.07	14.44	18.42	10.70	1.02	27.92	17.07	4.46
1100	17.10	42.78	16.18	17.95	9.24	1.01	28.16	17.02	4.48
1200	17.16	41.94	17.91	17.46	8.38	1.00	28.14	17.02	4.50
1300	17.21	40.90	19.74	17.15	7.45	0.99	27.98	17.00	4.49
1400	17.25	39.97	21.45	16.62	6.67	0.98	27.74	16.81	4.41
1500	17.25	39.44	23.55	16.22	6.28	0.98	27.86	16.85	4.41
1600	17.25	38.80	25.65	15.86	5.84	0.97	27.63	16.79	4.47
1700	17.23	38.49	28.27	15.69	5.66	0.97	27.53	16.63	4.42
1800	17.20	38.22	31.99	15.45	5.50	0.96	27.26	16.56	4.52
1900	17.15	37.29	33.04	15.05	4.97	0.96	27.24	16.38	4.42
2000	17.08	36.97	36.46	14.93	4.82	0.96	27.23	16.46	4.49
2100	16.97	36.70	37.80	14.67	4.73	0.96	27.06	16.30	4.42
2200	16.89	36.72	38.37	14.52	4.78	0.95	27.07	16.32	4.45
2300	16.75	36.19	38.90	14.33	4.57	0.95	26.85	16.08	4.46
2400	16.60	35.84	38.16	14.39	4.46	0.95	26.71	15.97	4.53
2500	16.47	35.65	40.22	14.19	4.43	0.95	26.61	15.83	4.48
2600	16.23	35.61	38.50	14.12	4.53	0.95	26.47	15.70	4.48
2700	16.08	34.84	37.20	14.28	4.23	0.95	26.43	15.81	4.52
2800	15.77	35.44	31.78	14.34	4.68	0.95	26.26	15.47	4.53
2900	15.54	35.15	29.12	14.39	4.65	0.95	26.02	15.39	4.55
3000	15.26	34.71	25.90	14.96	4.58	0.96	25.98	15.08	4.59
3100	14.99	34.45	23.70	14.85	4.57	0.96	26.03	15.24	4.59
3200	14.67	34.73	21.66	14.65	4.87	0.96	25.42	14.86	4.58
3300	14.40	34.22	19.92	15.27	4.74	0.97	25.13	14.85	4.60
3400	14.10	34.03	18.62	15.20	4.79	0.97	25.24	14.67	4.65
3500	13.76	34.03	17.10	15.33	4.95	0.98	25.23	14.43	4.73
3600	13.36	34.26	15.78	15.17	5.28	0.99	25.00	14.38	4.81
3700	13.08	33.67	14.56	15.46	5.07	1.00	24.84	14.15	4.85
3800	12.76	33.20	13.91	15.26	4.95	1.00	24.72	14.00	4.88
3900	12.29	33.65	12.66	15.18	5.41	1.01	24.49	13.81	4.99
4000	12.03	33.70	11.87	15.46	5.55	1.03	24.52	13.77	5.02
4100	11.55	33.61	11.03	15.16	5.71	1.04	24.43	13.55	5.14
4200	11.14	33.90	10.08	15.01	6.06	1.06	24.20	13.28	5.29
4300	10.87	32.50	9.69	14.33	5.25	1.06	24.02	13.13	5.34
4400	10.60	33.71	8.96	14.92	6.10	1.08	24.06	12.95	5.42
4500	10.24	32.74	8.59	14.28	5.60	1.09	23.82	12.81	5.51
4600	9.90	32.15	8.17	13.84	5.34	1.09	23.82	12.83	5.61
4700	9.51	32.18	7.57	13.68	5.46	1.11	23.42	12.60	5.78
4800	9.18	33.24	7.21	13.78	6.28	1.13	23.38	12.42	5.85
4900	8.85	32.32	6.83	13.32	5.74	1.14	23.19	12.29	6.00
5000	8.52	33.14	6.53	13.49	6.43	1.16	23.21	12.23	6.12
5100	8.10	33.20	6.20	13.37	6.62	1.17	22.98	12.10	6.32
5200	7.77	32.33	5.96	13.21	6.12	1.18	22.82	11.79	6.46
5300	7.39	32.54	5.69	13.21	6.41	1.20	22.53	11.44	6.65
5400	6.85	32.55	5.55	13.38	6.77	1.21	22.57	11.25	6.93
5500	6.31	32.81	5.35	13.71	7.30	1.22	21.94	10.99	7.10





## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.8V, Id = 71.01 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
400	12.93	47.94	3.36	9.69	13.37	1.31	21.59	9.98	5.48
500	14.17	51.04	5.48	12.20	23.40	1.21	22.63	10.98	5.63
600	14.75	49.40	7.53	13.22	21.11	1.12	22.82	11.23	4.95
700	15.06	47.55	9.41	13.41	17.74	1.07	23.23	11.37	4.76
800	15.24	44.59	11.16	13.22	12.87	1.03	23.28	11.48	4.59
1000	15.42	42.40	14.41	12.74	10.17	0.98	23.33	11.80	4.56
1100	15.46	41.47	16.01	12.48	9.18	0.97	23.63	11.78	4.59
1200	15.49	40.62	17.57	12.26	8.35	0.96	23.63	11.83	4.61
1300	15.49	39.79	19.18	12.14	7.62	0.95	23.58	11.82	4.56
1400	15.49	39.00	20.64	11.92	6.96	0.94	23.48	11.75	4.47
1500	15.47	38.55	22.33	11.78	6.64	0.94	23.54	11.86	4.47
1600	15.43	37.93	23.98	11.65	6.21	0.93	23.45	11.81	4.53
1700	15.38	37.37	25.75	11.62	5.87	0.93	23.46	11.84	4.49
1800	15.32	37.17	27.85	11.58	5.78	0.93	23.31	11.86	4.65
1900	15.25	36.37	28.91	11.41	5.31	0.92	23.42	11.82	4.50
2000	15.17	36.08	30.73	11.43	5.19	0.92	23.47	11.96	4.60
2100	15.05	35.54	32.10	11.34	4.94	0.92	23.34	11.93	4.52
2200	14.95	35.70	34.45	11.34	5.09	0.92	23.33	11.87	4.56
2300	14.81	35.35	34.09	11.27	4.97	0.92	23.27	11.91	4.60
2400	14.66	34.77	34.45	11.36	4.74	0.92	23.19	11.89	4.46
2500	14.53	34.63	33.88	11.33	4.73	0.92	23.23	12.05	4.59
2600	14.32	34.59	31.51	11.31	4.82	0.92	23.26	11.96	4.57
2700	14.17	33.63	31.62	11.46	4.41	0.92	23.18	12.11	4.62
2800	13.90	34.27	27.60	11.52	4.88	0.92	23.07	11.93	4.63
2900	13.69	33.92	25.78	11.58	4.81	0.92	22.96	11.98	4.70
3000	13.44	33.44	23.64	11.95	4.70	0.93	23.00	11.91	4.69
3100	13.20	33.12	22.06	11.90	4.64	0.93	23.06	12.05	4.71
3200	12.92	33.40	20.29	11.80	4.93	0.94	22.52	11.86	4.71
3300	12.68	32.88	18.95	12.16	4.78	0.94	22.28	11.94	4.73
3400	12.40	32.58	17.73	12.17	4.75	0.95	22.45	11.91	4.75
3500	12.10	32.59	16.48	12.23	4.89	0.95	22.55	11.78	4.85
3600	11.73	32.93	15.30	12.16	5.26	0.96	22.28	11.73	4.91
3700	11.48	32.45	14.17	12.30	5.09	0.97	22.18	11.65	4.99
3800	11.19	32.10	13.55	12.20	5.02	0.97	22.01	11.69	5.05
3900	10.76	32.39	12.41	12.17	5.38	0.99	21.90	11.42	5.12
4000	10.52	32.37	11.66	12.33	5.46	1.00	21.93	11.44	5.19
4100	10.10	32.37	10.89	12.19	5.65	1.01	21.94	11.26	5.28
4200	9.71	32.42	9.98	12.06	5.82	1.02	21.73	11.06	5.40
4300	9.45	31.21	9.58	11.57	5.13	1.02	21.57	10.93	5.48
4400	9.20	32.14	8.91	11.89	5.77	1.05	21.63	10.86	5.56
4500	8.86	31.41	8.53	11.49	5.42	1.05	21.40	10.79	5.60
4600	8.55	30.85	8.12	11.17	5.17	1.05	21.39	10.60	5.71
4700	8.18	30.89	7.54	11.07	5.28	1.07	21.00	10.39	5.91
4800	7.88	31.89	7.17	11.13	6.01	1.09	21.04	10.33	5.98
4900	7.56	31.00	6.82	10.77	5.50	1.09	20.82	10.39	6.14
5000	7.25	31.67	6.53	10.91	6.06	1.11	20.91	10.24	6.23
5100	6.87	31.68	6.21	10.80	6.19	1.12	20.62	10.12	6.43
5200	6.56	30.75	5.96	10.67	5.67	1.13	20.47	9.80	6.62
5300	6.20	30.79	5.69	10.70	5.82	1.14	20.20	9.62	6.70
5400	5.67	31.11	5.56	10.86	6.36	1.16	20.31	9.50	7.09
5500	5.15	31.30	5.37	11.18	6.81	1.18	19.51	9.22	7.25

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)








Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 76.11 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
400	14.44	44.40	3.11	9.30	6.88	1.33	29.87	17.91	5.37
500	15.95	48.39	5.20	13.00	13.76	1.24	30.92	18.74	5.42
600	16.72	50.02	7.25	16.56	18.30	1.16	31.20	19.03	4.85
700	17.16	50.00	9.17	20.22	19.07	1.11	31.22	19.05	4.66
800	17.46	47.17	10.99	23.82	14.02	1.08	31.29	19.05	4.54
1000	17.81	45.37	14.50	27.56	11.50	1.03	30.84	18.89	4.44
1100	17.92	43.54	16.32	26.14	9.32	1.02	30.81	18.78	4.49
1200	18.02	42.60	18.15	24.19	8.34	1.01	30.97	18.82	4.48
1300	18.09	41.87	20.10	23.00	7.64	1.00	30.64	18.65	4.49
1400	18.16	40.79	21.94	21.54	6.72	0.99	30.10	18.36	4.40
1500	18.19	40.11	24.19	20.37	6.19	0.99	30.12	18.34	4.38
1600	18.21	39.61	26.28	19.50	5.84	0.98	30.05	18.34	4.43
1700	18.22	39.52	28.87	18.83	5.76	0.98	29.59	18.00	4.40
1800	18.20	38.98	31.75	18.20	5.43	0.98	29.49	17.95	4.48
1900	18.17	38.16	31.93	17.61	4.95	0.97	29.28	17.63	4.42
2000	18.12	37.77	32.48	17.12	4.76	0.97	29.08	17.62	4.46
2100	18.01	37.45	32.14	16.75	4.63	0.97	28.80	17.52	4.44
2200	17.94	37.42	30.90	16.28	4.64	0.97	28.84	17.53	4.43
2300	17.80	37.29	32.21	16.06	4.65	0.97	28.55	17.22	4.44
2400	17.64	36.61	32.55	16.06	4.38	0.96	28.34	17.15	4.43
2500	17.50	36.54	34.42	15.68	4.41	0.96	27.98	16.85	4.52
2600	17.24	36.72	38.63	15.76	4.63	0.96	28.04	16.80	4.45
2700	17.07	35.65	37.72	15.81	4.19	0.96	28.00	16.85	4.49
2800	16.74	36.56	35.52	16.03	4.83	0.97	27.73	16.50	4.46
2900	16.48	36.11	31.39	16.13	4.72	0.97	27.47	16.39	4.53
3000	16.18	35.90	27.17	16.73	4.79	0.97	27.37	16.09	4.58
3100	15.87	35.47	24.32	16.77	4.71	0.97	27.40	16.12	4.57
3200	15.52	36.03	21.75	16.57	5.20	0.98	26.82	15.74	4.59
3300	15.22	35.27	19.92	17.42	4.94	0.98	26.55	15.82	4.58
3400	14.88	35.05	18.48	17.33	4.98	0.99	26.59	15.57	4.61
3500	14.51	35.05	16.85	17.66	5.17	0.99	26.46	15.31	4.68
3600	14.08	35.15	15.48	17.49	5.45	1.00	26.34	15.22	4.74
3700	13.76	34.83	14.21	17.91	5.40	1.01	26.12	15.07	4.80
3800	13.43	34.27	13.53	17.67	5.23	1.02	26.11	14.91	4.86
3900	12.92	34.89	12.28	17.79	5.86	1.03	25.76	14.57	4.92
4000	12.64	34.61	11.53	18.06	5.80	1.04	25.83	14.50	4.99
4100	12.13	34.58	10.68	17.69	6.02	1.06	25.74	14.31	5.12
4200	11.68	34.83	9.75	17.49	6.37	1.08	25.45	14.08	5.21
4300	11.39	33.44	9.36	16.64	5.54	1.08	25.33	13.93	5.29
4400	11.08	34.95	8.63	17.49	6.68	1.11	25.18	13.79	5.38
4500	10.70	33.85	8.26	16.61	6.05	1.11	25.02	13.67	5.49
4600	10.34	33.38	7.84	16.15	5.86	1.13	25.08	13.60	5.56
4700	9.93	33.31	7.25	15.96	5.93	1.15	24.67	13.42	5.72
4800	9.58	34.30	6.93	16.04	6.78	1.16	24.59	13.17	5.81
4900	9.22	33.57	6.56	15.50	6.34	1.18	24.42	13.17	5.97
5000	8.87	34.49	6.27	15.66	7.20	1.19	24.33	12.89	6.12
5100	8.42	34.30	5.95	15.58	7.23	1.21	24.13	12.89	6.31
5200	8.07	33.51	5.72	15.37	6.75	1.22	23.98	12.48	6.50
5300	7.68	33.75	5.45	15.29	7.08	1.24	23.72	12.31	6.66
5400	7.13	33.61	5.31	15.45	7.34	1.25	23.60	11.93	6.84
5500	6.59	33.98	5.12	15.78	8.00	1.26	23.22	11.80	7.11

## Typical Performance Curves



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	