

# Voltage Controlled Oscillator **MOS-1797-119+**

50Ω    1618 to 1797 MHz

## The Big Deal:

- Good Harmonic Suppression
- Low Phase Noise
- Robust design and construction
- Small size .375" x .375" x .131"



CASE STYLE: CZ682

## Product Overview:

The MOS-1797-119+ is a Voltage Controlled Oscillator, designed to operate from 1618 to 1797 MHz for radio applications. The MOS-1797-119+ is packaged in a metal case (size of .375" x .375" x .131") to shield against unwanted signals and noise.

## Key Features

Feature	Advantages
Linear Tuning Sensitivity Ratio: 1.07:1 typ.	Optimal for loop filter design.
Good Harmonic Suppression, -20dBc typ.	Provides clear signals suitable for systems requiring high spectral purity.
Low Phase Noise: -98 dBc/Hz typ at 10kHz offset	Low phase noise improves system EVM (Error Vector Magnitude).
Good Pushing, 2 MHz/V typ.	Provides increased immunity against noisy DC lines and improves output frequency stability vs. variations in supply voltage.
Robust design and construction	Each internal component of the MOS-1797-119+ is bonded to the substrate, providing better immunity to microphonics, reduced phase hit, and decreased tombstoning risk during subsequent reflow operations.
Small size, .375" x .375 x .131"	The small size enables the MOS-1797-119+ to be used in compact designs.

# Voltage Controlled Oscillator

## MOS-1797-119+

Linear Tuning 1618 to 1797 MHz

### Features

- low phase noise, -98 dBc/Hz typ. @ 10kHz offset
- linear tuning characteristics
- low harmonics, -20 dBc typ.
- low pushing, 2 MHz/V typ.
- aqueous washable

### Applications

- wireless communications
- radio



CASE STYLE: CZ682

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)		HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER				
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)		SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.	Typ.	Typ.			Max.	Typ.	Max.	Vcc	Current (mA)
									Min.	Max.													
MOS-1797-119+	1618	1797	+2.5	-70	-98	-121	-141	1	4	88 - 94	20	90	-90	-20	-10	2.5	2	5	33				

### Pin Connections

RF OUT	5
VCC	3
V-TUNE	1
GROUND	2,4,6,7,8

### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	6V
All specifications	50 ohm system


Permanent damage may occur if any of these limits are exceeded.

### Tape & Reel: F60


7" Reels with 10, 20, 50, 100 devices  
13" Reels with 200, 500, 1000 devices

### Environmental Ratings: ENV65T2

### Outline Drawing



### Demo Board MCL P/N: TB-128 Suggested PCB Layout (PL-023)



### Outline Dimensions (inch/mm)







A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	wt.
.375	.375	.131	.188	.035	.033	.154	.050	.425	.183	.060	.425	.028	.154	.060	grams
9.52	9.52	3.33	4.77	0.89	0.84	3.91	1.27	10.80	4.65	1.52	10.80	0.71	3.91	1.52	.60

# Performance Data & Curves\*

# MOS-1797-119+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			I <sub>cc</sub> (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 1708 MHz (dBc/Hz)
		-40°C	+25°C	+85°C	-40°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	121.91	1490.7	1475.9	1463.0	3.04	2.46	1.30	25.49	-19.4	-35.0	-45.5	3.78	2.31	-70.55	-96.6	-117.9	-138.2	1.0	-69.75
0.50	100.38	1547.7	1534.2	1521.4	3.72	3.29	2.66	25.86	-15.6	-31.6	-44.7	4.04	1.37	-69.35	-97.7	-120.1	-140.2	3.1	-84.84
0.75	95.92	1572.5	1559.3	1547.0	3.88	3.40	2.72	25.88	-15.7	-30.7	-45.6	3.35	2.18	-70.60	-98.8	-121.0	-140.9	4.9	-90.26
1.00	92.40	1596.2	1583.3	1571.0	3.87	3.51	2.81	25.86	-15.7	-30.6	-48.0	2.86	2.91	-70.20	-98.9	-121.1	-141.2	6.2	-93.25
1.25	88.97	1618.7	1606.4	1594.4	3.74	3.33	2.75	25.89	-15.5	-29.7	-50.3	2.38	2.13	-70.30	-98.8	-121.4	-141.5	7.8	-96.06
1.50	89.47	1640.8	1628.6	1617.0	3.67	3.17	2.53	25.91	-16.2	-29.6	-54.6	2.00	1.60	-72.07	-99.6	-121.5	-141.6	10.0	-98.42
1.75	91.31	1663.4	1651.0	1639.2	3.53	3.06	2.43	25.91	-17.3	-29.8	-61.5	1.63	2.32	-72.81	-99.1	-121.5	-141.7	19.7	-106.11
2.00	92.93	1686.7	1673.8	1661.5	3.26	2.94	2.38	25.90	-19.5	-29.3	-67.7	1.27	2.15	-70.78	-98.7	-121.4	-141.7	39.4	-113.06
2.36	91.15	1720.2	1707.2	1694.1	2.80	2.64	2.28	25.91	-22.6	-29.2	-62.4	0.88	1.79	-69.75	-98.4	-121.7	-142.0	62.7	-117.48
2.50	90.07	1733.0	1720.1	1706.9	2.70	2.48	2.20	25.92	-23.9	-28.9	-59.9	0.77	2.28	-69.54	-98.5	-121.9	-142.2	79.0	-119.66
2.75	91.92	1756.1	1742.6	1729.3	2.74	2.43	2.06	25.93	-26.0	-28.1	-58.5	0.73	2.27	-70.30	-98.6	-121.1	-141.7	100.0	-121.66
3.00	92.83	1779.5	1765.6	1751.7	2.74	2.52	2.12	25.91	-27.7	-28.9	-57.5	0.80	2.05	-69.80	-97.7	-121.4	-142.1	158.5	-126.13
3.25	92.02	1802.8	1788.8	1774.7	2.70	2.51	2.18	25.91	-28.7	-30.1	-58.5	1.01	2.54	-67.76	-97.7	-121.5	-141.9	199.9	-128.23
3.50	89.78	1825.7	1811.8	1797.7	2.63	2.45	2.16	25.91	-28.7	-30.3	-58.3	1.37	2.63	-68.93	-97.8	-121.1	-141.6	252.1	-130.32
3.75	86.86	1847.9	1834.2	1820.4	2.60	2.36	2.08	25.93	-29.8	-30.8	-57.6	1.80	1.80	-68.65	-97.2	-121.2	-141.9	317.9	-132.39
4.00	86.05	1869.8	1855.9	1842.4	2.71	2.38	2.02	25.91	-31.0	-30.5	-59.2	2.35	1.89	-68.69	-97.1	-120.9	-141.4	400.9	-134.48
4.25	83.19	1891.3	1877.4	1863.9	2.69	2.47	2.10	25.90	-30.5	-30.3	-58.0	2.89	2.53	-66.94	-95.9	-120.5	-141.2	505.5	-136.58
4.50	78.41	1911.8	1898.2	1885.0	2.65	2.44	2.12	25.89	-31.3	-30.6	-58.1	3.40	2.24	-66.93	-96.3	-120.3	-141.0	637.4	-138.61
4.75	73.65	1931.2	1917.8	1905.0	2.58	2.40	2.07	25.89	-30.9	-30.6	-56.6	3.84	2.32	-66.43	-95.7	-120.3	-141.0	803.8	-140.59
5.00	67.47	1949.2	1936.3	1923.6	2.51	2.31	2.03	25.89	-30.4	-31.5	-56.3	4.16	2.78	-66.07	-96.1	-120.4	-141.0	1000.0	-141.98

\*at 25°C unless mentioned otherwise



## Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Voltage Controlled Oscillator

# MOS-1797-119+

## Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (kHz)	PHASE NOISE (dBc/Hz)
		-40°C	+25°C	+85°C	-40°C	+25°C	+85°C	F2	F3	F4			
0.00	121.9	1490.7	1475.9	1463.0	3.0	2.5	1.3	-19.4	-35.0	-45.5	3.8	1	-70
0.25	111.2	1520.6	1506.4	1493.2	3.6	3.1	2.3	-16.4	-33.2	-43.6	4.3	10	-98
0.50	100.4	1547.7	1534.2	1521.4	3.7	3.3	2.7	-15.6	-31.6	-44.7	4.0	100	-121
0.75	95.9	1572.5	1559.3	1547.0	3.9	3.4	2.7	-15.7	-30.7	-45.6	3.4	1000	-141
1.00	92.4	1596.2	1583.3	1571.0	3.9	3.5	2.8	-15.7	-30.6	-48.0	2.9		
1.25	89.0	1618.7	1606.4	1594.4	3.7	3.3	2.8	-15.5	-29.7	-50.3	2.4		
1.50	89.5	1640.8	1628.6	1617.0	3.7	3.2	2.5	-16.2	-29.6	-54.6	2.0		
1.75	91.3	1663.4	1651.0	1639.2	3.5	3.1	2.4	-17.3	-29.8	-61.5	1.6		
2.00	92.9	1686.7	1673.8	1661.5	3.3	2.9	2.4	-19.5	-29.3	-67.7	1.3		
2.36	91.1	1720.2	1707.2	1694.1	2.8	2.6	2.3	-22.6	-29.2	-62.4	0.9		
2.50	90.1	1733.0	1720.1	1706.9	2.7	2.5	2.2	-23.9	-28.9	-59.9	0.8		
2.75	91.9	1756.1	1742.6	1729.3	2.7	2.4	2.1	-26.0	-28.1	-58.5	0.7		
3.00	92.8	1779.5	1765.6	1751.7	2.7	2.5	2.1	-27.7	-28.9	-57.5	0.8		
3.25	92.0	1802.8	1788.8	1774.7	2.7	2.5	2.2	-28.7	-30.1	-58.5	1.0		
3.50	89.8	1825.7	1811.8	1797.7	2.6	2.5	2.2	-28.7	-30.3	-58.3	1.4		
3.75	86.9	1847.9	1834.2	1820.4	2.6	2.4	2.1	-29.8	-30.8	-57.6	1.8		
4.00	86.0	1869.8	1855.9	1842.4	2.7	2.4	2.0	-31.0	-30.5	-59.2	2.4		
4.25	83.2	1891.3	1877.4	1863.9	2.7	2.5	2.1	-30.5	-30.3	-58.0	2.9		
4.50	78.4	1911.8	1898.2	1885.0	2.7	2.4	2.1	-31.3	-30.6	-58.1	3.4		
4.75	73.6	1931.2	1917.8	1905.0	2.6	2.4	2.1	-30.9	-30.6	-56.6	3.8		
5.00	67.5	1949.2	1936.3	1923.6	2.5	2.3	2.0	-30.4	-31.5	-56.3	4.2		
5.25	62.1	1965.9	1953.1	1941.0	2.5	2.2	2.0	-31.4	-31.7	-55.9	4.4		
5.50	57.4	1981.5	1968.7	1956.7	2.6	2.2	1.9	-31.1	-32.7	-54.8	4.5		
5.75	52.6	1995.9	1983.0	1971.2	2.6	2.3	1.9	-31.4	-32.9	-53.4	4.5		
6.00	52.6	2008.7	1996.1	1984.3	2.6	2.3	2.0	-31.4	-33.8	-53.7	4.4		

**Notes**






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCULStore/terms.jsp](http://www.minicircuits.com/MCULStore/terms.jsp)



# Voltage Controlled Oscillator

# MOS-1797-119+


## Typical Performance Data




**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)


### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm 0.002$



CASE #	A	B	C	D	E	F	G	H	J	K
CZ682	.375 (9.52)	.375 (9.52)	.131 (3.33)	.188 (4.77)	.035 (0.89)	.033 (0.84)	.154 (3.91)	.050 (1.27)	.425 (10.80)	.183 (4.65)

CASE #	L	M	N	P	Q	WT. GRAM
CZ682	.060 (1.52)	.425 (10.80)	.028 (0.71)	.154 (3.91)	.060 (1.52)	.60

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .010$

### Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate  
For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F60



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
				500
				1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M76040	NEW RELEASE (FROM RAVON)	03/01	DK	HH
A	M82575	UPDATED DRAWING	08/08/02	GF	MM
B	M101142	ADDED NOTE 2 & TB-128 TO DESCRIPTION	10/10/05	MMG	MM
C	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR CZ682 CASE STYLE, "my" PIN CONNECTION



- NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAV)	03/22/01
	CHECKED	DE (RAV)	03/27/01
	APPROVED	HH (RAV)	03/27/01

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


PL, my, CZ682, MOS, TB-128

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.  
 ASHEETA1.DWG REV:A DATE:01/12/95


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-023	REV: C
FILE: 98PL023	SCALE: 5:1	SHEET: 1 OF 1	



# Evaluation Board and Circuit




TB-128



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=4.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215