

Voltage Controlled Oscillator **MOS-1797-119+**

50Ω 1618 to 1797 MHz

The Big Deal:

- Good Harmonic Suppression
- Low Phase Noise
- Robust design and construction
- Small size .375" x .375" x .131"



CASE STYLE: CZ682

Product Overview:

The MOS-1797-119+ is a Voltage Controlled Oscillator, designed to operate from 1618 to 1797 MHz for radio applications. The MOS-1797-119+ is packaged in a metal case (size of .375" x .375" x .131") to shield against unwanted signals and noise.

Key Features

| Feature | Advantages |
|--|--|
| Linear Tuning Sensitivity Ratio: 1.07:1 typ. | Optimal for loop filter design. |
| Good Harmonic Suppression, -20dBc typ. | Provides clear signals suitable for systems requiring high spectral purity. |
| Low Phase Noise: -98 dBc/Hz typ at 10kHz offset | Low phase noise improves system EVM (Error Vector Magnitude). |
| Good Pushing, 2 MHz/V typ. | Provides increased immunity against noisy DC lines and improves output frequency stability vs. variations in supply voltage. |
| Robust design and construction | Each internal component of the MOS-1797-119+ is bonded to the substrate, providing better immunity to microphonics, reduced phase hit, and decreased tombstoning risk during subsequent reflow operations. |
| Small size, .375" x .375 x .131" | The small size enables the MOS-1797-119+ to be used in compact designs. |

Voltage Controlled Oscillator

MOS-1797-119+

Linear Tuning 1618 to 1797 MHz

Features

- low phase noise, -98 dBc/Hz typ. @ 10kHz offset
- linear tuning characteristics
- low harmonics, -20 dBc typ.
- low pushing, 2 MHz/V typ.
- aqueous washable

Applications

- wireless communications
- radio



CASE STYLE: CZ682

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

| MODEL NO. | FREQ. (MHz) | | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies, kHz | | | | TUNING | | | | | NON HARMONIC SPURIOUS (dBc) | | HARMONICS (dBc) | | PULLING pk-pk @12 dB (MHz) | PUSHING (MHz/V) | DC OPERATING POWER | | | | |
|---------------|-------------|------|--------------------|---|-----|------|------|--------|-------------------|---------|-----------------------|---------------|---------------------------------|------|-----------------|------|----------------------------|-----------------|--------------------|------|------|-----|--------------|
| | Min. | Max. | | Typ. | 1 | 10 | 100 | 1000 | VOLTAGE RANGE (V) | | SENSI- TIVITY (MHz/V) | PORT CAP (pF) | 3 dB MODULATION BANDWIDTH (MHz) | Typ. | Typ. | Typ. | | | Max. | Typ. | Max. | Vcc | Current (mA) |
| | | | | | | | | | Min. | Max. | | | | | | | | | | | | | |
| MOS-1797-119+ | 1618 | 1797 | +2.5 | -70 | -98 | -121 | -141 | 1 | 4 | 88 - 94 | 20 | 90 | -90 | -20 | -10 | 2.5 | 2 | 5 | 33 | | | | |

Pin Connections

| | |
|--------|-----------|
| RF OUT | 5 |
| VCC | 3 |
| V-TUNE | 1 |
| GROUND | 2,4,6,7,8 |

Maximum Ratings

| | |
|--------------------------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc) | 7V |
| Absolute Max. Tuning Voltage (Vtune) | 6V |
| All specifications | 50 ohm system |


Permanent damage may occur if any of these limits are exceeded.

Tape & Reel: F60


7" Reels with 10, 20, 50, 100 devices
13" Reels with 200, 500, 1000 devices

Environmental Ratings: ENV65T2

Outline Drawing



Demo Board MCL P/N: TB-128 Suggested PCB Layout (PL-023)



NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Dimensions (inch/mm)







| A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | wt. |
|------|------|------|------|------|------|------|------|-------|------|------|-------|------|------|------|-------|
| .375 | .375 | .131 | .188 | .035 | .033 | .154 | .050 | .425 | .183 | .060 | .425 | .028 | .154 | .060 | grams |
| 9.52 | 9.52 | 3.33 | 4.77 | 0.89 | 0.84 | 3.91 | 1.27 | 10.80 | 4.65 | 1.52 | 10.80 | 0.71 | 3.91 | 1.52 | .60 |

Performance Data & Curves*

MOS-1797-119+

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) | | | POWER OUTPUT (dBm) | | | I _{cc} (mA) | HARMONICS (dBc) | | | FREQ. PUSH (MHz/V) | FREQ. PULL (MHz) | PHASE NOISE (dBc/Hz) at offsets | | | | FREQ OFFSET (kHz) | PHASE NOISE at 1708 MHz (dBc/Hz) |
|--------|-------------------|-----------------|--------|--------|--------------------|-------|-------|----------------------|-----------------|-------|-------|--------------------|------------------|---------------------------------|-------|--------|--------|-------------------|----------------------------------|
| | | -40°C | +25°C | +85°C | -40°C | +25°C | +85°C | | F2 | F3 | F4 | | | 1kHz | 10kHz | 100kHz | 1MHz | | |
| 0.00 | 121.91 | 1490.7 | 1475.9 | 1463.0 | 3.04 | 2.46 | 1.30 | 25.49 | -19.4 | -35.0 | -45.5 | 3.78 | 2.31 | -70.55 | -96.6 | -117.9 | -138.2 | 1.0 | -69.75 |
| 0.50 | 100.38 | 1547.7 | 1534.2 | 1521.4 | 3.72 | 3.29 | 2.66 | 25.86 | -15.6 | -31.6 | -44.7 | 4.04 | 1.37 | -69.35 | -97.7 | -120.1 | -140.2 | 3.1 | -84.84 |
| 0.75 | 95.92 | 1572.5 | 1559.3 | 1547.0 | 3.88 | 3.40 | 2.72 | 25.88 | -15.7 | -30.7 | -45.6 | 3.35 | 2.18 | -70.60 | -98.8 | -121.0 | -140.9 | 4.9 | -90.26 |
| 1.00 | 92.40 | 1596.2 | 1583.3 | 1571.0 | 3.87 | 3.51 | 2.81 | 25.86 | -15.7 | -30.6 | -48.0 | 2.86 | 2.91 | -70.20 | -98.9 | -121.1 | -141.2 | 6.2 | -93.25 |
| 1.25 | 88.97 | 1618.7 | 1606.4 | 1594.4 | 3.74 | 3.33 | 2.75 | 25.89 | -15.5 | -29.7 | -50.3 | 2.38 | 2.13 | -70.30 | -98.8 | -121.4 | -141.5 | 7.8 | -96.06 |
| 1.50 | 89.47 | 1640.8 | 1628.6 | 1617.0 | 3.67 | 3.17 | 2.53 | 25.91 | -16.2 | -29.6 | -54.6 | 2.00 | 1.60 | -72.07 | -99.6 | -121.5 | -141.6 | 10.0 | -98.42 |
| 1.75 | 91.31 | 1663.4 | 1651.0 | 1639.2 | 3.53 | 3.06 | 2.43 | 25.91 | -17.3 | -29.8 | -61.5 | 1.63 | 2.32 | -72.81 | -99.1 | -121.5 | -141.7 | 19.7 | -106.11 |
| 2.00 | 92.93 | 1686.7 | 1673.8 | 1661.5 | 3.26 | 2.94 | 2.38 | 25.90 | -19.5 | -29.3 | -67.7 | 1.27 | 2.15 | -70.78 | -98.7 | -121.4 | -141.7 | 39.4 | -113.06 |
| 2.36 | 91.15 | 1720.2 | 1707.2 | 1694.1 | 2.80 | 2.64 | 2.28 | 25.91 | -22.6 | -29.2 | -62.4 | 0.88 | 1.79 | -69.75 | -98.4 | -121.7 | -142.0 | 62.7 | -117.48 |
| 2.50 | 90.07 | 1733.0 | 1720.1 | 1706.9 | 2.70 | 2.48 | 2.20 | 25.92 | -23.9 | -28.9 | -59.9 | 0.77 | 2.28 | -69.54 | -98.5 | -121.9 | -142.2 | 79.0 | -119.66 |
| 2.75 | 91.92 | 1756.1 | 1742.6 | 1729.3 | 2.74 | 2.43 | 2.06 | 25.93 | -26.0 | -28.1 | -58.5 | 0.73 | 2.27 | -70.30 | -98.6 | -121.1 | -141.7 | 100.0 | -121.66 |
| 3.00 | 92.83 | 1779.5 | 1765.6 | 1751.7 | 2.74 | 2.52 | 2.12 | 25.91 | -27.7 | -28.9 | -57.5 | 0.80 | 2.05 | -69.80 | -97.7 | -121.4 | -142.1 | 158.5 | -126.13 |
| 3.25 | 92.02 | 1802.8 | 1788.8 | 1774.7 | 2.70 | 2.51 | 2.18 | 25.91 | -28.7 | -30.1 | -58.5 | 1.01 | 2.54 | -67.76 | -97.7 | -121.5 | -141.9 | 199.9 | -128.23 |
| 3.50 | 89.78 | 1825.7 | 1811.8 | 1797.7 | 2.63 | 2.45 | 2.16 | 25.91 | -28.7 | -30.3 | -58.3 | 1.37 | 2.63 | -68.93 | -97.8 | -121.1 | -141.6 | 252.1 | -130.32 |
| 3.75 | 86.86 | 1847.9 | 1834.2 | 1820.4 | 2.60 | 2.36 | 2.08 | 25.93 | -29.8 | -30.8 | -57.6 | 1.80 | 1.80 | -68.65 | -97.2 | -121.2 | -141.9 | 317.9 | -132.39 |
| 4.00 | 86.05 | 1869.8 | 1855.9 | 1842.4 | 2.71 | 2.38 | 2.02 | 25.91 | -31.0 | -30.5 | -59.2 | 2.35 | 1.89 | -68.69 | -97.1 | -120.9 | -141.4 | 400.9 | -134.48 |
| 4.25 | 83.19 | 1891.3 | 1877.4 | 1863.9 | 2.69 | 2.47 | 2.10 | 25.90 | -30.5 | -30.3 | -58.0 | 2.89 | 2.53 | -66.94 | -95.9 | -120.5 | -141.2 | 505.5 | -136.58 |
| 4.50 | 78.41 | 1911.8 | 1898.2 | 1885.0 | 2.65 | 2.44 | 2.12 | 25.89 | -31.3 | -30.6 | -58.1 | 3.40 | 2.24 | -66.93 | -96.3 | -120.3 | -141.0 | 637.4 | -138.61 |
| 4.75 | 73.65 | 1931.2 | 1917.8 | 1905.0 | 2.58 | 2.40 | 2.07 | 25.89 | -30.9 | -30.6 | -56.6 | 3.84 | 2.32 | -66.43 | -95.7 | -120.3 | -141.0 | 803.8 | -140.59 |
| 5.00 | 67.47 | 1949.2 | 1936.3 | 1923.6 | 2.51 | 2.31 | 2.03 | 25.89 | -30.4 | -31.5 | -56.3 | 4.16 | 2.78 | -66.07 | -96.1 | -120.4 | -141.0 | 1000.0 | -141.98 |

*at 25°C unless mentioned otherwise



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Voltage Controlled Oscillator

MOS-1797-119+

Typical Performance Data

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) | | | POWER OUTPUT (dBm) | | | HARMONICS (dBc) | | | FREQ. PUSH (MHz/V) | FREQ OFFSET (kHz) | PHASE NOISE (dBc/Hz) |
|-----------|-------------------------|--------------------|--------|--------|-----------------------|-------|-------|-----------------|-------|-------|--------------------------|-------------------------|----------------------------|
| | | -40°C | +25°C | +85°C | -40°C | +25°C | +85°C | F2 | F3 | F4 | | | |
| 0.00 | 121.9 | 1490.7 | 1475.9 | 1463.0 | 3.0 | 2.5 | 1.3 | -19.4 | -35.0 | -45.5 | 3.8 | 1 | -70 |
| 0.25 | 111.2 | 1520.6 | 1506.4 | 1493.2 | 3.6 | 3.1 | 2.3 | -16.4 | -33.2 | -43.6 | 4.3 | 10 | -98 |
| 0.50 | 100.4 | 1547.7 | 1534.2 | 1521.4 | 3.7 | 3.3 | 2.7 | -15.6 | -31.6 | -44.7 | 4.0 | 100 | -121 |
| 0.75 | 95.9 | 1572.5 | 1559.3 | 1547.0 | 3.9 | 3.4 | 2.7 | -15.7 | -30.7 | -45.6 | 3.4 | 1000 | -141 |
| 1.00 | 92.4 | 1596.2 | 1583.3 | 1571.0 | 3.9 | 3.5 | 2.8 | -15.7 | -30.6 | -48.0 | 2.9 | | |
| 1.25 | 89.0 | 1618.7 | 1606.4 | 1594.4 | 3.7 | 3.3 | 2.8 | -15.5 | -29.7 | -50.3 | 2.4 | | |
| 1.50 | 89.5 | 1640.8 | 1628.6 | 1617.0 | 3.7 | 3.2 | 2.5 | -16.2 | -29.6 | -54.6 | 2.0 | | |
| 1.75 | 91.3 | 1663.4 | 1651.0 | 1639.2 | 3.5 | 3.1 | 2.4 | -17.3 | -29.8 | -61.5 | 1.6 | | |
| 2.00 | 92.9 | 1686.7 | 1673.8 | 1661.5 | 3.3 | 2.9 | 2.4 | -19.5 | -29.3 | -67.7 | 1.3 | | |
| 2.36 | 91.1 | 1720.2 | 1707.2 | 1694.1 | 2.8 | 2.6 | 2.3 | -22.6 | -29.2 | -62.4 | 0.9 | | |
| 2.50 | 90.1 | 1733.0 | 1720.1 | 1706.9 | 2.7 | 2.5 | 2.2 | -23.9 | -28.9 | -59.9 | 0.8 | | |
| 2.75 | 91.9 | 1756.1 | 1742.6 | 1729.3 | 2.7 | 2.4 | 2.1 | -26.0 | -28.1 | -58.5 | 0.7 | | |
| 3.00 | 92.8 | 1779.5 | 1765.6 | 1751.7 | 2.7 | 2.5 | 2.1 | -27.7 | -28.9 | -57.5 | 0.8 | | |
| 3.25 | 92.0 | 1802.8 | 1788.8 | 1774.7 | 2.7 | 2.5 | 2.2 | -28.7 | -30.1 | -58.5 | 1.0 | | |
| 3.50 | 89.8 | 1825.7 | 1811.8 | 1797.7 | 2.6 | 2.5 | 2.2 | -28.7 | -30.3 | -58.3 | 1.4 | | |
| 3.75 | 86.9 | 1847.9 | 1834.2 | 1820.4 | 2.6 | 2.4 | 2.1 | -29.8 | -30.8 | -57.6 | 1.8 | | |
| 4.00 | 86.0 | 1869.8 | 1855.9 | 1842.4 | 2.7 | 2.4 | 2.0 | -31.0 | -30.5 | -59.2 | 2.4 | | |
| 4.25 | 83.2 | 1891.3 | 1877.4 | 1863.9 | 2.7 | 2.5 | 2.1 | -30.5 | -30.3 | -58.0 | 2.9 | | |
| 4.50 | 78.4 | 1911.8 | 1898.2 | 1885.0 | 2.7 | 2.4 | 2.1 | -31.3 | -30.6 | -58.1 | 3.4 | | |
| 4.75 | 73.6 | 1931.2 | 1917.8 | 1905.0 | 2.6 | 2.4 | 2.1 | -30.9 | -30.6 | -56.6 | 3.8 | | |
| 5.00 | 67.5 | 1949.2 | 1936.3 | 1923.6 | 2.5 | 2.3 | 2.0 | -30.4 | -31.5 | -56.3 | 4.2 | | |
| 5.25 | 62.1 | 1965.9 | 1953.1 | 1941.0 | 2.5 | 2.2 | 2.0 | -31.4 | -31.7 | -55.9 | 4.4 | | |
| 5.50 | 57.4 | 1981.5 | 1968.7 | 1956.7 | 2.6 | 2.2 | 1.9 | -31.1 | -32.7 | -54.8 | 4.5 | | |
| 5.75 | 52.6 | 1995.9 | 1983.0 | 1971.2 | 2.6 | 2.3 | 1.9 | -31.4 | -32.9 | -53.4 | 4.5 | | |
| 6.00 | 52.6 | 2008.7 | 1996.1 | 1984.3 | 2.6 | 2.3 | 2.0 | -31.4 | -33.8 | -53.7 | 4.4 | | |

Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCULStore/terms.jsp



Voltage Controlled Oscillator

MOS-1797-119+


Typical Performance Data




Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp


Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$



| CASE # | A | B | C | D | E | F | G | H | J | K |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|----------------|
| CZ682 | .375 (9.52) | .375 (9.52) | .131 (3.33) | .188 (4.77) | .035 (0.89) | .033 (0.84) | .154 (3.91) | .050 (1.27) | .425 (10.80) | .183 (4.65) |

| CASE # | L | M | N | P | Q | WT. GRAM |
|--------|----------------|-----------------|----------------|----------------|----------------|----------|
| CZ682 | .060 (1.52) | .425 (10.80) | .028 (0.71) | .154 (3.91) | .060 (1.52) | .60 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .010$

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate
For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F60



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 24 | 16 | 7 | Small quantity standards (see note) | 10 |
| | | | | 20 |
| | | | | 50 |
| | | | | 100 |
| | | 13 | Standard | 200 |
| | | | | 500 |
| | | | | 1000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|--------------------------------------|----------|-----|------|
| OR | M76040 | NEW RELEASE (FROM RAVON) | 03/01 | DK | HH |
| A | M82575 | UPDATED DRAWING | 08/08/02 | GF | MM |
| B | M101142 | ADDED NOTE 2 & TB-128 TO DESCRIPTION | 10/10/05 | MMG | MM |
| C | M102713 | ADDED "...WITH SMOBC" | 01/12/06 | GF | IL |

SUGGESTED MOUNTING CONFIGURATION FOR CZ682 CASE STYLE, "my" PIN CONNECTION



- NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |
|--|----------|----------|----------|
| DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± | DRAWN | DK (RAV) | 03/22/01 |
| | CHECKED | DE (RAV) | 03/27/01 |
| | APPROVED | HH (RAV) | 03/27/01 |


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, my, CZ682, MOS, TB-128


Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.
 ASHEETA1.DWG REV:A DATE:01/12/95

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|-------|------------|-------------|---------------|
| A | 15542 | 98-PL-023 | C |
| FILE: | 98PL023 | SCALE: 5:1 | SHEET: 1 OF 1 |

Evaluation Board and Circuit




TB-128



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=4.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 20-2000 Hz, 4 times in each of three axes (total 12) | MIL-STD-883, Method 2007.3, Condition A |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |