


Fast Switching - MMIC SPDT RF Switch

MSW2-50+

50Ω DC to 5000 MHz

The Big Deal

- Very fast switching, 5ns rise/fall time typ.
- High isolation, 53 dB typ. at 1 GHz
- High IP3, +54 dBm typ. at 1 GHz



CASE STYLE: DQ1225

Product Overview

Mini-Circuits' MSW2-50+ is a reflective GaAs MESFET SPDT MMIC Switch supporting a wide range of switching applications from DC to 5000 MHz. This model provides high isolation and ultra-fast switching 5ns Rise/Fall time. It is produced using GaAs MESFET process and comes in a tiny 3x3mm QFN package rated MSL1.

Key Features

Feature	Advantages
Wideband, DC to 5000 MHz	One model can be used in many applications, saving component count. Also ideal for wideband applications such as military and instrumentation.
High Isolation, 53 dB at 1000 MHz	High isolation significantly reduces leakage of power to the OFF port.
High linearity, +54 dBm IP3 at 1000 MHz	High linearity minimizes unwanted intermodulation products which are difficult or impossible to filter out in multi-carrier environments or in the presence of strong interfering signals from adjacent circuitry or received by an antenna.
Very fast switching, 5ns typ. rise/fall time	Fast switching makes this model suitable for applications where extremely fast transition between ports is required such as automated switching networks.
Small size, 3x3mm QFN package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.



Fast Switching - MMIC SPDT RF Switch

50Ω DC - 5000 MHz

Reflective

Product Features


- High Isolation, 53 dB typ. at 1 GHz
- Low insertion loss, 0.7 dB typ. at 1 GHz
- High IP3, 54 dBm typ. at 1 GHz
- Fast switching, Rise/fall time, 5ns typ.
- Low current consumption, 6μA typ.

Typical Applications

- Automated switching networks
- Cellular/ PCS infrastructure
- Test instruments
- Military

General Description

Mini-Circuits' MSW2-50+ is a reflective GaAs MESFET SPDT MMIC Switch supporting a wide range of switching applications from DC to 5000 MHz. This model provides high isolation and ultra-fast switching 5ns Rise/Fall time. It is produced using GaAs MESFET process and comes in a tiny 3x3mm QFN package rated MSL1.



Generic photo used for illustration purposes only



MSW2-50+

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Simplified Schematic and Pad Description



Pad Number	Function
8	RF-IN
11	RF-OUT1
5	RF-OUT2
1	Control #1
3	Control #2
2	NO CONNECTION (NC)
4,6,7,9,10,12 & paddle	GROUND (GND)

RF Electrical Specifications¹, DC - 5000 MHz, T_{AMB}=25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units			
Frequency range ⁴		DC		5000	MHz			
Insertion loss ²	0.3 - 100	—	0.5	0.8	dB			
	100 - 1000	—	0.6	1.0				
	1000 - 2000	—	0.8	1.3				
	2000 - 4500	—	1.0	1.7				
	4500 - 5000	—	1.5	2.2				
Isolation between Common port and RF1/RF2 Ports	0.3 - 100	60	87	—	dB			
	100 - 1000	43	57	—				
	1000 - 2000	37	47	—				
	2000 - 4500	26	39	—				
	4500 - 5000	23	30	—				
Isolation between RF1 and RF2 ports	0.3 - 100	70	89	—	dB			
	100 - 1000	49	59	—				
	1000 - 2000	40	48	—				
	2000 - 4500	25	36	—				
	4500 - 5000	21	26	—				
Return loss (ON STATE)	0.3 - 100		27		dB			
	100 - 1000		23					
	1000 - 2000		17					
	2000 - 4500		17					
	4500 - 5000		13					
Input Compression 0.1 dB ³	V _{DD} =-5V	10		15	dBm			
		100		21				
		1000		24				
		5000		23				
		10		16				
	V _{DD} =-8V	100		28				
		1000		30				
		5000		29				
		Input IP3	V _{DD} =-5V	10			34	dBm
				100			57	
1000				54				
5000				44				
10				34				
V _{DD} =-8V	100			56				
	1000			58				
	5000			51				

Notes:

1. Tested on Mini-Circuit's test board TB-971+, using Agilent's N5230A network analyzer (see Characterization Test Circuit, Fig.1).
2. Insertion loss values are deembedded from test board loss.
3. Do not exceed RF input power as shown in Absolute Maximum Rating table.
4. All RF connections must be DC blocked or held at 0V DC.

DC Electrical Specifications

Parameter	Min.	Typ.	Max.	Units
Control voltage Low (V _L)	-0.2		0	V
Control voltage High (V _H)	-8		-5	V
Control Current at V _L		9		μA
Control Current at V _H		75		μA

Switching Specifications

Parameter	Min.	Typ.	Max.	Units
Rise/Fall Time (10 to 90% or 90 to 10% RF)		4		nSec
Switching Time, 50% CTRL to 90/10% RF		7		nSec
Video Feedthrough, (control 0 to -5V, freq.=500 KHz)		21		mV _{P-P}



Absolute Maximum Ratings⁶

Parameter	Ratings
Operating temperature	-40°C to + 85°C
Storage temperature	-65°C to +150°C
Control Voltage	-8.5V
RF Input Power	31dBm

6. Operation of this device above any of these conditions may cause permanent damage.

Truth Table (State of control voltage selects the desired switch state)

Control Voltage #1	Control Voltage #2	RF-IN	
		RF-Out 1	RF-Out 2
0	-5/-8	OFF	ON
-5/-8	0	ON	OFF

ON- low insertion loss state OFF- reflective State

Characterization Test Circuit




Figure 1. Block Diagram of test Circuit used for characterization (DUT soldered on Mini-Circuit's TB-971+)

Test Equipment:

For Insertion loss, Isolation, Return loss and DC current:

Agilent's N5230A Network Analyzer, E3631A power supply. Cblock: Internal to network Analyzer.

For Switching Time and DC Current:

Agilent's 54832B oscilloscope, 81110A pulse generator and E3631 A power supply. Cblock: Mini-Circuits BLK-18-S+

For Input IP3:

Mini-Circuits DC blocks: BLK-18-S+ on all ports, Agilent's E8257D signal generators, 437B power meter, N9020A Signal analyzer and E3631 A power supply.

For Compression:

Mini-Circuits DC blocks: BLK-18-S+ on all ports. ZVE-8G and ZHL-42W amplifier as driver amplifier at RF Common. Agilent's N5230A Network Analyzer, E3631A power supply

Conditions:


Control Voltage = 0 and -5V/-8V

For Insertion loss, isolation and return loss: Pin=0 dBm

For Input IP3: Pin=-5dBm/tone.

For Switching time: RF frequency: 500 MHz at 0 dBm, Control Frequency: 500 KHz and 0 and -5V/-8V.

Product Marking



Marking may contain other features or characters for internal lot control

Recommended Application Circuit




Fig. 2: Evaluation board includes case, connectors and components soldered to PCB.

Additional Detailed Technical Information	
<i>additional information is available on our dash board. To access this information click here</i>	
Performance Data	Data Table
	Swept Graphs
Case Style	DQ1225 <i>Plastic package; Lead finish: Matte tin</i>
Tape & Reel	F66
Standard quantities available on reel	<i>7" reels with 20, 50, 100, 200, 500, 1K, 2K devices</i>
Suggested Layout for PCB Design	PL-545
Evaluation Board	TB-971+
Environmental Ratings	ENV12


ESD Rating

Human Body Model (HBM): Class 1A (250V to <500V) in accordance with ANSI/ESD STM 5.1-2001

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL Test Flow Chart



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

RF FREQ (MHz)	INSERTION LOSS (dB)				RF FREQ (MHz)	ISOLATION (dB)							
	VDD=-5V		VDD=-8V			VDD=-5V		VDD=-8V		VDD=-5V		VDD=-8V	
	RF IN-RF1	RF IN-RF2	RF IN-RF1	RF IN-RF2		RF IN-RF1	RF IN-RF2	RF IN-RF1	RF IN-RF2	RF1-RF2 RF1 (ON)	RF1-RF2 RF1 (OFF)	RF1-RF2 RF1 (ON)	RF1-RF2 RF1 (OFF)
0.3	0.43	0.43	0.43	0.43	0.3	113.66	98.49	95.70	91.27	89.12	92.72	85.97	92.43
2	0.43	0.43	0.42	0.42	2	92.82	93.14	97.98	105.31	96.14	95.72	94.83	92.81
5	0.44	0.44	0.43	0.43	5	93.74	91.30	91.78	95.55	92.00	92.64	86.27	93.53
10	0.46	0.46	0.45	0.45	10	90.94	90.03	89.93	90.04	92.58	92.27	93.48	91.66
50	0.52	0.52	0.49	0.49	50	76.03	75.22	76.13	75.68	79.14	77.87	78.71	78.10
100	0.53	0.54	0.51	0.51	100	69.35	69.97	69.41	69.89	72.90	73.33	72.68	73.18
200	0.56	0.56	0.53	0.54	200	63.87	64.02	63.88	64.07	66.73	66.79	66.60	66.76
300	0.57	0.58	0.54	0.55	300	60.12	60.18	60.08	60.14	63.87	63.76	63.84	63.77
400	0.60	0.60	0.57	0.58	400	58.03	57.99	57.99	57.97	60.92	60.78	60.90	60.79
500	0.62	0.62	0.59	0.60	500	56.06	56.07	56.03	56.04	58.97	58.82	58.97	58.83
600	0.63	0.63	0.61	0.62	600	54.41	54.40	54.40	54.38	57.50	57.27	57.47	57.22
700	0.66	0.66	0.64	0.64	700	53.14	53.12	53.11	53.12	55.91	55.72	55.94	55.75
800	0.68	0.68	0.67	0.66	800	51.99	51.96	51.94	51.96	54.57	54.42	54.59	54.43
900	0.70	0.70	0.69	0.69	900	50.92	50.92	50.89	50.89	53.39	53.24	53.43	53.28
1000	0.73	0.73	0.71	0.71	1000	49.97	49.99	49.96	49.96	52.28	52.14	52.33	52.20
1100	0.75	0.75	0.74	0.74	1100	49.15	49.18	49.12	49.15	51.18	51.09	51.26	51.15
1200	0.78	0.77	0.76	0.76	1200	48.36	48.39	48.32	48.36	50.20	50.11	50.31	50.18
1300	0.80	0.80	0.78	0.78	1300	47.63	47.65	47.57	47.61	49.29	49.18	49.39	49.29
1400	0.82	0.81	0.80	0.80	1400	46.94	47.02	46.90	46.97	48.34	48.29	48.45	48.40
1500	0.84	0.83	0.82	0.81	1500	46.30	46.38	46.26	46.33	47.48	47.43	47.61	47.55
1600	0.86	0.84	0.84	0.82	1600	45.69	45.79	45.66	45.74	46.63	46.57	46.79	46.70
1700	0.88	0.86	0.86	0.84	1700	45.11	45.19	45.05	45.12	45.87	45.77	46.04	45.93
1800	0.89	0.87	0.87	0.85	1800	44.58	44.68	44.47	44.61	45.06	44.95	45.25	45.19
1900	0.91	0.88	0.89	0.86	1900	44.06	44.15	44.00	44.08	44.31	44.19	44.51	44.40
2000	0.92	0.89	0.90	0.87	2000	43.55	43.62	43.50	43.56	43.63	43.47	43.86	43.69
2100	0.93	0.90	0.91	0.88	2100	43.10	43.15	43.05	43.08	42.95	42.73	43.20	42.96
2200	0.94	0.90	0.92	0.88	2200	42.71	42.80	42.64	42.74	42.21	41.99	42.48	42.24
2300	0.95	0.91	0.92	0.88	2300	42.29	42.41	42.22	42.36	41.51	41.29	41.79	41.58
2400	0.96	0.91	0.93	0.89	2400	41.88	42.01	41.82	41.96	40.86	40.64	41.16	40.93
2500	0.96	0.92	0.93	0.90	2500	41.49	41.63	41.44	41.60	40.22	39.98	40.55	40.29
2600	0.97	0.93	0.94	0.91	2600	41.15	41.30	41.11	41.27	39.56	39.31	39.90	39.66
2700	0.97	0.94	0.94	0.91	2700	40.77	40.89	40.74	40.88	38.97	38.73	39.34	39.10
2800	0.97	0.94	0.95	0.92	2800	40.44	40.49	40.43	40.51	38.38	38.12	38.78	38.51
2900	0.97	0.95	0.95	0.93	2900	40.09	40.11	40.11	40.14	37.81	37.55	38.23	37.96
3000	0.98	0.96	0.95	0.93	3000	39.72	39.70	39.78	39.76	37.21	36.96	37.66	37.39
3100	0.98	0.96	0.96	0.94	3100	39.32	39.29	39.39	39.39	36.60	36.39	37.07	36.85
3200	0.99	0.97	0.96	0.94	3200	38.93	38.90	39.03	39.04	35.99	35.85	36.49	36.36
3300	0.99	0.98	0.97	0.95	3300	38.46	38.34	38.61	38.51	35.45	35.31	35.98	35.83
3400	1.00	0.99	0.97	0.96	3400	38.03	37.82	38.21	38.03	34.87	34.75	35.44	35.30
3500	1.01	0.99	0.98	0.97	3500	37.53	37.33	37.77	37.59	34.33	34.20	34.92	34.78
3600	1.02	1.00	0.99	0.98	3600	37.02	36.79	37.31	37.11	33.78	33.66	34.40	34.26
3700	1.03	1.01	1.00	0.98	3700	36.48	36.20	36.81	36.58	33.23	33.11	33.89	33.76
3800	1.04	1.02	1.01	0.99	3800	35.88	35.62	36.30	36.05	32.60	32.53	33.30	33.21
3900	1.05	1.04	1.02	1.01	3900	35.23	35.02	35.69	35.49	32.02	31.95	32.74	32.67
4000	1.07	1.05	1.04	1.02	4000	34.59	34.45	35.11	34.98	31.42	31.34	32.17	32.09
4100	1.09	1.07	1.05	1.04	4100	33.92	33.78	34.50	34.37	30.76	30.69	31.54	31.46
4200	1.11	1.09	1.07	1.05	4200	33.29	33.10	33.93	33.75	30.08	30.03	30.89	30.84
4300	1.14	1.12	1.10	1.07	4300	32.68	32.44	33.37	33.14	29.39	29.37	30.24	30.21
4400	1.17	1.16	1.12	1.10	4400	32.03	31.79	32.77	32.54	28.70	28.68	29.58	29.55
4500	1.21	1.19	1.15	1.13	4500	31.28	31.08	32.08	31.85	28.02	27.99	28.92	28.88
4600	1.26	1.24	1.19	1.17	4600	30.60	30.34	31.43	31.15	27.27	27.26	28.19	28.17
4700	1.32	1.31	1.24	1.23	4700	29.98	29.60	30.85	30.45	26.46	26.51	27.39	27.44
4800	1.39	1.40	1.31	1.30	4800	29.30	28.87	30.21	29.75	25.66	25.76	26.61	26.70
4900	1.48	1.48	1.38	1.37	4900	28.66	28.17	29.59	29.08	24.88	25.02	25.84	25.97
5000	1.58	1.59	1.47	1.46	5000	28.04	27.45	28.99	28.39	24.09	24.26	25.07	25.23
5500	2.34	2.64	2.14	2.42	5500	25.53	23.88	26.61	24.91	20.02	20.86	21.02	21.86
6000	3.38	3.46	3.10	3.19	6000	22.30	20.66	23.39	21.67	16.40	17.06	17.38	18.10

Note:

Control Voltage #1	Control Voltage #2	RF IN	
		RF1	RF2
0	-5/-8	OFF	ON
-5/-8	0	ON	OFF

ON - Low insertion loss state
OFF - Reflective state



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

Typical Performance Data

RF FREQ (MHz)	VSWR (:1)											
	VDD=-5V						VDD=-8V					
	RF IN		RF1		RF2		RF IN		RF1		RF2	
	RF1 (ON)	RF2 (ON)	RF1 (ON)	RF1 (OFF)	RF2 (ON)	RF2 (OFF)	RF1 (ON)	RF2 (ON)	RF1 (ON)	RF1 (OFF)	RF2 (ON)	RF2 (OFF)
0.3	1.10	1.10	1.09	7.20	1.09	7.22	1.10	1.10	1.09	7.22	1.09	7.22
2	1.09	1.10	1.09	7.21	1.09	7.24	1.09	1.09	1.09	7.24	1.09	7.23
5	1.09	1.09	1.09	7.20	1.09	7.23	1.09	1.09	1.08	7.23	1.08	7.23
10	1.09	1.09	1.08	7.19	1.08	7.22	1.08	1.08	1.08	7.22	1.08	7.22
50	1.08	1.08	1.07	7.15	1.07	7.15	1.07	1.07	1.07	7.18	1.07	7.15
100	1.08	1.08	1.07	7.10	1.07	7.08	1.08	1.07	1.07	7.13	1.07	7.08
200	1.10	1.10	1.09	6.99	1.09	6.96	1.09	1.09	1.09	7.01	1.08	6.96
300	1.12	1.12	1.11	6.88	1.11	6.87	1.11	1.11	1.11	6.90	1.10	6.87
400	1.14	1.14	1.13	6.80	1.13	6.81	1.13	1.13	1.13	6.83	1.13	6.81
500	1.17	1.17	1.16	6.72	1.16	6.74	1.16	1.16	1.15	6.74	1.15	6.74
600	1.19	1.19	1.18	6.64	1.18	6.68	1.19	1.19	1.18	6.66	1.17	6.68
700	1.22	1.22	1.21	6.55	1.20	6.59	1.21	1.21	1.20	6.58	1.19	6.59
800	1.25	1.25	1.23	6.47	1.23	6.50	1.24	1.24	1.23	6.49	1.22	6.50
900	1.28	1.27	1.26	6.38	1.26	6.40	1.27	1.26	1.25	6.41	1.25	6.41
1000	1.30	1.30	1.28	6.30	1.28	6.30	1.29	1.28	1.27	6.33	1.27	6.31
1100	1.32	1.32	1.30	6.21	1.30	6.20	1.31	1.30	1.29	6.24	1.29	6.21
1200	1.35	1.34	1.32	6.12	1.32	6.09	1.33	1.32	1.31	6.15	1.31	6.10
1300	1.36	1.35	1.34	6.03	1.33	6.00	1.35	1.34	1.32	6.06	1.32	6.01
1400	1.38	1.36	1.35	5.93	1.34	5.91	1.36	1.34	1.34	5.97	1.33	5.92
1500	1.39	1.36	1.36	5.84	1.34	5.82	1.37	1.35	1.34	5.87	1.33	5.83
1600	1.40	1.36	1.37	5.74	1.34	5.70	1.38	1.34	1.35	5.78	1.33	5.72
1700	1.40	1.36	1.37	5.66	1.34	5.58	1.39	1.34	1.35	5.70	1.32	5.61
1800	1.41	1.36	1.37	5.58	1.34	5.51	1.39	1.34	1.35	5.61	1.32	5.54
1900	1.41	1.36	1.37	5.50	1.33	5.48	1.39	1.34	1.35	5.54	1.31	5.50
2000	1.40	1.35	1.37	5.42	1.32	5.47	1.38	1.33	1.35	5.46	1.30	5.49
2100	1.40	1.34	1.36	5.35	1.30	5.46	1.37	1.32	1.34	5.39	1.28	5.48
2200	1.39	1.33	1.35	5.29	1.28	5.45	1.36	1.31	1.33	5.33	1.26	5.48
2300	1.37	1.32	1.34	5.23	1.26	5.46	1.35	1.29	1.32	5.27	1.24	5.50
2400	1.36	1.31	1.32	5.18	1.24	5.44	1.33	1.28	1.30	5.23	1.22	5.48
2500	1.34	1.30	1.31	5.13	1.22	5.43	1.32	1.27	1.29	5.18	1.20	5.47
2600	1.32	1.29	1.29	5.10	1.21	5.42	1.30	1.26	1.26	5.15	1.19	5.46
2700	1.30	1.28	1.27	5.08	1.20	5.41	1.28	1.25	1.24	5.14	1.18	5.45
2800	1.28	1.27	1.24	5.07	1.18	5.44	1.25	1.24	1.22	5.13	1.16	5.49
2900	1.26	1.26	1.22	5.08	1.16	5.50	1.23	1.23	1.20	5.14	1.14	5.55
3000	1.24	1.25	1.20	5.09	1.15	5.54	1.21	1.22	1.18	5.16	1.12	5.60
3100	1.21	1.23	1.18	5.12	1.13	5.58	1.19	1.20	1.16	5.19	1.10	5.64
3200	1.19	1.21	1.17	5.16	1.12	5.57	1.17	1.18	1.15	5.23	1.09	5.63
3300	1.18	1.20	1.15	5.21	1.11	5.56	1.15	1.17	1.13	5.29	1.09	5.63
3400	1.17	1.19	1.14	5.27	1.11	5.56	1.13	1.16	1.12	5.35	1.08	5.64
3500	1.15	1.18	1.13	5.33	1.10	5.59	1.12	1.15	1.11	5.42	1.07	5.66
3600	1.15	1.17	1.12	5.41	1.09	5.63	1.11	1.14	1.10	5.50	1.07	5.72
3700	1.14	1.16	1.11	5.48	1.08	5.73	1.11	1.13	1.09	5.58	1.06	5.82
3800	1.14	1.15	1.10	5.55	1.07	5.87	1.10	1.12	1.09	5.66	1.04	5.97
3900	1.15	1.16	1.10	5.63	1.06	6.00	1.11	1.12	1.08	5.74	1.03	6.12
4000	1.16	1.16	1.10	5.69	1.06	6.08	1.11	1.12	1.08	5.82	1.03	6.20
4100	1.17	1.17	1.10	5.76	1.07	6.11	1.12	1.13	1.08	5.90	1.03	6.25
4200	1.19	1.20	1.11	5.82	1.10	6.14	1.14	1.15	1.08	5.97	1.06	6.29
4300	1.23	1.24	1.13	5.87	1.13	6.29	1.17	1.18	1.09	6.03	1.09	6.46
4400	1.26	1.29	1.15	5.90	1.18	6.40	1.20	1.23	1.11	6.07	1.13	6.58
4500	1.31	1.34	1.19	5.92	1.24	6.46	1.25	1.27	1.14	6.11	1.18	6.66
4600	1.37	1.40	1.24	5.92	1.31	6.45	1.30	1.33	1.19	6.12	1.25	6.67
4700	1.44	1.49	1.29	5.88	1.41	6.47	1.36	1.41	1.23	6.10	1.34	6.72
4800	1.52	1.59	1.36	5.84	1.50	6.45	1.44	1.50	1.29	6.07	1.43	6.72
4900	1.62	1.70	1.43	5.76	1.60	6.28	1.52	1.60	1.37	6.01	1.52	6.56
5000	1.72	1.82	1.51	5.66	1.71	6.00	1.62	1.71	1.44	5.92	1.62	6.29
5500	2.46	2.77	2.05	4.75	2.42	4.30	2.30	2.59	1.94	5.09	2.30	4.62
6000	3.50	3.62	2.69	3.37	2.86	2.80	3.27	3.38	2.59	3.73	2.77	3.09

Note:

Control Voltage #1	Control Voltage #2	RF IN	
		RF1	RF2
0	-5/-8	OFF	ON
-5/-8	0	ON	OFF

ON - Low insertion loss state
OFF - Reflective state



Typical Performance Data

RF FREQ (MHz)	INPUT IP3 (dBm)				RF FREQ (MHz)	Pin @ 0.1 dB COMPRESSION (dBm)			
	VDD=-5V		VDD=-8V			VDD=-5V		VDD=-8V	
	RF IN-RF1	RF IN-RF2	RF IN-RF1	RF IN-RF2		RF IN-RF1	RF IN-RF2	RF IN-RF1	RF IN-RF2
10	33.43	34.03	33.43	34.05	10	13.92	15.64	15.18	15.33
50	51.37	53.61	50.97	53.07	50	20.75	20.13	24.65	22.62
100	61.87	60.96	62.41	62.31	100	21.49	21.48	27.62	27.74
200	58.57	59.09	64.54	61.38	200	22.78	22.92	28.64	28.65
300	58.08	59.03	60.08	61.93	300	23.23	23.53	28.63	28.64
400	58.43	59.87	63.96	67.61	400	23.53	23.67	28.92	28.93
500	55.20	56.08	57.78	59.42	500	23.58	23.73	28.57	28.58
600	56.32	56.25	65.19	63.68	600	23.65	23.64	28.85	28.86
700	55.51	56.09	58.96	60.41	700	23.64	23.82	30.08	30.06
800	54.40	54.48	58.82	59.14	800	23.69	23.86	29.79	29.78
900	56.86	56.87	62.34	62.07	900	23.69	23.87	29.97	29.97
1000	53.75	53.88	57.17	58.14	1000	24.02	24.20	29.88	29.87
1100	54.94	55.01	63.27	61.15	1100	24.01	24.20	29.90	29.88
1200	54.58	54.99	56.84	57.69	1200	23.87	24.04	29.93	29.93
1300	52.93	53.19	58.18	58.77	1300	24.05	24.25	30.02	30.00
1400	55.44	55.86	60.62	60.65	1400	23.84	24.04	29.88	29.89
1500	53.21	53.36	59.39	60.37	1500	24.15	24.31	29.49	29.49
1600	54.40	54.58	60.42	60.04	1600	23.92	24.12	29.76	29.75
1700	52.99	53.26	57.57	58.97	1700	24.23	24.42	29.62	29.62
1800	52.25	52.38	58.00	58.31	1800	24.02	24.22	29.77	29.76
1900	53.68	53.73	64.47	66.31	1900	24.26	24.43	29.43	29.44
2000	51.55	51.67	57.15	57.79	2000	23.91	24.11	29.77	29.76
2100	53.12	53.09	60.64	59.97	2100	24.32	24.40	29.74	29.73
2200	52.32	52.51	57.76	58.98	2200	24.30	24.50	29.52	29.53
2300	51.39	51.54	58.69	58.50	2300	24.16	24.37	29.53	29.53
2400	51.38	51.59	60.22	62.15	2400	24.29	24.47	29.51	29.51
2500	50.94	51.02	57.43	58.04	2500	24.14	24.23	29.57	29.56
2600	52.36	52.43	64.90	63.42	2600	24.13	24.21	29.38	29.39
2700	50.60	50.75	57.13	58.25	2700	24.32	24.23	29.26	29.26
2800	50.48	50.32	59.89	59.14	2800	24.29	24.33	29.54	29.55
2900	49.87	49.85	55.78	56.41	2900	24.30	24.38	29.38	29.37
3000	50.93	50.71	57.74	57.01	3000	24.26	24.33	29.46	29.47
3100	50.48	50.41	59.93	60.45	3100	24.30	24.23	29.28	29.26
3200	49.48	49.21	56.13	56.64	3200	24.39	24.48	29.41	29.42
3300	50.21	49.95	58.41	59.44	3300	24.17	24.26	29.36	29.35
3400	49.63	49.50	56.15	56.83	3400	24.29	24.37	29.24	29.25
3500	49.01	48.73	56.38	55.59	3500	24.37	24.38	29.21	29.19
3600	49.08	48.83	57.66	58.29	3600	24.02	24.10	29.18	29.21
3700	48.66	48.28	56.90	56.46	3700	24.07	23.96	29.21	29.19
3800	48.91	48.58	58.54	58.96	3800	23.86	23.92	29.13	29.13
3900	48.02	47.64	55.93	55.91	3900	23.77	23.67	29.12	29.11
4000	47.85	47.52	56.86	57.12	4000	23.59	23.65	29.13	29.13
4100	47.23	46.83	54.81	55.03	4100	23.36	23.39	29.11	29.12
4200	47.38	47.09	56.65	56.38	4200	23.34	23.32	28.97	28.93
4300	47.25	47.15	58.60	60.50	4300	23.08	23.11	29.05	29.06
4400	45.82	45.54	52.70	52.23	4400	23.05	23.08	29.05	29.02
4500	47.02	46.95	59.37	60.44	4500	23.08	23.11	28.92	29.18
4600	45.46	45.26	52.88	52.64	4600	22.74	22.87	28.75	29.00
4700	45.44	45.44	55.65	57.29	4700	22.79	22.79	28.75	28.99
4800	44.87	44.86	51.13	51.01	4800	22.62	22.79	28.54	28.79
4900	45.16	45.19	55.14	55.37	4900	22.75	22.90	28.59	28.96
5000	43.95	44.04	50.69	50.90	5000	22.62	22.92	28.57	28.81









Note:

Control Voltage #1	Control Voltage #2	RF IN	
		RF1	RF2
0	-5/-8	OFF	ON
-5/-8	0	ON	OFF

ON - Low insertion loss state
OFF - Reflective state



Typical Performance Curves




Note:


Control Voltage #1	Control Voltage #2	RF IN	
		RF1	RF2
0	-5/-8	OFF	ON
-5/-8	0	ON	OFF

ON - Low insertion loss state
OFF - Reflective state

Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

 **Mini-Circuits**[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M165831	NEW RELEASE	01/24/18	ITG	WILSON P

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12SW03" PIN CODE




NOTES:

- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010 \pm .001$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS \pm 3 PL DECIMALS \pm .005 ANGLES \pm FRACTIONS \pm	DRAWN	ITG 01/23/18
	CHECKED	GF 01/24/18
	APPROVED	WILSON P 01/24/18

 **Mini-Circuits[®]** 13 Neptune Avenue
Brooklyn NY 11235



PL, 12SW03, DQ1225, TB-971+/TB-971A+

 Mini-Circuits[®]
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-545	OR
FILE:	98PL545	SCALE: 10:1	SHEET: 1 OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D