


# Ultra High Dynamic Range Monolithic Amplifier Die

## PHA-202-D+

50Ω 0.3 to 2.7 GHz



### The Big Deal

- Ultra High IP3, +46.1 dBm
- Broadband High Dynamic Range without external Matching Components
- Medium power, 1W
- Excellent return loss over 15 dB

### Product Overview

PHA-202-D+ (RoHS compliant) is a medium power amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PHA-202-D+ has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability.

### Key Features

Feature	Advantages
Broad Band: 0.03 to 2.7 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE
Extremely High IP3 Versus DC power Consumption 46 dBm typical at 1.0 GHz	The PHA-202-D+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 14-23 dB above the P1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"><li>• Driver amplifiers for complex waveform up converter paths</li><li>• Drivers in linearized transmit systems</li><li>• Secondary amplifiers in ultra High Dynamic range receivers</li></ul>
No External Matching Components Required	Unlike competing products, Mini-Circuits PHA-202-D+ provides Input and Output Return Loss of over 15 dB up to 2 GHz without the need for any external matching components




# Ultra High Dynamic Range Monolithic Amplifier Die

## PHA-202-D+

50Ω 0.3 to 2.7 GHz

### Product Features

- High IP3, 46.1 dBm typ. at 1 GHz
- Gain, 17.0 dB typ. at 1 GHz
- High Pout, P1dB 30.4 dBm typ. at 1 GHz
- No external matching components required



### Typical Applications

- Base station infrastructure
- CATV & DBS
- LTE


**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page


### General Description

PHA-202-D+ (RoHS compliant) is a medium power amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PHA-202-D+ has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability.

### Simplified Schematic and Pad description



### Bonding Pad Position



Pad#	Function	Description
1	RF-IN	RF input pad. This pad requires the use of an external DC blocking capacitor chosen for the frequency of operation
4	RF-OUT & DC-IN	RF output pad and bias pad. DC voltage is present on this pad, therefore, a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection.
2,3	GND	Connections to ground. Bottom of die.

Note: 1. Bond Pad material - Gold  
2. Bottom of Die - Gold plated

Dimensions in  $\mu\text{m}$ , Typical

L1	L2	L3	H1	H2	H3	H4	Thickness	Width	Length	RF-IN Bond Pad Size	RF-OUT + DC-IN Bond Pad Size	Ground Bond Pad Size
77.5	436	1325	73	517.5	782.5	1030	100	1325	1030	140 x 70	280 x 65	70 x 170



Electrical Specifications at 25°C, 50 ohms, unless noted

Parameter	Condition (MHz)	Vd=11V <sup>1</sup>			Units
		Min.	Typ.	Max.	
Frequency range		0.03		2.7	GHz
Gain	30		18.3		dB
	500		17.9		
	1000		17.0		
	2000		14.7		
	2700		12.7		
Input return loss	30		21.2		dB
	500		21.7		
	1000		19.5		
	2000		20.3		
	2700		14.9		
Output return loss	30		15.1		dB
	500		16.4		
	1000		19.4		
	2000		22.5		
	2700		9.8		
Reverse isolation	2000		23		dB
Output power @ 1dB compression	30		28.4		dBm
	500		30.2		
	1000		30.4		
	2000		28.1		
	2700		25.7		
Output IP3 <sup>2</sup>	30		51.0		dBm
	500		48.5		
	1000		46.1		
	2000		43.2		
	2700		39.4		
Noise figure	30		3.2		dB
	500		3.3		
	1000		3.5		
	2000		4.4		
	2700		5.4		
Device operating voltage			11		V
Device operating current		—	350	416	mA
Device current variation vs voltage <sup>3</sup>			0.0485		mA/mV
Thermal Resistance, junction-to-ground lead at 85°C stage temp.			16.1		°C/W

1. Measured on Mini-Circuits Characterization test board. Die package in 5x6mm, 8-lead MCLP package and soldered on test board MB018

2. Tested at Pout=16dBm / tone.

3. (Current at 11.5V-current - Current at 10.5V)/1000

Absolute Maximum Ratings<sup>4</sup>

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Junction Temperature	179°C
Power Dissipation	5.8W
Input Power (CW) <sup>1</sup>	+24 dBm (5 minutes max.) +19 dBm (continuous)
DC Voltage on Pad#4 <sup>1</sup>	14V

4 Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

## Characterization Test Circuit




Fig 1. Characterization Circuit


Note: This block diagram is used for characterization. (Die packaged in 5x6mm, 8-lead MCLP package and soldered on Mini-Circuits Characterization test board MB018)

Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 16 dBm/tone at output.

## Assembly Diagram



## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC E-PHEMT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The Die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total Die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic Die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the Die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

<b>Additional Detailed Technical Information</b> <i>additional information is available on our dash board.</i>	
<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
<b>Case Style</b>	Die
<b>Die Ordering and packaging information</b>	Quantity, Package <span style="float: right;">Model No.</span>
	Small, Gel - Pak: 5,10,50,100 KGD* <span style="float: right;">PHA-202-DG+</span> Medium†, Partial wafer: KGD*<1215 <span style="float: right;">PHA-202-DP+</span> Large†, Full Wafer <span style="float: right;">PHA-202-DF+</span>
	†Available upon request contact sales representative
	Refer to <a href="#">AN-60-067</a>
<b>Environmental Ratings</b>	ENV-80

\*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

**ESD Rating\*\***

Human Body Model (HBM): Class 1B (pass 500V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard 5x6mm, 8-lead MCLP package

**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 11V, Id = 348.23 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
30	18.34	23.27	21.98	15.44	1.12	0.67	51.27	28.39	3.07
50	18.26	23.16	22.96	15.54	1.12	0.67	51.70	30.30	2.94
100	18.24	23.10	23.04	15.66	1.12	0.66	51.48	29.68	3.04
150	18.22	23.10	23.17	15.74	1.12	0.67	50.11	29.77	3.09
200	18.18	23.09	22.87	15.84	1.13	0.67	50.24	29.97	3.06
250	18.14	23.11	22.85	15.94	1.13	0.67	50.33	30.23	3.07
300	18.10	23.09	22.53	16.08	1.13	0.68	49.61	30.37	3.12
350	18.05	23.06	22.34	16.25	1.13	0.68	48.97	30.31	3.11
400	17.99	23.04	22.14	16.39	1.14	0.68	48.79	30.20	3.11
450	17.93	23.05	21.87	16.64	1.14	0.69	48.56	30.19	3.14
500	17.87	23.01	21.63	16.83	1.15	0.69	48.45	30.15	3.17
550	17.80	23.02	21.33	17.09	1.15	0.70	47.81	30.41	3.21
600	17.73	23.03	21.12	17.35	1.16	0.71	47.55	30.39	3.24
650	17.65	23.02	20.80	17.68	1.16	0.71	47.18	30.38	3.25
700	17.56	23.01	20.57	18.00	1.17	0.72	46.90	30.34	3.28
750	17.48	23.00	20.33	18.34	1.18	0.72	46.61	30.27	3.31
800	17.39	22.98	20.12	18.71	1.18	0.73	46.35	30.15	3.33
850	17.29	22.99	19.99	19.07	1.19	0.74	46.08	30.40	3.35
900	17.19	22.96	19.72	19.52	1.20	0.74	46.19	30.32	3.39
950	17.09	22.95	19.63	19.96	1.21	0.75	45.71	30.00	3.41
1000	16.99	22.95	19.46	20.52	1.22	0.76	45.95	30.38	3.43
1050	16.89	22.94	19.35	20.97	1.23	0.76	45.35	30.12	3.48
1100	16.78	22.95	19.30	21.55	1.24	0.77	45.45	30.10	3.52
1150	16.67	22.92	19.26	22.15	1.25	0.78	45.12	29.91	3.57
1200	16.56	22.92	19.22	22.79	1.26	0.78	45.24	30.19	3.62
1250	16.45	22.90	19.23	23.54	1.27	0.79	44.97	29.58	3.66
1300	16.33	22.90	19.27	24.29	1.28	0.79	45.07	29.93	3.71
1350	16.22	22.91	19.31	25.22	1.29	0.80	44.98	29.41	3.76
1400	16.11	22.89	19.34	26.20	1.30	0.80	44.65	29.60	3.80
1450	15.99	22.88	19.44	27.15	1.31	0.81	44.93	29.83	3.84
1500	15.87	22.86	19.58	28.23	1.32	0.81	44.59	29.54	3.88
1550	15.76	22.90	19.69	29.41	1.34	0.82	44.61	29.50	3.94
1600	15.64	22.88	19.84	30.36	1.35	0.82	44.25	29.12	3.98
1650	15.52	22.87	20.02	30.97	1.36	0.83	43.97	28.74	4.03
1700	15.41	22.85	20.15	30.86	1.38	0.83	43.44	28.38	4.07
1750	15.29	22.87	20.41	30.07	1.39	0.84	43.67	28.64	4.22
1800	15.17	22.90	20.63	28.83	1.41	0.84	43.48	28.52	4.13
1850	15.06	22.93	20.76	27.45	1.42	0.85	43.85	29.08	4.21
1900	14.94	22.92	20.87	25.87	1.44	0.85	43.23	28.41	4.21
1950	14.82	22.92	21.03	24.46	1.45	0.85	42.96	28.10	4.26
2000	14.70	22.95	21.13	22.86	1.47	0.86	42.96	28.06	4.31
2100	14.45	22.97	21.01	20.49	1.49	0.86	42.71	27.66	4.38
2200	14.20	23.07	20.67	18.42	1.53	0.87	41.85	27.26	4.48
2300	13.95	23.10	20.00	16.53	1.55	0.87	40.95	26.63	4.59
2400	13.69	23.26	19.19	14.83	1.59	0.88	40.49	26.47	4.71
2500	13.41	23.38	18.23	13.30	1.62	0.88	39.26	25.63	4.85
2600	13.11	23.50	17.18	11.86	1.65	0.88	38.72	25.24	5.00
2700	12.78	23.73	16.05	10.53	1.68	0.87	38.98	25.75	5.18

Note: "Test data of Die packaged in industry standard, 5x6mm, 8-lead MCLP package"

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 10.5V, Id = 322.53 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
30	18.32	23.24	21.77	15.52	1.12	0.66	51.15	28.02	3.02
50	18.25	23.12	22.82	15.62	1.12	0.66	51.93	29.82	2.89
100	18.24	23.10	22.85	15.72	1.12	0.66	49.91	29.28	2.99
150	18.21	23.08	22.96	15.80	1.12	0.67	50.26	29.39	3.03
200	18.18	23.06	22.68	15.91	1.12	0.67	50.05	29.51	3.01
250	18.13	23.06	22.65	16.00	1.13	0.67	49.87	29.77	3.01
300	18.09	23.07	22.37	16.15	1.13	0.68	48.57	29.91	3.07
350	18.04	23.06	22.17	16.31	1.13	0.68	48.82	29.85	3.07
400	17.98	23.04	21.98	16.48	1.14	0.68	47.94	29.74	3.07
450	17.92	23.02	21.71	16.68	1.14	0.69	47.63	29.74	3.10
500	17.86	23.02	21.48	16.92	1.15	0.69	47.20	29.75	3.13
550	17.78	23.03	21.21	17.15	1.15	0.70	47.00	30.00	3.15
600	17.72	23.03	20.93	17.46	1.16	0.71	46.64	29.92	3.17
650	17.63	23.00	20.63	17.75	1.16	0.71	46.32	29.92	3.19
700	17.55	23.01	20.48	18.07	1.17	0.72	46.08	29.87	3.23
750	17.46	22.97	20.21	18.44	1.18	0.72	45.57	29.81	3.22
800	17.37	22.99	20.01	18.79	1.19	0.73	45.31	29.77	3.28
850	17.27	22.96	19.87	19.16	1.19	0.74	45.27	29.94	3.29
900	17.17	22.95	19.64	19.62	1.20	0.74	45.09	29.94	3.35
950	17.07	22.95	19.54	20.09	1.21	0.75	44.52	29.55	3.37
1000	16.97	22.94	19.36	20.63	1.22	0.76	44.93	29.90	3.40
1050	16.86	22.92	19.30	21.13	1.23	0.76	44.33	29.73	3.43
1100	16.75	22.94	19.18	21.69	1.24	0.77	44.40	29.64	3.47
1150	16.64	22.92	19.21	22.24	1.25	0.78	44.00	29.45	3.50
1200	16.53	22.91	19.14	22.94	1.26	0.78	44.15	29.73	3.55
1250	16.42	22.92	19.17	23.68	1.27	0.79	43.65	29.22	3.61
1300	16.30	22.88	19.21	24.39	1.28	0.79	43.81	29.55	3.64
1350	16.18	22.93	19.24	25.23	1.30	0.80	43.58	29.05	3.68
1400	16.08	22.89	19.27	26.19	1.30	0.81	43.36	29.22	3.74
1450	15.95	22.87	19.37	27.09	1.31	0.81	43.75	29.43	3.78
1500	15.83	22.84	19.53	27.93	1.32	0.81	43.26	29.14	3.83
1550	15.72	22.87	19.61	28.90	1.34	0.82	43.24	29.10	3.87
1600	15.59	22.88	19.81	29.38	1.36	0.83	42.82	28.74	3.93
1650	15.47	22.92	19.98	29.59	1.37	0.83	42.44	28.37	3.94
1700	15.36	22.88	20.12	29.29	1.38	0.83	41.96	28.02	3.99
1750	15.24	22.90	20.36	28.51	1.40	0.84	42.21	28.27	4.05
1800	15.12	22.89	20.57	27.39	1.41	0.84	41.99	28.15	4.08
1850	15.00	22.91	20.70	26.20	1.43	0.85	42.52	28.68	4.14
1900	14.88	22.90	20.82	24.88	1.44	0.85	41.79	28.03	4.14
1950	14.76	22.91	20.99	23.65	1.45	0.85	41.47	27.73	4.17
2000	14.62	22.94	21.07	21.98	1.47	0.86	41.58	27.68	4.22
2100	14.37	22.96	20.91	19.82	1.50	0.86	41.03	27.28	4.30
2200	14.12	23.05	20.59	17.93	1.53	0.87	40.46	26.97	4.41
2300	13.87	23.13	19.93	16.14	1.56	0.87	39.45	26.25	4.51
2400	13.60	23.21	19.11	14.55	1.59	0.88	39.12	26.08	4.61
2500	13.31	23.34	18.16	13.06	1.62	0.88	37.64	25.34	4.77
2600	13.01	23.51	17.14	11.70	1.66	0.88	37.04	24.86	4.92
2700	12.68	23.73	16.03	10.41	1.69	0.87	37.95	25.36	5.10

Note: "Test data of Die packaged in industry standard, 5x6mm, 8-lead MCLP package"



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 11.5V, Id = 371.94 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
30	18.36	23.27	22.03	15.31	1.12	0.67	50.91	28.70	3.12
50	18.27	23.20	23.17	15.36	1.12	0.67	51.62	30.67	3.00
100	18.26	23.13	23.22	15.61	1.12	0.66	50.36	30.07	3.08
150	18.23	23.10	23.43	15.65	1.12	0.66	51.67	30.09	3.12
200	18.19	23.08	23.09	15.76	1.12	0.67	50.33	30.31	3.10
250	18.15	23.10	23.07	15.86	1.13	0.67	50.51	30.58	3.11
300	18.12	23.09	22.75	16.01	1.13	0.67	49.24	30.72	3.16
350	18.06	23.09	22.49	16.18	1.14	0.68	49.55	30.65	3.16
400	18.01	23.08	22.34	16.34	1.14	0.68	49.10	30.58	3.18
450	17.95	23.06	22.04	16.56	1.14	0.69	48.82	30.52	3.19
500	17.89	23.04	21.83	16.73	1.15	0.69	48.59	30.54	3.22
550	17.82	23.04	21.47	16.99	1.15	0.70	48.10	30.80	3.24
600	17.75	23.06	21.27	17.25	1.16	0.70	48.18	30.72	3.28
650	17.67	23.04	20.92	17.57	1.16	0.71	47.62	30.72	3.30
700	17.59	23.01	20.70	17.89	1.17	0.72	47.30	30.67	3.33
750	17.51	23.02	20.48	18.22	1.18	0.72	47.09	30.60	3.36
800	17.42	22.99	20.22	18.60	1.18	0.73	46.88	30.55	3.37
850	17.32	23.01	20.10	18.92	1.19	0.74	46.80	30.73	3.39
900	17.23	22.97	19.83	19.38	1.20	0.74	46.69	30.73	3.45
950	17.13	22.98	19.73	19.81	1.21	0.75	46.28	30.32	3.47
1000	17.03	22.95	19.58	20.34	1.21	0.75	46.50	30.71	3.52
1050	16.93	22.94	19.44	20.81	1.22	0.76	46.26	30.44	3.54
1100	16.82	22.94	19.40	21.33	1.23	0.77	46.05	30.42	3.57
1150	16.71	22.93	19.36	21.94	1.24	0.77	45.90	30.23	3.62
1200	16.60	22.94	19.35	22.53	1.25	0.78	45.81	30.52	3.68
1250	16.49	22.92	19.32	23.30	1.26	0.78	45.89	29.89	3.72
1300	16.38	22.92	19.36	24.04	1.28	0.79	45.99	30.24	3.76
1350	16.27	22.92	19.39	25.03	1.29	0.80	45.39	29.72	3.81
1400	16.16	22.90	19.45	25.94	1.30	0.80	45.99	29.92	3.87
1450	16.05	22.90	19.53	26.98	1.31	0.81	45.77	30.15	3.91
1500	15.93	22.89	19.63	28.22	1.32	0.81	45.55	29.86	3.95
1550	15.82	22.89	19.80	29.57	1.33	0.82	45.67	29.83	3.99
1600	15.70	22.87	19.94	30.99	1.35	0.82	45.15	29.43	4.08
1650	15.58	22.89	20.12	32.25	1.36	0.83	44.99	29.04	4.10
1700	15.47	22.86	20.28	32.95	1.37	0.83	44.55	28.59	4.12
1750	15.36	22.92	20.52	32.29	1.39	0.83	44.69	28.95	4.16
1800	15.24	22.92	20.72	30.78	1.40	0.84	44.53	28.74	4.22
1850	15.13	22.91	20.90	29.08	1.42	0.84	44.83	29.41	4.29
1900	15.01	22.87	20.94	27.31	1.42	0.84	44.28	28.71	4.29
1950	14.90	22.92	21.10	25.59	1.44	0.85	43.96	28.41	4.33
2000	14.74	23.00	21.15	23.62	1.47	0.86	44.12	28.37	4.36
2100	14.51	22.98	21.04	21.01	1.49	0.86	43.40	27.97	4.45
2200	14.26	23.06	20.67	18.76	1.52	0.87	43.26	27.57	4.55
2300	14.01	23.14	20.01	16.79	1.55	0.87	41.99	26.86	4.67
2400	13.75	23.22	19.20	15.02	1.58	0.88	41.79	26.69	4.77
2500	13.47	23.37	18.24	13.43	1.61	0.88	40.36	25.94	4.93
2600	13.17	23.52	17.19	11.96	1.64	0.87	39.75	25.46	5.10
2700	12.85	23.75	16.07	10.60	1.68	0.87	40.85	25.99	5.27

Note: "Test data of Die packaged in industry standard, 5x6mm, 8-lead MCLP package"



## Typical Performance Curves



Note: "Test data of Die packaged in industry standard, 5x6mm, 8-lead MCLP package"

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	