

Plug-In

Voltage Controlled Oscillator

POS-2120W+

Wideband 1060 to 2120 MHz



CASE STYLE: A06

Features

- octave frequency range
- 3 dB modulation bandwidth, 20 MHz typ.
- low phase noise
- output suitable for LO drive to 7 dBm mixers
- hermetically sealed

Applications

- test instruments-signal generators
- wideband frequency synthesizers
- agile communications systems
- cellular up and down converters

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING				NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @ 12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER		
								VOLTAGE RANGE (V)	SENSITIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)						V _{cc}	Current	
	Min.	Max.		Typ.	1	10	100	1000	Min.	Max.	Typ.		Typ.	Typ.			Typ.	Typ.	Max.
POS-2120W+	1060	2120	+7	-63	-93	-117	-139	0.5	20	25 - 108	35	20	-90	-15	-	20	2	12	28

Pin Connections


RF OUT	2
VCC	1
V-TUNE	8
GROUND	3,4,5,6,7
CASE GROUND	3,4,5,6,7

Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	+13V
Absolute Max. Tuning Voltage (Vtune)	+22V

all specifications: 50 ohm system
Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	wt
.770	.800	.285	.310	.370	.400	.200	.20	.14	.031	grams
19.56	20.32	7.24	7.87	9.40	10.16	5.08	5.08	3.56	0.79	5.2

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Performance Data & Curves*

POS-2120W+


V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 1590 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	62.45	981.4	967.4	954.0	8.68	8.05	7.80	23.18	-10.2	-35.2	-39.9	1.21	10.72	-64.57	-91.2	-113.4	-134.5	1.0	-64.44
2.00	73.31	1113.5	1099.4	1086.9	8.93	7.75	6.98	23.29	-8.7	-29.7	-34.7	0.87	5.49	-65.72	-93.5	-117.2	-139.2	2.5	-77.18
3.00	78.50	1185.1	1172.7	1161.6	8.85	7.47	6.33	23.29	-9.9	-26.2	-31.9	0.79	3.54	-65.91	-94.4	-118.3	-140.6	4.2	-84.29
4.00	89.08	1262.8	1251.2	1241.2	8.81	7.36	6.21	23.28	-11.5	-28.0	-32.2	0.99	4.34	-65.78	-93.9	-118.6	-141.5	7.1	-90.78
5.00	103.98	1353.0	1340.3	1329.4	6.73	6.03	5.71	23.24	-20.2	-25.2	-32.9	1.43	4.23	-66.80	-94.3	-118.6	-140.7	10.0	-94.70
6.00	105.21	1457.1	1444.2	1432.8	6.78	6.04	5.58	23.23	-31.5	-23.9	-29.2	1.15	1.83	-65.08	-94.4	-118.8	-141.5	11.7	-96.43
7.40	99.71	1599.0	1590.3	1582.5	7.03	6.36	5.84	23.23	-27.4	-22.7	-34.9	1.53	3.72	-64.44	-94.7	-118.7	-140.8	23.1	-103.70
8.00	96.11	1658.8	1651.6	1644.9	7.07	6.47	5.98	23.22	-23.6	-21.8	-38.0	2.82	5.22	-64.03	-94.2	-117.9	-139.7	38.8	-108.96
9.00	87.67	1754.4	1747.7	1741.7	7.28	6.69	6.22	23.21	-19.1	-22.1	-41.6	4.23	6.84	-63.54	-93.3	-116.8	-138.5	64.0	-113.87
10.00	76.34	1843.8	1835.3	1828.2	7.48	6.91	6.40	23.19	-18.6	-22.3	-39.6	4.50	3.54	-61.73	-92.4	-116.4	-138.4	89.8	-117.40
11.00	64.10	1923.6	1911.7	1902.8	7.63	7.07	6.60	23.17	-19.7	-23.8	-36.4	3.63	1.20	-60.80	-92.7	-116.8	-139.0	100.0	-118.74
12.00	53.79	1990.0	1975.8	1965.0	7.59	7.20	6.78	23.17	-19.0	-27.3	-36.7	2.24	5.26	-61.71	-92.9	-117.5	-139.8	150.8	-122.44
13.00	41.16	2044.9	2029.6	2016.7	7.74	7.31	6.91	23.17	-18.6	-27.9	-39.2	1.14	11.85	-61.84	-92.5	-116.9	-139.4	177.0	-124.00
14.00	36.06	2089.2	2070.7	2057.8	7.75	7.50	7.17	23.17	-19.4	-27.1	-42.2	0.34	4.03	-62.35	-92.7	-117.2	-139.5	211.6	-125.78
15.00	28.57	2125.6	2106.8	2092.1	7.98	7.54	7.24	23.16	-20.2	-27.0	-43.9	0.25	12.21	-60.24	-91.6	-115.8	-138.0	297.1	-129.11
16.00	22.52	2153.7	2135.4	2121.3	8.00	7.78	7.47	23.18	-19.5	-27.4	-44.8	0.59	6.87	-60.96	-91.8	-116.0	-138.1	348.8	-130.56
17.00	20.28	2179.8	2157.9	2143.4	8.01	7.81	7.60	23.18	-19.9	-28.4	-46.0	0.85	12.18	-63.16	-91.5	-115.6	-137.7	489.7	-133.94
18.00	16.65	2200.3	2178.2	2161.9	8.21	7.84	7.60	23.18	-20.7	-29.3	-47.0	1.16	16.06	-62.13	-89.9	-114.1	-136.1	585.4	-135.67
19.00	13.54	2216.6	2194.8	2179.0	8.30	7.99	7.66	23.20	-20.0	-29.9	-48.0	1.22	17.19	-62.95	-90.7	-114.5	-136.6	964.9	-140.58
20.00	11.06	2230.2	2208.4	2192.9	8.33	8.11	7.85	23.21	-19.9	-31.7	-47.6	1.34	13.66	-59.39	-90.0	-114.3	-136.4	1000.0	-140.83

*at 25°C unless mentioned otherwise


POS-2120W+
Frequency and Tuning Sensitivity




POS-2120W+
Power Output




POS-2120W+
Harmonics Level




POS-2120W+
Frequency Pulling & Pushing (Vcc ± 5%)



POS-2120W+
Phase Noise Vs. Tuning Voltage



POS-2120W+
Phase Noise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Voltage Controlled Oscillator

POS-2120W+

Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (KHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
2.0	65.50	1075.8	1053.3	1034.2	8.68	8.43	7.32	-15.4	-20.1	-37.1	1.69	1	-70
4.0	95.50	1249.7	1224.5	1205.3	9.73	9.22	8.15	-13.9	-35.4	-32.1	2.31	10	-97
6.0	120.90	1486.9	1465.6	1450.0	10.05	9.27	8.27	-6.3	-28.5	-30.5	0.17	100	-117
8.0	97.40	1692.8	1674.7	1660.7	9.64	8.70	7.88	-6.3	-24.8	-44.8	1.14	1000	-137
10.0	64.10	1837.1	1817.8	1803.1	9.01	8.56	8.11	-11.1	-25.1	-35.4	0.63		
12.0	49.00	1942.1	1921.8	1906.6	9.28	8.46	7.90	-20.5	-23.6	-37.8	1.58		
14.0	43.20	2030.6	2009.9	1994.1	8.43	8.05	7.72	-30.2	-23.7	-38.0	2.08		
16.0	42.00	2116.5	2094.2	2077.4	8.78	8.29	7.72	-20.1	-29.7	-38.9	2.35		
18.0	38.80	2197.8	2174.4	2156.5	8.16	8.13	7.72	-17.5	-36.0	-38.5	2.49		
20.0	32.40	2264.7	2242.8	2224.1	8.44	7.78	7.44	-16.2	-43.4	-40.1	2.42		

REV. X1
 POS-2120W+
 070205
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Voltage Controlled Oscillator


POS-2120W+

Typical Performance Data


Frequency and Tuning Sensitivity




Power Output




Harmonics Level



Frequency Pushing



Phase Noise



REV. X1
 POS-2120W+
 070205
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Case Style

A

A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01			.385 (9.78)	.400 (10.16)							5.2
A04	.770 (19.56)	.800 (20.32)	.200 (5.08)	.210 (5.33)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

Mini-Circuits[®]

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D