


Low Noise, High IP3 Monolithic Amplifier Die

PSA-0012-D+

50Ω 0.05 to 6 GHz



The Big Deal

- Ideal IF Amplifier
 - Low Gain
 - Low Noise Figure, 2.4dB
 - High Output Power
- Wide band

Product Overview

The PSA-0012-D+ is an advanced wide band, high dynamic range, low noise, high IP3, high output power, monolithic amplifier die. Manufactured using E-PHEMT* technology enables it to work with a single positive supply voltage.

Key Features

| Feature | Advantages |
|--|--|
| Ideal Combined Performance Low Noise: 2.4 dB High IP3: +35 dBm High P1dB: +22 dBm Low Gain: 15dB | The PSA-0012-D+ design is optimized for use in critical IF Amplifier applications having an ideal combination of Low Gain, Low Noise, and High Output Power. |
| Wide band operation 50 MHz to 6000 MHz | Operating over a broad frequency range, the PSA-0012-D+ covers a wide range of typical IF bands making this amplifier ideal for use in a variety of applications. |
| Excellent Return Loss Input: 10 dB at 3.5 GHz Output: 13 dB at 4.5 GHz | With 10 dB input and 13 dB output return loss, the PSA-0012-D+ can be integrated into critical circuits with confidence that VSWR interactions with input and output components will have minimum affect on performance. |
| Unpackaged Die | Enables user to integrate it directly into hybrids. |

Low Noise, High IP3 Monolithic Amplifier Die

PSA-0012-D+

50Ω 0.05 to 6 GHz

Product Features


- Low Noise Figure, 2.4dB typ. at 1 GHz
- High IP3, up to 36 dBm typ. at 1 GHz
- Output Power at 1dB comp., up to +22 dBm typ.
- Gain, 15.6 dB typ. at 1GHz

Typical Applications

- Cellular
- ISM
- GSM
- WCDMA
- LTE
- WiMax
- WLAN
- UNII and HIPERLAN

General Description

PSA-0012-D+ is an advanced wideband, high dynamic range, low noise, high IP3, high output power, monolithic amplifier die. Manufactured using E-PHEMT* technology enables it to work with a single positive supply voltage.




+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

Simplified Schematic and Pad description



| Pad | Description |
|----------------|-----------------------|
| RF-IN | RF input pad |
| RF-OUT & DC-IN | RF output pad |
| GROUND | Connections to ground |

* Enhancement mode pseudomorphic High Electron Mobility Transistor.

Note: 1. Bond Pad material - Gold
2. Bottom of Die - Gold plated

Electrical Specifications¹ at 25°C, Zo=50Ω

| Parameter | Condition (GHz) | Min. | Typ. | Max. | Units |
|---|-----------------|------|------|------|-------|
| Frequency range | | 0.05 | | 6.0 | GHz |
| DC current (Id) | | | 92 | | mA |
| at DC Volts (Vd) | | | 5.0 | | V |
| Noise figure | 0.05 | | 2.4 | | dB |
| | 0.5 | | 2.5 | | |
| | 1.0 | | 2.4 | | |
| | 2.0 | | 2.4 | | |
| | 3.0 | | 2.7 | | |
| | 4.0 | | 2.9 | | |
| | 5.0 | | 3.3 | | |
| Gain | 0.05 | | 18.0 | | dB |
| | 0.5 | | 16.2 | | |
| | 1.0 | | 15.6 | | |
| | 2.0 | | 14.2 | | |
| | 3.0 | | 12.7 | | |
| | 4.0 | | 11.2 | | |
| | 5.0 | | 9.9 | | |
| Input return loss | 0.05 | | 9.8 | | dB |
| | 3.0 | | 10.1 | | |
| | 6.0 | | 6.0 | | |
| Output return loss | 0.05 | | 11.2 | | dB |
| | 3.0 | | 13.9 | | |
| | 6.0 | | 8.4 | | |
| Output IP3 | 0.05 | | 33.9 | | dBm |
| | 0.5 | | 35.5 | | |
| | 1.0 | | 35.7 | | |
| | 2.0 | | 35.7 | | |
| | 3.0 | | 35.8 | | |
| | 4.0 | | 35.2 | | |
| | 5.0 | | 35.4 | | |
| 6.0 | | 33.8 | | | |
| Output power @ 1dB compression ² | 0.05 | | 20.2 | | dBm |
| | 0.5 | | 21.8 | | |
| | 1.0 | | 22.2 | | |
| | 2.0 | | 22.1 | | |
| | 3.0 | | 21.9 | | |
| | 4.0 | | 21.9 | | |
| | 5.0 | | 21.7 | | |
| 6.0 | | 21.0 | | | |
| Thermal resistance | | | 69 | | °C/W |

1. Measured in Mini-Circuits die characterization test board. See Figure 1 for Test Circuit.
 2. Current increases at P1dB

Absolute Maximum Ratings³

| Parameter | Ratings |
|-------------------------------------|-----------------------------------|
| Operating temperature | -40°C to 85°C |
| DC voltage (Pad RF-OUT & DC-IN) | 6V |
| Device current (Pad RF-OUT & DC-IN) | 130 mA |
| Power dissipation | 650 mW |
| Input power (CW) | 0.05-3GHz, 14dBm 3-6GHz, 19dBm |

3. Permanent damage may occur if any of these limits are exceeded.
 These ratings are not intended for continuous normal operation.
 Die performance measured in industry standard SOT-363 package.

Characterization Test Circuit




Figure 1. Block Diagram of Test Circuit used for characterization. Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin=-25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

Die Layout




Fig 2. Die Layout

Bonding Pad Position
(Dimensions in μm , Typical)




Fig 3. Bonding Pad Positions


Critical Dimensions

| Parameter | Values |
|------------------------------|----------|
| Die Thickness, μm | 100 |
| Die Width, μm | 400 |
| Die Length, μm | 420 |
| Bond Pad Size, μm | 75 x 75 |
| Ground Bond Pad Size | 75 X 150 |

Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC EPHEMPT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.


Assembly Diagram



Recommended Wire Length, Typical

| Wire | Wire Length (mm) | Wire Loop Height (mm) |
|-----------------------|------------------|-----------------------|
| Ground | 0.50 | 0.15 |
| RF-IN, RF-OUT & DC-IN | 0.70 | 0.15 |

RF Reference Plane - No port extension



| Additional Detailed Technical Information <i>additional information is available on our dash board.</i> | |
|---|--|
| Performance Data | Data Table |
| | Swept Graphs |
| | S-Parameter (S2P Files) Data Set with and without port extension(.zip file) |
| Case Style | Die |
| Die Ordering and packaging information (Note 4) | Quantity, Package Model No. Small, Gel - Pak: 10,50,100 PSA-0012-DG+ Medium†, Partial wafer: <3660 PSA-0012-DP+ Large†, Full Wafer PSA-0012-DF+ |
| | † Available upon request contact sales representative Refer to AN-60-067 |
| Environmental Ratings | ENV-80 |

Note 4. Dice taken from PCM good wafer, No RF or DC test performed.

ESD Rating**

Human Body Model (HBM): Class 0 (<250V) in accordance with ANSI/ESD STM 5.1 - 2001; passes 150V

** Tested in industry standard SOT-363 package.

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

Typical Performance Data

Full 2-Port Extension

Definitions:

- Input Return Loss = -S11 (dB)
- Gain(Power Gain) = S21 (dB)
- Reverse Isolation = -S12 (dB)
- Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 93mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 18.05 | 25.62 | 9.84 | 11.24 | 1.27 | 0.79 | 34.85 | 20.52 | 2.40 |
| 100 | 17.55 | 24.45 | 10.90 | 12.62 | 1.21 | 0.79 | 35.20 | 22.22 | 2.27 |
| 200 | 16.90 | 23.19 | 12.98 | 15.01 | 1.20 | 0.78 | 35.63 | 21.89 | 2.27 |
| 300 | 16.58 | 22.75 | 14.01 | 16.42 | 1.20 | 0.78 | 35.92 | 21.61 | 2.40 |
| 500 | 16.23 | 22.33 | 14.48 | 17.27 | 1.20 | 0.77 | 36.40 | 21.83 | 2.51 |
| 600 | 16.12 | 22.17 | 14.45 | 17.34 | 1.19 | 0.77 | 35.99 | 21.85 | 2.48 |
| 800 | 15.89 | 21.92 | 14.17 | 17.10 | 1.18 | 0.78 | 35.94 | 22.10 | 2.36 |
| 1000 | 15.63 | 21.62 | 13.81 | 16.77 | 1.17 | 0.78 | 35.77 | 22.23 | 2.36 |
| 1200 | 15.38 | 21.29 | 13.50 | 16.57 | 1.16 | 0.78 | 35.83 | 22.04 | 2.38 |
| 1400 | 15.11 | 20.94 | 13.32 | 16.53 | 1.15 | 0.78 | 35.80 | 22.06 | 2.35 |
| 1600 | 14.84 | 20.55 | 13.21 | 16.58 | 1.13 | 0.78 | 35.97 | 22.18 | 2.44 |
| 1700 | 14.70 | 20.36 | 13.17 | 16.65 | 1.13 | 0.78 | 35.90 | 22.19 | 2.39 |
| 1900 | 14.42 | 19.98 | 13.07 | 16.90 | 1.12 | 0.78 | 36.08 | 22.19 | 2.42 |
| 2100 | 14.15 | 19.57 | 12.92 | 17.20 | 1.11 | 0.78 | 36.00 | 22.20 | 2.45 |
| 2300 | 13.87 | 19.23 | 12.76 | 17.33 | 1.10 | 0.78 | 36.00 | 22.13 | 2.50 |
| 2500 | 13.59 | 18.86 | 12.43 | 17.36 | 1.09 | 0.78 | 36.14 | 22.12 | 2.52 |
| 2700 | 13.29 | 18.49 | 11.96 | 17.16 | 1.08 | 0.78 | 36.10 | 22.15 | 2.64 |
| 2900 | 12.99 | 18.17 | 11.45 | 16.67 | 1.07 | 0.78 | 35.87 | 22.04 | 2.71 |
| 3000 | 12.84 | 18.02 | 11.22 | 16.42 | 1.07 | 0.78 | 35.85 | 21.98 | 2.74 |
| 3200 | 12.53 | 17.71 | 10.74 | 15.92 | 1.06 | 0.78 | 36.17 | 21.60 | 2.74 |
| 3400 | 12.23 | 17.40 | 10.34 | 15.31 | 1.05 | 0.78 | 35.79 | 21.89 | 2.79 |
| 3600 | 11.93 | 17.13 | 9.94 | 14.79 | 1.04 | 0.79 | 35.90 | 21.96 | 2.83 |
| 3800 | 11.63 | 16.87 | 9.63 | 14.45 | 1.04 | 0.79 | 36.15 | 22.09 | 2.87 |
| 4000 | 11.33 | 16.60 | 9.40 | 14.14 | 1.04 | 0.79 | 35.66 | 22.01 | 2.91 |
| 4100 | 11.20 | 16.46 | 9.30 | 13.98 | 1.04 | 0.79 | 35.53 | 22.07 | 3.01 |
| 4300 | 10.92 | 16.20 | 9.13 | 13.74 | 1.03 | 0.79 | 36.31 | 21.75 | 3.00 |
| 4500 | 10.65 | 15.94 | 8.94 | 13.49 | 1.03 | 0.79 | 36.12 | 21.92 | 3.09 |
| 4700 | 10.39 | 15.69 | 8.78 | 13.16 | 1.03 | 0.78 | 36.08 | 22.06 | 3.14 |
| 4900 | 10.13 | 15.44 | 8.63 | 12.72 | 1.03 | 0.77 | 35.82 | 22.01 | 3.24 |
| 5100 | 9.86 | 15.21 | 8.43 | 12.26 | 1.03 | 0.77 | 35.87 | 21.80 | 3.28 |
| 5300 | 9.60 | 15.00 | 8.12 | 11.71 | 1.03 | 0.76 | 35.47 | 21.54 | 3.41 |
| 5400 | 9.45 | 14.91 | 7.98 | 11.38 | 1.03 | 0.75 | 35.37 | 21.29 | 3.38 |
| 5600 | 9.17 | 14.73 | 7.66 | 10.70 | 1.03 | 0.74 | 34.98 | 21.13 | 3.56 |
| 5800 | 8.87 | 14.56 | 7.31 | 10.03 | 1.03 | 0.74 | 34.55 | 21.16 | 3.64 |
| 6000 | 8.58 | 14.43 | 6.94 | 9.42 | 1.02 | 0.73 | 34.36 | 21.23 | 3.73 |
| 6200 | 8.25 | 14.30 | 6.56 | 8.87 | 1.02 | 0.73 | 34.41 | 20.77 | 3.77 |
| 6400 | 7.95 | 14.18 | 6.26 | 8.43 | 1.01 | 0.72 | 34.55 | 20.76 | 3.89 |
| 6600 | 7.65 | 14.05 | 6.01 | 8.03 | 1.01 | 0.72 | 34.98 | 20.78 | 3.93 |
| 6800 | 7.36 | 13.94 | 5.79 | 7.80 | 1.00 | 0.73 | 34.38 | 21.03 | 4.10 |
| 7000 | 7.09 | 13.82 | 5.61 | 7.67 | 1.00 | 0.74 | 34.53 | 20.97 | 4.23 |



Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 83mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 17.92 | 26.06 | 9.86 | 11.60 | 1.32 | 0.82 | 34.86 | 19.16 | 2.13 |
| 100 | 17.43 | 24.40 | 10.92 | 12.57 | 1.22 | 0.80 | 35.07 | 21.71 | 2.18 |
| 200 | 16.77 | 23.13 | 13.00 | 14.95 | 1.20 | 0.78 | 35.13 | 21.29 | 2.24 |
| 300 | 16.45 | 22.61 | 14.05 | 16.30 | 1.20 | 0.77 | 35.64 | 21.05 | 2.36 |
| 500 | 16.11 | 22.23 | 14.54 | 17.20 | 1.20 | 0.78 | 35.09 | 21.28 | 2.48 |
| 600 | 15.99 | 22.11 | 14.50 | 17.28 | 1.20 | 0.78 | 35.87 | 21.30 | 2.47 |
| 800 | 15.76 | 21.83 | 14.22 | 17.04 | 1.19 | 0.78 | 35.93 | 21.54 | 2.32 |
| 1000 | 15.51 | 21.52 | 13.86 | 16.69 | 1.17 | 0.78 | 35.42 | 21.66 | 2.34 |
| 1200 | 15.26 | 21.22 | 13.55 | 16.49 | 1.16 | 0.79 | 35.48 | 21.48 | 2.41 |
| 1400 | 14.99 | 20.85 | 13.35 | 16.45 | 1.15 | 0.78 | 35.57 | 21.50 | 2.34 |
| 1600 | 14.73 | 20.46 | 13.25 | 16.50 | 1.13 | 0.78 | 35.50 | 21.56 | 2.43 |
| 1700 | 14.59 | 20.29 | 13.19 | 16.61 | 1.13 | 0.78 | 35.17 | 21.57 | 2.40 |
| 1900 | 14.32 | 19.88 | 13.08 | 16.84 | 1.12 | 0.78 | 35.40 | 21.62 | 2.39 |
| 2100 | 14.05 | 19.50 | 12.95 | 17.10 | 1.11 | 0.78 | 35.93 | 21.59 | 2.43 |
| 2300 | 13.76 | 19.13 | 12.77 | 17.25 | 1.10 | 0.78 | 35.58 | 21.58 | 2.48 |
| 2500 | 13.49 | 18.79 | 12.43 | 17.27 | 1.09 | 0.78 | 35.59 | 21.57 | 2.49 |
| 2700 | 13.19 | 18.42 | 11.97 | 17.06 | 1.08 | 0.78 | 35.22 | 21.60 | 2.57 |
| 2900 | 12.90 | 18.10 | 11.50 | 16.58 | 1.07 | 0.78 | 36.20 | 21.50 | 2.70 |
| 3000 | 12.75 | 17.95 | 11.25 | 16.30 | 1.07 | 0.78 | 36.41 | 21.48 | 2.70 |
| 3200 | 12.44 | 17.64 | 10.76 | 15.84 | 1.06 | 0.78 | 36.21 | 21.12 | 2.72 |
| 3400 | 12.15 | 17.35 | 10.34 | 15.21 | 1.05 | 0.78 | 35.86 | 21.33 | 2.73 |
| 3600 | 11.84 | 17.06 | 9.95 | 14.71 | 1.05 | 0.79 | 36.63 | 21.46 | 2.77 |
| 3800 | 11.54 | 16.80 | 9.62 | 14.35 | 1.04 | 0.79 | 36.58 | 21.52 | 2.82 |
| 4000 | 11.25 | 16.53 | 9.38 | 14.04 | 1.04 | 0.79 | 35.95 | 21.51 | 2.88 |
| 4100 | 11.11 | 16.41 | 9.29 | 13.89 | 1.04 | 0.79 | 36.66 | 21.50 | 2.94 |
| 4300 | 10.83 | 16.13 | 9.12 | 13.64 | 1.03 | 0.79 | 36.05 | 21.20 | 2.94 |
| 4500 | 10.56 | 15.89 | 8.94 | 13.39 | 1.03 | 0.79 | 36.38 | 21.36 | 3.03 |
| 4700 | 10.30 | 15.64 | 8.77 | 13.06 | 1.03 | 0.78 | 36.20 | 21.50 | 3.05 |
| 4900 | 10.04 | 15.38 | 8.62 | 12.62 | 1.03 | 0.77 | 36.21 | 21.44 | 3.17 |
| 5100 | 9.78 | 15.15 | 8.42 | 12.16 | 1.03 | 0.77 | 36.39 | 21.31 | 3.21 |
| 5300 | 9.52 | 14.95 | 8.12 | 11.61 | 1.03 | 0.76 | 35.98 | 21.05 | 3.32 |
| 5400 | 9.38 | 14.87 | 7.98 | 11.29 | 1.03 | 0.75 | 35.36 | 20.75 | 3.32 |
| 5600 | 9.09 | 14.68 | 7.65 | 10.63 | 1.03 | 0.74 | 35.28 | 20.66 | 3.46 |
| 5800 | 8.80 | 14.52 | 7.31 | 9.96 | 1.03 | 0.74 | 35.33 | 20.68 | 3.53 |
| 6000 | 8.51 | 14.38 | 6.93 | 9.35 | 1.02 | 0.73 | 34.76 | 20.68 | 3.65 |
| 6200 | 8.18 | 14.27 | 6.57 | 8.81 | 1.02 | 0.73 | 35.21 | 20.24 | 3.67 |
| 6400 | 7.88 | 14.15 | 6.25 | 8.38 | 1.01 | 0.72 | 34.89 | 20.29 | 3.80 |
| 6600 | 7.58 | 14.02 | 6.02 | 7.98 | 1.01 | 0.72 | 35.19 | 20.24 | 3.86 |
| 6800 | 7.30 | 13.90 | 5.80 | 7.73 | 1.00 | 0.73 | 34.52 | 20.55 | 4.00 |
| 7000 | 7.02 | 13.79 | 5.62 | 7.64 | 1.00 | 0.74 | 34.73 | 20.43 | 4.12 |

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 101mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 18.15 | 25.88 | 9.92 | 11.44 | 1.28 | 0.80 | 33.81 | 21.09 | 2.24 |
| 100 | 17.64 | 24.47 | 10.97 | 12.71 | 1.21 | 0.79 | 35.07 | 22.74 | 2.21 |
| 200 | 16.98 | 23.26 | 13.07 | 15.15 | 1.20 | 0.78 | 35.77 | 22.36 | 2.25 |
| 300 | 16.67 | 22.80 | 14.10 | 16.56 | 1.20 | 0.77 | 35.70 | 22.12 | 2.38 |
| 500 | 16.32 | 22.41 | 14.61 | 17.46 | 1.20 | 0.77 | 35.76 | 22.34 | 2.49 |
| 600 | 16.21 | 22.27 | 14.56 | 17.52 | 1.19 | 0.78 | 35.92 | 22.31 | 2.47 |
| 800 | 15.97 | 21.99 | 14.29 | 17.27 | 1.18 | 0.78 | 35.76 | 22.58 | 2.35 |
| 1000 | 15.72 | 21.66 | 13.91 | 16.95 | 1.17 | 0.78 | 35.60 | 22.77 | 2.36 |
| 1200 | 15.46 | 21.34 | 13.62 | 16.73 | 1.16 | 0.78 | 35.72 | 22.57 | 2.39 |
| 1400 | 15.20 | 20.97 | 13.42 | 16.70 | 1.14 | 0.78 | 35.92 | 22.59 | 2.34 |
| 1600 | 14.92 | 20.61 | 13.31 | 16.72 | 1.13 | 0.78 | 36.03 | 22.72 | 2.41 |
| 1700 | 14.79 | 20.45 | 13.26 | 16.84 | 1.13 | 0.78 | 35.83 | 22.67 | 2.38 |
| 1900 | 14.51 | 20.03 | 13.13 | 17.10 | 1.12 | 0.78 | 36.02 | 22.72 | 2.39 |
| 2100 | 14.23 | 19.65 | 13.03 | 17.38 | 1.11 | 0.77 | 35.76 | 22.73 | 2.44 |
| 2300 | 13.95 | 19.27 | 12.84 | 17.51 | 1.10 | 0.77 | 35.93 | 22.65 | 2.49 |
| 2500 | 13.67 | 18.91 | 12.52 | 17.55 | 1.09 | 0.77 | 35.82 | 22.64 | 2.51 |
| 2700 | 13.37 | 18.54 | 12.04 | 17.33 | 1.08 | 0.77 | 36.37 | 22.67 | 2.59 |
| 2900 | 13.07 | 18.21 | 11.53 | 16.84 | 1.07 | 0.77 | 35.65 | 22.55 | 2.70 |
| 3000 | 12.92 | 18.06 | 11.29 | 16.59 | 1.07 | 0.78 | 35.61 | 22.51 | 2.70 |
| 3200 | 12.61 | 17.76 | 10.80 | 16.11 | 1.06 | 0.78 | 36.11 | 22.05 | 2.73 |
| 3400 | 12.31 | 17.45 | 10.39 | 15.45 | 1.05 | 0.78 | 35.71 | 22.36 | 2.74 |
| 3600 | 12.00 | 17.17 | 9.98 | 14.91 | 1.04 | 0.78 | 35.26 | 22.49 | 2.80 |
| 3800 | 11.70 | 16.90 | 9.66 | 14.58 | 1.04 | 0.79 | 35.88 | 22.57 | 2.86 |
| 4000 | 11.41 | 16.62 | 9.43 | 14.26 | 1.04 | 0.79 | 35.52 | 22.55 | 2.91 |
| 4100 | 11.27 | 16.51 | 9.35 | 14.09 | 1.04 | 0.79 | 35.63 | 22.55 | 2.98 |
| 4300 | 10.99 | 16.23 | 9.17 | 13.82 | 1.04 | 0.78 | 36.14 | 22.21 | 2.97 |
| 4500 | 10.72 | 15.97 | 9.00 | 13.55 | 1.03 | 0.78 | 35.50 | 22.39 | 3.05 |
| 4700 | 10.46 | 15.71 | 8.83 | 13.23 | 1.03 | 0.78 | 35.75 | 22.54 | 3.10 |
| 4900 | 10.20 | 15.49 | 8.67 | 12.79 | 1.03 | 0.77 | 36.04 | 22.48 | 3.19 |
| 5100 | 9.93 | 15.24 | 8.46 | 12.33 | 1.03 | 0.76 | 35.43 | 22.33 | 3.24 |
| 5300 | 9.67 | 15.03 | 8.15 | 11.78 | 1.03 | 0.76 | 34.80 | 21.99 | 3.36 |
| 5400 | 9.52 | 14.93 | 8.02 | 11.43 | 1.03 | 0.75 | 35.31 | 21.68 | 3.34 |
| 5600 | 9.24 | 14.76 | 7.68 | 10.78 | 1.03 | 0.74 | 34.80 | 21.65 | 3.51 |
| 5800 | 8.95 | 14.59 | 7.33 | 10.08 | 1.02 | 0.73 | 34.12 | 21.62 | 3.59 |
| 6000 | 8.65 | 14.45 | 6.96 | 9.45 | 1.02 | 0.73 | 34.14 | 21.69 | 3.71 |
| 6200 | 8.32 | 14.33 | 6.59 | 8.93 | 1.02 | 0.72 | 34.10 | 21.23 | 3.72 |
| 6400 | 8.02 | 14.21 | 6.28 | 8.51 | 1.01 | 0.72 | 34.11 | 21.22 | 3.83 |
| 6600 | 7.72 | 14.08 | 6.03 | 8.08 | 1.01 | 0.72 | 34.46 | 21.23 | 3.90 |
| 6800 | 7.43 | 13.95 | 5.82 | 7.85 | 1.00 | 0.73 | 34.37 | 21.56 | 4.04 |
| 7000 | 7.17 | 13.83 | 5.64 | 7.74 | 1.00 | 0.74 | 34.34 | 21.43 | 4.18 |

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 93mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 18.09 | 25.90 | 9.79 | 11.54 | 1.29 | 0.81 | 34.85 | 20.52 | 2.40 |
| 100 | 17.59 | 24.42 | 10.87 | 12.59 | 1.21 | 0.79 | 35.20 | 22.22 | 2.27 |
| 200 | 16.92 | 23.20 | 12.97 | 15.00 | 1.19 | 0.78 | 35.63 | 21.89 | 2.27 |
| 300 | 16.58 | 22.74 | 14.01 | 16.38 | 1.20 | 0.77 | 35.92 | 21.61 | 2.40 |
| 500 | 16.22 | 22.37 | 14.51 | 17.29 | 1.20 | 0.78 | 36.40 | 21.83 | 2.51 |
| 600 | 16.09 | 22.27 | 14.49 | 17.36 | 1.20 | 0.78 | 35.99 | 21.85 | 2.48 |
| 800 | 15.84 | 21.98 | 14.24 | 17.15 | 1.19 | 0.78 | 35.94 | 22.10 | 2.36 |
| 1000 | 15.56 | 21.69 | 13.89 | 16.84 | 1.18 | 0.79 | 35.77 | 22.23 | 2.36 |
| 1200 | 15.28 | 21.37 | 13.60 | 16.64 | 1.17 | 0.79 | 35.83 | 22.04 | 2.38 |
| 1400 | 15.00 | 21.05 | 13.45 | 16.62 | 1.17 | 0.79 | 35.80 | 22.06 | 2.35 |
| 1600 | 14.71 | 20.66 | 13.35 | 16.71 | 1.15 | 0.79 | 35.97 | 22.18 | 2.44 |
| 1700 | 14.56 | 20.52 | 13.31 | 16.77 | 1.15 | 0.80 | 35.90 | 22.19 | 2.39 |
| 1900 | 14.26 | 20.11 | 13.24 | 17.04 | 1.14 | 0.79 | 36.08 | 22.19 | 2.42 |
| 2100 | 13.98 | 19.78 | 13.13 | 17.36 | 1.14 | 0.80 | 36.00 | 22.20 | 2.45 |
| 2300 | 13.67 | 19.42 | 12.98 | 17.49 | 1.13 | 0.80 | 36.00 | 22.13 | 2.50 |
| 2500 | 13.38 | 19.06 | 12.67 | 17.53 | 1.12 | 0.80 | 36.14 | 22.12 | 2.52 |
| 2700 | 13.06 | 18.74 | 12.22 | 17.34 | 1.12 | 0.80 | 36.10 | 22.15 | 2.64 |
| 2900 | 12.75 | 18.42 | 11.74 | 16.88 | 1.11 | 0.80 | 35.87 | 22.04 | 2.71 |
| 3000 | 12.59 | 18.28 | 11.51 | 16.62 | 1.11 | 0.81 | 35.85 | 21.98 | 2.74 |
| 3200 | 12.26 | 17.99 | 11.05 | 16.16 | 1.10 | 0.81 | 36.17 | 21.60 | 2.74 |
| 3400 | 11.94 | 17.69 | 10.66 | 15.55 | 1.10 | 0.81 | 35.79 | 21.89 | 2.79 |
| 3600 | 11.62 | 17.45 | 10.29 | 15.05 | 1.10 | 0.82 | 35.90 | 21.96 | 2.83 |
| 3800 | 11.31 | 17.20 | 10.00 | 14.72 | 1.09 | 0.82 | 36.15 | 22.09 | 2.87 |
| 4000 | 11.00 | 16.94 | 9.79 | 14.43 | 1.09 | 0.82 | 35.66 | 22.01 | 2.91 |
| 4100 | 10.85 | 16.82 | 9.71 | 14.28 | 1.09 | 0.82 | 35.53 | 22.07 | 3.01 |
| 4300 | 10.56 | 16.57 | 9.55 | 14.03 | 1.09 | 0.83 | 36.31 | 21.75 | 3.00 |
| 4500 | 10.27 | 16.30 | 9.39 | 13.80 | 1.09 | 0.82 | 36.12 | 21.92 | 3.09 |
| 4700 | 9.99 | 16.08 | 9.24 | 13.48 | 1.10 | 0.82 | 36.08 | 22.06 | 3.14 |
| 4900 | 9.72 | 15.85 | 9.10 | 13.05 | 1.10 | 0.82 | 35.82 | 22.01 | 3.24 |
| 5100 | 9.44 | 15.62 | 8.93 | 12.62 | 1.10 | 0.81 | 35.87 | 21.80 | 3.28 |
| 5300 | 9.15 | 15.44 | 8.64 | 12.07 | 1.10 | 0.81 | 35.47 | 21.54 | 3.41 |
| 5400 | 9.00 | 15.35 | 8.52 | 11.76 | 1.10 | 0.80 | 35.37 | 21.29 | 3.38 |
| 5600 | 8.71 | 15.19 | 8.20 | 11.07 | 1.10 | 0.80 | 34.98 | 21.13 | 3.56 |
| 5800 | 8.39 | 15.05 | 7.88 | 10.41 | 1.10 | 0.79 | 34.55 | 21.16 | 3.64 |
| 6000 | 8.08 | 14.91 | 7.52 | 9.83 | 1.10 | 0.79 | 34.36 | 21.23 | 3.73 |
| 6200 | 7.74 | 14.81 | 7.18 | 9.28 | 1.10 | 0.78 | 34.41 | 20.77 | 3.77 |
| 6400 | 7.43 | 14.70 | 6.88 | 8.84 | 1.10 | 0.78 | 34.55 | 20.76 | 3.89 |
| 6600 | 7.11 | 14.60 | 6.65 | 8.47 | 1.10 | 0.79 | 34.98 | 20.78 | 3.93 |
| 6800 | 6.81 | 14.49 | 6.45 | 8.25 | 1.10 | 0.79 | 34.38 | 21.03 | 4.10 |
| 7000 | 6.52 | 14.38 | 6.29 | 8.13 | 1.10 | 0.80 | 34.53 | 20.97 | 4.23 |

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 83mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 17.97 | 25.46 | 9.86 | 11.23 | 1.26 | 0.79 | 34.86 | 19.16 | 2.13 |
| 100 | 17.46 | 24.34 | 10.90 | 12.56 | 1.21 | 0.79 | 35.07 | 21.71 | 2.18 |
| 200 | 16.79 | 23.12 | 12.99 | 14.94 | 1.20 | 0.78 | 35.13 | 21.29 | 2.24 |
| 300 | 16.46 | 22.67 | 14.04 | 16.34 | 1.20 | 0.78 | 35.64 | 21.05 | 2.36 |
| 500 | 16.09 | 22.27 | 14.58 | 17.22 | 1.21 | 0.78 | 35.09 | 21.28 | 2.48 |
| 600 | 15.96 | 22.14 | 14.55 | 17.29 | 1.20 | 0.78 | 35.87 | 21.30 | 2.47 |
| 800 | 15.71 | 21.88 | 14.29 | 17.10 | 1.20 | 0.79 | 35.93 | 21.54 | 2.32 |
| 1000 | 15.44 | 21.58 | 13.95 | 16.78 | 1.19 | 0.79 | 35.42 | 21.66 | 2.34 |
| 1200 | 15.16 | 21.28 | 13.66 | 16.58 | 1.18 | 0.79 | 35.48 | 21.48 | 2.41 |
| 1400 | 14.88 | 20.97 | 13.50 | 16.57 | 1.17 | 0.80 | 35.57 | 21.50 | 2.34 |
| 1600 | 14.59 | 20.58 | 13.40 | 16.62 | 1.16 | 0.80 | 35.50 | 21.56 | 2.43 |
| 1700 | 14.45 | 20.43 | 13.35 | 16.73 | 1.16 | 0.80 | 35.17 | 21.57 | 2.40 |
| 1900 | 14.16 | 20.07 | 13.27 | 16.99 | 1.15 | 0.80 | 35.40 | 21.62 | 2.39 |
| 2100 | 13.87 | 19.67 | 13.16 | 17.28 | 1.14 | 0.80 | 35.93 | 21.59 | 2.43 |
| 2300 | 13.57 | 19.33 | 13.01 | 17.44 | 1.13 | 0.80 | 35.58 | 21.58 | 2.48 |
| 2500 | 13.27 | 18.99 | 12.69 | 17.47 | 1.13 | 0.80 | 35.59 | 21.57 | 2.49 |
| 2700 | 12.96 | 18.67 | 12.25 | 17.26 | 1.12 | 0.80 | 35.22 | 21.60 | 2.57 |
| 2900 | 12.65 | 18.34 | 11.79 | 16.80 | 1.11 | 0.80 | 36.20 | 21.50 | 2.70 |
| 3000 | 12.50 | 18.19 | 11.56 | 16.51 | 1.11 | 0.80 | 36.41 | 21.48 | 2.70 |
| 3200 | 12.17 | 17.90 | 11.08 | 16.05 | 1.10 | 0.81 | 36.21 | 21.12 | 2.72 |
| 3400 | 11.85 | 17.62 | 10.68 | 15.45 | 1.10 | 0.81 | 35.86 | 21.33 | 2.73 |
| 3600 | 11.53 | 17.37 | 10.31 | 14.98 | 1.10 | 0.82 | 36.63 | 21.46 | 2.77 |
| 3800 | 11.22 | 17.14 | 10.00 | 14.61 | 1.09 | 0.82 | 36.58 | 21.52 | 2.82 |
| 4000 | 10.91 | 16.86 | 9.78 | 14.30 | 1.09 | 0.82 | 35.95 | 21.51 | 2.88 |
| 4100 | 10.77 | 16.78 | 9.70 | 14.18 | 1.10 | 0.83 | 36.66 | 21.50 | 2.94 |
| 4300 | 10.47 | 16.49 | 9.54 | 13.94 | 1.09 | 0.82 | 36.05 | 21.20 | 2.94 |
| 4500 | 10.18 | 16.25 | 9.39 | 13.71 | 1.10 | 0.82 | 36.38 | 21.36 | 3.03 |
| 4700 | 9.91 | 16.03 | 9.23 | 13.38 | 1.10 | 0.82 | 36.20 | 21.50 | 3.05 |
| 4900 | 9.64 | 15.80 | 9.11 | 12.95 | 1.10 | 0.82 | 36.21 | 21.44 | 3.17 |
| 5100 | 9.36 | 15.59 | 8.92 | 12.52 | 1.10 | 0.81 | 36.39 | 21.31 | 3.21 |
| 5300 | 9.08 | 15.40 | 8.64 | 11.98 | 1.10 | 0.81 | 35.98 | 21.05 | 3.32 |
| 5400 | 8.93 | 15.33 | 8.52 | 11.65 | 1.11 | 0.80 | 35.36 | 20.75 | 3.32 |
| 5600 | 8.63 | 15.15 | 8.20 | 11.01 | 1.11 | 0.80 | 35.28 | 20.66 | 3.46 |
| 5800 | 8.32 | 15.01 | 7.88 | 10.36 | 1.11 | 0.79 | 35.33 | 20.68 | 3.53 |
| 6000 | 8.01 | 14.88 | 7.53 | 9.75 | 1.10 | 0.79 | 34.76 | 20.68 | 3.65 |
| 6200 | 7.67 | 14.78 | 7.17 | 9.22 | 1.11 | 0.78 | 35.21 | 20.24 | 3.67 |
| 6400 | 7.36 | 14.67 | 6.88 | 8.80 | 1.11 | 0.78 | 34.89 | 20.29 | 3.80 |
| 6600 | 7.05 | 14.58 | 6.67 | 8.42 | 1.10 | 0.78 | 35.19 | 20.24 | 3.86 |
| 6800 | 6.75 | 14.45 | 6.46 | 8.19 | 1.10 | 0.79 | 34.52 | 20.55 | 4.00 |
| 7000 | 6.46 | 14.35 | 6.29 | 8.09 | 1.11 | 0.80 | 34.73 | 20.43 | 4.12 |

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)








Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 101mA @Temperature = +25°C

| FREQ. | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 50 | 18.20 | 25.84 | 9.82 | 11.51 | 1.28 | 0.80 | 33.81 | 21.09 | 2.24 |
| 100 | 17.68 | 24.43 | 10.91 | 12.67 | 1.20 | 0.79 | 35.07 | 22.74 | 2.21 |
| 200 | 17.00 | 23.23 | 13.04 | 15.12 | 1.19 | 0.78 | 35.77 | 22.36 | 2.25 |
| 300 | 16.68 | 22.77 | 14.07 | 16.51 | 1.19 | 0.77 | 35.70 | 22.12 | 2.38 |
| 500 | 16.31 | 22.40 | 14.62 | 17.48 | 1.20 | 0.77 | 35.76 | 22.34 | 2.49 |
| 600 | 16.18 | 22.30 | 14.59 | 17.54 | 1.20 | 0.78 | 35.92 | 22.31 | 2.47 |
| 800 | 15.92 | 22.02 | 14.33 | 17.33 | 1.19 | 0.78 | 35.76 | 22.58 | 2.35 |
| 1000 | 15.65 | 21.74 | 13.98 | 17.02 | 1.18 | 0.79 | 35.60 | 22.77 | 2.36 |
| 1200 | 15.37 | 21.42 | 13.71 | 16.80 | 1.17 | 0.79 | 35.72 | 22.57 | 2.39 |
| 1400 | 15.09 | 21.08 | 13.54 | 16.78 | 1.16 | 0.79 | 35.92 | 22.59 | 2.34 |
| 1600 | 14.79 | 20.74 | 13.45 | 16.84 | 1.16 | 0.79 | 36.03 | 22.72 | 2.41 |
| 1700 | 14.65 | 20.55 | 13.41 | 16.98 | 1.15 | 0.79 | 35.83 | 22.67 | 2.38 |
| 1900 | 14.35 | 20.23 | 13.31 | 17.19 | 1.15 | 0.80 | 36.02 | 22.72 | 2.39 |
| 2100 | 14.06 | 19.83 | 13.23 | 17.53 | 1.14 | 0.79 | 35.76 | 22.73 | 2.44 |
| 2300 | 13.75 | 19.46 | 13.05 | 17.67 | 1.13 | 0.79 | 35.93 | 22.65 | 2.49 |
| 2500 | 13.45 | 19.12 | 12.75 | 17.72 | 1.12 | 0.79 | 35.82 | 22.64 | 2.51 |
| 2700 | 13.14 | 18.76 | 12.31 | 17.54 | 1.12 | 0.80 | 36.37 | 22.67 | 2.59 |
| 2900 | 12.82 | 18.48 | 11.81 | 17.06 | 1.11 | 0.80 | 35.65 | 22.55 | 2.70 |
| 3000 | 12.67 | 18.31 | 11.58 | 16.79 | 1.11 | 0.80 | 35.61 | 22.51 | 2.70 |
| 3200 | 12.34 | 18.02 | 11.11 | 16.35 | 1.10 | 0.81 | 36.11 | 22.05 | 2.73 |
| 3400 | 12.02 | 17.75 | 10.72 | 15.70 | 1.10 | 0.81 | 35.71 | 22.36 | 2.74 |
| 3600 | 11.70 | 17.49 | 10.34 | 15.18 | 1.10 | 0.81 | 35.26 | 22.49 | 2.80 |
| 3800 | 11.38 | 17.24 | 10.04 | 14.84 | 1.09 | 0.82 | 35.88 | 22.57 | 2.86 |
| 4000 | 11.07 | 16.97 | 9.83 | 14.54 | 1.09 | 0.82 | 35.52 | 22.55 | 2.91 |
| 4100 | 10.93 | 16.86 | 9.76 | 14.38 | 1.09 | 0.82 | 35.63 | 22.55 | 2.98 |
| 4300 | 10.63 | 16.59 | 9.59 | 14.12 | 1.09 | 0.82 | 36.14 | 22.21 | 2.97 |
| 4500 | 10.34 | 16.35 | 9.44 | 13.87 | 1.10 | 0.82 | 35.50 | 22.39 | 3.05 |
| 4700 | 10.06 | 16.12 | 9.30 | 13.56 | 1.10 | 0.82 | 35.75 | 22.54 | 3.10 |
| 4900 | 9.79 | 15.89 | 9.15 | 13.12 | 1.10 | 0.81 | 36.04 | 22.48 | 3.19 |
| 5100 | 9.51 | 15.67 | 8.96 | 12.67 | 1.10 | 0.81 | 35.43 | 22.33 | 3.24 |
| 5300 | 9.23 | 15.47 | 8.67 | 12.14 | 1.10 | 0.80 | 34.80 | 21.99 | 3.36 |
| 5400 | 9.07 | 15.39 | 8.56 | 11.78 | 1.10 | 0.80 | 35.31 | 21.68 | 3.34 |
| 5600 | 8.78 | 15.21 | 8.22 | 11.15 | 1.10 | 0.79 | 34.80 | 21.65 | 3.51 |
| 5800 | 8.47 | 15.07 | 7.90 | 10.48 | 1.10 | 0.79 | 34.12 | 21.62 | 3.59 |
| 6000 | 8.16 | 14.94 | 7.55 | 9.86 | 1.10 | 0.78 | 34.14 | 21.69 | 3.71 |
| 6200 | 7.81 | 14.85 | 7.20 | 9.34 | 1.10 | 0.78 | 34.10 | 21.23 | 3.72 |
| 6400 | 7.50 | 14.73 | 6.90 | 8.93 | 1.10 | 0.79 | 34.11 | 21.22 | 3.83 |
| 6600 | 7.18 | 14.62 | 6.67 | 8.51 | 1.10 | 0.78 | 34.46 | 21.23 | 3.90 |
| 6800 | 6.88 | 14.50 | 6.48 | 8.30 | 1.10 | 0.79 | 34.37 | 21.56 | 4.04 |
| 7000 | 6.60 | 14.40 | 6.32 | 8.21 | 1.10 | 0.80 | 34.34 | 21.43 | 4.18 |

Typical Performance Curves

Full 2-Port Extension










MMIC Amplifier Die

PSA-0012-D+

Typical Performance Curves

Without Full 2-Port Extension



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|--------------------------------------|
| Operating Temperature | -40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment | Refer to Individual Model Data Sheet |
| Storage Environment (Die) | -65° to 150°C | Individual Model Data Sheet |
| Storage Environment(Packaging) | -40° to 70°C and 40 to 60% humidity (In Factory Shipped Package) | |