


*Low Noise, High IP3*  
**Monolithic Amplifier Die**

**PSA-0012-D+**

**50Ω      0.05 to 6 GHz**

### The Big Deal

- Ideal IF Amplifier
  - Low Gain
  - Low Noise Figure, 2.4dB
  - High Output Power
- Wide band



### Product Overview

The PSA-0012-D+ is an advanced wide band, high dynamic range, low noise, high IP3, high output power, monolithic amplifier die. Manufactured using E-PHEMT\* technology enables it to work with a single positive supply voltage.

### Key Features

Feature	Advantages
Ideal Combined Performance Low Noise: 2.4 dB High IP3: +35 dBm High P1dB: +22 dBm Low Gain: 15dB	The PSA-0012-D+ design is optimized for use in critical IF Amplifier applications having an ideal combination of Low Gain, Low Noise, and High Output Power.
Wide band operation 50 MHz to 6000 MHz	Operating over a broad frequency range, the PSA-0012-D+ covers a wide range of typical IF bands making this amplifier ideal for use in a variety of applications.
Excellent Return Loss Input: 10 dB at 3.5 GHz Output: 13 dB at 4.5 GHz	With 10 dB input and 13 dB output return loss, the PSA-0012-D+ can be integrated into critical circuits with confidence that VSWR interactions with input and output components will have minimum affect on performance.
Unpackaged Die	Enables user to integrate it directly into hybrids.




*Low Noise, High IP3*  
**Monolithic Amplifier Die**

**PSA-0012-D+**

**50Ω      0.05 to 6 GHz**

**Product Features**

- Low Noise Figure, 2.4dB typ. at 1 GHz
- High IP3, up to 36 dBm typ. at 1 GHz
- Output Power at 1dB comp., up to +22 dBm typ.
- Gain, 15.6 dB typ. at 1GHz



**Typical Applications**

- Cellular
- ISM
- GSM
- WCDMA
- LTE
- WiMax
- WLAN
- UNII and HIPERLAN

**+RoHS Compliant**


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

*Ordering Information: Refer to Last Page*

**General Description**

PSA-0012-D+ is an advanced wideband, high dynamic range, low noise, high IP3, high output power, monolithic amplifier die. Manufactured using E-PHEMT\* technology enables it to work with a single positive supply voltage.

**Simplified Schematic and Pad description**



Pad	Description
RF-IN	RF input pad
RF-OUT & DC-IN	RF output pad
GROUND	Connections to ground

\* Enhancement mode pseudomorphic High Electron Mobility Transistor.

Note: 1. Bond Pad material - Gold  
2. Bottom of Die - Gold plated

REV. A  
M167172  
PSA-0012-D+  
MCL NY  
180424  
Page 2 of 6



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

**Electrical Specifications<sup>1</sup> at 25°C, Zo=50Ω**

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency range		0.05		6.0	GHz
DC current (Id)			92		mA
at DC Volts (Vd)			5.0		V
Noise figure	0.05 0.5 1.0 2.0 3.0 4.0 5.0 6.0		2.4 2.5 2.4 2.4 2.7 2.9 3.3 3.7		dB
Gain	0.05 0.5 1.0 2.0 3.0 4.0 5.0 6.0		18.0 16.2 15.6 14.2 12.7 11.2 9.9 8.4		dB
Input return loss	0.05 3.0 6.0		9.8 10.1 6.0		dB
Output return loss	0.05 3.0 6.0		11.2 13.9 8.4		dB
Output IP3	0.05 0.5 1.0 2.0 3.0 4.0 5.0 6.0		33.9 35.5 35.7 35.7 35.8 35.2 35.4 33.8		dBm
Output power @ 1dB compression <sup>2</sup>	0.05 0.5 1.0 2.0 3.0 4.0 5.0 6.0		20.2 21.8 22.2 22.1 21.9 21.9 21.7 21.0		dBm
Thermal resistance			69		°C/W

1. Measured in Mini-Circuits die characterization test board. See Figure 1 for Test Circuit.

2. Current increases at P1dB

**Absolute Maximum Ratings<sup>3</sup>**

Parameter	Ratings
Operating temperature	-40°C to 85°C
DC voltage (Pad RF-OUT & DC-IN)	6V
Device current (Pad RF-OUT & DC-IN)	130 mA
Power dissipation	650 mW
Input power (CW)	0.05-3GHz, 14dBm 3-6GHz, 19dBm

3. Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation.

Die performance measured in industry standard SOT-363 package.



## Characterization Test Circuit




Figure 1. Block Diagram of Test Circuit used for characterization. Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

### Conditions:

1. Gain and Return loss: Pin=-25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

## Die Layout




Fig 2. Die Layout

## Critical Dimensions

Parameter	Values
Die Thickness, $\mu\text{m}$	100
Die Width, $\mu\text{m}$	400
Die Length, $\mu\text{m}$	420
Bond Pad Size, $\mu\text{m}$	75 x 75
Ground Bond Pad Size	75 X 150

## Bonding Pad Position (Dimensions in $\mu\text{m}$ , Typical)





Fig 3. Bonding Pad Positions

## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC EPHEMPT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as reasonable to minimize performance degradation due to undesirable series inductance.


## Assembly Diagram



### Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
Ground	0.50	0.15
RF-IN, RF-OUT & DC-IN	0.70	0.15

## RF Reference Plane - No port extension



**Additional Detailed Technical Information***additional information is available on our dash board.*

<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
<b>Case Style</b>	Die
<b>Die Ordering and packaging information (Note 4)</b>	Quantity, Package Small, Gel - Pak: 10,50,100 Medium <sup>†</sup> , Partial wafer: <3660 Large <sup>†</sup> , Full Wafer <sup>†</sup> Available upon request contact sales representative Refer to <a href="#">AN-60-067</a>
<b>Environmental Ratings</b>	ENV-80

Note 4. Dice taken from PCM good wafer, No RF or DC test performed.

**ESD Rating\*\***

Human Body Model (HBM): Class 0 (&lt;250V) in accordance with ANSI/ESD STM 5.1 - 2001; passes 150V

\*\* Tested in industry standard SOT-363 package.

**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



## Typical Performance Data

## Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 93mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.05	25.62	9.84	11.24	1.27	0.79	34.85	20.52	2.40
100	17.55	24.45	10.90	12.62	1.21	0.79	35.20	22.22	2.27
200	16.90	23.19	12.98	15.01	1.20	0.78	35.63	21.89	2.27
300	16.58	22.75	14.01	16.42	1.20	0.78	35.92	21.61	2.40
500	16.23	22.33	14.48	17.27	1.20	0.77	36.40	21.83	2.51
600	16.12	22.17	14.45	17.34	1.19	0.77	35.99	21.85	2.48
800	15.89	21.92	14.17	17.10	1.18	0.78	35.94	22.10	2.36
1000	15.63	21.62	13.81	16.77	1.17	0.78	35.77	22.23	2.36
1200	15.38	21.29	13.50	16.57	1.16	0.78	35.83	22.04	2.38
1400	15.11	20.94	13.32	16.53	1.15	0.78	35.80	22.06	2.35
1600	14.84	20.55	13.21	16.58	1.13	0.78	35.97	22.18	2.44
1700	14.70	20.36	13.17	16.65	1.13	0.78	35.90	22.19	2.39
1900	14.42	19.98	13.07	16.90	1.12	0.78	36.08	22.19	2.42
2100	14.15	19.57	12.92	17.20	1.11	0.78	36.00	22.20	2.45
2300	13.87	19.23	12.76	17.33	1.10	0.78	36.00	22.13	2.50
2500	13.59	18.86	12.43	17.36	1.09	0.78	36.14	22.12	2.52
2700	13.29	18.49	11.96	17.16	1.08	0.78	36.10	22.15	2.64
2900	12.99	18.17	11.45	16.67	1.07	0.78	35.87	22.04	2.71
3000	12.84	18.02	11.22	16.42	1.07	0.78	35.85	21.98	2.74
3200	12.53	17.71	10.74	15.92	1.06	0.78	36.17	21.60	2.74
3400	12.23	17.40	10.34	15.31	1.05	0.78	35.79	21.89	2.79
3600	11.93	17.13	9.94	14.79	1.04	0.79	35.90	21.96	2.83
3800	11.63	16.87	9.63	14.45	1.04	0.79	36.15	22.09	2.87
4000	11.33	16.60	9.40	14.14	1.04	0.79	35.66	22.01	2.91
4100	11.20	16.46	9.30	13.98	1.04	0.79	35.53	22.07	3.01
4300	10.92	16.20	9.13	13.74	1.03	0.79	36.31	21.75	3.00
4500	10.65	15.94	8.94	13.49	1.03	0.79	36.12	21.92	3.09
4700	10.39	15.69	8.78	13.16	1.03	0.78	36.08	22.06	3.14
4900	10.13	15.44	8.63	12.72	1.03	0.77	35.82	22.01	3.24
5100	9.86	15.21	8.43	12.26	1.03	0.77	35.87	21.80	3.28
5300	9.60	15.00	8.12	11.71	1.03	0.76	35.47	21.54	3.41
5400	9.45	14.91	7.98	11.38	1.03	0.75	35.37	21.29	3.38
5600	9.17	14.73	7.66	10.70	1.03	0.74	34.98	21.13	3.56
5800	8.87	14.56	7.31	10.03	1.03	0.74	34.55	21.16	3.64
6000	8.58	14.43	6.94	9.42	1.02	0.73	34.36	21.23	3.73
6200	8.25	14.30	6.56	8.87	1.02	0.73	34.41	20.77	3.77
6400	7.95	14.18	6.26	8.43	1.01	0.72	34.55	20.76	3.89
6600	7.65	14.05	6.01	8.03	1.01	0.72	34.98	20.78	3.93
6800	7.36	13.94	5.79	7.80	1.00	0.73	34.38	21.03	4.10
7000	7.09	13.82	5.61	7.67	1.00	0.74	34.53	20.97	4.23

## Typical Performance Data

## Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 83mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	17.92	26.06	9.86	11.60	1.32	0.82	34.86	19.16	2.13
100	17.43	24.40	10.92	12.57	1.22	0.80	35.07	21.71	2.18
200	16.77	23.13	13.00	14.95	1.20	0.78	35.13	21.29	2.24
300	16.45	22.61	14.05	16.30	1.20	0.77	35.64	21.05	2.36
500	16.11	22.23	14.54	17.20	1.20	0.78	35.09	21.28	2.48
600	15.99	22.11	14.50	17.28	1.20	0.78	35.87	21.30	2.47
800	15.76	21.83	14.22	17.04	1.19	0.78	35.93	21.54	2.32
1000	15.51	21.52	13.86	16.69	1.17	0.78	35.42	21.66	2.34
1200	15.26	21.22	13.55	16.49	1.16	0.79	35.48	21.48	2.41
1400	14.99	20.85	13.35	16.45	1.15	0.78	35.57	21.50	2.34
1600	14.73	20.46	13.25	16.50	1.13	0.78	35.50	21.56	2.43
1700	14.59	20.29	13.19	16.61	1.13	0.78	35.17	21.57	2.40
1900	14.32	19.88	13.08	16.84	1.12	0.78	35.40	21.62	2.39
2100	14.05	19.50	12.95	17.10	1.11	0.78	35.93	21.59	2.43
2300	13.76	19.13	12.77	17.25	1.10	0.78	35.58	21.58	2.48
2500	13.49	18.79	12.43	17.27	1.09	0.78	35.59	21.57	2.49
2700	13.19	18.42	11.97	17.06	1.08	0.78	35.22	21.60	2.57
2900	12.90	18.10	11.50	16.58	1.07	0.78	36.20	21.50	2.70
3000	12.75	17.95	11.25	16.30	1.07	0.78	36.41	21.48	2.70
3200	12.44	17.64	10.76	15.84	1.06	0.78	36.21	21.12	2.72
3400	12.15	17.35	10.34	15.21	1.05	0.78	35.86	21.33	2.73
3600	11.84	17.06	9.95	14.71	1.05	0.79	36.63	21.46	2.77
3800	11.54	16.80	9.62	14.35	1.04	0.79	36.58	21.52	2.82
4000	11.25	16.53	9.38	14.04	1.04	0.79	35.95	21.51	2.88
4100	11.11	16.41	9.29	13.89	1.04	0.79	36.66	21.50	2.94
4300	10.83	16.13	9.12	13.64	1.03	0.79	36.05	21.20	2.94
4500	10.56	15.89	8.94	13.39	1.03	0.79	36.38	21.36	3.03
4700	10.30	15.64	8.77	13.06	1.03	0.78	36.20	21.50	3.05
4900	10.04	15.38	8.62	12.62	1.03	0.77	36.21	21.44	3.17
5100	9.78	15.15	8.42	12.16	1.03	0.77	36.39	21.31	3.21
5300	9.52	14.95	8.12	11.61	1.03	0.76	35.98	21.05	3.32
5400	9.38	14.87	7.98	11.29	1.03	0.75	35.36	20.75	3.32
5600	9.09	14.68	7.65	10.63	1.03	0.74	35.28	20.66	3.46
5800	8.80	14.52	7.31	9.96	1.03	0.74	35.33	20.68	3.53
6000	8.51	14.38	6.93	9.35	1.02	0.73	34.76	20.68	3.65
6200	8.18	14.27	6.57	8.81	1.02	0.73	35.21	20.24	3.67
6400	7.88	14.15	6.25	8.38	1.01	0.72	34.89	20.29	3.80
6600	7.58	14.02	6.02	7.98	1.01	0.72	35.19	20.24	3.86
6800	7.30	13.90	5.80	7.73	1.00	0.73	34.52	20.55	4.00
7000	7.02	13.79	5.62	7.64	1.00	0.74	34.73	20.43	4.12

## Typical Performance Data

## Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 101mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.15	25.88	9.92	11.44	1.28	0.80	33.81	21.09	2.24
100	17.64	24.47	10.97	12.71	1.21	0.79	35.07	22.74	2.21
200	16.98	23.26	13.07	15.15	1.20	0.78	35.77	22.36	2.25
300	16.67	22.80	14.10	16.56	1.20	0.77	35.70	22.12	2.38
500	16.32	22.41	14.61	17.46	1.20	0.77	35.76	22.34	2.49
600	16.21	22.27	14.56	17.52	1.19	0.78	35.92	22.31	2.47
800	15.97	21.99	14.29	17.27	1.18	0.78	35.76	22.58	2.35
1000	15.72	21.66	13.91	16.95	1.17	0.78	35.60	22.77	2.36
1200	15.46	21.34	13.62	16.73	1.16	0.78	35.72	22.57	2.39
1400	15.20	20.97	13.42	16.70	1.14	0.78	35.92	22.59	2.34
1600	14.92	20.61	13.31	16.72	1.13	0.78	36.03	22.72	2.41
1700	14.79	20.45	13.26	16.84	1.13	0.78	35.83	22.67	2.38
1900	14.51	20.03	13.13	17.10	1.12	0.78	36.02	22.72	2.39
2100	14.23	19.65	13.03	17.38	1.11	0.77	35.76	22.73	2.44
2300	13.95	19.27	12.84	17.51	1.10	0.77	35.93	22.65	2.49
2500	13.67	18.91	12.52	17.55	1.09	0.77	35.82	22.64	2.51
2700	13.37	18.54	12.04	17.33	1.08	0.77	36.37	22.67	2.59
2900	13.07	18.21	11.53	16.84	1.07	0.77	35.65	22.55	2.70
3000	12.92	18.06	11.29	16.59	1.07	0.78	35.61	22.51	2.70
3200	12.61	17.76	10.80	16.11	1.06	0.78	36.11	22.05	2.73
3400	12.31	17.45	10.39	15.45	1.05	0.78	35.71	22.36	2.74
3600	12.00	17.17	9.98	14.91	1.04	0.78	35.26	22.49	2.80
3800	11.70	16.90	9.66	14.58	1.04	0.79	35.88	22.57	2.86
4000	11.41	16.62	9.43	14.26	1.04	0.79	35.52	22.55	2.91
4100	11.27	16.51	9.35	14.09	1.04	0.79	35.63	22.55	2.98
4300	10.99	16.23	9.17	13.82	1.04	0.78	36.14	22.21	2.97
4500	10.72	15.97	9.00	13.55	1.03	0.78	35.50	22.39	3.05
4700	10.46	15.71	8.83	13.23	1.03	0.78	35.75	22.54	3.10
4900	10.20	15.49	8.67	12.79	1.03	0.77	36.04	22.48	3.19
5100	9.93	15.24	8.46	12.33	1.03	0.76	35.43	22.33	3.24
5300	9.67	15.03	8.15	11.78	1.03	0.76	34.80	21.99	3.36
5400	9.52	14.93	8.02	11.43	1.03	0.75	35.31	21.68	3.34
5600	9.24	14.76	7.68	10.78	1.03	0.74	34.80	21.65	3.51
5800	8.95	14.59	7.33	10.08	1.02	0.73	34.12	21.62	3.59
6000	8.65	14.45	6.96	9.45	1.02	0.73	34.14	21.69	3.71
6200	8.32	14.33	6.59	8.93	1.02	0.72	34.10	21.23	3.72
6400	8.02	14.21	6.28	8.51	1.01	0.72	34.11	21.22	3.83
6600	7.72	14.08	6.03	8.08	1.01	0.72	34.46	21.23	3.90
6800	7.43	13.95	5.82	7.85	1.00	0.73	34.37	21.56	4.04
7000	7.17	13.83	5.64	7.74	1.00	0.74	34.34	21.43	4.18

## Typical Performance Data

## Without Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 93mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.09	25.90	9.79	11.54	1.29	0.81	34.85	20.52	2.40
100	17.59	24.42	10.87	12.59	1.21	0.79	35.20	22.22	2.27
200	16.92	23.20	12.97	15.00	1.19	0.78	35.63	21.89	2.27
300	16.58	22.74	14.01	16.38	1.20	0.77	35.92	21.61	2.40
500	16.22	22.37	14.51	17.29	1.20	0.78	36.40	21.83	2.51
600	16.09	22.27	14.49	17.36	1.20	0.78	35.99	21.85	2.48
800	15.84	21.98	14.24	17.15	1.19	0.78	35.94	22.10	2.36
1000	15.56	21.69	13.89	16.84	1.18	0.79	35.77	22.23	2.36
1200	15.28	21.37	13.60	16.64	1.17	0.79	35.83	22.04	2.38
1400	15.00	21.05	13.45	16.62	1.17	0.79	35.80	22.06	2.35
1600	14.71	20.66	13.35	16.71	1.15	0.79	35.97	22.18	2.44
1700	14.56	20.52	13.31	16.77	1.15	0.80	35.90	22.19	2.39
1900	14.26	20.11	13.24	17.04	1.14	0.79	36.08	22.19	2.42
2100	13.98	19.78	13.13	17.36	1.14	0.80	36.00	22.20	2.45
2300	13.67	19.42	12.98	17.49	1.13	0.80	36.00	22.13	2.50
2500	13.38	19.06	12.67	17.53	1.12	0.80	36.14	22.12	2.52
2700	13.06	18.74	12.22	17.34	1.12	0.80	36.10	22.15	2.64
2900	12.75	18.42	11.74	16.88	1.11	0.80	35.87	22.04	2.71
3000	12.59	18.28	11.51	16.62	1.11	0.81	35.85	21.98	2.74
3200	12.26	17.99	11.05	16.16	1.10	0.81	36.17	21.60	2.74
3400	11.94	17.69	10.66	15.55	1.10	0.81	35.79	21.89	2.79
3600	11.62	17.45	10.29	15.05	1.10	0.82	35.90	21.96	2.83
3800	11.31	17.20	10.00	14.72	1.09	0.82	36.15	22.09	2.87
4000	11.00	16.94	9.79	14.43	1.09	0.82	35.66	22.01	2.91
4100	10.85	16.82	9.71	14.28	1.09	0.82	35.53	22.07	3.01
4300	10.56	16.57	9.55	14.03	1.09	0.83	36.31	21.75	3.00
4500	10.27	16.30	9.39	13.80	1.09	0.82	36.12	21.92	3.09
4700	9.99	16.08	9.24	13.48	1.10	0.82	36.08	22.06	3.14
4900	9.72	15.85	9.10	13.05	1.10	0.82	35.82	22.01	3.24
5100	9.44	15.62	8.93	12.62	1.10	0.81	35.87	21.80	3.28
5300	9.15	15.44	8.64	12.07	1.10	0.81	35.47	21.54	3.41
5400	9.00	15.35	8.52	11.76	1.10	0.80	35.37	21.29	3.38
5600	8.71	15.19	8.20	11.07	1.10	0.80	34.98	21.13	3.56
5800	8.39	15.05	7.88	10.41	1.10	0.79	34.55	21.16	3.64
6000	8.08	14.91	7.52	9.83	1.10	0.79	34.36	21.23	3.73
6200	7.74	14.81	7.18	9.28	1.10	0.78	34.41	20.77	3.77
6400	7.43	14.70	6.88	8.84	1.10	0.78	34.55	20.76	3.89
6600	7.11	14.60	6.65	8.47	1.10	0.79	34.98	20.78	3.93
6800	6.81	14.49	6.45	8.25	1.10	0.79	34.38	21.03	4.10
7000	6.52	14.38	6.29	8.13	1.10	0.80	34.53	20.97	4.23

## Typical Performance Data

## Without Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 83mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	17.97	25.46	9.86	11.23	1.26	0.79	34.86	19.16	2.13
100	17.46	24.34	10.90	12.56	1.21	0.79	35.07	21.71	2.18
200	16.79	23.12	12.99	14.94	1.20	0.78	35.13	21.29	2.24
300	16.46	22.67	14.04	16.34	1.20	0.78	35.64	21.05	2.36
500	16.09	22.27	14.58	17.22	1.21	0.78	35.09	21.28	2.48
600	15.96	22.14	14.55	17.29	1.20	0.78	35.87	21.30	2.47
800	15.71	21.88	14.29	17.10	1.20	0.79	35.93	21.54	2.32
1000	15.44	21.58	13.95	16.78	1.19	0.79	35.42	21.66	2.34
1200	15.16	21.28	13.66	16.58	1.18	0.79	35.48	21.48	2.41
1400	14.88	20.97	13.50	16.57	1.17	0.80	35.57	21.50	2.34
1600	14.59	20.58	13.40	16.62	1.16	0.80	35.50	21.56	2.43
1700	14.45	20.43	13.35	16.73	1.16	0.80	35.17	21.57	2.40
1900	14.16	20.07	13.27	16.99	1.15	0.80	35.40	21.62	2.39
2100	13.87	19.67	13.16	17.28	1.14	0.80	35.93	21.59	2.43
2300	13.57	19.33	13.01	17.44	1.13	0.80	35.58	21.58	2.48
2500	13.27	18.99	12.69	17.47	1.13	0.80	35.59	21.57	2.49
2700	12.96	18.67	12.25	17.26	1.12	0.80	35.22	21.60	2.57
2900	12.65	18.34	11.79	16.80	1.11	0.80	36.20	21.50	2.70
3000	12.50	18.19	11.56	16.51	1.11	0.80	36.41	21.48	2.70
3200	12.17	17.90	11.08	16.05	1.10	0.81	36.21	21.12	2.72
3400	11.85	17.62	10.68	15.45	1.10	0.81	35.86	21.33	2.73
3600	11.53	17.37	10.31	14.98	1.10	0.82	36.63	21.46	2.77
3800	11.22	17.14	10.00	14.61	1.09	0.82	36.58	21.52	2.82
4000	10.91	16.86	9.78	14.30	1.09	0.82	35.95	21.51	2.88
4100	10.77	16.78	9.70	14.18	1.10	0.83	36.66	21.50	2.94
4300	10.47	16.49	9.54	13.94	1.09	0.82	36.05	21.20	2.94
4500	10.18	16.25	9.39	13.71	1.10	0.82	36.38	21.36	3.03
4700	9.91	16.03	9.23	13.38	1.10	0.82	36.20	21.50	3.05
4900	9.64	15.80	9.11	12.95	1.10	0.82	36.21	21.44	3.17
5100	9.36	15.59	8.92	12.52	1.10	0.81	36.39	21.31	3.21
5300	9.08	15.40	8.64	11.98	1.10	0.81	35.98	21.05	3.32
5400	8.93	15.33	8.52	11.65	1.11	0.80	35.36	20.75	3.32
5600	8.63	15.15	8.20	11.01	1.11	0.80	35.28	20.66	3.46
5800	8.32	15.01	7.88	10.36	1.11	0.79	35.33	20.68	3.53
6000	8.01	14.88	7.53	9.75	1.10	0.79	34.76	20.68	3.65
6200	7.67	14.78	7.17	9.22	1.11	0.78	35.21	20.24	3.67
6400	7.36	14.67	6.88	8.80	1.11	0.78	34.89	20.29	3.80
6600	7.05	14.58	6.67	8.42	1.10	0.78	35.19	20.24	3.86
6800	6.75	14.45	6.46	8.19	1.10	0.79	34.52	20.55	4.00
7000	6.46	14.35	6.29	8.09	1.11	0.80	34.73	20.43	4.12



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



## Typical Performance Data

## Without Full 2-Port Extension

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 101mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.20	25.84	9.82	11.51	1.28	0.80	33.81	21.09	2.24
100	17.68	24.43	10.91	12.67	1.20	0.79	35.07	22.74	2.21
200	17.00	23.23	13.04	15.12	1.19	0.78	35.77	22.36	2.25
300	16.68	22.77	14.07	16.51	1.19	0.77	35.70	22.12	2.38
500	16.31	22.40	14.62	17.48	1.20	0.77	35.76	22.34	2.49
600	16.18	22.30	14.59	17.54	1.20	0.78	35.92	22.31	2.47
800	15.92	22.02	14.33	17.33	1.19	0.78	35.76	22.58	2.35
1000	15.65	21.74	13.98	17.02	1.18	0.79	35.60	22.77	2.36
1200	15.37	21.42	13.71	16.80	1.17	0.79	35.72	22.57	2.39
1400	15.09	21.08	13.54	16.78	1.16	0.79	35.92	22.59	2.34
1600	14.79	20.74	13.45	16.84	1.16	0.79	36.03	22.72	2.41
1700	14.65	20.55	13.41	16.98	1.15	0.79	35.83	22.67	2.38
1900	14.35	20.23	13.31	17.19	1.15	0.80	36.02	22.72	2.39
2100	14.06	19.83	13.23	17.53	1.14	0.79	35.76	22.73	2.44
2300	13.75	19.46	13.05	17.67	1.13	0.79	35.93	22.65	2.49
2500	13.45	19.12	12.75	17.72	1.12	0.79	35.82	22.64	2.51
2700	13.14	18.76	12.31	17.54	1.12	0.80	36.37	22.67	2.59
2900	12.82	18.48	11.81	17.06	1.11	0.80	35.65	22.55	2.70
3000	12.67	18.31	11.58	16.79	1.11	0.80	35.61	22.51	2.70
3200	12.34	18.02	11.11	16.35	1.10	0.81	36.11	22.05	2.73
3400	12.02	17.75	10.72	15.70	1.10	0.81	35.71	22.36	2.74
3600	11.70	17.49	10.34	15.18	1.10	0.81	35.26	22.49	2.80
3800	11.38	17.24	10.04	14.84	1.09	0.82	35.88	22.57	2.86
4000	11.07	16.97	9.83	14.54	1.09	0.82	35.52	22.55	2.91
4100	10.93	16.86	9.76	14.38	1.09	0.82	35.63	22.55	2.98
4300	10.63	16.59	9.59	14.12	1.09	0.82	36.14	22.21	2.97
4500	10.34	16.35	9.44	13.87	1.10	0.82	35.50	22.39	3.05
4700	10.06	16.12	9.30	13.56	1.10	0.82	35.75	22.54	3.10
4900	9.79	15.89	9.15	13.12	1.10	0.81	36.04	22.48	3.19
5100	9.51	15.67	8.96	12.67	1.10	0.81	35.43	22.33	3.24
5300	9.23	15.47	8.67	12.14	1.10	0.80	34.80	21.99	3.36
5400	9.07	15.39	8.56	11.78	1.10	0.80	35.31	21.68	3.34
5600	8.78	15.21	8.22	11.15	1.10	0.79	34.80	21.65	3.51
5800	8.47	15.07	7.90	10.48	1.10	0.79	34.12	21.62	3.59
6000	8.16	14.94	7.55	9.86	1.10	0.78	34.14	21.69	3.71
6200	7.81	14.85	7.20	9.34	1.10	0.78	34.10	21.23	3.72
6400	7.50	14.73	6.90	8.93	1.10	0.79	34.11	21.22	3.83
6600	7.18	14.62	6.67	8.51	1.10	0.78	34.46	21.23	3.90
6800	6.88	14.50	6.48	8.30	1.10	0.79	34.37	21.56	4.04
7000	6.60	14.40	6.32	8.21	1.10	0.80	34.34	21.43	4.18










P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS










## Typical Performance Curves

### Full 2-Port Extension



## Typical Performance Curves

### Without Full 2-Port Extension





## Environmental Specifications

## ENV80

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	