

Bandpass Filter

RBP-75+

50Ω 60 to 90 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.1W at 25°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	2
RF OUT	6
GROUND	1, 3, 4, 5, 7, 8

Outline Drawing





Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R	wt	
.050	.040	.195	.390	.120	.390	.070	grams	
1.27	1.02	4.95	9.91	3.05	9.91	1.78	0.25	

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



Features

- linear phase, up to ± 4 deg. typ @ Fc ± 15 MHz
- good VSWR, 1.3:1 typ @ passband
- high rejection
- small size 0.35" X 0.35"
- shielded case
- aqueous washable

Applications

- military radar
- harmonic rejection
- transmitters/receivers



CASE STYLE: GP731

Generic photo used for illustration purposes only

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.)	VSWR (:1)		
		Loss > 20dB	Loss > 35dB	Passband	Stopband				
Fc	F1 - F2	F3	F4	F5	F6	Fc ± 15MHz	Typ.	Max.	
75	60 - 90	37	122	30	155 - 2000	±8	1.3	1.7	18

Typical Frequency Response




Functional Schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg.)
0.5	81.04	10825.01	60.0	4.61
28.0	50.32	99.37	62.0	1.92
37.0	29.43	29.94	64.0	0.11
43.0	14.77	8.67	66.0	-1.04
46.5	7.36	2.96	68.0	-1.69
50.0	3.52	1.36	70.0	-1.86
60.0	2.02	1.25	71.0	-1.82
70.0	1.81	1.13	73.0	-1.49
75.0	1.82	1.17	74.0	-1.25
80.0	1.89	1.09	75.0	-0.97
90.0	2.50	1.27	76.0	-0.68
95.0	4.21	2.21	78.0	-0.07
100.0	8.84	5.56	80.0	0.49
105.0	14.58	10.93	82.0	0.97
122.0	29.82	30.01	84.0	1.22
173.0	51.75	83.61	86.0	1.15
500.0	94.19	250.42	88.0	0.44
2000.0	50.37	55.92	90.0	-0.76

RBP-75+ VSWR



RBP-75+ INSERTION PHASE & DEVIATION FROM LINEAR PHASE



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Metal Shield Band Pass Filter

RBP-75+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	93.86	94.10	96.31	0.00	0.01	0.00	0.01	0.01	0.01
10	101.27	101.38	96.42	0.01	0.01	0.02	0.01	0.01	0.01
20	69.39	69.29	69.90	0.05	0.06	0.08	0.04	0.06	0.07
28	50.29	50.01	49.80	0.14	0.17	0.20	0.12	0.16	0.20
37	29.59	29.34	29.12	0.50	0.61	0.70	0.47	0.58	0.69
43	14.70	14.61	14.53	1.71	2.02	2.29	1.71	2.02	2.30
50	3.14	3.51	3.79	14.52	15.40	16.15	16.31	17.39	18.02
60	1.84	2.11	2.32	17.86	18.05	18.37	16.91	17.15	17.58
70	1.62	1.87	2.08	33.78	32.88	30.96	39.66	46.96	37.83
75	1.66	1.91	2.11	28.73	32.85	40.72	27.14	31.41	42.33
80	1.76	2.02	2.25	34.64	29.91	26.73	28.65	29.24	28.34
90	2.36	2.73	3.04	22.09	20.85	19.76	28.53	27.69	25.68
95	3.94	4.51	4.99	9.62	9.07	8.60	9.89	9.51	9.15
100	8.45	9.09	9.61	3.41	3.43	3.43	3.41	3.51	3.59
105	14.20	14.73	15.15	1.63	1.73	1.80	1.60	1.75	1.87
110	19.50	19.93	20.27	1.02	1.11	1.19	0.99	1.12	1.23
120	28.11	28.43	28.68	0.59	0.66	0.72	0.56	0.66	0.74
122	29.58	29.89	30.11	0.54	0.61	0.67	0.52	0.61	0.68
130	34.81	35.04	35.24	0.41	0.47	0.53	0.39	0.47	0.53
140	40.20	40.38	40.54	0.31	0.37	0.42	0.30	0.37	0.42
150	44.65	44.80	44.89	0.26	0.31	0.35	0.24	0.31	0.36
160	48.38	48.46	48.51	0.21	0.27	0.31	0.20	0.27	0.31
170	51.58	51.61	51.60	0.19	0.23	0.28	0.17	0.23	0.28
173	52.44	52.42	52.45	0.18	0.23	0.27	0.16	0.23	0.27
200	58.54	58.44	58.35	0.13	0.18	0.22	0.11	0.18	0.23
300	69.59	69.41	69.76	0.07	0.13	0.18	0.04	0.12	0.18
400	75.71	76.44	76.39	0.06	0.13	0.18	0.03	0.13	0.19
500	84.13	84.25	83.06	0.07	0.14	0.20	0.02	0.14	0.21
600	91.01	94.52	99.33	0.07	0.16	0.23	0.02	0.16	0.25
700	90.82	85.99	91.26	0.08	0.18	0.26	0.02	0.18	0.27
800	83.59	84.17	87.74	0.09	0.20	0.29	0.02	0.20	0.30
900	83.33	84.82	84.76	0.10	0.22	0.32	0.03	0.22	0.33
1000	84.22	89.26	85.49	0.11	0.24	0.35	0.04	0.24	0.35
1200	84.68	85.59	84.33	0.14	0.29	0.40	0.05	0.27	0.40
1400	75.30	80.58	74.96	0.17	0.32	0.44	0.06	0.29	0.43
1500	67.73	64.73	68.70	0.19	0.34	0.47	0.06	0.30	0.45
1600	69.80	66.51	68.38	0.19	0.35	0.48	0.07	0.32	0.47
1700	67.14	65.21	66.90	0.20	0.36	0.50	0.08	0.33	0.49
1800	60.70	65.47	59.72	0.21	0.37	0.51	0.09	0.34	0.51
2000	64.47	65.52	61.74	0.22	0.39	0.54	0.08	0.35	0.56
2200	61.45	54.83	61.54	0.22	0.42	0.57	0.08	0.38	0.58
2400	54.41	51.96	57.10	0.23	0.43	0.59	0.08	0.39	0.61
2500	49.34	52.69	53.06	0.24	0.44	0.61	0.09	0.40	0.63
2600	48.73	51.52	48.72	0.25	0.46	0.63	0.09	0.42	0.63
2700	48.32	47.90	47.73	0.26	0.47	0.64	0.08	0.42	0.63
2800	46.52	47.35	47.82	0.28	0.50	0.69	0.10	0.44	0.64
3000	44.21	44.31	43.99	0.77	0.74	0.82	0.47	0.76	0.83
3200	40.01	41.11	42.44	0.30	0.57	0.72	0.09	0.53	0.69
3400	38.44	38.90	38.94	0.30	0.60	0.77	0.09	0.52	0.76
3500	38.66	37.53	36.66	0.38	0.66	0.82	0.09	0.54	0.79
3600	37.75	35.95	36.62	0.37	0.68	0.90	0.10	0.57	0.85
3700	36.39	34.30	35.13	0.43	0.75	1.00	0.12	0.63	0.93
3800	32.23	32.65	31.80	0.51	0.87	1.23	0.16	0.66	1.03
4000	28.85	28.84	26.96	1.06	1.87	2.81	0.26	0.82	1.32

REV. X2
RBP-75+
101006
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Metal Shield Band Pass Filter

RBP-75+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
60	27.68	27.57	27.46
61	26.91	26.80	26.69
62	26.24	26.14	26.06
63	25.66	25.58	25.49
64	25.20	25.10	25.03
65	24.77	24.67	24.59
66	24.34	24.26	24.16
67	23.97	23.91	23.83
68	23.63	23.57	23.48
69	23.32	23.28	23.21
70	23.04	23.01	22.97
71	22.79	22.78	22.75
72	22.59	22.59	22.58
73	22.40	22.39	22.40
74	22.27	22.28	22.29
75	22.17	22.21	22.22
76	22.14	22.18	22.19
77	22.11	22.15	22.19
78	22.12	22.18	22.20
79	22.19	22.23	22.25
80	22.26	22.29	22.34
81	22.39	22.42	22.47
82	22.53	22.58	22.62
83	22.70	22.77	22.82
84	22.95	23.03	23.10
85	23.25	23.36	23.45
86	23.63	23.78	23.88
87	24.14	24.31	24.44
88	24.79	24.98	25.13
89	25.60	25.79	25.94
90	26.58	26.73	26.83
95	30.34	29.75	29.15
100	23.55	22.74	22.03
110	9.58	9.48	9.40
120	5.21	5.21	5.22
130	3.54	3.52	3.54
140	2.58	2.60	2.67
150	2.13	2.06	2.12
160	1.61	1.91	1.62
170	1.32	1.28	1.59
210	0.88	1.04	0.88
220	0.87	0.88	0.99
230	0.68	0.62	0.87
240	0.73	0.74	0.48
250	0.69	0.88	0.64
260	0.94	0.85	0.46
270	0.45	0.49	0.50
280	0.76	0.23	0.70
290	0.85	0.40	0.91
300	0.66	0.90	0.55
310	0.51	0.96	0.47
320	0.40	0.30	0.65
330	0.24	0.78	0.64

REV. X2
RBP-75+
101006
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves



REV. X2
RBP-75+
101006
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions

GP731



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP731	.350 (8.89)	.350 (8.89)	.100 (2.54)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP731	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.4 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	R59289	NEW RELEASE (FROM RAVON)	02/05	DK	HH
A	M101151	ADDED "RBP" & CORRECTED PIN CONNECTION TO DESCRIPTION OF PL-DWG.	10/10/05	MMG	DJ
B	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR GP731 CASE STYLE, "qf" PIN CONNECTION.**



- NOTES:**
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAVON) 10 FEB 05
	CHECKED	RZ (RAVON) 10 FEB 05
	APPROVED	HH (RAVON) 10 FEB 05



Mini-Circuits®


13 Neptune Avenue
Brooklyn NY 11235

PL, qf, GP731, RBP, TB-332

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-176	B
FILE:	98PL176	SCALE: 5:1	SHEET: 1 OF 1

Evaluation Board and Circuit




TB-332



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215