



USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix RC-1SP6T-26

50Ω DC to 26.5 GHz SMA-Female

THE BIG DEAL

- Mechanical SP6T switch
- Excellent performance to 26.5 GHz
- High reliability, 2 million switch cycles
- 5W power rating (cold switching)

APPLICATIONS

- 5G node / device testing
- Automated test equipment
- Fail-safe / redundancy switching



CASE STYLE: PF2909

[DOWNLOAD](#) SOFTWARE PACKAGE

RoHS Compliant

See our website for RoHS Compliance methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits' RC-1SP6T-26 is an electro-mechanical SP6T switch operating over an extremely wide bandwidth, from DC to 26.5 GHz with high isolation and low insertion loss. The absorptive switch is of a failsafe and break-before-make-configuration, with a minimum lifetime of 2 million cycles per switch position, when used within the noted specifications.

The switch box is constructed in a compact, rugged metal case (5.5 x 6.0 x 2.75") with 7 SMA (f) RF connectors on the front panel. The switch is controlled via USB or Ethernet, allowing control directly from a PC, or remotely over a network. Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

KEY FEATURES

Feature	Advantages
Mechanical SP6T switch	Mechanical absorptive switches provide high reliability, repeatable high performance and internal terminations of input signals on the disconnected paths
Operation from DC to 26.5 GHz	Supports a wide range of RF test and signal routing applications, including 2G, 3G, 4G and 5G, with a single device
Break-before-make configuration	Prevents a momentary connection of the old and new signal paths, reducing the inconsistent transient effects that could otherwise be observed during switching
USB & Ethernet control	USB HID and Ethernet (HTTP / Telnet) interfaces provide easy compatibility with a wide range of software setups and programming environments
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments

REV. A
ECO-009505
RC-1SP6T-26
MCL NY
240229





USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix **RC-1SP6T-26**

Mini-Circuits

50Ω DC to 26.5 GHz SMA-Female

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Conditions (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		26.5	GHz
Insertion Loss	DC - 8	—	0.10	0.30	dB
	8 - 18	—	0.25	0.50	
	18 - 26.5	—	0.40	0.70	
Isolation	DC - 6	70	90	—	dB
	6 - 18	60	90	—	
	18 - 26.5	55	80	—	
VSWR	DC - 8	—	1.20	—	:1
	8 - 18	—	1.35	—	
	18 - 26.5	—	1.50	—	
Switching Time	—	—	25	—	ms
RF Input Power (Cold Switching) ¹	DC - 8	—	—	20	W
	8 - 18	—	—	10	
	18 - 26.5	—	—	5	
Switch Lifetime	100mW hot switching ²	2	—	—	million cycles
	1W hot switching	—	1	—	
Rated Voltage	24V _{DC} input	23	24	25	V
	USB port	—	5	—	
Rated Current (24V DC Input)	in state 1-6	—	330	—	mA
	in state 0	—	90	120	
Rated Current (USB)		—	10	20	mA

1. Maximum power for any connected through path as stated; maximum power into any internal termination is 1W per port, 3W total per switch

2. Hot switching powers above this level will degrade the switch lifetime

ABSOLUTE MAXIMUM RATINGS

Parameters	Ratings
Operating Temperature	0°C to 40°C
Storage Temperature	-15°C to 85°C
Supply Voltage	26V





USB & ETHERNET CONTROLLED


RF SP6T Switch Matrix RC-1SP6T-26

Mini-Circuits

50Ω DC to 26.5 GHz SMA-Female

SWITCHING CONFIGURATION:


- Normally open (all port disconnected)
- Absorptive (internal terminations on ports J1-J6)



CONNECTIONS

Port Name	Connector Type
RF Switch (Com, 1, 2, 3, 4, 5 & 6)	SMA female
USB	USB type-B
Ethernet / LAN	RJ45
24V _{DC} Input	2.1mm center positive DC socket

OUTLINE DRAWING (PF2909)



Weight: 1110 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl.± .01 inch; 3 Pl.± .005 inch.

Mini-Circuits






USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix RC-1SP6T-26

Mini-Circuits

50Ω DC to 26.5 GHz SMA-Female

TYPICAL PERFORMANCE DATA





USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix **RC-1SP6T-26**

Mini-Circuits

50Ω DC to 26.5 GHz SMA-Female

SOFTWARE SPECIFICATIONS

SOFTWARE & DOCUMENTATION DOWNLOAD:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from: <https://www.minicircuits.com/softwaredownload/rfswitchcontroller.html>
- Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID & Ethernet (HTTP & Telnet)	
System Requirements	GUI	Windows 98 or later
	USB API DLL	Windows 98 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 98 or later
	Ethernet	Windows, Linux or Mac computer with a network port and Ethernet TCP/IP support
Hardware	Pentium II or later with 256 MB RAM	

APPLICATION PROGRAMMING INTERFACE (API)

ETHERNET SUPPORT:

- Simple ASCII / SCPI command set for attenuator control
- Communication via HTTP or Telnet
- Supported by most common programming environment

USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note AN-49-001 for summary of supported environments)

USB SUPPORT (LINUX):

- Direct USB programming using a series of USB interrupt codes

Full programming instructions and examples available for a wide range of programming environments / languages.





USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix RC-1SP6T-26

50Ω DC to 26.5 GHz SMA-Female

MAIN SOFTWARE CONTROL SCREEN: INDEPENDENT CONTROL OF ONE SP6T SWITCH

- Power handling is specified with RF applied to the COM port and output load connected to either 1,2,3,4,5 or 6 of the respective switch.
- When connecting a coaxial semi flex cable, tighten connectors alternately using an 8in/lb torque wrench to insure proper contact at each end.

Step	SWA	dwell Time	Units	Exec Program
Step 1	COM->1	500	mSec	
Step 2	COM->2	600	mSec	
Step 3	COM->3	670	mSec	
Step 4	COM->4	1020	mSec	
Step 5	COM->5	1400	mSec	
Step 6	COM->6	804	mSec	
Step 7	COM->2	1200	mSec	
Step 8	COM->3	1500	mSec	





USB & ETHERNET CONTROLLED

RF SP6T Switch Matrix RC-1SP6T-26



Mini-Circuits






50Ω DC to 26.5 GHz SMA-Female

ORDERING INFORMATION

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
RC-1SP6T-26	USB & Ethernet controlled SP6T switch matrix

Included Accessories	Part No.	Description
	AC/DC-24-3W1	AC/DC 24V _{DC} Grounded Power Adaptor. Operating temperature: 0°C to +40°C, I _{Max} =2.5A
See Below	CBL-3W1-XX	AC Power Cord (Select one power cord from below with each Switch Matrix box)
	USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)

AC Power Cords ³	Part No.	Description
	CBL-3W1-US	Power Cord for United States
	CBL-3W1-EU	Power Cord for Europe
	CBL-3W1-UK	Power Cord for United Kingdom
	CBL-3W1-AU	Power Cord for Australia and China
	CBL-3W1-IL	Power Cord for Israel

3. If you need a Power cord for a country not listed please contact testsolutions@minicircuits.com

OPTIONAL ACCESSORIES

USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-7+	6.8 ft (2.1 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-11+	11 ft (3.4 m) USB Cable: USB type A(Male) to USB type B(Male)
CBL-RJ45-MM-5+	5 ft (1.5 m) Ethernet cable: RJ45(Male) to RJ45(Male) Cat 5E cable
BKT-272-08+	Bracket (One set of 2 each)

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)						ISOLATION (Inactive Paths) (dB)					
	IN-J1	IN-J2	IN-J3	IN-J4	IN-J5	IN-J6	IN-J1 (J2 Active)	IN-J2 (J3 Active)	IN-J3 (J4 Active)	IN-J4 (J5 Active)	IN-J5 (J6 Active)	IN-J6 (J1 Active)
100	0.01	0.01	0.01	0.01	0.01	0.01	104.73	109.61	99.92	110.55	104.62	102.15
200	0.01	0.01	0.01	0.01	0.01	0.01	110.49	104.65	112.01	108.99	105.82	103.88
400	0.02	0.02	0.02	0.02	0.02	0.02	102.85	104.10	106.56	106.05	109.96	111.53
600	0.02	0.02	0.02	0.02	0.02	0.02	111.15	110.31	111.70	116.16	104.29	107.61
800	0.03	0.03	0.02	0.03	0.03	0.03	106.60	109.95	106.10	101.34	112.00	106.92
1000	0.03	0.03	0.03	0.03	0.03	0.03	113.28	106.98	114.39	103.55	109.55	110.73
1200	0.03	0.03	0.03	0.03	0.03	0.04	103.89	130.18	114.95	105.76	113.86	112.09
1400	0.04	0.04	0.04	0.04	0.04	0.04	110.22	106.79	111.39	102.76	115.02	108.69
1600	0.04	0.04	0.04	0.04	0.04	0.04	103.73	112.09	119.83	114.76	105.94	105.25
1800	0.04	0.04	0.04	0.04	0.04	0.04	113.13	111.40	111.83	116.91	116.78	111.03
2000	0.05	0.05	0.04	0.05	0.05	0.04	111.38	112.95	115.10	108.20	109.12	106.96
2200	0.05	0.05	0.04	0.05	0.05	0.05	103.92	127.41	112.68	103.23	116.29	104.57
2600	0.05	0.06	0.05	0.06	0.05	0.05	106.25	115.83	100.56	98.84	123.42	107.23
2800	0.06	0.06	0.06	0.06	0.05	0.06	103.20	107.42	103.06	99.72	112.22	112.11
3000	0.06	0.06	0.06	0.06	0.06	0.06	110.11	106.64	114.12	98.82	115.45	109.27
3200	0.06	0.06	0.06	0.06	0.06	0.06	99.60	109.01	108.31	99.72	110.96	109.01
3400	0.06	0.06	0.06	0.06	0.06	0.06	106.22	101.57	114.64	108.04	106.87	109.98
3600	0.06	0.06	0.06	0.06	0.06	0.06	109.49	99.68	110.60	106.35	103.98	110.17
3800	0.07	0.06	0.06	0.07	0.06	0.07	111.30	105.11	112.37	104.82	112.52	101.07
4000	0.07	0.07	0.06	0.07	0.06	0.07	105.20	113.15	113.64	102.55	120.62	116.41
4200	0.07	0.07	0.06	0.07	0.06	0.07	109.86	108.86	112.87	101.02	116.36	109.98
4400	0.07	0.07	0.07	0.07	0.06	0.07	104.45	101.91	105.31	108.45	106.56	101.51
4600	0.07	0.07	0.07	0.07	0.06	0.07	103.55	102.65	111.45	108.96	106.62	106.02
4800	0.07	0.07	0.07	0.07	0.07	0.07	108.81	108.47	115.16	103.80	112.46	109.39
5000	0.08	0.07	0.07	0.07	0.07	0.07	107.31	107.21	105.47	102.26	102.85	112.18
5200	0.08	0.07	0.07	0.08	0.07	0.08	113.88	108.80	106.99	106.78	110.55	108.56
5400	0.08	0.07	0.07	0.08	0.07	0.08	106.82	111.37	105.30	109.61	115.47	105.80
5600	0.08	0.07	0.07	0.08	0.07	0.08	112.54	107.54	103.50	111.99	109.55	104.52
5800	0.09	0.08	0.08	0.09	0.08	0.08	108.32	106.95	101.22	105.44	102.39	111.99
6000	0.09	0.08	0.08	0.09	0.08	0.09	114.07	104.99	119.56	116.06	113.19	101.22
6200	0.09	0.08	0.08	0.09	0.08	0.09	105.97	105.05	101.20	102.94	105.72	105.18
6400	0.10	0.08	0.09	0.10	0.09	0.09	108.42	108.95	106.97	116.81	111.14	100.81
6600	0.10	0.08	0.09	0.10	0.09	0.10	115.64	109.06	103.63	103.73	110.33	114.03
6800	0.10	0.09	0.09	0.10	0.09	0.10	110.15	107.59	98.56	108.89	108.88	108.77
7000	0.10	0.09	0.09	0.10	0.09	0.10	110.09	111.40	105.41	98.86	106.87	120.03
7200	0.10	0.09	0.09	0.11	0.09	0.10	119.16	105.54	103.48	112.70	105.81	111.76
7400	0.11	0.09	0.09	0.11	0.10	0.10	109.12	111.83	113.43	104.43	110.83	98.84
7600	0.11	0.09	0.10	0.11	0.10	0.11	125.41	111.23	105.88	112.05	101.64	133.35
7800	0.11	0.09	0.10	0.11	0.10	0.11	104.87	118.71	105.90	100.99	104.37	106.29
8000	0.11	0.10	0.10	0.11	0.10	0.11	101.01	117.20	108.73	100.74	101.57	103.68
8200	0.11	0.10	0.10	0.11	0.10	0.11	103.21	115.74	100.53	102.05	111.04	98.03
8400	0.11	0.10	0.10	0.11	0.10	0.11	104.90	111.66	124.37	103.28	105.28	107.15
8600	0.11	0.10	0.10	0.11	0.10	0.11	107.33	104.44	105.55	105.51	105.72	105.80
8800	0.11	0.10	0.10	0.11	0.10	0.11	99.41	117.44	120.35	111.55	121.71	111.29
9000	0.11	0.10	0.10	0.11	0.10	0.11	106.11	104.99	110.45	104.95	111.39	102.03
9200	0.11	0.10	0.10	0.11	0.10	0.11	105.20	110.99	106.58	109.27	105.70	112.71
9400	0.11	0.10	0.10	0.11	0.10	0.11	111.51	106.82	111.48	104.84	102.88	109.12
9600	0.11	0.11	0.10	0.12	0.11	0.11	104.74	99.23	104.41	98.98	102.20	101.69
9800	0.11	0.10	0.10	0.11	0.11	0.11	106.36	111.58	107.20	107.07	112.48	102.26
10000	0.11	0.11	0.11	0.12	0.11	0.11	102.38	97.35	132.04	105.23	106.33	104.36
12000	0.13	0.11	0.11	0.14	0.11	0.12	106.77	102.12	106.97	101.90	111.62	103.33
14000	0.13	0.12	0.12	0.13	0.12	0.12	101.38	99.73	111.48	102.72	104.28	103.10
16000	0.19	0.17	0.17	0.20	0.16	0.19	116.91	92.27	94.60	105.12	93.21	99.14
18000	0.27	0.24	0.25	0.29	0.24	0.27	100.84	101.53	100.57	105.49	92.87	112.61
20000	0.23	0.21	0.21	0.23	0.22	0.22	94.36	107.61	87.07	90.26	98.36	93.14
22000	0.23	0.21	0.20	0.24	0.23	0.20	89.79	83.88	90.19	86.35	93.67	84.31
24000	0.36	0.35	0.35	0.40	0.37	0.33	84.43	96.95	89.43	98.07	93.65	99.43
26000	0.23	0.25	0.24	0.24	0.26	0.26	91.38	88.14	98.24	85.03	94.66	97.27
26500	0.23	0.23	0.23	0.23	0.24	0.27	105.85	92.19	91.50	101.34	93.21	92.80



Xtra Long Life

USB/ETHERNET RF SP6T SWITCH MATRIX

RC-1SP6T-26

Typical Performance Data

FREQUENCY (MHz)	VSWR (Active Ports) (:1)							VSWR (Inactive Ports) (:1)					
	IN	J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6
100	1.00	1.00	1.00	1.00	1.00	1.00	1.00	1.01	1.01	1.00	1.01	1.02	1.01
200	1.01	1.01	1.01	1.01	1.01	1.01	1.01	1.00	1.00	1.00	1.01	1.02	1.00
400	1.02	1.02	1.02	1.02	1.02	1.02	1.01	1.00	1.00	1.01	1.01	1.02	1.00
600	1.02	1.02	1.03	1.03	1.03	1.03	1.02	1.00	1.00	1.01	1.01	1.01	1.00
800	1.03	1.03	1.04	1.03	1.03	1.04	1.03	1.01	1.00	1.01	1.02	1.01	1.01
1000	1.04	1.04	1.04	1.04	1.04	1.05	1.04	1.01	1.01	1.01	1.02	1.01	1.01
1200	1.05	1.05	1.05	1.05	1.05	1.05	1.04	1.01	1.01	1.02	1.03	1.01	1.01
1400	1.06	1.06	1.06	1.06	1.06	1.06	1.05	1.01	1.01	1.02	1.03	1.00	1.01
1600	1.06	1.06	1.07	1.07	1.07	1.07	1.06	1.02	1.02	1.02	1.03	1.01	1.02
1800	1.07	1.07	1.08	1.07	1.07	1.07	1.06	1.02	1.02	1.03	1.04	1.01	1.02
2000	1.07	1.07	1.08	1.08	1.07	1.08	1.07	1.02	1.02	1.03	1.04	1.01	1.02
2200	1.08	1.08	1.09	1.08	1.08	1.08	1.07	1.02	1.02	1.04	1.04	1.02	1.03
2600	1.09	1.09	1.10	1.09	1.08	1.09	1.08	1.03	1.03	1.04	1.05	1.03	1.03
2800	1.09	1.09	1.10	1.09	1.09	1.09	1.08	1.03	1.03	1.05	1.05	1.03	1.03
3000	1.09	1.09	1.10	1.09	1.08	1.09	1.08	1.03	1.04	1.05	1.05	1.04	1.03
3200	1.09	1.09	1.10	1.09	1.08	1.09	1.08	1.04	1.04	1.05	1.05	1.05	1.04
3400	1.09	1.09	1.10	1.09	1.08	1.09	1.08	1.04	1.04	1.05	1.05	1.05	1.04
3600	1.09	1.09	1.10	1.08	1.07	1.08	1.07	1.04	1.04	1.05	1.05	1.05	1.04
3800	1.08	1.08	1.10	1.08	1.07	1.08	1.07	1.04	1.05	1.06	1.05	1.06	1.04
4000	1.08	1.08	1.10	1.08	1.07	1.07	1.07	1.05	1.05	1.06	1.05	1.06	1.04
4200	1.07	1.07	1.09	1.07	1.06	1.07	1.06	1.05	1.05	1.06	1.05	1.07	1.05
4400	1.07	1.07	1.09	1.06	1.05	1.07	1.06	1.05	1.05	1.06	1.05	1.07	1.05
4600	1.06	1.07	1.08	1.06	1.05	1.06	1.06	1.05	1.05	1.06	1.05	1.07	1.05
4800	1.05	1.06	1.08	1.05	1.04	1.06	1.06	1.05	1.05	1.07	1.05	1.08	1.05
5000	1.04	1.05	1.07	1.05	1.03	1.06	1.06	1.06	1.05	1.07	1.05	1.08	1.05
5200	1.04	1.05	1.07	1.05	1.04	1.06	1.06	1.06	1.05	1.07	1.04	1.08	1.05
5400	1.03	1.05	1.06	1.05	1.03	1.06	1.06	1.06	1.05	1.07	1.04	1.08	1.05
5600	1.03	1.05	1.06	1.06	1.04	1.07	1.07	1.06	1.05	1.07	1.04	1.08	1.05
5800	1.03	1.05	1.05	1.06	1.05	1.07	1.07	1.06	1.05	1.07	1.04	1.08	1.05
6000	1.03	1.05	1.05	1.07	1.05	1.07	1.08	1.06	1.05	1.07	1.04	1.08	1.05
6200	1.04	1.06	1.05	1.07	1.06	1.08	1.08	1.06	1.05	1.07	1.04	1.08	1.05
6400	1.05	1.06	1.05	1.07	1.06	1.08	1.09	1.06	1.05	1.06	1.05	1.08	1.05
6600	1.05	1.06	1.05	1.08	1.06	1.09	1.09	1.07	1.05	1.07	1.05	1.07	1.06
6800	1.05	1.06	1.05	1.08	1.07	1.09	1.09	1.07	1.04	1.07	1.05	1.07	1.06
7000	1.06	1.07	1.05	1.08	1.07	1.09	1.09	1.07	1.04	1.06	1.06	1.07	1.06
7200	1.06	1.06	1.04	1.08	1.07	1.09	1.09	1.07	1.04	1.07	1.06	1.07	1.06
7400	1.06	1.06	1.04	1.08	1.06	1.08	1.09	1.07	1.04	1.06	1.07	1.06	1.06
7600	1.07	1.06	1.04	1.08	1.06	1.08	1.09	1.07	1.04	1.06	1.07	1.06	1.06
7800	1.07	1.06	1.04	1.07	1.06	1.08	1.09	1.07	1.04	1.07	1.07	1.06	1.06
8000	1.07	1.05	1.03	1.07	1.05	1.07	1.08	1.07	1.04	1.06	1.08	1.05	1.07
8200	1.07	1.05	1.03	1.07	1.05	1.07	1.08	1.07	1.04	1.06	1.08	1.05	1.07
8400	1.07	1.04	1.03	1.06	1.04	1.06	1.07	1.07	1.05	1.06	1.09	1.05	1.07
8600	1.07	1.04	1.03	1.06	1.04	1.05	1.06	1.07	1.05	1.06	1.09	1.05	1.07
8800	1.07	1.04	1.03	1.06	1.03	1.05	1.06	1.07	1.05	1.06	1.09	1.05	1.07
9000	1.07	1.04	1.03	1.06	1.04	1.05	1.06	1.07	1.05	1.06	1.09	1.04	1.08
9200	1.07	1.04	1.03	1.06	1.04	1.05	1.05	1.07	1.05	1.06	1.09	1.04	1.08
9400	1.08	1.04	1.04	1.06	1.05	1.05	1.05	1.07	1.06	1.06	1.09	1.04	1.08
9600	1.08	1.05	1.05	1.07	1.06	1.05	1.05	1.06	1.06	1.06	1.09	1.04	1.08
9800	1.09	1.06	1.05	1.08	1.07	1.05	1.06	1.07	1.06	1.06	1.09	1.04	1.08
10000	1.09	1.06	1.06	1.08	1.08	1.05	1.06	1.07	1.07	1.06	1.09	1.05	1.08
12000	1.07	1.08	1.07	1.08	1.09	1.04	1.07	1.09	1.11	1.08	1.12	1.10	1.11
14000	1.07	1.06	1.05	1.05	1.05	1.02	1.07	1.19	1.23	1.19	1.26	1.25	1.22
16000	1.25	1.23	1.19	1.19	1.24	1.18	1.22	1.24	1.31	1.24	1.31	1.33	1.30
18000	1.42	1.41	1.34	1.36	1.43	1.35	1.38	1.18	1.25	1.16	1.21	1.26	1.24
20000	1.28	1.28	1.22	1.22	1.28	1.24	1.26	1.15	1.24	1.16	1.20	1.23	1.22
22000	1.25	1.24	1.22	1.23	1.25	1.25	1.24	1.18	1.24	1.10	1.19	1.19	1.17
24000	1.50	1.50	1.47	1.49	1.55	1.50	1.42	1.05	1.05	1.09	1.07	1.05	1.02
26000	1.20	1.22	1.25	1.26	1.20	1.26	1.26	1.29	1.26	1.40	1.42	1.36	1.34
26500	1.19	1.14	1.16	1.17	1.07	1.19	1.26	1.35	1.34	1.45	1.49	1.43	1.41



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com





REV. OR
 RC-1SP6T-26
 6/21/2019
 Page 2 of 2

Xtra Long Life

USB/ETHERNET RF SP6T SWITCH MATRIX

RC-1SP6T-26

Typical Performance Data



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

REV. OR
RC-1SP6T-26
6/21/2019
Page 1 of 1

Outline Dimensions

PF2909



SHOWN WITH RUBBER FEET REMOVED AND BRACKETS INSTALLED.

Notes:

1. Case material: Aluminum (with protective coating to prevent corrosion).
2. Dimensions are in inches (mm). Tolerances: 2 Pl. \pm .01 inch; 3 Pl. \pm .005 inch.
3. Weight: 1110 grams.
4. Marking may contain other features or characters for internal lot control.

INSTRUCTIONS FOR MOUNTING BRACKETS:
TOOL REQUIRED: PHILLIPS HEAD SCREWDRIVER
STEP 1: REMOVE RUBBER FEET FROM THE BOTTOM OF THE UNIT. DO NOT DISCARD THE FASTENERS.
STEP 2: MOUNT THE BRACKETS WITH THE FASTENERS REMOVED IN STEP 1, USING THE COUNTER BORE HOLES IN THE BRACKET.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 40° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-15° to 85°C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F class 3