



USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly RCM-3SPDT-75F

75Ω DC to 2150 MHz F-Type Female

THE BIG DEAL


- 3 x mechanical SPDT absorptive switches
- Ethernet & USB control
- High isolation, 70 dB typ
- Fail-safe / redundancy switching
- 75Ω F-type connectors



APPLICATIONS

- Automated test & measurement systems
- L-band satellite communications infrastructure
- CATV / MoCA test systems
- DOCSIS 4.0
- Switch matrices

FUNCTIONAL BLOCK DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' RCM-3SPDT-75F houses 3 independently controlled electro-mechanical SPDT switches. Each switch operates over a wide bandwidth, from DC to 2150 MHz with high isolation and low insertion loss. The absorptive switches are fail-safe, with a break before make configuration, and excellent 75Ω impedance match.

The switch box is constructed in a compact, rugged metal case with all F-type (female) RF connectors on the front panel to enable easy access on a test bench. The switch box can be controlled via USB or Ethernet (supporting both HTTP and Telnet network protocols). Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments.

KEY FEATURES

Feature	Advantages
Mechanical switches	Mechanical absorptive switches provide low loss, high isolation, high reliability, repeatable performance and internal termination of input signals on the disconnected paths
75Ω characteristic impedance	Route or test 75Ω signals in their characteristic impedance for optimal performance, rather than working with 50Ω equipment and impedance matching
Fail-safe design	The switches revert to a known default state when the DC supply is removed, allowing their use in systems that must continue to operate safely in the event of power failure
Compact benchtop chassis	Compact chassis allows for flexible operation, both in lab and production test environments
Ethernet & USB control	USB HID and Ethernet (HTTP / Telnet) interfaces ensure compatibility with most software environments and connection requirements.

REV. A
ECO-017289
RCM-3SPDT-75F
MCL NY
230330





USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly **RCM-3SPDT-75F**

75Ω DC to 2150 MHz F-Type Female

Mini-Circuits

ELECTRICAL SPECIFICATIONS @ +25°C (EACH SWITCH)

Parameter	Conditions	Min.	Typ.	Max.	Units
Frequency Range		DC		2150	MHz
Insertion Loss	DC - 950 MHz		0.25	1.25	dB
	950 - 1850 MHz		0.60	1.50	
	1850 - 2150 MHz		0.75	1.50	
Isolation	DC - 950 MHz	50	77		dB
	950 - 1850 MHz	45	71		
	1850 - 2150 MHz	45	62		
Return Loss	DC - 950 MHz		17		dB
	950 - 1850 MHz		12		
	1850 - 2150 MHz		12		
Switching Time			25		ms
RF Input Power	Hot & cold switching			+20	dBm
	Into internal termination			+20	



USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly **RCM-3SPDT-75F**

75Ω DC to 2150 MHz F-Type Female

CONTROL INTERFACES

Ethernet Control	Supported Protocols	TCP / IP, HTTP, Telnet, DHCP, UDP (limited)
	Max Data Rate	10 Mbps (10Base-T Half Duplex)
USB Control	Supported Protocols	HID - Full Speed
	Min Communication Time ¹	3 ms typ

1. Based on the polling interval of the USB HID protocol (1 ms with 64 bytes per packet) and no other significant CPU or USB activity

SOFTWARE & DOCUMENTATION

Mini-Circuits' full software and support package including user guide, Windows GUI, API, programming manual and examples can be downloaded free of charge (refer to the last page for the download path).

A comprehensive set of software control options is provided:

- GUI for Windows – Simple software interface for control via Ethernet and USB
- Programming / automation via Ethernet
 - Complete set of control commands which can be sent via any supported protocol – simple to implement in the majority of modern programming environments
- Programming / automation via USB
 - DLL files provide a full API for Windows with a set of intuitive functions which can be implemented in any programming environment supporting .Net Framework or ActiveX
 - Direct USB programming is possible in any other environment (not supporting .Net or ActiveX)

Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS

	Requirements
Hardware	Intel i3 (or equivalent) or later
GUI (USB or Ethernet Control)	Windows 7 or later
USB API DLL	Windows 7 or later with support for Microsoft .Net Framework or ActiveX
USB Direct Programming	Windows 7 or later; Linux
Ethernet	Windows, Linux or macOS with Ethernet TCP / IP support

PROGRAMMING COMMANDS

The key ASCII / SCPI commands for control of the system for control via the Ethernet or USB API are summarized below (refer to the programming manual for full details):

Command / Query	Description
:MN?	Read model name
:SN?	Read serial number
:FIRMWARE?	Read firmware version
:SPDT:[sw_number]:STATE:[port]	Set a single switch state: <ul style="list-style-type: none"> • [sw_number] = 1 to 3 • [port] = 1 (J1 to J2) or 2 (J1 to J3) • Example :SPDT:1:STATE:2 (set SPDT 1 with J1 to J3)
:SPDT:[sw_number]:STATE?	Return a single switch state: <ul style="list-style-type: none"> • [sw_number] = 1 to 3 • Example :SPDT:1:STATE? (return the state of SPDT 1)






USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly RCM-3SPDT-75F


75Ω DC to 2150 MHz F-Type Female

GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS

- Connect via USB or Ethernet
- Run GUI in "demo mode" to evaluate software without a hardware connection






- View and set all switch states at the click of a button
- Update firmware





TYPICAL PERFORMANCE GRAPHS





USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly RCM-3SPDT-75F

75Ω DC to 2150 MHz F-Type Female

ABSOLUTE MAXIMUM RATINGS²

Parameter	Conditions	Limits	Units
Temperature	Operating	0 to +40	°C
	Storage	-15 to +85	
DC Supply Voltage		26	V
Input Power (No Damage)	Cold switching	+20	dBm
	Hot switching	+20	
	Into internal termination	+20	


2. Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

POWER SUPPLY

DC Voltage Input ³	+24V DC
-------------------------------	---------

3. Using included AC/DC-24-3W1 power supply adapter (110 / 240 V AC input)

FUNCTIONAL BLOCK DIAGRAM



CONNECTIONS

Port	Connector
SW 1 - J1, J2 & J3	F-type female
SW 2 - J1, J2 & J3	F-type female
SW 3 - J1, J2 & J3	F-type female
USB	USB type B
Ethernet / LAN	RJ45
24V DC Input	2.1mm center positive DC socket

J1 = Common port
J2, J3 = Input / output ports

SWITCH CONTROL LOGIC

Switch Command	1	2	3
:SPDT:1:STATE:1	J1 to J2	x	x
:SPDT:1:STATE:2	J1 to J3	x	x
:SPDT:2:STATE:1	x	J1 to J2	x
:SPDT:2:STATE:2	x	J1 to J3	x
:SPDT:3:STATE:1	x	x	J1 to J2
:SPDT:3:STATE:2	x	x	J1 to J3

x = Switch state not affected by this switch command




USB & ETHERNET CONTROLLED

3xSP2T Mechanical Switch Assembly RCM-3SPDT-75F

75Ω DC to 2150 MHz F-Type Female

CASE STYLE DRAWING



Weight: 2350 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03 inch; 3 Pl. ±.015 inch

PRODUCT MARKING

Product Marking: RCM-3SPDT-75F

Product Frequency: DC - 2150 MHz

Product ID: Contains product marking, regulatory compliance, bar code and serial number

Marking may contain other features or characters for internal lot control





USB & ETHERNET CONTROLLED




3xSP2T Mechanical Switch Assembly **RCM-3SPDT-75F**






75Ω DC to 2150 MHz F-Type Female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE [CLICK HERE](#)

Case Style	UV2068
Software, User Guide & Programming Manual	www.minicircuits.com/softwaredownload/ztm_rcm.html
Environmental Rating	ENV56
Regulatory Compliance	<p>Refer to our website for compliance methodologies and qualifications</p>  <p>www.minicircuits.com/quality/environmental_introduction.html</p>

Contact Us: testsolutions@minicircuits.com




Included Accessories	Part Number	Description
	AC/DC-24-3W1	AC/DC 24V DC grounded power adaptor. Operating temperature 0 to +40 °C, max current 2.5A, IEC C6 AC inlet.
	CBL-3W1-xx	AC power cord (IEC C5 connector to local plug) Select one option from the list below. Please contact testsolutions@minicircuits.com if your regions is not listed.
	USB-CBL-AB-7+	USB cable (6.8ft) type A to type B
	CBL-RJ45-MM-5+	Ethernet cable (5 ft)

AC Power Cord Options	Part Number	Description
	CBL-3W1-US	USA NEMA 5-15 plug (type B) to IEC C5 connector
	CBL-3W1-EU	Europe CEE 7/7 plug (type E/F) to IEC C5 connector
	CBL-3W1-UK	UK BS-1363 plug (type G) to IEC C5 connector
	CBL-3W1-AU	Australia & China AS/NZS 3112 plug (type I) to IEC C5 connector
	CBL-3W1-IL	Israel SI-32 plug (type H) to IEC C13 connector


- NOTES**
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Outline Dimensions

UV2068



FRONT PANEL FOR RCM WITH RUDAT, SPDT, SP4T, SP6T & MTS SWITCHES



FRONT PANEL FOR RCM WITH SP8T SWITCHES

Notes:

1. Case material: Aluminum alloy.
2. Finish: Clear chemical conversion coating
3. Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.03 inch; 3 Pl. ± 0.015 inch
4. Weight: 2350 grams.
5. Marking may contain other features or characters for internal lot control.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

RUDAT Programmable Attenuator Options:


UV2068



FRONT PANEL




FRONT PANEL



REAR PANEL

SINGLE RUDAT




REAR PANEL


DUAL RUDAT

SPDT Switch Options:


UV2068




SPDTA 18GHz
SPDTA 26GHz




DUAL SPDTA 18GHz
DUAL SPDTA 26GHz



SPDT 40GHz
SPDT 50GHz




DUAL SPDT 40GHz
DUAL SPDT 50GHz




SPDT 2.15GHz

MTS (Transfer) Switch Options:


UV2068




MTS 18GHz



DUAL MTS 18GHz




MTS 26GHz




DUAL MTS 26GHz

SP4T and SP6T Switch Options:

UV2068




SP4TA 18GHz




SP4TA 26GHz
SP4TA 40GHz
SP4TA 50GHz

5x FEMALE
CONNECTOR
26GHz SMA
40GHz 2.92mm
50GHz 2.4mm



SP6TA 12GHz
SP6TA 18GHz





SP6TA 26GHz
SP6TA 40GHz
SP6TA 50GHz

7x FEMALE
CONNECTOR
26GHz SMA
40GHz 2.92mm
50GHz 2.4mm

SP8T Switch Options:

UV2068



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



Environmental Specifications **ENV56**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 40° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-15° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3