

Surface Mount

Diplexer

RDP-272+

50Ω DC to 2700 MHz
(DC-950, 1700-2700 MHz)

The Big Deal

- Low insertion loss
- High isolation
- Miniature shielded package



CASE STYLE: CK605

Product Overview

RDP-272+ is a low-pass + high-pass combination device. Low pass port is designed for DC to 950 MHz and high pass port is designed for 1700 to 2700 MHz. This diplexer can be used in satellite systems, vehicle tracking, communication test sets and other multiband radio systems.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
Extended stopband rejection	Spurious rejection and avoids using additional filters.
Miniature shielded package	Reduced interference with the surrounding components.

 **Mini-Circuits**[®]

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine



Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS

For detailed performance specs
& shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

Surface Mount Diplexer

RDP-272+

50Ω DC to 2700 MHz (DC-950, 1700-2700 MHz)

Maximum Ratings

Operating Temperature -40C to 85°C

Storage Temperature -55°C to 100°C


RF Power Input 0.5W at 25°C

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

Pin Connections

HIGH PASS PORT	14
LOW PASS PORT	10
COMMON PORT	2
GROUND	1,3-9,11-13,15,16


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
.500	.500	.180	.100	.080	.115	.060	.040	.540	.060
12.7	12.7	4.572	2.54	2.032	2.921	1.524	1.016	13.72	1.524
L	M	N	P	Q	R	S	T	wt.	
.100	.135	.135	.115	.140	.070	.150	.070	grams	
2.54	3.429	3.429	2.921	3.556	1.778	3.81	1.778	1.0	

Demo Board MCL P/N: TB-10+ Suggested PCB Layout (PL-012)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
□ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- Low insertion loss
- 50Ω Impedance
- Combination of Low pass and High pass filters
- Miniature shielded package
- Aqueous washable

Applications

- Satellite systems
- Vehicle tracking
- Multiband radio systems



Generic photo used for illustration purposes only
CASE STYLE: CK605

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	Low Pass	DC-950	-	0.7	2.5	dB
		High Pass	1700-2700	-	0.7	1.5	
	Return Loss	Low Pass	DC-950	12	18	-	dB
		High Pass	1700-2700	12	17	-	
Common		1700-2700	12	17	-		
Stop Band Isolation	Low Pass	1360-2700	20	31	-	dB	
		1700-2700	36	48	-		
	High Pass	DC-980	-	30	-	dB	
DC-950	20	35	-				

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
10	0.03	102.79	48.98	50.10	0.00
30	0.06	104.68	43.87	44.92	0.00
120	0.12	81.00	30.90	32.24	0.02
360	0.24	54.54	21.45	22.24	0.08
858	0.50	51.81	29.28	28.58	0.40
950	0.69	36.22	22.33	21.02	0.53
980	0.82	31.11	19.06	17.73	0.59
1020	1.19	24.62	13.78	12.67	0.70
1080	3.09	14.94	6.79	5.63	1.10
1120	6.38	9.96	4.28	2.71	1.72
1140	8.79	8.79	3.78	1.88	2.16
1200	18.17	4.57	4.36	0.87	4.04
1220	21.58	3.79	5.01	0.76	4.88
1360	31.58	1.16	14.42	0.50	15.38
1480	41.41	0.76	33.54	0.43	30.23
1550	50.81	0.70	22.97	0.40	21.17
1620	72.56	0.68	19.66	0.38	18.57
1700	54.49	0.66	18.29	0.37	17.63
1850	49.88	0.62	18.09	0.35	18.03
2000	48.64	0.57	18.82	0.34	19.62
2450	48.35	0.56	17.23	0.33	19.06
2700	48.38	0.59	15.66	0.33	16.99

Functional Schematic



Mini-Circuits®






ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS

For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.









Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		CROSS OVER ISOLATION (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Low Pass port	High Pass port		Common port	Low Pass port	High Pass port
10.0	0.03	102.79	102.61	48.98	50.10	0.00
20.0	0.04	103.15	100.10	46.19	47.03	0.00
30.0	0.06	104.68	100.82	43.87	44.92	0.00
40.0	0.07	107.39	93.44	41.88	42.45	0.00
50.0	0.07	95.03	99.52	39.75	40.40	0.01
60.0	0.08	93.06	90.47	37.92	38.50	0.01
80.0	0.09	90.37	92.43	34.83	35.97	0.01
100.0	0.10	84.19	88.89	32.84	34.13	0.01
120.0	0.12	81.00	81.94	30.90	32.24	0.02
150.0	0.13	75.81	76.71	28.88	29.83	0.02
200.0	0.16	68.70	69.50	26.12	27.44	0.04
260.0	0.19	62.02	62.59	24.03	25.07	0.05
300.0	0.21	58.81	59.01	22.80	23.85	0.07
350.0	0.23	55.14	55.19	21.65	22.45	0.08
360.0	0.24	54.54	54.50	21.45	22.24	0.08
400.0	0.26	52.17	52.01	20.79	21.46	0.10
500.0	0.31	47.53	46.98	20.06	20.38	0.14
600.0	0.35	44.20	43.38	20.70	20.62	0.20
700.0	0.38	42.26	41.47	23.54	23.06	0.26
800.0	0.44	43.63	42.77	29.73	28.46	0.34
858.0	0.50	51.81	48.36	29.28	28.58	0.40
900.0	0.57	49.43	47.91	26.53	25.49	0.45
950.0	0.69	36.22	36.35	22.33	21.02	0.53
960.0	0.73	34.44	34.66	21.33	19.99	0.54
980.0	0.82	31.11	31.62	19.06	17.73	0.59
990.0	0.88	29.50	30.26	17.80	16.52	0.61
1000.0	0.96	27.89	28.95	16.48	15.26	0.64
1020.0	1.19	24.62	26.56	13.78	12.67	0.70
1060.0	2.15	18.01	22.62	8.79	7.72	0.92
1080.0	3.09	14.94	21.19	6.79	5.63	1.10
1100.0	4.48	12.22	20.22	5.27	3.94	1.37
1120.0	6.38	9.96	19.74	4.28	2.71	1.72
1140.0	8.79	8.14	19.71	3.78	1.88	2.16
1160.0	11.62	6.69	20.04	3.69	1.36	2.69
1180.0	14.79	5.52	20.63	3.90	1.05	3.32
1200.0	18.17	4.57	21.41	4.36	0.87	4.04
1220.0	21.58	3.79	22.34	5.01	0.76	4.88
1300.0	28.85	1.81	27.09	9.31	0.57	9.68
1340.0	30.51	1.33	29.98	12.50	0.52	13.20
1360.0	31.58	1.16	31.53	14.42	0.50	15.38
1400.0	34.23	0.94	34.87	19.30	0.47	21.23
1480.0	41.41	0.76	42.87	33.54	0.43	30.23
1500.0	43.67	0.74	45.36	29.03	0.42	26.01
1550.0	50.81	0.70	53.60	22.97	0.40	21.17
1600.0	65.06	0.69	68.21	20.29	0.39	19.09
1620.0	72.56	0.68	61.42	19.66	0.38	18.57
1650.0	60.30	0.67	55.99	18.97	0.38	18.05
1700.0	54.49	0.66	52.20	18.29	0.37	17.63
1750.0	51.98	0.64	50.48	18.00	0.36	17.52
1800.0	50.68	0.63	49.62	17.99	0.36	17.73
1850.0	49.88	0.62	49.11	18.09	0.35	18.03
1900.0	49.30	0.60	48.87	18.32	0.35	18.52
2000.0	48.64	0.57	48.71	18.82	0.34	19.62
2200.0	48.27	0.55	48.77	18.93	0.33	20.89
2300.0	48.27	0.54	48.81	18.37	0.33	20.46
2400.0	48.34	0.55	48.87	17.65	0.33	19.59
2450.0	48.35	0.56	48.84	17.23	0.33	19.06
2500.0	48.37	0.56	48.90	16.87	0.33	18.59
2600.0	48.40	0.58	49.05	16.19	0.33	17.70
2700.0	48.38	0.59	49.23	15.66	0.33	16.99
3000.0	48.36	0.64	50.10	14.47	0.33	15.39
3500.0	46.30	0.87	48.69	13.76	0.33	13.75
4000.0	45.67	1.04	47.99	10.40	0.37	10.54





Typical Performance Curves



Outline Dimensions

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
CK605	.500 (12.70)	.500 (12.70)	.180 (4.57)	.100 (2.54)	.080 (2.03)	.115 (2.92)	.060 (1.52)	.040 (1.02)	.540 (13.72)	.060 (1.52)

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
CK605	.100 (2.54)	.135 (3.43)	.135 (3.43)	.115 (2.92)	.140 (3.56)	.070 (1.78)	.150 (3.81)	.070 (1.78)	1.2 +0.5 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
			500	

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M105563	ADDED "r1" PIN CONNECTION	06/02/06	MMG	DJ
F	M105640	CORRECTED NOTE 2	06/08/06	MMG	MM
G	M124395	ADDED "RAMP"	09/09	EM	HH
G	R77589	ADDED "RAMP"	09/09	EM	HH

SUGGESTED MOUNTING CONFIGURATION FOR CK605 CASE STYLE, "kg/rl/16AM01" PIN CONNECTION




NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	AV	08/07/00
TOLERANCES ON:	SK	08/08/00
2 PL DECIMALS ±	DB	08/08/00
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

PL,kg/rl/16AM01,CK605,ROS/LAVI/RAMP

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-012	REV: G
FILE: 98PL012	SCALE: 5:1	SHEET: 1 OF 1	

 Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215