

+12 to +33 dBm

# Limiter

## RLM-33-2W+

50Ω Broadband 0.2 to 3000 MHz

### Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Input Power        | 2.5W           |

Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

|        |         |
|--------|---------|
| INPUT  | 1       |
| OUTPUT | 4       |
| GROUND | 2,3,5,6 |


### Outline Drawing



### Outline Dimensions (inch/mm)

| A    | B    | C    | D    | E    | F    | G    | H     |
|------|------|------|------|------|------|------|-------|
| .25  | .31  | .16  | .100 | .040 | .055 | .060 | .065  |
| 6.35 | 7.87 | 4.06 | 2.54 | 1.02 | 1.40 | 1.52 | 1.65  |
| J    | K    | L    | M    | N    | P    | Q    | wt.   |
| .300 | .060 | .160 | .025 | .100 | .110 | .070 | grams |
| 7.62 | 1.52 | 4.06 | 0.64 | 2.54 | 2.79 | 1.78 | 0.16  |

### Demo Board MCL P/N: TB-393 Suggested PCB Layout (PL-258)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- 

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- wideband, 0.2 to 3000 MHz
- low insertion loss 0.25 dB typ.
- good recovery time, 22.5nsec typ.
- excellent VSWR 1.33:1 typ.
- low output power, 13 dBm typ.

### Applications

- military, hi-rel applications
- stabilizing generator outputs
- reducing amplitude variations
- protects low noise amplifiers and other devices from ESD or input power damage



Generic photo used for illustration purposes only

CASE STYLE: TT1224

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications







### Electrical Specifications

| Parameter             | Condition  | Min. | Typ. | Max. | Units |
|-----------------------|--|------|------|------|-------|
| Frequency Range       |  | 0.2  |      | 3000 | MHz   |
| <b>Linear Range</b>   |  |      |      |      |       |
| Max Input Power       | less than 1 dB compression   | —    | —    | 5    | dBm   |
| Insertion Loss        | less than -10 dBm input power  | —    | 0.25 | 0.9  | dB    |
| VSWR                  | less than -10 dBm input power  | —    | 1.33 | 1.5  | :1    |
| <b>Limiting Range</b> |  |      |      |      |       |
| Input Power           | >1dB compression filtered signal frequency   | +12  | —    | +33  | dBm   |
| Output Power          |  | —    | +13  | —    | dBm   |
| Δ Output/ Δ 1dB Input | Input Power Range (dBm)  |      |      |      |       |
|                       | 12 to 20   | —    | 0.3  | —    |       |
|                       | 20 to 25   | —    | 0.1  | —    | dB/dB |
|                       | 25 to 30   | —    | 0.1  | —    |       |
|                       | 30 to 33   | —    | 0.2  | —    |       |
| Recovery Time         | 1 watt pulse 50 μsec pw 1kHz duty cycle recovery to within 90% of final value @ 33 dBm | —    | 22.5 | —    | nsec  |
| Response Time         | 33 dBm input 50 μsec PW 1 kHz duty cycle   | —    | 5.6  | —    | nsec  |

### Typical Performance Data

| Freq. (MHz) | I. Loss (dB) in Linear Range at -10 dBm | VSWR (:1) in Linear Range at -10 dBm | Power Output (dBm) |               |               |               |              | Δ Output / Δ 1dB Input |                      |                      |                      |
|-------------|---|--------------------------------------|--------------------|---------------|---------------|---------------|--------------|------------------------|----------------------|----------------------|----------------------|
|             |   |                                      | +12 dBm Input      | +20 dBm Input | +25 dBm Input | +30 dBm Input | +33dBm Input | +12 to +20 dBm Input   | +20 to +25 dBm Input | +25 to +30 dBm Input | +30 to +33 dBm Input |
| 0.20        | 0.11                                    | 1.35                                 | 9.45               | 9.72          | 10.42         | 13.09         | 13.53        | 0.03                   | 0.14                 | 0.53                 | 0.15                 |
| 0.50        | 0.03                                    | 1.12                                 | 9.55               | 9.91          | 10.60         | 13.33         | 13.94        | 0.04                   | 0.14                 | 0.55                 | 0.20                 |
| 1.00        | 0.02                                    | 1.06                                 | 9.57               | 9.95          | 10.64         | 13.36         | 14.00        | 0.05                   | 0.14                 | 0.54                 | 0.21                 |
| 5.00        | 0.02                                    | 1.01                                 | 9.86               | 9.93          | 10.56         | 13.15         | 13.74        | 0.01                   | 0.13                 | 0.52                 | 0.20                 |
| 10.00       | 0.02                                    | 1.01                                 | 9.93               | 9.80          | 10.30         | 12.66         | 13.21        | -0.02                  | 0.10                 | 0.47                 | 0.18                 |
| 50.00       | 0.05                                    | 1.01                                 | 9.86               | 8.85          | 9.17          | 11.30         | 11.57        | -0.13                  | 0.06                 | 0.43                 | 0.09                 |
| 100.00      | 0.07                                    | 1.01                                 | 9.72               | 8.78          | 9.20          | 11.45         | 12.08        | -0.12                  | 0.08                 | 0.45                 | 0.21                 |
| 700.00      | 0.19                                    | 1.08                                 | 8.79               | 10.83         | 12.18         | 12.26         | 12.21        | 0.26                   | 0.27                 | 0.02                 | -0.02                |
| 1700.00     | 0.36                                    | 1.20                                 | 8.57               | 10.78         | 8.06          | 11.17         | 13.74        | 0.28                   | -0.54                | 0.62                 | 0.86                 |
| 2200.00     | 0.43                                    | 1.17                                 | 8.49               | 9.90          | 9.83          | 10.60         | 12.80        | 0.18                   | -0.01                | 0.15                 | 0.73                 |
| 3000.00     | 0.55                                    | 1.16                                 | 8.40               | 4.47          | 6.64          | 12.06         | 14.61        | -0.49                  | 0.43                 | 1.08                 | 0.85                 |





**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Limiter


# RLM-33-2W+

## Typical Performance Data

| FREQUENCY<br>(MHz) | LOW INPUT POWER        |      | POWER OUTPUT (dBm) |                  |                  |                  |                  | DELTA OUTPUT/1dB DELTA INPUT (dB/dB) |                         |                         |                         |                         |
|--------------------|------------------------|------|--------------------|------------------|------------------|------------------|------------------|--------------------------------------|-------------------------|-------------------------|-------------------------|-------------------------|
|                    | INSERTION LOSS<br>(dB) | VSWR |                    | +12 dBm<br>INPUT | +20 dBm<br>INPUT | +25 dBm<br>INPUT | +30 dBm<br>INPUT | +33 dBm<br>INPUT                     | +12 to +20 dBm<br>INPUT | +20 to +25 dBm<br>INPUT | +25 to +30 dBm<br>INPUT | +30 to +33 dBm<br>INPUT |
| 0.2                | 0.11                   | 1.35 | 1.37               | 9.45             | 9.72             | 10.42            | 13.09            | 13.53                                | 0.03                    | 0.14                    | 0.53                    | 0.15                    |
| 0.5                | 0.03                   | 1.12 | 1.13               | 9.55             | 9.91             | 10.60            | 13.33            | 13.94                                | 0.04                    | 0.14                    | 0.55                    | 0.20                    |
| 1.0                | 0.02                   | 1.06 | 1.06               | 9.57             | 9.95             | 10.64            | 13.36            | 14.00                                | 0.05                    | 0.14                    | 0.54                    | 0.21                    |
| 5.0                | 0.02                   | 1.01 | 1.01               | 9.86             | 9.93             | 10.56            | 13.15            | 13.74                                | 0.01                    | 0.13                    | 0.52                    | 0.20                    |
| 10.0               | 0.02                   | 1.01 | 1.01               | 9.93             | 9.80             | 10.30            | 12.66            | 13.21                                | -0.02                   | 0.10                    | 0.47                    | 0.18                    |
| 50.0               | 0.05                   | 1.01 | 1.01               | 9.86             | 8.85             | 9.17             | 11.30            | 11.57                                | -0.13                   | 0.06                    | 0.43                    | 0.09                    |
| 100.0              | 0.07                   | 1.01 | 1.01               | 9.72             | 8.78             | 9.20             | 11.45            | 12.08                                | -0.12                   | 0.08                    | 0.45                    | 0.21                    |
| 700.0              | 0.19                   | 1.08 | 1.08               | 8.79             | 10.83            | 12.18            | 12.26            | 12.21                                | 0.26                    | 0.27                    | 0.02                    | -0.02                   |
| 1700.0             | 0.36                   | 1.20 | 1.22               | 8.57             | 10.78            | 8.06             | 11.17            | 13.74                                | 0.28                    | -0.54                   | 0.62                    | 0.86                    |
| 2200.0             | 0.43                   | 1.17 | 1.18               | 8.49             | 9.90             | 9.83             | 10.60            | 12.80                                | 0.18                    | -0.01                   | 0.15                    | 0.73                    |
| 3000.0             | 0.55                   | 1.16 | 1.21               | 8.40             | 4.47             | 6.64             | 12.06            | 14.61                                | -0.49                   | 0.43                    | 1.08                    | 0.85                    |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
RLM-33-2W+  
8/28/2012  
Page 1 of 2

# Surface Mount Limiter







# RLM-33-2W+

## Typical Performance Data


| POWER INPUT | POWER OUTPUT | POWER INPUT | POWER OUTPUT | POWER INPUT | POWER OUTPUT |
|-------------|--------------|-------------|--------------|-------------|--------------|
| @ .2 MHz    |              | @ 1700 MHz  |              | @ 3000 MHz  |              |
| (dBm)       |              | (dBm)       |              | (dBm)       |              |
| 12          | 9.45         | 12          | 8.57         | 12          | 8.23         |
| 20          | 9.72         | 20          | 10.78        | 20          | 4.65         |
| 25          | 10.42        | 25          | 8.06         | 25          | 7.02         |
| 30          | 13.09        | 30          | 11.17        | 30          | 11.50        |
| 33          | 13.53        | 33          | 13.74        | 33          | 14.20        |




## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A             | B             | C             | D              | E              | F              | G              | H              | J              | K              | L              |
|--------|---------------|---------------|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| TT1224 | .25<br>(6.35) | .31<br>(7.87) | .16<br>(4.06) | .100<br>(2.54) | .040<br>(1.02) | .055<br>(1.40) | .060<br>(1.52) | .065<br>(1.65) | .300<br>(7.62) | .060<br>(1.52) | .160<br>(4.06) |

| CASE # | M             | N              | P              | Q              | WT. GRAM |
|--------|---------------|----------------|----------------|----------------|----------|
| TT1224 | .025<br>(.64) | .100<br>(2.54) | .110<br>(2.79) | .070<br>(1.78) | .16      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

1. Case material: Plastic.
2. Termination: 2-10  $\mu$  inch (.05-.25 microns) Gold over 100-300  $\mu$  inch (2.54-7.62 microns) Nickel plate




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F2



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel<br>See note |
|----------------|-------------------------|-------------------|------------------------------|
| 16             | 12                      | 7                 | 10                           |
|                |                         |                   | 20                           |
|                |                         |                   | 50                           |
|                |                         |                   | 100                          |
|                |                         |                   | 200                          |
|                |                         | 13                | 500                          |
|                |                         |                   | 1000                         |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION




REVISIONS

| REV | ECN No. | DESCRIPTION | DATE     | DR | AUTH |
|-----|---------|-------------|----------|----|------|
| OR  | M108897 | NEW RELEASE | 01/04/07 | AV | DJ   |
|     |         |             |          |    |      |
|     |         |             |          |    |      |

SUGGESTED MOUNTING CONFIGURATION  
FOR TT1224 CASE STYLE "rv" PIN CONNECTION

.066 TRACE WIDTH, 3 PL.  
(SEE NOTE BELOW)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

12/14/06

TOLERANCES ON:

CHECKED

IL

01/04/07

2 PL DECIMALS ± .005


APPROVED

DJ

01/04/07

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, rv, TT1224, RMK-3-662+, TB-393

SIZE  
A

CODE IDENT  
15542

DRAWING NO:  
98-PL-258

REV:  
OR


FILE: 98PL258

SCALE: 8:1


SHEET: 1 OF 1



# Evaluation Board and Circuit




TB-393



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition   | Reference/Spec   |
|--------------------------------|---|--|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment   | Individual Model Data Sheet  |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles   | MIL-STD-202, Method 107, Condition A-3, except +100°C  |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak  | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability                  | 10X Magnification   | J-STD-002, 95% Coverage  |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)   | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes   | MIL-STD-202, Method 213, Condition A   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215  |