

# X5 Frequency Multiplier

RMK-5-751+

50Ω Output 500 to 750 MHz

## The Big Deal

- High rejection of adjacent harmonics, >60 dBc
- 50 Ω in/out, no tuning necessary



CASE STYLE: TT1224

## Product Overview

The RMK-5-751+ is a cost-effective X5 frequency multiplier that utilizes specially selected silicon Schottky diodes and compatible filter circuitry to achieve a low conversion loss, yet have a high rejection of unwanted harmonics near its F5 output. It makes the RMK-5-751+ ideal for a wide range of applications. The tiny plastic case, 0.25" x 0.31" x 0.16" high, is aqueous washable and RoHS compliant.

Feature	Advantages
<22 dB conversion loss	Efficient choice for converting 100 MHz source to 500 MHz output while maintaining useful signal power, especially for reference crystal oscillators. Only 12 dBm input required for -10 dBm output, especially useful for low-loss systems such as instrumentation
>60 dB rejection of F4 and F6	Proprietary internal circuitry achieves high suppression and minimizes filter requirements for undesired signals, as in wireless Tx/Rx applications including broadcast TV, SAP/SAB, medical telemetry, and PMR
Internally balanced to 50Ω in/out, no DC power required	Saves PCB space and simplifies application design, with no external matching or biasing circuits required
Small surface mount package	Easily integrated in systems with minimal PCB area available

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# X5 Frequency Multiplier

## RMK-5-751+

50Ω Output 500 to 750 MHz

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Input Power	21 dBm

Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

INPUT	1
OUTPUT	4
GROUND	2,3,5,6


### Outline Drawing



### Outline Dimensions (inches/mm)

A	B	C	D	E	F	G	H
.25	.31	.16	.100	.040	.055	.060	.065
6.35	7.87	4.06	2.54	1.02	1.40	1.52	1.65
J	K	L	M	N	P	Q	wt.
.300	.060	.160	.025	.100	.110	.070	grams
7.62	1.52	4.06	0.64	2.54	2.79	1.78	0.16

### Demo Board MCL P/N: TB-393 Suggested PCB Layout (PL-258)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- Denotes PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
  - Denotes COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- low conversion loss, 22 dB typ.
- high adjacent harmonic rejection, F4, 60 dBc typ., F6, 67 dBc typ.
- aqueous washable

### Applications

- synthesizers
- local oscillators
- satellite up and down converters



Generic photo used for illustration purposes only  
CASE STYLE: TT1224

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

### Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Multiplier Factor		5		
Frequency Range, Input (F1)	100		150	MHz
Frequency Range, Output (F5)	500		750	MHz
Input Power	—	17.0	—	dBm
Conversion Loss	—	22	24.5	dB
Harmonic Output*	F1	-3	-1.0	—
	F2	40	62	—
	F3	-10	-6.8	—
	F4	40	60	—
	F6	40	67	—
	F7	3	7.0	—








\* Harmonics of input frequency below the power level of F5

### Typical Performance Data

Frequency	Conv. Loss (dB)	Harmonic Rejection Below F5, (dB) at RF Input Power 17 dBm						
		Input (MHz)	Output (MHz)	F5	F1	F2	F3	F4
100.0	500.0	21.84	6.32	70.63	-0.62	62.49	74.25	7.32
110.0	550.0	21.00	5.45	72.18	-1.72	61.85	70.59	6.99
120.0	600.0	20.81	4.08	81.19	-3.24	62.22	73.65	7.03
130.0	650.0	21.34	2.16	81.77	-4.85	63.14	73.68	7.87
140.0	700.0	21.39	0.82	73.31	-5.76	62.99	71.81	7.69
141.0	705.0	21.44	0.60	72.45	-5.93	62.86	71.58	7.71
142.0	710.0	21.48	0.47	71.83	-6.02	62.77	71.26	7.63
143.0	715.0	21.51	0.26	71.06	-6.15	62.84	70.96	7.68
144.0	720.0	21.53	0.15	70.56	-6.20	62.85	70.53	7.64
145.0	725.0	21.55	-0.03	69.95	-6.29	62.90	70.42	7.73
147.0	735.0	21.56	-0.31	68.73	-6.40	63.07	69.88	7.92
148.0	740.0	21.60	-0.42	68.19	-6.44	63.08	69.42	7.90
149.0	745.0	21.66	-0.61	67.52	-6.57	63.11	69.02	7.93
150.0	750.0	21.73	-0.80	66.82	-6.69	63.17	68.72	7.95



# RMK-5-751+



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Multiplier (X5)

RMK-5-751+

## Typical Performance Data

FREQUENCY (MHz)							CONVERSION LOSS (dB)	RF IN = +17 dBm					
X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X5 OUTPUT	X6 OUTPUT	X7 OUTPUT		X5 OUTPUT	HARMONIC OUTPUT* (-dBc)				
X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X5 OUTPUT	X6 OUTPUT	X7 OUTPUT	X5 OUTPUT	X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X6 OUTPUT	X7 OUTPUT
100	200	300	400	500	600	700	21.84	6.32	70.63	-0.62	62.49	74.25	7.32
102	204	306	408	510	612	714	21.92	5.93	70.18	-0.96	62.57	71.61	7.65
104	208	312	416	520	624	728	21.84	5.61	70.18	-1.26	62.42	70.24	7.71
106	212	318	424	530	636	742	21.55	5.60	70.47	-1.34	62.03	70.19	7.45
108	216	324	432	540	648	756	21.19	5.56	71.39	-1.47	61.90	70.33	7.37
110	220	330	440	550	660	770	21.00	5.45	72.18	-1.72	61.85	70.59	6.99
112	224	336	448	560	672	784	20.84	5.23	73.54	-2.08	61.93	71.13	6.97
114	228	342	456	570	684	798	20.75	5.02	74.87	-2.36	62.03	71.89	7.00
116	232	348	464	580	696	812	20.73	4.75	76.57	-2.66	62.11	72.29	6.97
118	236	354	472	590	708	826	20.75	4.43	78.60	-2.95	62.22	72.96	6.96
120	240	360	480	600	720	840	20.81	4.08	81.19	-3.24	62.22	73.65	7.03
122	244	366	488	610	732	854	20.85	3.74	84.83	-3.51	62.26	74.06	7.20
124	248	372	496	620	744	868	20.93	3.37	90.45	-3.83	62.42	74.16	7.46
126	252	378	504	630	756	882	21.10	2.92	91.07	-4.26	62.62	73.72	7.58
128	256	384	512	640	768	896	21.26	2.55	86.35	-4.57	62.84	73.56	7.57
130	260	390	520	650	780	910	21.34	2.16	81.77	-4.85	63.14	73.68	7.87
132	264	396	528	660	792	924	21.39	1.90	79.59	-4.98	63.20	73.77	7.81
134	268	402	536	670	804	938	21.38	1.64	77.95	-5.13	63.26	73.35	7.78
136	272	408	544	680	816	952	21.37	1.38	76.33	-5.32	63.26	72.70	7.75
138	276	414	552	690	828	966	21.34	1.13	74.69	-5.50	63.20	72.35	7.76
140	280	420	560	700	840	980	21.39	0.82	73.31	-5.76	62.99	71.81	7.69
141	282	423	564	705	846	987	21.44	0.60	72.45	-5.93	62.86	71.58	7.71
142	284	426	568	710	852	994	21.48	0.47	71.83	-6.02	62.77	71.26	7.63
143	286	429	572	715	858	1001	21.51	0.26	71.06	-6.15	62.84	70.96	7.68
144	288	432	576	720	864	1008	21.53	0.15	70.56	-6.20	62.85	70.53	7.64
145	290	435	580	725	870	1015	21.55	-0.03	69.95	-6.29	62.90	70.42	7.73
146	292	438	584	730	876	1022	21.53	-0.11	69.43	-6.29	62.96	70.06	7.76
147	294	441	588	735	882	1029	21.56	-0.31	68.73	-6.40	63.07	69.88	7.92
148	296	444	592	740	888	1036	21.60	-0.42	68.19	-6.44	63.08	69.42	7.90
149	298	447	596	745	894	1043	21.66	-0.61	67.52	-6.57	63.11	69.02	7.93
150	300	450	600	750	900	1050	21.73	-0.80	66.82	-6.69	63.17	68.72	7.95

\* Harmonic Output below power level of X5 Output.










P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

REV. OR  
 RMK-5-751+  
 7/7/2011  
 Page 1 of 1


## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
TT1224	.25 (6.35)	.31 (7.87)	.16 (4.06)	.100 (2.54)	.040 (1.02)	.055 (1.40)	.060 (1.52)	.065 (1.65)	.300 (7.62)	.060 (1.52)	.160 (4.06)

CASE #	M	N	P	Q	WT. GRAM
TT1224	.025 (.64)	.100 (2.54)	.110 (2.79)	.070 (1.78)	.16

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

1. Case material: Plastic.
2. Termination: 2-10  $\mu$  inch (.05-.25 microns) Gold over 100-300  $\mu$  inch (2.54-7.62 microns) Nickel plate




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F2



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
16	12	7	10
			20
			50
			100
			200
		13	500
			1000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M108897	NEW RELEASE	01/04/07	AV	DJ

**SUGGESTED MOUNTING CONFIGURATION  
FOR TT1224 CASE STYLE "rv" PIN CONNECTION**

.066 TRACE WIDTH, 3 PL.  
(SEE NOTE BELOW)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	AV	12/14/06
CHECKED	IL	01/04/07
APPROVED	DJ	01/04/07



**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235

PL, rv, TT1224, RMK-3-662+, TB-393


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-258	OR


FILE:	SCALE:	SHEET:
98PL258	8:1	1 OF 1



# Evaluation Board and Circuit




TB-393



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215