

Frequency Mixer

RMS-11X+

Level 7 (LO Power + 7dBm) 5 to 1900 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	1
RF	5
IF	4
GROUND	2,3,6


Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F
.250	.31	.20	.100	.050	.055
6.35	7.87	5.08	2.54	1.27	1.40
G	H	J	K		wt
.040	.070	.270	.050		grams
1.02	1.78	6.86	1.27		0.50

Demo Board MCL P/N: TB-03
Suggested PCB Layout (PL-052)



Notes

A. Performance and quality attributes and condition not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are deemed to be bound to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms_iso

Features

- excellent L-R isolation, 35 dB typ.
- conversion loss, 7.1 dB typ.
- small size, 0.25"x0.31x0.2"

Applications

- PCN
- satellite distribution
- GPS

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)						IP3 at center band (dBm)
LO/RF	IF					L		M		U		L		M		U		
f_L - f_U		$\overline{X}$	σ	Max.	Total Range Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.
5-1900	5-1000	7.1	.10	8.2	9.8	58	45	35	20	27	18	56	45	37	20	27	20	10

1 dB COMP.: +1 dBm typ.
For phase detection, DC output positive with in-phase RF & LO.


L = low range [f_L to $10 f_L$]
m= mid band [$2f_L$ to $f_U/2$]







M = mid range [$10 f_i$ to $f_{i+1}/2$] U = upper range [$f_{i+1}/2$ to f_{i+1}]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7 dBm	LO +7 dBm	LO +7 dBm	LO +7 dBm	LO +7 dBm
5.00	35.00	6.69	57.72	66.80	1.21	2.98
10.01	40.01	6.67	57.22	64.98	1.22	2.83
50.04	80.04	6.66	51.74	53.60	1.23	2.78
103.56	73.56	6.72	46.56	47.68	1.23	2.75
189.86	159.86	6.79	42.32	43.39	1.26	2.72
241.95	211.95	6.90	40.60	41.62	1.31	2.59
308.34	278.34	7.00	38.96	39.89	1.32	2.59
392.94	362.94	7.11	37.54	38.49	1.37	2.56
500.75	470.75	7.20	35.72	37.03	1.44	2.60
638.14	608.14	6.65	34.40	36.08	1.52	2.53
720.38	690.38	7.33	33.17	35.36	1.54	2.52
918.04	888.04	7.35	31.46	34.64	1.53	2.61
950.00	920.00	7.26	30.90	34.39	1.54	2.63
1036.36	1006.36	7.24	30.00	34.46	1.52	2.68
1200.00	1170.00	7.58	30.35	34.77	1.40	2.79
1320.71	1290.71	7.59	32.03	34.21	1.34	2.90
1500.00	1470.00	7.67	35.10	33.40	1.26	2.89
1800.00	1770.00	8.36	38.63	32.68	1.42	3.62
1850.00	1820.00	8.56	36.54	32.31	1.47	3.73
1900.00	1870.00	8.80	34.84	32.78	2.04	3.94

Electrical Schematic





Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

RMS-11X+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		+4	+7	+10
5.0	35.0	7.17	6.69	6.52
10.0	40.0	7.17	6.67	6.52
70.4	100.4	7.12	6.75	6.55
130.7	160.7	7.24	6.87	6.66
190.9	220.9	7.34	6.94	6.73
251.2	281.2	7.38	6.97	6.78
311.5	341.5	7.49	7.09	6.89
371.8	401.8	7.63	7.22	6.99
432.0	462.0	7.60	7.20	7.00
492.3	522.3	7.74	7.32	7.08
552.6	582.6	7.82	7.35	7.11
612.9	642.9	7.83	7.40	7.15
673.1	703.1	7.86	7.47	7.26
733.4	763.4	7.87	7.45	7.26
793.7	823.7	7.85	7.46	7.25
854.0	884.0	7.95	7.56	7.33
914.2	944.2	8.03	7.57	7.36
974.5	1004.5	8.09	7.63	7.42
1034.8	1064.8	8.19	7.69	7.45
1095.1	1125.1	8.32	7.85	7.54
1155.3	1185.3	8.41	7.98	7.68
1215.6	1245.6	8.46	8.02	7.79
1275.9	1305.9	8.54	8.08	7.86
1336.2	1366.2	8.56	8.15	7.93
1396.4	1426.4	8.55	8.15	7.95
1436.6	1466.6	8.57	8.21	8.00
1496.9	1526.9	8.61	8.24	8.08
1537.1	1567.1	8.58	8.25	8.09
1597.3	1627.3	8.75	8.33	8.17
1637.5	1667.5	8.72	8.39	8.25
1697.8	1727.8	8.90	8.53	8.38
1798.3	1828.3	9.18	8.76	8.64
1838.4	1868.4	9.35	8.94	8.76
1898.7	1928.7	9.57	9.10	9.00
1938.9	1968.9	9.72	9.23	9.08
1999.2	2029.2	9.96	9.44	9.32
2039.4	2069.4	10.16	9.64	9.48
2099.6	2129.6	10.50	9.87	9.73
2139.8	2169.8	10.80	10.16	9.95
2200.1	2230.1	11.11	10.37	10.15

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		+4	+7	+10
10.1	40.1	16.21	17.20	17.33
70.4	100.4	12.83	13.65	14.56
130.7	160.7	11.33	13.87	19.15
190.9	220.9	11.29	16.00	21.79
251.2	281.2	12.86	16.49	17.48
311.5	341.5	15.06	15.78	17.72
371.8	401.8	14.02	14.67	16.99
432.0	462.0	13.32	14.27	15.74
492.3	522.3	11.27	12.68	15.31
552.6	582.6	9.59	11.84	13.90
612.9	642.9	9.11	10.92	12.97
673.1	703.1	8.43	9.73	12.06
733.4	763.4	8.29	10.49	12.20
793.7	823.7	8.27	11.06	13.31
854.0	884.0	8.20	10.21	13.22
914.2	944.2	8.66	10.32	12.74
974.5	1004.5	9.45	10.80	13.14
1034.8	1064.8	9.69	11.75	13.52
1095.1	1125.1	10.03	11.76	14.98
1155.3	1185.3	9.35	12.29	14.01
1215.6	1245.6	10.31	12.43	13.88
1275.9	1305.9	9.96	11.33	12.28
1336.2	1366.2	10.01	10.95	11.64
1396.4	1426.4	9.97	11.16	12.11
1436.6	1466.6	10.32	11.64	12.54
1496.9	1526.9	10.66	12.84	12.02
1537.1	1567.1	11.32	14.08	14.73
1597.3	1627.3	10.42	13.25	15.31
1637.5	1667.5	10.78	13.55	16.23
1697.8	1727.8	10.25	13.34	15.88
1738.0	1768.0	10.49	14.18	15.19
1798.3	1828.3	10.17	14.07	15.77
1838.4	1868.4	10.19	13.74	15.36
1898.7	1928.7	10.18	13.74	16.03
1938.9	1968.9	10.43	15.45	17.51
1999.2	2029.2	12.30	17.28	19.59
2039.4	2069.4	12.53	16.08	19.63
2099.6	2129.6	13.57	16.81	18.92
2139.8	2169.8	13.13	15.88	17.38
2200.1	2230.1	12.26	15.93	19.34

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+1dBm (dB)		
		@LO (dBm)		
		+4	+7	+10
10.1	40.1	1.23	0.71	0.29
70.4	100.4	1.32	0.84	0.56
130.7	160.7	1.49	0.93	0.66
190.9	220.9	1.34	0.90	0.60
251.2	281.2	1.47	1.01	0.68
311.5	341.5	1.48	1.13	0.72
371.8	401.8	1.51	1.12	0.78
432.0	462.0	1.50	1.14	0.89
492.3	522.3	1.69	1.25	0.99
552.6	582.6	1.57	1.19	0.88
612.9	642.9	1.38	1.11	0.93
673.1	703.1	1.56	1.36	1.04
733.4	763.4	1.58	1.25	0.95
793.7	823.7	1.41	1.13	0.95
854.0	884.0	1.36	1.11	0.91
914.2	944.2	1.37	1.08	0.93
974.5	1004.5	1.35	1.06	0.89
1034.8	1064.8	1.10	0.87	0.66
1095.1	1125.1	1.03	0.83	0.63
1155.3	1185.3	1.03	0.67	0.61
1215.6	1245.6	0.93	0.60	0.54
1275.9	1305.9	0.85	0.60	0.42
1336.2	1366.2	1.12	0.71	0.59
1396.4	1426.4	1.01	0.52	0.37
1436.6	1466.6	1.02	0.51	0.39
1496.9	1526.9	1.13	0.56	0.41
1537.1	1567.1	1.03	0.54	0.20
1597.3	1627.3	0.99	0.47	0.25
1637.5	1667.5	0.99	0.47	0.35
1697.8	1727.8	1.12	0.43	0.30
1738.0	1768.0	0.95	0.42	0.17
1798.3	1828.3	1.04	0.44	0.08
1838.4	1868.4	1.07	0.48	0.32
1898.7	1928.7	0.88	0.30	0.23
1938.9	1968.9	0.94	0.36	0.13
1999.2	2029.2	0.84	0.40	0.13
2039.4	2069.4	0.89	0.43	0.09
2099.6	2129.6	0.90	0.48	0.16
2139.8	2169.8	0.84	0.51	0.20
2200.1	2230.1	0.92	0.48	0.29

Frequency Mixer

RMS-11X+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=510.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1010.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+7			+7			+7
500.0	10.1	7.19	10.0	20.1	6.56	1000.0	10.1	7.90
487.4	22.7	7.24	30.0	40.1	6.51	979.8	30.3	7.86
474.9	35.2	7.25	50.0	60.1	6.48	959.6	50.5	7.94
462.3	47.8	7.25	70.0	80.1	6.55	939.4	70.7	7.90
449.7	60.4	7.28	90.0	100.1	6.51	919.2	90.9	7.86
437.2	72.9	7.34	110.0	120.1	6.53	899.0	111.1	7.87
424.6	85.5	7.36	130.0	140.1	6.52	878.8	131.3	7.84
412.1	98.0	7.38	150.0	160.1	6.53	858.6	151.5	7.78
399.5	110.6	7.38	170.0	180.1	6.57	838.4	171.7	7.75
386.9	123.2	7.37	190.0	200.1	6.57	818.2	191.9	7.72
374.4	135.7	7.35	210.0	220.1	6.57	798.0	212.1	7.72
361.8	148.3	7.38	230.0	240.1	6.52	777.8	232.3	7.67
349.2	160.9	7.40	250.0	260.1	6.54	757.6	252.5	7.64
336.7	173.4	7.40	270.0	280.1	6.52	737.3	272.8	7.59
324.1	186.0	7.39	290.0	300.1	6.58	717.1	293.0	7.64
311.5	198.6	7.40	310.0	320.1	6.50	696.9	313.2	7.62
299.0	211.1	7.40	330.0	340.1	6.54	676.7	333.4	7.61
286.4	223.7	7.36	350.0	360.1	6.53	656.5	353.6	7.59
273.8	236.3	7.36	370.0	380.1	6.53	636.3	373.8	7.57
261.3	248.8	7.39	390.0	400.1	6.53	616.1	394.0	7.61
248.7	261.4	7.39	430.0	440.1	6.55	575.7	434.4	7.56
236.2	273.9	7.38	450.0	460.1	6.52	555.5	454.6	7.54
223.6	286.5	7.39	490.0	500.1	6.54	515.1	495.0	7.56
211.0	299.1	7.40	510.0	520.1	6.58	494.9	515.2	7.53
198.5	311.6	7.40	550.0	560.1	6.53	454.5	555.6	7.55
185.9	324.2	7.39	570.0	580.1	6.56	434.3	575.8	7.59
173.3	336.8	7.41	610.0	620.1	6.58	393.9	616.2	7.59
160.8	349.3	7.40	630.0	640.1	6.56	373.7	636.4	7.57
148.2	361.9	7.38	670.0	680.1	6.63	333.3	676.8	7.58
135.6	374.5	7.38	690.0	700.1	6.63	313.1	697.0	7.57
123.1	387.0	7.42	730.0	740.1	6.62	272.7	737.4	7.63
110.5	399.6	7.43	750.0	760.1	6.72	252.4	757.7	7.69
97.9	412.2	7.41	790.0	800.1	6.75	212.0	798.1	7.73
85.4	424.7	7.39	810.0	820.1	6.77	191.8	818.3	7.72
72.8	437.3	7.40	850.0	860.1	6.83	151.4	858.7	7.73
60.3	449.8	7.36	870.0	880.1	6.87	131.2	878.9	7.73
47.7	462.4	7.36	910.0	920.1	6.88	90.8	919.3	7.72
35.1	475.0	7.39	930.0	940.1	6.96	70.6	939.5	7.72
22.6	487.5	7.34	970.0	980.1	7.08	30.2	979.9	7.64
10.0	500.1	7.61	990.0	1000.1	7.17	10.0	1000.1	7.96

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10
5.0	58.78	57.72	57.53	66.40	66.80	67.41
10.0	58.07	57.22	56.74	65.60	64.98	65.00
70.4	46.59	44.92	44.01	46.39	45.78	45.50
130.7	41.70	40.27	39.31	42.07	41.37	40.82
190.9	39.34	37.94	36.92	39.40	38.74	38.05
251.2	37.79	36.36	35.26	37.59	36.80	36.11
311.5	36.39	35.00	33.85	36.18	35.32	34.55
371.8	35.05	33.74	32.69	34.87	33.97	33.20
432.0	33.81	32.74	31.81	33.69	32.84	32.11
492.3	32.51	31.60	30.77	32.64	31.84	31.15
552.6	31.23	30.54	29.80	31.55	30.84	30.23
612.9	30.08	29.60	29.06	30.60	29.96	29.43
673.1	29.02	28.59	28.14	29.71	29.16	28.66
733.4	28.06	27.66	27.13	28.75	28.29	27.85
793.7	27.25	27.13	26.69	27.97	27.62	27.27
854.0	26.59	26.75	26.45	27.26	27.01	26.73
914.2	25.95	26.40	26.33	26.59	26.46	26.26
974.5	25.29	25.91	26.08	26.04	26.01	25.90
1034.8	24.82	25.52	25.90	25.46	25.53	25.48
1095.1	24.53	25.25	25.77	25.00	25.16	25.18
1155.3	24.42	25.03	25.53	24.61	24.88	24.97
1215.6	24.60	25.18	25.56	24.18	24.58	24.77
1275.9	24.95	25.75	26.16	23.81	24.33	24.60
1336.2	25.31	26.33	26.84	23.50	24.09	24.41
1396.4	25.58	26.95	27.67	23.13	23.80	24.19
1436.6	25.82	27.40	28.32	22.97	23.65	24.06
1496.9	25.84	27.78	29.06	22.66	23.37	23.81
1537.1	25.79	27.83	29.28	22.54	23.26	23.72
1597.3	25.70	27.71	29.20	22.35	23.12	23.62
1637.5	25.58	27.49	28.87	22.16	22.97	23.50
1697.8	25.39	26.96	28.01	21.99	22.88	23.50
1798.3	24.72	25.64	26.17	21.71	22.73	23.51
1838.4	24.33	25.00	25.34	21.64	22.72	23.58
1898.7	23.77	24.16	24.34	21.49	22.62	23.58
1938.9	23.35	23.55	23.64	21.53	22.71	23.73
1999.2	22.84	22.83	22.84	21.46	22.71	23.85
2039.4	22.45	22.37	22.36	21.55	22.86	24.07
2099.6	21.87	21.68	21.65	21.56	22.93	24.24
2139.8	21.41	21.20	21.16	21.63	23.05	24.42
2200.1	20.75	20.53	20.48	21.75	23.29	24.81

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+4	+7	+10
10.1	40.1	32.59	37.74	36.11
70.4	100.4	31.75	31.37	30.83
130.7	160.7	26.88	26.70	26.44
190.9	220.9	24.10	23.99	23.84
251.2	281.2	22.35	22.26	22.15
311.5	341.5	21.24	21.22	21.12
371.8	401.8	20.48	20.47	20.42
432.0	462.0	19.95	19.97	19.92
492.3	522.3	19.49	19.52	19.48
552.6	582.6	19.15	19.18	19.13
612.9	642.9	18.55	18.62	18.61
673.1	703.1	17.57	17.65	17.69
733.4	763.4	16.49	16.57	16.57
793.7	823.7	15.39	15.48	15.49
854.0	884.0	14.38	14.45	14.49
914.2	944.2	13.49	13.57	13.63
974.5	1004.5	12.71	12.77	12.86
1034.8	1064.8	12.10	12.16	12.23
1095.1	1125.1	11.64	11.72	11.80
1155.3	1185.3	11.22	11.33	11.43
1215.6	1245.6	10.98	11.11	11.22
1275.9	1305.9	10.85	11.02	11.15
1336.2	1366.2	10.79	11.02	11.20
1396.4	1426.4	10.78	11.04	11.25
1436.6	1466.6	10.79	11.07	11.30
1496.9	1526.9	10.78	11.10	11.32
1537.1	1567.1	10.81	11.11	11.32
1597.3	1627.3	10.80	11.11	11.28
1637.5	1667.5	10.83	11.09	11.24
1697.8	1727.8	10.71	10.92	11.02
1738.0	1768.0	10.62	10.78	10.84
1798.3	1828.3	10.35	10.40	10.39
1838.4	1868.4	10.13	10.10	10.05
1898.7	1928.7	9.64	9.51	9.40
1938.9	1968.9	9.32	9.11	8.97
1999.2	2029.2	8.91	8.59	8.40
2039.4	2069.4	8.70	8.32	8.10
2099.6	2129.6	8.41	7.94	7.69
2139.8	2169.8	8.21	7.72	7.45
2200.1	2230.1	7.98	7.42	7.14

Frequency Mixer

RMS-11X+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)		
		@LO (dBm)		
		+4	+7	+10
5.0	35.0	1.35	1.21	1.11
10.0	40.0	1.36	1.22	1.12
70.4	100.4	1.17	1.02	1.12
130.7	160.7	1.18	1.03	1.08
190.9	220.9	1.21	1.08	1.04
251.2	281.2	1.25	1.10	1.02
311.5	341.5	1.28	1.13	1.05
371.8	401.8	1.34	1.19	1.10
432.0	462.0	1.38	1.24	1.16
492.3	522.3	1.45	1.31	1.23
552.6	582.6	1.48	1.34	1.26
612.9	642.9	1.50	1.37	1.30
673.1	703.1	1.53	1.41	1.35
733.4	763.4	1.53	1.43	1.39
793.7	823.7	1.49	1.41	1.38
854.0	884.0	1.50	1.42	1.41
914.2	944.2	1.51	1.44	1.45
974.5	1004.5	1.48	1.41	1.44
1034.8	1064.8	1.46	1.38	1.39
1095.1	1125.1	1.47	1.40	1.40
1155.3	1185.3	1.43	1.39	1.40
1215.6	1245.6	1.37	1.36	1.38
1275.9	1305.9	1.35	1.34	1.36
1336.2	1366.2	1.33	1.34	1.38
1396.4	1426.4	1.31	1.36	1.43
1436.6	1466.6	1.28	1.34	1.42
1496.9	1526.9	1.28	1.38	1.47
1537.1	1567.1	1.30	1.42	1.52
1597.3	1627.3	1.29	1.43	1.55
1637.5	1667.5	1.35	1.50	1.62
1697.8	1727.8	1.35	1.52	1.64
1738.0	1768.0	1.36	1.54	1.68
1798.3	1828.3	1.28	1.48	1.62
1838.4	1868.4	1.36	1.55	1.69
1898.7	1928.7	1.35	1.55	1.69
1938.9	1968.9	1.32	1.51	1.64
1999.2	2029.2	1.36	1.56	1.70
2039.4	2069.4	1.30	1.48	1.60
2099.6	2129.6	1.33	1.51	1.63
2139.8	2169.8	1.27	1.43	1.55
2200.1	2230.1	1.27	1.40	1.51

LO (MHz)	LO VSWR (:1)		
	@LO (dBm)		
	+4	+7	+10
5.0	2.14	2.98	4.12
10.0	1.99	2.83	3.95
70.4	1.81	2.59	3.56
130.7	1.81	2.58	3.52
190.9	1.83	2.57	3.49
251.2	1.84	2.57	3.49
311.5	1.87	2.61	3.52
371.8	1.92	2.69	3.62
432.0	1.93	2.67	3.58
492.3	1.94	2.67	3.55
552.6	2.02	2.78	3.69
612.9	2.02	2.75	3.61
673.1	2.05	2.77	3.62
733.4	2.15	2.89	3.76
793.7	2.16	2.86	3.69
854.0	2.22	2.91	3.72
914.2	2.32	3.01	3.84
974.5	2.37	3.06	3.85
1034.8	2.44	3.12	3.91
1095.1	2.49	3.16	3.94
1155.3	2.59	3.26	4.04
1215.6	2.60	3.23	3.97
1275.9	2.66	3.25	3.98
1336.2	2.75	3.34	4.08
1396.4	2.77	3.30	3.98
1436.6	2.83	3.35	4.04
1496.9	2.89	3.35	4.00
1537.1	2.95	3.40	4.04
1597.3	3.07	3.48	4.09
1637.5	3.18	3.54	4.13
1697.8	3.34	3.66	4.21
1738.0	3.49	3.76	4.29
1798.3	3.69	3.88	4.33
1838.4	3.89	4.02	4.45
1898.7	4.09	4.09	4.43
1938.9	4.30	4.26	4.57
1999.2	4.51	4.32	4.53
2039.4	4.70	4.46	4.66
2099.6	4.91	4.55	4.63
2139.8	5.06	4.67	4.72
2200.1	5.30	4.78	4.75

IF (OUT) (MHz)	IF VSWR @LO=1010.1MHz (:1)		
	@LO (dBm)		
	+4	+7	+10
5.0	1.27	1.29	1.32
10.1	1.06	1.15	1.16
30.3	1.11	1.12	1.27
50.5	1.14	1.27	1.34
70.7	1.16	1.26	1.31
90.9	1.17	1.26	1.33
111.1	1.14	1.22	1.31
131.3	1.14	1.23	1.30
151.5	1.15	1.23	1.30
171.7	1.14	1.25	1.32
191.9	1.15	1.22	1.29
212.1	1.14	1.22	1.28
232.3	1.14	1.22	1.29
252.5	1.15	1.23	1.30
272.8	1.17	1.25	1.33
293.0	1.17	1.26	1.33
313.2	1.19	1.27	1.35
333.4	1.19	1.28	1.36
353.6	1.21	1.31	1.38
373.8	1.22	1.32	1.39
394.0	1.22	1.31	1.38
434.4	1.23	1.33	1.40
454.6	1.25	1.34	1.42
495.0	1.25	1.34	1.41
515.2	1.27	1.36	1.43
555.6	1.30	1.39	1.47
575.8	1.31	1.40	1.48
616.2	1.34	1.42	1.50
636.4	1.36	1.44	1.52
676.8	1.38	1.47	1.54
697.0	1.40	1.47	1.55
737.4	1.44	1.52	1.59
757.7	1.46	1.54	1.61
798.1	1.49	1.56	1.62
818.3	1.52	1.59	1.65
858.7	1.60	1.67	1.73
878.9	1.62	1.68	1.74
919.3	1.68	1.73	1.78
939.5	1.72	1.78	1.83
979.9	1.79	1.84	1.88
1000.1	1.81	1.85	1.89

REV. X2
RMS-11X+
100818
Page 4 of 5

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+4	11	9	22	14	51	42	43	45	43
1	-	7	+0	27	18	24	30	32	40	40	43	42
2	108	52	64	43	53	53	59	58	44	59	59	57
3	114	59	62	67	57	68	64	58	70	72	67	68
4	109	86	82	77	85	75	84	83	79	81	75	81
5	116	92	106	95	95	118	85	101	93	87	103	94
6	117	105	102	101	110	111	101	95	103	107	95	100
7	115	106	110	109	102	100	107	109	86	98	103	118
8	109	95	97	104	100	102	104	98	102	92	98	100
9	117	100	108	106	105	109	104	110	103	108	97	103
10	125	104	100	94	101	105	120	107	106	114	122	89
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 950.1 MHz; -14.00 dBm.
LO IN: 980.01 MHz; +7.00 dBm
IF OUT: 29.91 MHz; -21.96 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	7	21	19	35	28	50	63	61	54	57
1	-	7	+0	29	18	28	33	37	50	50	58	63
2	89	50	66	39	47	51	47	53	40	65	59	62
3	112	41	45	49	42	48	63	42	52	51	56	57
4	119	70	76	59	66	52	60	61	71	66	53	65
5	124	76	77	71	60	78	53	75	58	59	70	73
6	113	88	78	91	81	71	75	68	73	78	72	74
7	117	88	99	83	98	81	78	79	70	76	75	71
8	99	92	93	92	89	91	85	83	90	76	85	87
9	119	99	109	96	107	87	99	92	93	95	85	90
10	110	96	100	99	102	97	97	97	94	89	92	84
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 950.1 MHz; -4.00 dBm.
LO IN: 980.01 MHz; +7.00 dBm
IF OUT: 29.91 MHz; -11.94 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
RMS-11X+
100818
Page 5 of 5




Frequency Mixer


RMS-11X+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=510.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=1010.1MHz



IP3 Input



Compression @ RF IN=+1dBm



REV. X2
RMS-11X+
100818
Page 1 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+4	11	9	22	14	51	42	43	45	43
1	-	7	+0	27	18	24	30	32	40	40	43	42
2	108	52	64	43	53	53	59	58	44	59	59	57
3	114	59	62	67	57	68	64	58	70	72	67	68
4	109	86	82	77	85	75	84	83	79	81	75	81
5	116	92	106	95	95	118	85	101	93	87	103	94
6	117	105	102	101	110	111	101	95	103	107	95	100
7	115	106	110	109	102	100	107	109	86	98	103	118
8	109	95	97	104	100	102	104	98	102	92	98	100
9	117	100	108	106	105	109	104	110	103	108	97	103
10	125	104	100	94	101	105	120	107	106	114	122	89
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 950.1 MHz; -14.00 dBm.
LO IN: 980.01 MHz; +7.00 dBm
IF OUT: 29.91 MHz; -21.96 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	7	21	19	35	28	50	63	61	54	57
1	-	7	+0	29	18	28	33	37	50	50	58	63
2	89	50	66	39	47	51	47	53	40	65	59	62
3	112	41	45	49	42	48	63	42	52	51	56	57
4	119	70	76	59	66	52	60	61	71	66	53	65
5	124	76	77	71	60	78	53	75	58	59	70	73
6	113	88	78	91	81	71	75	68	73	78	72	74
7	117	88	99	83	98	81	78	79	70	76	75	71
8	99	92	93	92	89	91	85	83	90	76	85	87
9	119	99	109	96	107	87	99	92	93	95	85	90
10	110	96	100	99	102	97	97	97	94	89	92	84
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER


Test conditions: RF IN: 950.1 MHz; -4.00 dBm.
LO IN: 980.01 MHz; +7.00 dBm
IF OUT: 29.91 MHz; -11.94 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.


REV. X2
RMS-11X+
100818
Page 3 of 3



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
TT240	.250 (6.35)	.31 (7.87)	.20 (5.08)	.100 (2.54)	.050 (1.27)	.055 (1.40)	.040 (1.02)	.070 (1.78)	.270 (6.86)	.050 (1.27)	.50

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: 2-10 μ inch (.05-.25 microns) Gold plate over 100-300 μ inch (2.54-7.62 microns) Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F2



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
16	12	7	10
			20
			50
			100
			200
		13	500
			1000


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION
FOR BH292, CD541/542/636/637, TT100/240 CASE
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

MMG

07/17/02

CHECKED

WL

08/02/02

APPROVED

DJ

08/05/02



Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,
 CD541/542/636/637, TT100/240, TB-03

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-052

REV:

C

FILE:

98PL052

SCALE:

8:1

SHEET:

1 OF 1


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to
Data Sheet of the DUT



TB-03



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215