



Mini-Circuits

SURFACE MOUNT

Power Splitter/Combiner **SBTC-2-10-75+**

2 Way-0° 75Ω 10 to 1000 MHz

FEATURES

- Low Insertion Loss, 0.8 dB Typ.
- High Isolation
- Excellent Amplitude Unbalance, 0.15 dB Typ.
- Very Good Phase Unbalance, 1.0 deg. Typ.
- Temperature Stable LTCC Base
- Small Size
- Low Cost
- Aqueous Washable

For Model
with Leads see
[SBTC-2-10-75L+](#)



Generic photo used for illustration purposes only

CASE STYLE: AT790

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- UHF/VHF Receivers/Transmitters
- Cellular

ELECTRICAL SPECIFICATIONS AT +25°C


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		1000	MHz
Insertion Loss Above 3.0 dB	10-100		0.7	1.2	dB
	100-500		0.6	1.2	
	500-1000		0.7	1.4	
Isolation	10-100	20	35		dB
	100-500	20	28		
	500-1000	17	21		
Phase Unbalance	10-100			3	Degree
	100-500			3	
	500-1000			5	
Amplitude Unbalance	10-100			0.7	dB
	100-500			0.6	
	500-1000			0.6	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Power Input (as a Splitter)	0.5 W max.
Internal Dissipation	0.125 W max

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
ECO-015187
SBTC-2-10-75+
MCL NY
250414

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT

Power Splitter/Combiner **SBTC-2-10-75+**


2 Way-0° 75Ω 10 to 1000 MHz

PIN CONNECTIONS

SUM PORT	6
PORT 1	3
PORT 2	4
GROUND	1,2
NOT USED	5

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-277+
SUGGESTED PCB LAYOUT (PL-153)




NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.030" \pm 0.002"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F	G	H	J	K	wt
.150	.150	.150	.050	.030	.025	.028	.050	.160	.030	grams
3.81	3.81	3.81	1.27	0.76	0.64	0.71	1.27	4.06	0.76	0.10

TAPE & REEL INFORMATION: F15



Mini-Circuits

SURFACE MOUNT

Power Splitter/Combiner




SBTC-2-10-75+

2 Way-0° 75Ω 10 to 1000 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.74	3.42	0.31	37.11	0.66	1.04	1.33	1.23
50	3.73	3.43	0.3	40.95	0.14	1.02	1.29	1.21
70	3.73	3.44	0.29	39.94	0.14	1.03	1.28	1.21
100	3.74	3.46	0.29	38.55	0.13	1.04	1.27	1.2
200	3.77	3.54	0.22	35.75	0.09	1.1	1.26	1.21
300	3.79	3.57	0.22	32.58	0.54	1.13	1.27	1.22
400	3.8	3.6	0.2	30.37	0.6	1.17	1.28	1.26
500	3.85	3.69	0.16	28.37	0.64	1.2	1.24	1.27
600	3.87	3.75	0.12	25.52	0.74	1.18	1.21	1.28
700	3.82	3.75	0.07	24.07	0.75	1.19	1.2	1.3
800	3.83	3.82	0.03	22.85	0.77	1.19	1.26	1.32
850	3.84	3.86	0.03	22.4	0.73	1.18	1.23	1.31
900	3.85	3.9	0.06	22.15	0.69	1.17	1.23	1.32
950	3.86	3.93	0.08	21.95	0.64	1.18	1.25	1.35
1000	3.86	3.98	0.11	21.68	0.58	1.18	1.25	1.35

1. Total Loss = Insertion Loss + 3 dB splitter loss.



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



2 Way-0° Power Splitter/Combiner SBTC-2-10-75+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
10	3.74	3.43	0.31	0.40	38.17	1.04	1.33	1.25
20	3.74	3.43	0.31	0.14	40.42	1.01	1.32	1.24
30	3.75	3.44	0.31	0.07	40.25	1.01	1.32	1.24
40	3.75	3.44	0.31	0.04	39.82	1.01	1.31	1.24
50	3.76	3.45	0.31	0.01	39.20	1.02	1.31	1.24
60	3.76	3.45	0.31	0.00	38.60	1.02	1.31	1.24
70	3.77	3.46	0.31	0.04	38.09	1.03	1.31	1.24
80	3.77	3.46	0.31	0.10	37.71	1.04	1.31	1.24
90	3.78	3.47	0.31	0.06	37.33	1.05	1.31	1.24
100	3.78	3.47	0.31	0.09	36.86	1.05	1.31	1.24
150	3.80	3.49	0.31	0.16	35.41	1.08	1.30	1.22
200	3.81	3.51	0.30	0.23	34.69	1.11	1.28	1.23
250	3.82	3.52	0.30	0.33	33.78	1.14	1.27	1.25
300	3.83	3.54	0.29	0.42	31.91	1.16	1.26	1.25
350	3.83	3.57	0.26	0.52	30.17	1.18	1.25	1.23
400	3.84	3.59	0.25	0.62	29.14	1.19	1.24	1.24
450	3.86	3.61	0.25	0.69	28.73	1.20	1.23	1.26
475	3.89	3.62	0.27	0.76	28.37	1.20	1.23	1.27
500	3.88	3.64	0.24	0.77	28.42	1.21	1.22	1.27
550	3.90	3.66	0.24	0.84	27.43	1.21	1.22	1.25
600	3.93	3.70	0.23	0.91	26.12	1.22	1.22	1.25
650	3.96	3.73	0.23	1.01	25.28	1.22	1.21	1.26
700	3.99	3.75	0.24	1.12	24.90	1.21	1.22	1.28
750	4.02	3.77	0.25	1.27	24.43	1.20	1.22	1.27
800	4.04	3.81	0.23	1.42	23.64	1.17	1.22	1.25
850	4.05	3.83	0.22	1.50	22.66	1.16	1.23	1.25
900	4.08	3.87	0.21	1.55	21.80	1.14	1.24	1.26
925	4.11	3.88	0.23	1.37	21.56	1.13	1.25	1.26
950	4.11	3.90	0.21	1.53	21.36	1.12	1.26	1.26
975	4.14	3.91	0.23	1.44	21.01	1.10	1.26	1.25
1000	4.14	3.93	0.21	1.51	20.93	1.09	1.27	1.24
1025	4.17	3.94	0.23	1.49	20.67	1.08	1.28	1.24
1050	4.17	3.96	0.21	1.40	20.27	1.07	1.29	1.24
1075	4.19	3.97	0.22	1.42	20.21	1.06	1.30	1.24
1100	4.20	4.00	0.20	1.36	19.64	1.05	1.30	1.24
1200	4.25	4.07	0.18	1.17	19.05	1.00	1.34	1.26
1300	4.31	4.16	0.16	1.02	19.18	1.02	1.38	1.29
1400	4.37	4.23	0.14	1.15	19.44	1.04	1.42	1.32
1500	4.41	4.32	0.08	1.37	20.37	1.04	1.46	1.34
1600	4.49	4.47	0.02	1.65	22.35	1.06	1.50	1.36
1700	4.68	4.68	0.00	1.87	24.09	1.07	1.55	1.39
1800	4.99	4.95	0.04	1.95	23.16	1.09	1.61	1.44
1900	5.27	5.12	0.15	1.44	21.07	1.11	1.68	1.52
2000	5.47	5.13	0.34	1.42	19.25	1.15	1.77	1.63
2100	5.42	5.10	0.33	1.14	18.21	1.19	1.87	1.77
2200	5.32	4.95	0.37	0.90	17.84	1.20	1.95	1.87
2300	5.31	4.90	0.42	1.42	17.92	1.19	2.01	1.94
2400	5.33	5.09	0.25	1.29	17.27	1.16	2.04	1.93
2500	5.72	5.67	0.06	0.76	15.76	1.16	2.07	1.92
2600	6.26	6.20	0.06	0.39	14.03	1.17	2.09	1.84
2700	7.25	6.85	0.40	2.05	12.30	1.19	2.09	1.76
2800	8.14	7.49	0.65	5.41	11.31	1.23	2.08	1.68
2900	8.80	7.68	1.12	5.96	10.84	1.25	2.09	1.65
3000	9.09	7.36	1.73	5.76	10.47	1.28	2.08	1.64

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SBTC-2-10-75+
100627
Page 1 of 3



Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner SBTC-2-10-75+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
10	3.59	3.36	0.23	1.51	32.58	1.08	1.33	1.24
20	3.53	3.33	0.20	0.73	39.16	1.05	1.26	1.20
30	3.52	3.32	0.20	0.45	44.50	1.05	1.24	1.18
40	3.52	3.33	0.19	0.33	50.02	1.05	1.23	1.17
50	3.53	3.33	0.20	0.24	54.11	1.06	1.23	1.16
60	3.53	3.33	0.20	0.23	52.55	1.07	1.22	1.16
70	3.53	3.33	0.20	0.19	48.97	1.07	1.22	1.15
80	3.53	3.33	0.20	0.13	46.41	1.07	1.22	1.16
90	3.54	3.34	0.20	0.17	44.29	1.06	1.21	1.16
100	3.54	3.34	0.20	0.12	42.54	1.06	1.21	1.16
150	3.56	3.36	0.20	0.09	38.32	1.08	1.20	1.18
200	3.57	3.36	0.21	0.09	36.49	1.10	1.20	1.17
250	3.58	3.38	0.20	0.07	35.13	1.11	1.21	1.21
300	3.59	3.39	0.20	0.08	33.05	1.14	1.22	1.22
350	3.60	3.41	0.19	0.09	30.81	1.16	1.24	1.21
400	3.61	3.43	0.18	0.11	29.35	1.17	1.25	1.23
450	3.63	3.44	0.19	0.17	28.71	1.20	1.25	1.27
475	3.65	3.45	0.20	0.15	28.30	1.21	1.26	1.28
500	3.64	3.46	0.18	0.22	28.43	1.21	1.26	1.29
550	3.66	3.48	0.18	0.29	27.50	1.24	1.26	1.28
600	3.68	3.50	0.18	0.35	26.04	1.24	1.27	1.27
650	3.70	3.52	0.18	0.38	24.95	1.25	1.27	1.30
700	3.74	3.54	0.20	0.37	24.30	1.25	1.27	1.31
750	3.75	3.55	0.20	0.34	23.71	1.22	1.28	1.30
800	3.76	3.58	0.18	0.30	22.91	1.19	1.28	1.28
850	3.77	3.60	0.17	0.32	21.80	1.15	1.28	1.27
900	3.79	3.63	0.16	0.43	20.82	1.12	1.28	1.27
925	3.82	3.63	0.19	0.68	20.57	1.11	1.28	1.26
950	3.81	3.65	0.16	0.57	20.29	1.09	1.28	1.25
975	3.84	3.65	0.19	0.73	19.91	1.07	1.28	1.24
1000	3.84	3.67	0.17	0.76	19.82	1.05	1.28	1.22
1025	3.87	3.68	0.19	0.81	19.58	1.03	1.28	1.21
1050	3.87	3.69	0.18	0.98	19.21	1.02	1.28	1.20
1075	3.89	3.70	0.19	0.98	19.14	1.02	1.29	1.19
1100	3.90	3.72	0.18	1.13	18.60	1.03	1.29	1.19
1200	3.95	3.79	0.16	1.58	18.04	1.09	1.31	1.18
1300	4.01	3.86	0.15	2.05	18.26	1.10	1.33	1.21
1400	4.05	3.92	0.13	2.31	18.67	1.09	1.38	1.28
1500	4.06	3.99	0.07	2.45	19.81	1.06	1.47	1.39
1600	4.13	4.12	0.01	2.45	22.10	1.02	1.58	1.52
1700	4.31	4.33	0.02	2.42	24.23	1.02	1.69	1.64
1800	4.65	4.66	0.01	2.63	22.90	1.02	1.79	1.71
1900	4.92	4.78	0.14	3.48	20.52	1.04	1.84	1.73
2000	5.09	4.75	0.35	3.63	18.74	1.06	1.87	1.69
2100	5.00	4.65	0.35	4.37	17.87	1.14	1.88	1.64
2200	4.89	4.46	0.43	6.68	17.83	1.24	1.91	1.59
2300	4.89	4.46	0.43	7.81	18.20	1.30	1.94	1.63
2400	4.88	4.61	0.28	8.29	17.35	1.36	1.99	1.75
2500	5.27	5.21	0.06	7.63	15.03	1.37	2.10	1.99
2600	5.87	5.92	0.05	7.90	12.92	1.39	2.25	2.26
2700	6.99	6.66	0.33	5.86	11.17	1.30	2.33	2.48
2800	7.93	7.38	0.55	2.37	10.21	1.17	2.37	2.50
2900	8.43	7.51	0.92	2.21	9.87	1.05	2.34	2.35
3000	8.56	6.98	1.58	2.82	9.60	1.23	2.25	2.16

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SBTC-2-10-75+
100627
Page 2 of 3

2 Way-0° Power Splitter/Combiner SBTC-2-10-75+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
10	3.86	3.51	0.35	0.40	35.73	1.05	1.38	1.28
20	3.86	3.50	0.36	0.16	36.56	1.04	1.36	1.27
30	3.88	3.52	0.36	0.10	36.31	1.04	1.36	1.28
40	3.88	3.53	0.35	0.07	35.98	1.04	1.36	1.29
50	3.88	3.53	0.35	0.02	35.59	1.05	1.36	1.30
60	3.89	3.54	0.35	0.05	35.31	1.06	1.36	1.30
70	3.89	3.54	0.35	0.01	35.03	1.06	1.36	1.30
80	3.90	3.54	0.36	0.06	34.82	1.07	1.36	1.30
90	3.91	3.55	0.36	0.01	34.71	1.08	1.36	1.30
100	3.91	3.56	0.35	0.06	34.51	1.08	1.35	1.29
150	3.92	3.58	0.34	0.10	33.74	1.09	1.34	1.25
200	3.92	3.59	0.33	0.18	33.30	1.11	1.32	1.26
250	3.93	3.62	0.31	0.29	32.61	1.15	1.30	1.27
300	3.94	3.64	0.30	0.41	30.96	1.17	1.27	1.25
350	3.95	3.66	0.29	0.52	29.46	1.17	1.25	1.24
400	3.96	3.69	0.27	0.64	28.68	1.19	1.24	1.25
450	3.98	3.72	0.26	0.73	28.39	1.19	1.22	1.26
475	4.01	3.72	0.29	0.78	28.05	1.19	1.22	1.26
500	4.01	3.75	0.26	0.81	28.06	1.19	1.21	1.26
550	4.03	3.78	0.25	0.92	27.15	1.20	1.20	1.25
600	4.06	3.82	0.24	0.99	26.03	1.20	1.20	1.24
650	4.08	3.85	0.23	1.11	25.37	1.20	1.20	1.25
700	4.12	3.87	0.24	1.24	25.11	1.20	1.20	1.27
750	4.14	3.90	0.24	1.39	24.72	1.19	1.20	1.25
800	4.17	3.94	0.23	1.59	24.01	1.17	1.21	1.24
850	4.18	3.97	0.21	1.70	23.09	1.17	1.22	1.25
900	4.21	4.01	0.20	1.79	22.26	1.16	1.23	1.27
925	4.24	4.02	0.22	1.61	22.03	1.15	1.24	1.27
950	4.24	4.04	0.20	1.81	21.85	1.14	1.25	1.26
975	4.26	4.05	0.21	1.69	21.48	1.13	1.26	1.25
1000	4.27	4.08	0.19	1.77	21.41	1.12	1.27	1.25
1025	4.30	4.09	0.21	1.77	21.16	1.11	1.28	1.25
1050	4.30	4.11	0.19	1.74	20.73	1.11	1.29	1.25
1075	4.32	4.12	0.20	1.77	20.66	1.10	1.30	1.26
1100	4.32	4.15	0.17	1.75	20.08	1.09	1.31	1.26
1200	4.37	4.23	0.14	1.64	19.47	1.03	1.35	1.28
1300	4.44	4.31	0.13	1.57	19.54	1.02	1.39	1.30
1400	4.50	4.39	0.11	1.82	19.72	1.01	1.42	1.33
1500	4.55	4.49	0.05	2.08	20.60	1.03	1.45	1.32
1600	4.64	4.64	0.00	2.42	22.49	1.06	1.47	1.33
1700	4.83	4.85	0.02	2.70	24.10	1.09	1.50	1.33
1800	5.13	5.11	0.02	2.89	23.29	1.13	1.54	1.38
1900	5.41	5.28	0.13	2.48	21.29	1.17	1.62	1.47
2000	5.61	5.30	0.31	2.45	19.50	1.22	1.72	1.61
2100	5.57	5.27	0.31	2.37	18.44	1.27	1.83	1.80
2200	5.47	5.15	0.32	0.69	18.10	1.27	1.94	1.93
2300	5.48	5.12	0.37	0.12	18.22	1.24	2.01	2.00
2400	5.50	5.32	0.19	0.24	17.65	1.18	2.03	1.96
2500	5.87	5.89	0.01	0.68	16.27	1.15	2.05	1.90
2600	6.39	6.39	0.00	1.30	14.59	1.17	2.05	1.75
2700	7.33	7.01	0.32	3.88	12.82	1.24	2.03	1.64
2800	8.19	7.60	0.59	7.32	11.80	1.30	2.02	1.57
2900	8.83	7.75	1.08	8.20	11.30	1.34	2.04	1.58
3000	9.13	7.44	1.69	8.11	10.89	1.35	2.06	1.63

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SBTC-2-10-75+
100627
Page 3 of 3



Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




2 Way-0° Power Splitter/Combiner


SBTC-2-10-75+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE



REV. X2
SBTC-2-10-75+
100627
Page 1 of 2



Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SBTC-2-10-75+


Typical Performance Curves




REV. X2
SBTC-2-10-75+
100627
Page 2 of 2

Outline Dimensions

AT790



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT790	.150 (3.81)	.150 (3.81)	.150 (3.81)	.050 (1.27)	.030 (0.76)	.025 (0.64)	.028 (0.71)	.050 (1.27)	.160 (4.06)	.030 (0.76)	-- --	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Ceramic base.
2. Termination finish: Silver palladium or gold over nickel based on stock availability.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F15

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	20
			50
			100
			200
		13	500
			1000
			2000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M90457	NEW RELEASE	01/16/04	AV	WP
A	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR
AT1029 CASE STYLE, "nc" PIN CONNECTION




NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

01/07/04

TOLERANCES ON:

CHECKED

IL

01/16/04

2 PL DECIMALS $\pm$

APPROVED

WP

01/16/04

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, nc, 75, AT1029, SBTC, TB-277

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-153

REV:

A

FILE:

98PL153


SCALE:

10:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-277



Schematic Diagram

Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215