



CERAMIC

Power Splitter/Combiner

SCG-3-262+

Mini-Circuits

3 Way-0° 50Ω 1600 to 2600 MHz

FEATURES

- Isolation resistor, external 150 ohms
- Low insertion loss, 1.2 dB typ.
- Excellent amplitude unbalance, 0.4 dB typ.
- Excellent phase unbalance, 5 deg. typ.
- High isolation, 17 dB typ.
- ESD non-sensitive
- Temperature stable LTCC technology
- Wrap around terminations for excellent solderability
- Low cost



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-1

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- ISM
- WLAN
- Bluetooth

ELECTRICAL SPECIFICATIONS AT 25°C


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1600		2600	MHz
Insertion Loss, above 4.8 dB	1600 - 2600	—	1.2	1.8	dB
Isolation	1600 - 2600	12.5	17	—	dB
Phase Unbalance	1600 - 2600	—	5	8.5	Degree
Amplitude Unbalance	1600 - 2600	—	0.4	0.85	dB
Return Loss (Input)	1600 - 2600	—	12	—	dB
Return Loss (Output)	1600 - 2600	—	18	—	dB

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	2W* max.

* Derate linearly to 0.7W at 100°C ambient, power input as combiner is limited by rating of external resistor 150Ω resistor. Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC





CERAMIC

Power Splitter/Combiner

SCG-3-262+

Mini-Circuits


3 Way-0° 50Ω 1600 to 2600 MHz

PAD CONNECTIONS

SUM PORT	2
PORT 1	6
PORT 2	4
PORT 3	3
GROUND	1,5
PORT 1-2, 2-3, 1-3	resistor external 150 ohms

PRODUCT MARKING: SQ


DEMO BOARD MCL P/N: TB-1044+
SUGGESTED PCB LAYOUT (PL-622)



NOTES:

1. LINE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066±.0007. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS LINE WIDTH MAY NEED TO BE MODIFIED.
 2. UNIT FOOT PRINT IS OPTIMIZED FOR PERFORMANCE AND IS DIFFERENT FROM CASE STYLE GE0805C-1 RECOMMENDATIONS.
 3. CHIP COMPONENT FOOT PRINT IS SHOWN FOR REFERENCE. FOR COMPONENT VALUE REFER TO TB-1044+.
 4. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

OUTLINE DRAWING



*Shape of index marking may vary

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F
.079	.049	.033	.014	.012	.012
2.01	1.24	0.84	0.36	0.30	0.30
G	H	J	K		wt
.026	.014	.039	.110		grams
0.66	0.36	1.00	2.80		.008

TAPE & REEL INFORMATION: F74



CERAMIC

Power Splitter/Combiner

SCG-3-262+

Mini-Circuits




3 Way-0° 50Ω

1600 to 2600 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Total Loss ¹ (dB)			Amplitude Unbalance (dB)	Isolation (dB)			Phase Unbalance (deg.)	Return Loss (dB)		
	S-1	S-2	S-3		1-2	1-3	2-3		S	1	2
1600	5.42	5.85	5.94	0.53	14.86	14.43	15.07	0.79	9.14	27.90	33.33
1650	5.39	5.80	5.90	0.51	15.52	15.01	15.59	0.64	9.48	28.05	38.46
1700	5.36	5.75	5.85	0.49	16.22	15.62	16.15	0.41	9.83	27.76	49.81
1750	5.33	5.70	5.80	0.47	17.00	16.30	16.76	0.23	10.27	27.01	44.63
1800	5.31	5.65	5.75	0.45	17.85	17.03	17.43	0.19	10.75	26.20	36.91
1850	5.27	5.59	5.70	0.42	18.83	17.85	18.17	0.38	11.30	25.34	33.26
1900	5.25	5.54	5.64	0.39	19.92	18.75	18.99	0.64	11.94	24.61	30.86
1950	5.23	5.48	5.59	0.36	21.24	19.82	19.94	0.88	12.72	23.93	29.38
2000	5.21	5.44	5.54	0.33	22.80	21.02	21.02	1.14	13.63	23.41	28.34
2100	5.19	5.35	5.45	0.26	27.33	24.13	23.73	1.68	16.06	22.55	26.60

1. Total Loss = Insertion Loss + 4.8dB splitter loss.



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



3 Way-0° Power Splitter/Combiner

SCG-3-262+






Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	1-3	2-3			S	1	2	3
1000	5.70	6.16	6.22	0.53	9.60	9.64	10.51	2.99	1000	2.57	1.49	1.45	1.42
1050	5.68	6.15	6.21	0.53	9.92	9.95	10.82	2.86	1050	2.54	1.43	1.40	1.37
1100	5.66	6.14	6.20	0.54	10.25	10.26	11.13	2.71	1100	2.51	1.38	1.35	1.33
1150	5.64	6.12	6.19	0.55	10.60	10.59	11.46	2.49	1150	2.47	1.34	1.31	1.29
1200	5.61	6.11	6.17	0.56	10.97	10.94	11.80	2.30	1200	2.44	1.29	1.27	1.25
1250	5.59	6.08	6.15	0.56	11.37	11.30	12.15	2.13	1250	2.40	1.25	1.24	1.22
1300	5.57	6.06	6.13	0.56	11.78	11.68	12.51	1.93	1300	2.36	1.22	1.20	1.18
1350	5.55	6.03	6.11	0.56	12.22	12.08	12.89	1.71	1350	2.32	1.19	1.17	1.15
1400	5.53	6.00	6.09	0.56	12.68	12.49	13.28	1.51	1400	2.28	1.16	1.14	1.13
1450	5.50	5.97	6.05	0.55	13.18	12.94	13.69	1.31	1450	2.23	1.13	1.11	1.10
1500	5.47	5.93	6.02	0.55	13.70	13.40	14.12	1.16	1500	2.18	1.11	1.09	1.08
1550	5.44	5.89	5.98	0.54	14.27	13.91	14.58	0.99	1550	2.13	1.09	1.07	1.06
1600	5.42	5.85	5.94	0.53	14.86	14.43	15.07	0.79	1600	2.07	1.08	1.04	1.05
1650	5.39	5.80	5.90	0.51	15.52	15.01	15.59	0.64	1650	2.01	1.08	1.02	1.04
1700	5.36	5.75	5.85	0.49	16.22	15.62	16.15	0.41	1700	1.95	1.09	1.01	1.04
1750	5.33	5.70	5.80	0.47	17.00	16.30	16.76	0.23	1750	1.88	1.09	1.01	1.05
1800	5.31	5.65	5.75	0.45	17.85	17.03	17.43	0.19	1800	1.82	1.10	1.03	1.06
1850	5.27	5.59	5.70	0.42	18.83	17.85	18.17	0.38	1850	1.75	1.11	1.04	1.06
1900	5.25	5.54	5.64	0.39	19.92	18.75	18.99	0.64	1900	1.68	1.12	1.06	1.07
1950	5.23	5.48	5.59	0.36	21.24	19.82	19.94	0.88	1950	1.60	1.14	1.07	1.08
2000	5.21	5.44	5.54	0.33	22.80	21.02	21.02	1.14	2000	1.53	1.14	1.08	1.09
2050	5.19	5.38	5.49	0.29	24.77	22.46	22.27	1.42	2050	1.45	1.15	1.09	1.10
2100	5.19	5.35	5.45	0.26	27.33	24.13	23.73	1.68	2100	1.37	1.16	1.10	1.11
2150	5.19	5.31	5.41	0.22	31.14	26.20	25.49	1.93	2150	1.30	1.17	1.10	1.12
2200	5.20	5.28	5.38	0.18	37.43	28.50	27.49	2.18	2200	1.23	1.18	1.11	1.12
2250	5.22	5.27	5.36	0.14	40.89	30.49	29.46	2.45	2250	1.17	1.18	1.12	1.13
2300	5.25	5.26	5.35	0.10	32.96	30.46	30.39	2.74	2300	1.12	1.19	1.13	1.14
2350	5.30	5.27	5.35	0.07	28.27	28.34	29.30	2.97	2350	1.13	1.20	1.14	1.16
2400	5.36	5.30	5.37	0.07	25.21	25.86	27.17	3.24	2400	1.18	1.22	1.16	1.18
2450	5.44	5.34	5.40	0.10	22.92	23.66	24.97	3.53	2450	1.26	1.24	1.18	1.19
2500	5.55	5.40	5.45	0.14	21.14	21.81	23.03	3.82	2500	1.37	1.26	1.20	1.22
2550	5.67	5.48	5.52	0.19	19.67	20.27	21.42	4.11	2550	1.48	1.29	1.23	1.25
2600	5.82	5.58	5.61	0.23	18.47	18.95	20.03	4.35	2600	1.62	1.33	1.26	1.28
2650	5.99	5.71	5.72	0.28	17.45	17.85	18.86	4.70	2650	1.78	1.38	1.30	1.32
2700	6.19	5.87	5.87	0.32	16.58	16.90	17.85	5.02	2700	1.95	1.42	1.35	1.36
2750	6.40	6.04	6.03	0.38	15.83	16.08	16.98	5.35	2750	2.16	1.48	1.39	1.41
2800	6.65	6.24	6.21	0.43	15.19	15.36	16.23	5.72	2800	2.38	1.54	1.44	1.46
2850	6.91	6.45	6.42	0.49	14.66	14.76	15.61	6.15	2850	2.63	1.61	1.50	1.52
2900	7.20	6.70	6.66	0.54	14.20	14.24	15.05	6.55	2900	2.91	1.69	1.56	1.58
2950	7.51	6.96	6.92	0.59	13.83	13.80	14.59	6.94	2950	3.23	1.77	1.63	1.64
3000	7.85	7.27	7.21	0.64	13.52	13.42	14.18	7.35	3000	3.57	1.85	1.70	1.71

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss



Typical Performance Curves



Tape & Reel Packaging TR-F74

DEVICE ORIENTATION IN T&R



ILLUSTRATION 1

Applicable Case Styles

GE0805C-1
 GE0805C-1AP
 JV1210C-1
 GU2939



ILLUSTRATION 2

Applicable Case Styles

JV1210C
 JV1210C-2
 JV1210C-3
 JV1210C-4
 JV1210C-5
 JV1210C-6
 JV1210C-11



ILLUSTRATION 3

Applicable Case Styles

JC0603C-8
 JV1210C-7
 JV1210C-8
 JV1210C-9
 JV1210C-10
 JV1210C-13
 GE0805C-13

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000
				2000
			4000	

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M173102	NEW RELEASE	03/12/19	ITG	SL

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-1 CASE STYLE, "06SP18" PIN CODE




NOTES:

1. LINE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS LINE WIDTH MAY NEED TO BE MODIFIED.
2. UNIT FOOT PRINT IS OPTIMIZED FOR PERFORMANCE AND IS DIFFERENT FROM CASE STYLE GE0805C-1 RECOMMENDATIONS.
3. CHIP COMPONENT FOOT PRINT IS SHOWN FOR REFERENCE. FOR COMPONENT VALUE REFER TO TB-1044+.
4. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	ITG 03/07/19
	CHECKED	GF 03/12/19
	APPROVED	SL 03/12/19



Mini-Circuits®



13 Neptune Avenue
Brooklyn NY 11235

PL, 06SP18, GE0805C-1, TB-1044+

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-622	REV: OR
FILE: 98PL622	SCALE: 15:1	SHEET: 1 OF 1	


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A