

# Surface Mount Power Splitter/Combiner

## SCP-4-4-75+

4 Way-0° 75Ω

10 to 1000 MHz



Generic photo used for illustration purposes only  
CASE STYLE: YY161

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.375W max.

Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

SUM PORT	3
PORT 1	2
PORT 2	4
PORT 3	6
PORT 4	8
GROUND	1,5,7

### Outline Drawing



#### PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002


### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
0.75	0.38	0.28	0.01	0.05	0.02	0.2
19.05	9.65	7.11	0.25	1.27	0.51	5.08

H	J	K	M	N	P	wt
0.075	0.6	0.45	0.47	0.1	0.15	grams
1.91	15.24	11.43	11.94	2.54	3.81	1.60

### Demo Board MCL P/N: TB-184 Suggested PCB Layout (PL-175)



NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .030 ± .002; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- wideband, 10 to 1000 MHz
- high isolation, 32 dB typ
- excellent amplitude unbalance, 0.4 dB typ.

### Applications

- cellular
- CATV
- receivers/transmitters

### Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)			INSERTION LOSS (dB) ABOVE 6 dB			PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)								
	L	M	U	L	M	U	L	M	U	L	M	U						
f <sub>L</sub> -f <sub>U</sub>	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Max.	Typ. Max.	Typ. Max.	Max.	Max.	Max.	Max.	Max.	Max.						
10-1000	36	20	32	18	24	14	0.5	1.0	0.65	1.3	0.8	2.0	3	6	12	0.2	0.4	0.9

L = low range [f<sub>L</sub> to 10 f<sub>L</sub>] M = mid range [10 f<sub>L</sub> to f<sub>U</sub>/2] U = upper range [f<sub>U</sub>/2 to f<sub>U</sub>]

### Typical Performance Data

Freq. (MHz)	Total Loss <sup>1</sup> (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4						
10.00	6.56	6.48	6.57	6.50	0.09	26.09	39.05	25.95	0.09	1.11	1.27	1.27	1.28	1.28
28.00	6.58	6.51	6.59	6.53	0.08	25.99	39.79	25.80	0.07	1.11	1.26	1.26	1.27	1.27
82.00	6.63	6.56	6.64	6.58	0.08	25.86	38.34	25.94	0.11	1.11	1.27	1.27	1.28	1.26
125.00	6.66	6.58	6.65	6.58	0.08	26.12	37.42	26.25	0.20	1.11	1.27	1.27	1.27	1.26
200.00	6.71	6.64	6.71	6.63	0.08	26.87	35.99	26.84	0.20	1.10	1.26	1.27	1.27	1.26
275.00	6.73	6.67	6.74	6.63	0.11	27.64	34.09	27.28	0.26	1.10	1.25	1.26	1.26	1.25
350.00	6.72	6.68	6.75	6.65	0.10	27.84	31.86	27.36	0.27	1.10	1.25	1.26	1.25	1.24
425.00	6.80	6.77	6.80	6.68	0.13	27.09	29.59	26.76	0.34	1.10	1.24	1.25	1.24	1.22
500.00	6.85	6.82	6.85	6.71	0.15	25.59	27.43	25.69	0.37	1.08	1.22	1.24	1.22	1.21
575.00	6.90	6.89	6.88	6.73	0.17	23.96	25.56	24.52	0.52	1.07	1.21	1.22	1.20	1.19
650.00	6.98	6.99	6.95	6.78	0.22	22.67	23.98	23.58	0.59	1.07	1.19	1.21	1.18	1.17
750.00	7.07	7.14	7.06	6.85	0.29	21.62	22.43	23.02	0.94	1.09	1.17	1.20	1.17	1.15
850.00	7.16	7.28	7.14	6.89	0.39	21.38	21.37	23.46	1.76	1.13	1.18	1.22	1.18	1.15
950.00	7.27	7.45	7.23	6.92	0.52	21.57	20.80	24.89	2.57	1.14	1.21	1.26	1.22	1.17
1000.00	7.32	7.55	7.29	6.96	0.59	21.44	20.64	25.48	3.07	1.13	1.24	1.29	1.25	1.21

1. Total Loss = Insertion Loss + 6dB splitter loss.



### Electrical Schematic



# 4 Way-0° Power Splitter/Combiner

# SCP-4-4-75+

## Typical Performance Data

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
10.0	6.56	6.48	6.57	6.50	0.09	26.09	39.05	25.95	0.09	10.0	1.11	1.27	1.27	1.28	1.28
19.0	6.57	6.51	6.59	6.52	0.08	26.13	39.74	25.94	0.06	19.0	1.11	1.26	1.26	1.27	1.27
28.0	6.58	6.51	6.59	6.53	0.08	25.99	39.79	25.80	0.07	28.0	1.11	1.26	1.26	1.27	1.27
37.0	6.60	6.51	6.59	6.53	0.08	25.86	39.67	25.73	0.10	37.0	1.11	1.26	1.26	1.27	1.27
46.0	6.60	6.51	6.59	6.53	0.08	25.80	39.53	25.75	0.10	46.0	1.11	1.27	1.27	1.28	1.26
55.0	6.61	6.52	6.60	6.54	0.09	25.78	39.20	25.75	0.07	55.0	1.11	1.27	1.27	1.28	1.26
64.0	6.62	6.54	6.62	6.57	0.08	25.79	38.91	25.81	0.08	64.0	1.11	1.27	1.27	1.28	1.26
73.0	6.64	6.56	6.64	6.57	0.08	25.82	38.65	25.88	0.07	73.0	1.11	1.27	1.27	1.28	1.26
82.0	6.63	6.56	6.64	6.58	0.08	25.86	38.34	25.94	0.11	82.0	1.11	1.27	1.27	1.28	1.26
91.0	6.63	6.56	6.63	6.57	0.07	25.87	38.16	25.99	0.09	91.0	1.11	1.27	1.27	1.28	1.26
100.0	6.65	6.56	6.64	6.58	0.08	25.93	37.97	26.04	0.10	100.0	1.11	1.27	1.27	1.28	1.26
125.0	6.66	6.58	6.65	6.58	0.08	26.12	37.42	26.25	0.20	125.0	1.11	1.27	1.27	1.27	1.26
150.0	6.66	6.59	6.66	6.58	0.08	26.33	36.98	26.45	0.23	150.0	1.10	1.27	1.27	1.27	1.26
175.0	6.69	6.63	6.68	6.62	0.07	26.62	36.41	26.60	0.12	175.0	1.10	1.27	1.27	1.27	1.26
200.0	6.71	6.64	6.71	6.63	0.08	26.87	35.99	26.84	0.20	200.0	1.10	1.26	1.27	1.27	1.26
225.0	6.70	6.63	6.70	6.62	0.08	27.10	35.46	27.04	0.28	225.0	1.11	1.26	1.26	1.27	1.26
250.0	6.69	6.63	6.70	6.60	0.09	27.37	34.78	27.18	0.32	250.0	1.10	1.26	1.26	1.26	1.25
275.0	6.73	6.67	6.74	6.63	0.11	27.64	34.09	27.28	0.26	275.0	1.10	1.25	1.26	1.26	1.25
300.0	6.74	6.69	6.76	6.66	0.09	27.81	33.46	27.40	0.27	300.0	1.10	1.25	1.26	1.26	1.25
325.0	6.73	6.71	6.76	6.65	0.11	27.86	32.73	27.45	0.27	325.0	1.10	1.25	1.26	1.26	1.24
350.0	6.72	6.68	6.75	6.65	0.10	27.84	31.86	27.36	0.27	350.0	1.10	1.25	1.26	1.25	1.24
375.0	6.74	6.73	6.75	6.65	0.10	27.71	31.11	27.24	0.39	375.0	1.10	1.24	1.25	1.25	1.24
400.0	6.77	6.75	6.78	6.67	0.11	27.46	30.36	27.05	0.36	400.0	1.10	1.24	1.25	1.25	1.23
425.0	6.80	6.77	6.80	6.68	0.13	27.09	29.59	26.76	0.34	425.0	1.10	1.24	1.25	1.24	1.22
450.0	6.81	6.76	6.80	6.67	0.14	26.59	28.85	26.42	0.32	450.0	1.09	1.23	1.24	1.23	1.22
475.0	6.81	6.80	6.81	6.68	0.13	26.09	28.14	26.13	0.36	475.0	1.09	1.23	1.24	1.23	1.21
500.0	6.85	6.82	6.85	6.71	0.15	25.59	27.43	25.69	0.37	500.0	1.08	1.22	1.24	1.22	1.21
525.0	6.86	6.85	6.85	6.72	0.14	25.03	26.77	25.28	0.35	525.0	1.08	1.22	1.23	1.21	1.20
550.0	6.88	6.87	6.86	6.72	0.17	24.46	26.13	24.92	0.45	550.0	1.07	1.21	1.23	1.21	1.19
575.0	6.90	6.89	6.88	6.73	0.17	23.96	25.56	24.52	0.52	575.0	1.07	1.21	1.22	1.20	1.19
600.0	6.92	6.93	6.91	6.75	0.17	23.47	24.98	24.18	0.56	600.0	1.07	1.20	1.22	1.19	1.18
625.0	6.96	6.95	6.93	6.77	0.19	23.04	24.46	23.85	0.58	625.0	1.07	1.19	1.22	1.19	1.17
650.0	6.98	6.99	6.95	6.78	0.22	22.67	23.98	23.58	0.59	650.0	1.07	1.19	1.21	1.18	1.17
675.0	6.99	7.03	6.98	6.79	0.23	22.32	23.54	23.35	0.69	675.0	1.07	1.18	1.21	1.17	1.16
700.0	7.02	7.06	7.01	6.82	0.24	22.02	23.11	23.17	0.80	700.0	1.08	1.18	1.21	1.17	1.16
750.0	7.07	7.14	7.06	6.85	0.29	21.62	22.43	23.02	0.94	750.0	1.09	1.17	1.20	1.17	1.15
800.0	7.13	7.23	7.12	6.89	0.34	21.45	21.82	23.10	1.35	800.0	1.11	1.17	1.21	1.17	1.15
850.0	7.16	7.28	7.14	6.89	0.39	21.38	21.37	23.46	1.76	850.0	1.13	1.18	1.22	1.18	1.15
900.0	7.22	7.36	7.20	6.91	0.45	21.50	20.98	24.05	2.14	900.0	1.14	1.19	1.23	1.19	1.15
950.0	7.27	7.45	7.23	6.92	0.52	21.57	20.80	24.89	2.57	950.0	1.14	1.21	1.26	1.22	1.17
1000.0	7.32	7.55	7.29	6.96	0.59	21.44	20.64	25.48	3.07	1000.0	1.13	1.24	1.29	1.25	1.21






<sup>1</sup> Total Loss = Insertion Loss+ 6dB Splitter Loss



# 4 Way-0° Power Splitter/Combiner

# SCP-4-4-75+

## Typical Performance Curves



REV. X2  
SCP-4-4-75+  
100627  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# Case Style


YY

## Outline Dimensions

YY101  
YY109  
YY161



## PCB Land Pattern



Suggested Layout  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAMS
YY101*			.20 (5.08)							.450 (11.43)	-- (11.94)	.470 (11.94)				1.6
YY109*	.75 (19.05)	.38 (9.65)	.20 (5.08)	.010 (0.25)	.050 (1.27)	.020 (0.51)	.200 (5.08)	.075 (1.91)	.600 (15.24)	.720 (18.29)	-- (18.80)	.740 (18.80)	.100 (2.54)	.150 (3.81)	.148 (3.76)	1.6
YY161			.28 (7.11)							.450 (11.43)	-- (11.94)	.470 (11.94)				1.6

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.
- Special Tolerances: Termination thickness  $\pm .003$  inch.
- \* Denotes: For SCM mixers, long termination version (case YY109) is available upon request, consult factory. To order short termination version (case YY101) add -NL suffix.

**Mini-Circuits**<sup>®</sup>


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M96392	NEW RELEASE	01/27/05	MMG	HY
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

**SUGGESTED MOUNTING CONFIGURATION FOR YY161 CASE STYLE, "bv" PIN CONNECTION**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



SOLID BLUE DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 HATCHED BLUE DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES  
 TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ±  
 FRACTIONS ±

	INITIALS	DATE
DRAWN	MMG	01/24/05
CHECKED	AV	01/27/05
APPROVED	HY	01/27/05





**Mini-Circuits®** 13 Neptune Avenue  
 Brooklyn NY 11235

PL, bv, 75, YY161, SCP, TB-184

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-175	REV: A
FILE: 98PL175	SCALE: 5:1	SHEET: 1 OF 1	


# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215