

Surface Mount Phase Shifter

SCPHS-51+

50Ω 360° Voltage Variable 25 to 48 MHz

The Big Deal

- Low insertion loss, 2 dB typ.
- Wide phase shift, 360°
- Low frequency and small size



CASE STYLE: HU1371

Product Overview

Mini-Circuits' SCPHS-51+ is a voltage variable phase shifter providing 360° phase control from 25 to 48 MHz in a miniature surface mount package. This model has a control bandwidth of DC to 30 kHz and a control voltage range from 0 to +15V. Housed in a shielded, 12-lead package with wrap-around terminations, the unit measures only 0.87 x 0.80 x 0.25", offering a space-efficient, low-cost alternative to larger, expensive connectorized phase shifters typical for low frequency operation.

| Feature | Advantages |
|--|---|
| Low insertion loss, 2.0 dB typ. | Enables good transmission of signal power from input to output and minimizes effect on system noise figure. |
| Wide phase shift, 360° | In test environments, 360° phase control allows the user to experiment with various incident phases. This can be used to test residual phase noise of amplifiers and to determine the influence of phase between two mismatched components in a system. |
| Low frequency operation and tiny size, 0.87 x 0.80 x 0.25" | Typically, lower frequency phase shifters are large, connectorized designs. SCPHS-51+ provides low frequency phase shift capability in a tiny surface mount package, saving space and reducing system cost. |

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Phase Shifter

50Ω 360° Voltage Variable 25 to 48 MHz

SCPHS-51+



Generic photo used for illustration purposes only

CASE STYLE: HU1371

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size Devices/Reel
13" 200

Maximum Ratings

| | |
|---|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Input Power | 24 dBm max. |
| Control Voltage | 20V |
| Permanent damage may occur if any of these limits are exceeded. | |

Pin Connections

| | |
|--------|------------------------|
| IN | 1 |
| OUT | 6 |
| BIAS | 10,11 [^] |
| GROUND | 2,3,4,5,7,8,9,12,13,14 |

[^] proper operation is achieved with pins 10 or 11 or both connected to BIAS.

Features

- low insertion loss, 2 dB typ.
- wide phase shift, 360°
- aqueous washable

Applications

- cellular
- PCS
- DCS

Electrical Specifications at 25°C

| Parameter | Condition (MHz) | Min. | Typ. | Max. | Unit |
|-------------------|-----------------|------|-------|------|---------|
| Frequency Range | | 25 | | 48 | MHz |
| Phase Range | 25 - 48 | 360 | — | — | Degrees |
| Insertion Loss | 25 - 48 | — | 2 | 5 | dB |
| Control Voltage | 25 - 48 | — | 0-15 | — | V |
| Control Bandwidth | 25 - 48 | — | DC-30 | — | kHz |
| VSWR | 25 - 48 | — | 1.3 | — | :1 |


DC input resistance at Control port: 1460 ohms typ.

Typical Performance Data

| Control Voltage (V) | Phase Shift* (Degrees) | | | VSWR (:1) | | | Insertion Loss (dB) | | |
|---------------------|------------------------|--------|--------|-----------|--------|--------|---------------------|--------|--------|
| | 25 MHz | 36 MHz | 48 MHz | 25 MHz | 36 MHz | 48 MHz | 25 MHz | 36 MHz | 48 MHz |
| 0 | 0.00 | 0.00 | 0.00 | 1.05 | 1.31 | 1.98 | 1.30 | 1.24 | 1.82 |
| 1 | 30.63 | 8.93 | 3.27 | 1.01 | 1.37 | 1.97 | 1.41 | 1.33 | 1.84 |
| 2 | 61.71 | 17.67 | 6.36 | 1.01 | 1.43 | 1.96 | 1.50 | 1.42 | 1.86 |
| 3 | 96.98 | 27.52 | 9.71 | 1.12 | 1.47 | 1.95 | 1.59 | 1.52 | 1.88 |
| 4 | 139.22 | 39.87 | 13.73 | 1.43 | 1.52 | 1.94 | 1.80 | 1.63 | 1.90 |
| 5 | 189.01 | 57.10 | 19.07 | 1.97 | 1.53 | 1.92 | 2.24 | 1.77 | 1.93 |
| 6 | 242.80 | 83.57 | 26.73 | 2.31 | 1.47 | 1.88 | 2.43 | 1.92 | 1.97 |
| 7 | 297.41 | 126.54 | 38.22 | 1.79 | 1.25 | 1.81 | 1.77 | 2.09 | 2.03 |
| 8 | 347.41 | 191.95 | 55.35 | 1.11 | 1.11 | 1.69 | 1.18 | 2.35 | 2.13 |
| 9 | 384.48 | 272.98 | 80.40 | 1.49 | 1.11 | 1.52 | 1.23 | 2.37 | 2.31 |
| 10 | 409.11 | 350.06 | 116.80 | 1.89 | 1.34 | 1.33 | 1.44 | 2.21 | 2.66 |
| 11 | 425.41 | 406.15 | 167.54 | 2.14 | 1.47 | 1.19 | 1.58 | 1.95 | 3.23 |
| 12 | 436.27 | 443.24 | 230.39 | 2.28 | 1.33 | 1.12 | 1.66 | 1.60 | 3.82 |
| 13 | 443.66 | 467.67 | 295.74 | 2.35 | 1.18 | 1.25 | 1.69 | 1.37 | 4.07 |
| 14 | 448.92 | 484.24 | 352.40 | 2.39 | 1.09 | 1.51 | 1.70 | 1.23 | 4.07 |
| 15 | 452.83 | 496.02 | 395.47 | 2.42 | 1.09 | 1.81 | 1.71 | 1.16 | 4.03 |

* Normalized at control voltage = 0V


Outline Drawing



Outline Dimensions (inch/mm)


| A | B | C | D | E | F | G | H |
|-------|-------|------|------|------|-------|-------|---|
| .870 | .800 | .250 | .100 | .097 | -.060 | .040 | |
| 22.10 | 20.32 | 6.35 | 2.54 | 2.46 | -1.52 | 1.02 | |
| J | K | L | M | N | P | wt | |
| .105 | .910 | - | .060 | .060 | - | grams | |
| 2.67 | 23.11 | - | 1.52 | 1.52 | - | 2.85 | |

Demo Board MCL P/N: TB-1141+ Suggested PCB Layout (PL-690)




- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.002-.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.


SCPHS-51+ PHASE SHIFT




SCPHS-51+ VSWR



SCPHS-51+ INSERTION LOSS



Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-005108
SCPHS-51+
ZL/CP/AM
201208

PHASE SHIFTER




SCPHS-51+

Typical Performance Data

| CONTROL VOLTAGE (V) | PHASE SHIFT* (Deg.) | | | VSWR (:1) | | | INSERTION LOSS (dB) | | |
|---------------------|---------------------|--------|--------|-----------|--------|--------|---------------------|--------|--------|
| | 25 MHz | 36 MHz | 48 MHz | 25 MHz | 36 MHz | 48 MHz | 25 MHz | 36 MHz | 48 MHz |
| 0 | 0.00 | 0.00 | 0.00 | 1.05 | 1.31 | 1.98 | 1.30 | 1.24 | 1.82 |
| 1 | 30.63 | 8.93 | 3.27 | 1.01 | 1.37 | 1.97 | 1.41 | 1.33 | 1.84 |
| 2 | 61.71 | 17.67 | 6.36 | 1.01 | 1.43 | 1.96 | 1.50 | 1.42 | 1.86 |
| 3 | 96.98 | 27.52 | 9.71 | 1.12 | 1.47 | 1.95 | 1.59 | 1.52 | 1.88 |
| 4 | 139.22 | 39.87 | 13.73 | 1.43 | 1.52 | 1.94 | 1.80 | 1.63 | 1.90 |
| 5 | 189.01 | 57.10 | 19.07 | 1.97 | 1.53 | 1.92 | 2.24 | 1.77 | 1.93 |
| 6 | 242.80 | 83.57 | 26.73 | 2.31 | 1.47 | 1.88 | 2.43 | 1.92 | 1.97 |
| 7 | 297.41 | 126.54 | 38.22 | 1.79 | 1.25 | 1.81 | 1.77 | 2.09 | 2.03 |
| 8 | 347.41 | 191.95 | 55.35 | 1.11 | 1.11 | 1.69 | 1.18 | 2.35 | 2.13 |
| 9 | 384.48 | 272.98 | 80.40 | 1.49 | 1.11 | 1.52 | 1.23 | 2.37 | 2.31 |
| 10 | 409.11 | 350.06 | 116.80 | 1.89 | 1.34 | 1.33 | 1.44 | 2.21 | 2.66 |
| 11 | 425.41 | 406.15 | 167.54 | 2.14 | 1.47 | 1.19 | 1.58 | 1.95 | 3.23 |
| 12 | 436.27 | 443.24 | 230.39 | 2.28 | 1.33 | 1.12 | 1.66 | 1.60 | 3.82 |
| 13 | 443.66 | 467.67 | 295.74 | 2.35 | 1.18 | 1.25 | 1.69 | 1.37 | 4.07 |
| 14 | 448.92 | 484.24 | 352.40 | 2.39 | 1.09 | 1.51 | 1.70 | 1.23 | 4.07 |
| 15 | 452.83 | 496.02 | 395.47 | 2.42 | 1.09 | 1.81 | 1.71 | 1.16 | 4.03 |


*Normalized at control voltage = 0V

Typical Performance Curves




Outline Dimensions

HU1371



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N | P | WT, GRAM |
|--------|-----------------|-----------------|---------------|----------------|----------------|---|----------------|----------------|----------------|-----------------|---|----------------|----------------|---|----------|
| HU1371 | .870 (22.10) | .800 (20.32) | .25 (6.35) | .100 (2.54) | .097 (2.46) | - | .060 (1.52) | .040 (1.02) | .105 (2.67) | .910 (23.11) | - | .060 (1.52) | .060 (1.52) | - | 2.85 |

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over .120-.240 μ inch (3.05-6.10 microns) Nickel plate. All models (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel |
|---------------------------|------------------------------------|------------------------------|-------------------------|
| 32 | 32 | 13 | 200 |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|------------|-------------|----------|-----|------|
| OR | ECO-003790 | NEW RELEASE | 08/24/20 | ITG | IL |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR
HU1371 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030±.002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| | | | |
|----------------------------|----------|-----|----------|
| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |
| DIMENSIONS ARE IN INCHES | DRAWN | ITG | 08/24/20 |
| TOLERANCES ON: | CHECKED | GF | 08/24/20 |
| 2 PL DECIMALS ± | APPROVED | IL | 08/24/20 |
| 3 PL DECIMALS ± .005 | | | |
| ANGLES ± | | | |
| FRACTIONS ± | | | |



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, HU1371, TB-1141+

| | | | |
|------------------|---------------------|--------------------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-690 | REV: OR |
| FILE: 98PL690 | SCALE: 2.5:1 | SHEET: 1 OF 1 | |

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |