

Surface Mount Bandpass Filter

SXBP-169+

50Ω 164 to 174 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)




- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- high rejection
- good VSWR, 1.3:1 typ @ passband
- aqueous washable

Applications

- radio link
- receivers / transmitters
- professional mobile radio / public access mobile radio (PMR/ PAMR)



Generic photo used for illustration purposes only

CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
Fc	F1 - F2	F3	F4	F5	F6	Typ.	Max.	Typ.
169	164 - 174	137	205	122	240 - 2500	1.3	1.9	18

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	\bar{x}	σ			
1.0	82.10	2.30	0.38	155.0	41.11
110.0	62.23	0.84	0.15	156.0	38.37
122.0	50.32	0.82	0.15	158.0	34.97
126.0	45.85	0.92	0.17	160.0	32.58
137.0	31.35	1.24	0.40	161.0	31.67
140.0	26.73	1.37	0.53	162.0	31.02
150.0	7.41	1.62	5.90	163.0	30.49
152.0	4.56	1.09	12.24	164.0	30.13
164.0	2.04	0.03	18.54	165.0	29.92
169.0	2.00	0.02	20.31	166.0	29.86
174.0	2.28	0.07	14.37	167.0	29.85
185.0	7.34	1.60	3.16	168.0	29.85
190.0	15.14	1.79	1.33	169.0	29.87
205.0	31.92	1.00	0.52	170.0	29.85
240.0	51.59	0.57	0.22	172.0	29.68
1000.0	79.07	3.14	0.10	174.0	30.40
2000.0	60.93	0.84	0.32	175.0	31.30
2500.0	52.98	0.33	0.37	180.0	42.56



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
ECO-005139
EDR-8754UF1
SXBP-169+
URJ/RAV
201201
Page 1 of 1

Surface Mount Band Pass Filter

SXBP-169+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	95.93	94.03	103.06	0.30	0.38	0.47	0.28	0.39	0.47
10	84.42	87.68	89.83	0.35	0.44	0.53	0.33	0.44	0.52
50	78.59	89.18	84.19	0.27	0.31	0.33	0.26	0.31	0.34
100	71.87	71.80	71.29	0.10	0.15	0.18	0.10	0.15	0.19
110	62.15	61.54	61.61	0.10	0.15	0.18	0.09	0.14	0.18
122	50.03	49.56	49.39	0.12	0.18	0.21	0.11	0.17	0.20
126	45.26	45.00	44.75	0.14	0.21	0.25	0.13	0.19	0.23
137	30.45	30.09	29.69	0.33	0.44	0.51	0.27	0.37	0.42
140	25.48	25.08	24.63	0.48	0.63	0.74	0.38	0.51	0.60
150	5.42	5.44	5.32	6.45	7.83	9.18	5.28	6.31	7.30
152	3.16	3.44	3.57	14.72	17.27	20.04	11.53	12.93	14.32
164	1.80	2.13	2.33	15.75	15.99	16.20	14.83	15.23	15.67
169	1.74	2.09	2.34	19.37	19.31	19.02	26.07	31.11	35.30
174	1.99	2.39	2.66	15.13	14.75	14.54	16.44	16.11	16.03
185	9.04	10.15	11.11	2.52	2.52	2.44	3.17	3.19	3.11
190	16.92	17.79	18.58	1.01	1.13	1.19	1.26	1.40	1.46
205	32.98	33.48	33.91	0.36	0.46	0.50	0.43	0.53	0.59
220	42.83	43.18	43.46	0.22	0.30	0.35	0.26	0.34	0.39
230	47.88	48.09	48.38	0.18	0.25	0.29	0.19	0.27	0.32
240	51.98	52.36	52.67	0.14	0.21	0.25	0.16	0.23	0.28
300	68.73	69.59	69.29	0.05	0.13	0.16	0.06	0.13	0.17
400	89.03	83.54	86.29	0.01	0.08	0.13	0.01	0.08	0.13
500	92.95	99.73	108.34	0.02	0.07	0.12	0.00	0.08	0.13
600	99.20	92.64	84.54	0.01	0.08	0.14	0.02	0.09	0.15
700	86.40	90.55	92.70	0.01	0.10	0.16	0.02	0.09	0.16
800	87.72	98.28	90.97	0.01	0.11	0.17	0.02	0.11	0.18
900	83.31	95.42	83.15	0.00	0.12	0.19	0.01	0.14	0.20
1000	78.07	90.30	80.33	0.00	0.14	0.21	0.01	0.14	0.21
1200	75.00	89.33	74.88	0.01	0.17	0.25	0.02	0.19	0.28
1300	77.41	80.23	78.32	0.02	0.19	0.27	0.04	0.21	0.29
1400	69.00	79.61	69.81	0.02	0.20	0.31	0.02	0.20	0.31
1500	73.93	81.42	75.06	0.03	0.22	0.31	0.04	0.23	0.33
1600	80.64	72.69	86.53	0.03	0.23	0.33	0.05	0.24	0.36
1700	66.57	70.81	68.55	0.06	0.24	0.36	0.06	0.26	0.38
1800	66.45	76.49	75.28	0.07	0.27	0.37	0.05	0.28	0.39
1900	59.17	63.40	61.05	0.07	0.27	0.39	0.06	0.28	0.41
2000	66.70	65.29	65.07	0.06	0.29	0.40	0.04	0.29	0.39
2200	63.07	59.70	62.04	0.08	0.31	0.44	0.06	0.31	0.43
2300	56.58	51.76	53.87	0.09	0.34	0.47	0.07	0.33	0.46
2400	56.13	60.33	56.14	0.10	0.33	0.49	0.08	0.33	0.48
2500	52.45	56.36	52.39	0.09	0.35	0.51	0.08	0.33	0.50
2600	45.41	45.72	43.59	0.11	0.37	0.52	0.11	0.37	0.53
2700	48.32	49.59	46.66	0.12	0.36	0.53	0.12	0.37	0.58
2800	40.19	43.88	39.91	0.15	0.41	0.59	0.07	0.35	0.53
2900	43.61	45.20	47.93	0.12	0.40	0.58	0.11	0.38	0.58
3000	41.32	41.79	40.69	0.08	0.41	0.55	0.13	0.40	0.62
3200	39.89	37.57	37.83	0.13	0.53	0.66	0.13	0.47	0.68
3300	38.93	39.66	40.15	0.23	0.56	0.86	0.11	0.49	0.70
3400	41.15	36.88	38.60	0.36	0.95	1.28	0.17	0.64	0.80
3500	35.87	36.46	36.93	1.68	1.38	1.50	0.43	1.03	1.27
3600	34.59	34.56	35.25	0.47	0.71	0.97	0.64	0.82	0.97
3700	34.73	31.70	32.76	0.25	0.69	0.94	0.30	0.71	1.01
3800	32.87	32.17	30.87	0.31	0.67	1.03	0.35	0.70	1.10
4000	30.62	28.65	30.68	0.43	0.82	1.18	0.31	0.75	1.05

REV. X2
SXBP-169+
101118
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

SXBP-169+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
60	4.42	2.97	6.78
70	21.82	7.65	24.77
80	18.15	25.64	27.14
90	6.11	17.63	15.63
100	7.48	4.76	9.74
110	2.37	2.97	3.28
120	2.74	3.68	2.92
130	5.17	5.45	5.70
140	11.37	11.98	12.62
150	45.89	46.16	46.54
160	33.20	32.83	32.56
161	32.19	31.93	31.68
162	31.32	31.10	30.95
163	30.58	30.45	30.39
164	30.06	30.02	30.00
165	29.67	29.73	29.75
166	29.50	29.55	29.65
167	29.47	29.55	29.67
168	29.52	29.63	29.72
169	29.68	29.77	29.84
170	29.81	29.87	29.96
171	29.97	30.04	30.14
172	30.08	30.24	30.38
173	30.44	30.66	30.90
174	30.88	31.19	31.61
175	31.65	32.13	32.72
176	32.84	33.53	34.23
177	34.58	35.28	36.08
178	36.57	37.17	37.81
179	38.61	38.91	39.16
180	40.25	40.03	39.72
190	14.68	14.01	13.34
192	11.35	10.91	10.64
193	10.22	9.82	9.61
194	9.18	8.89	8.69
195	8.31	8.07	7.87
196	7.50	7.40	7.26
197	6.94	6.81	6.63
198	6.27	6.27	6.13
199	5.93	5.83	5.72
200	5.50	5.44	5.39
202	4.81	4.73	4.62
203	4.49	4.53	4.47
204	4.18	4.17	4.21
206	3.76	3.80	3.64
207	3.60	3.53	3.70
208	3.35	3.32	3.36
209	3.20	3.23	3.22
210	3.10	3.03	3.09
220	2.19	2.41	2.17
230	1.66	1.67	1.90
240	1.82	1.06	1.50
250	0.92	1.81	0.94
300	0.90	0.07	1.04

REV. X2
SXBP-169+
101118
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. TEMPERATURE




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

**SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.**




NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAVON)	29 NOV 05
	CHECKED	RZ (RAVON)	29 NOV 05
	APPROVED	HH (RAVON)	29 NOV 05



Mini-Circuits®


13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-230	REV: OR
FILE: 98PL230	SCALE: 4:1	SHEET: 1 OF 1	

Evaluation Board and Circuit




TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215