



COAXIAL

Adapter

SMPF-SF50+

50Ω DC to 18 GHz SMP-Female to SMA-Female

THE BIG DEAL

- Low Insertion Loss, 0.04 dB
- Excellent VSWR, 1.18
- Low cost adapters, available from stock
- Passivated stainless steel body (SMA) and gold-plated beryllium copper (SMP)



Generic photo used for illustration purposes only

Model No.	SMPF-SF50+
Case Style	DJ2142
Connectors	SMP-Female to SMA-Female

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Interconnection of RF cables and equipment

PRODUCT OVERVIEW

Mini-Circuits' SMPF-SF50+ is a coaxial SMP-F to SMA-F adapter supporting a wide range of applications from DC to 18 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The SMPF-SF50+ features passivated stainless steel (SMA side) and Gold-plated beryllium copper construction (SMP side) and measures only 0.28" (l) x 0.67" (dia.)

KEY FEATURES

Feature	Advantages
Wideband, DC to 18 GHz	Wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use.
Excellent VSWR, 1.18:1	Provides good matching for 50Ω systems and minimizes signal reflections across wide frequency range.
Low Insertion Loss, 0.04 dB	Provides excellent signal power transmission from input to output.
Passivated stainless steel (SMA side) and Gold-plated beryllium copper (SMP side) construction	Stands up to wear and tear in demanding environments and provides excellent reliability.
Very wide operating temperature range, -45 to +100 °C	Withstands extreme operating conditions and is suitable for use near high power componentry where heat rise is common.

REV. A
ECO-016727
SMPF-SF50+
MCL NY
230203





COAXIAL

Adapter

SMPF-SF50+

50Ω DC to 18 GHz SMP-Female to SMA-Female

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		18	GHz
Insertion Loss	DC - 18	–	0.04	–	dB
VSWR	DC - 8	–	1.04	1.2	:1
	DC - 12.4	–	1.07	1.2	
	DC - 18	–	1.07	1.2	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-45°C to +100°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded.






COAXIAL

Adapter

SMPF-SF50+

50Ω DC to 18 GHz SMP-Female to SMA-Female

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	wt
.28	.67	.250	grams
7.112	17.02	6.35	2.3



COAXIAL

Adapter



SMPF-SF50+

Mini-Circuits

50Ω DC to 18 GHz SMP-Female to SMA-Female

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	
		SMP-Female	SMA-Female
10	0.00	1.01	1.01
50	0.01	1.01	1.01
100	0.01	1.01	1.01
1000	0.04	1.01	1.02
2000	0.05	1.03	1.03
3000	0.05	1.03	1.03
4000	0.05	1.02	1.03
5000	0.05	1.03	1.03
6000	0.06	1.05	1.04
8000	0.04	1.08	1.11
9000	0.02	1.13	1.17
10000	0.01	1.13	1.18
11000	0.02	1.08	1.12
12000	0.03	1.07	1.07
13000	0.03	1.09	1.07
15000	0.04	1.06	1.01
16000	0.04	1.05	1.06
18000	0.01	1.10	1.09



NOTES




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html




Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE VSWR (:1)	SMA FEMALE VSWR (:1)
10	0.00	1.01	1.01
50	0.01	1.01	1.01
100	0.01	1.01	1.01
200	0.01	1.01	1.01
300	0.02	1.01	1.01
400	0.02	1.01	1.01
500	0.02	1.01	1.01
600	0.03	1.01	1.01
700	0.03	1.01	1.02
800	0.03	1.01	1.02
900	0.03	1.01	1.02
1000	0.04	1.01	1.02
1500	0.04	1.02	1.02
2000	0.05	1.03	1.03
2500	0.05	1.03	1.03
3000	0.05	1.03	1.03
3500	0.05	1.03	1.03
4000	0.05	1.02	1.03
4500	0.05	1.02	1.02
5000	0.05	1.03	1.03
5500	0.05	1.04	1.04
6000	0.05	1.05	1.04
6500	0.05	1.05	1.05
7000	0.05	1.04	1.06
7500	0.04	1.06	1.08
8000	0.04	1.08	1.11
8500	0.03	1.11	1.15
9000	0.01	1.13	1.17
9500	0.01	1.14	1.19
10000	0.02	1.13	1.18
10500	0.02	1.10	1.15
11000	0.03	1.08	1.12
11500	0.03	1.07	1.09
12000	0.03	1.07	1.07
12500	0.03	1.09	1.06
13000	0.03	1.09	1.06
13500	0.03	1.09	1.06
14000	0.04	1.08	1.04
14500	0.04	1.07	1.03
15000	0.04	1.06	1.02
15500	0.05	1.05	1.04
16000	0.05	1.05	1.07
16500	0.04	1.06	1.09
17000	0.03	1.07	1.11
17500	0.02	1.08	1.10
18000	0.01	1.10	1.09

Typical Performance Curves



Outline Dimensions



CASE #	A	B	C	D	E	WT. GRAM
DJ2142	.28 (7.1)	.67 (17.0)	.250 (6.4)	-	-	2.3

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. + .005

Notes:

1. Case material: Stainless steel.
2. Finish: Passivation.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I