


Surface Mount

# Bandpass Filter

SXBP-72+

50Ω      68 to 76 MHz



Generic photo used for illustration purposes only  
CASE STYLE: HF1139

## The Big Deal

- Narrow bandwidth
- Wide stopband rejection
- Miniature shielded package

## Product Overview

The SXBP-72+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 68-76 MHz. This filter is built with high Q capacitors and wire welded inductors for high reliability. This filter is developed for avionics and air traffic control. It has repeatable performance across lots and consistent performance across temperature.

## Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications such as avionics and air traffic control.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Shielded case	Reduced interference with and from the surrounding components.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Bandpass Filter

50Ω 68-76 MHz



SXB-72+

**Features**

- Narrow bandwidth
- Wide stopband rejection
- Miniature shielded package

**Applications**

- Avionics and air traffic control
- Harmonic rejection
- IF signal processing

**Functional Schematic****Typical Frequency Response**

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications





Electrical Specifications at 25°C							
	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
<b>Pass Band</b>	Center Frequency	—	—	—	72	—	MHz
	Insertion Loss	F1-F2	68-76	—	3.3	5.5	dB
	VSWR	F1-F2	68-76	—	1.5	2.1	:1
<b>Stop Band, Lower</b>	Insertion Loss	DC-F3	DC-60	20	30	—	dB
	VSWR	DC-F3	DC-60	—	20	—	:1
<b>Stop Band, Upper</b>	Insertion Loss	F4-F5	87-4000	20	27	—	dB
	VSWR	F4-F5	87-4000	—	20	—	:1

Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	100 mW

Permanent damage may occur if any of these limits are exceeded.

**Typical Performance Data at 25°C**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	94.38	11.46	68.0	99.74
30	87.51	102.19	68.5	92.99
50	58.12	217.15	69.0	86.81
57	40.63	91.43	69.5	81.77
60	31.32	45.72	70.0	77.93
63	19.97	18.11	70.5	74.91
65	11.09	6.78	71.0	72.72
68	2.95	1.13	71.5	71.11
72	2.36	1.12	71.8	70.38
76	2.69	1.29	72.0	69.89
78	3.44	1.14	72.3	69.30
80	7.69	3.18	72.5	68.91
82	14.39	7.22	73.0	68.40
87	27.77	18.70	73.3	68.11
89	31.77	23.49	73.5	67.92
95	41.06	37.77	74.0	67.80
500	97.94	434.30	74.5	68.01
1000	84.85	289.53	75.0	68.52
2500	52.82	96.51	75.5	69.51
4000	27.66	37.77	76.0	71.45

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)


**Mini-Circuits®**

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

**Pad Connections**


INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7

**Demo Board MCL P/N: TB-368+**  
**Suggested PCB Layout (PL-230)**

**NOTE:**

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS:  $.025'' \pm .002''$ . COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

**Outline Drawing****Outline Dimensions ( inch mm )**

A	B	C	D	E	F	G
.44	.74	.27	.200	.07	.060	.040
11.18	18.80	6.86	5.08	1.78	1.52	1.02
H	J	K	L	M	wt	
.660	.200	.470	.055	.060	grams	
16.76	5.08	11.94	1.40	1.52		3.0

Note: Please refer to case style drawing for details

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Band Pass Filter

# SXBP-72+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C
	1.0	111.68	94.38	93.30	1.17	1.52	1.92	1.15	1.49
39.0	87.12	84.34	97.70	0.08	0.09	0.11	0.07	0.09	0.10
44.0	72.41	72.13	72.45	0.06	0.07	0.08	0.06	0.07	0.09
57.5	39.57	39.17	38.60	0.18	0.21	0.26	0.20	0.25	0.32
60.0	31.74	31.32	30.69	0.31	0.38	0.46	0.37	0.46	0.57
62.5	22.52	22.05	21.38	0.66	0.80	0.99	0.78	0.96	1.21
63.0	20.44	19.97	19.32	0.79	0.96	1.19	0.93	1.15	1.44
65.0	11.42	11.09	10.61	2.14	2.58	3.22	2.52	3.03	3.75
68.0	2.72	2.95	3.23	20.72	24.11	31.15	25.00	25.77	26.19
70.0	2.18	2.44	2.74	24.02	22.72	21.44	22.39	22.14	22.38
70.5	2.14	2.40	2.71	23.78	22.64	21.85	23.50	23.18	23.57
72.0	2.09	2.36	2.68	24.02	25.16	27.74	25.44	26.91	30.70
76.0	2.37	2.69	3.08	18.79	17.98	17.49	18.82	18.48	18.63
77.0	2.53	2.89	3.36	20.72	21.52	23.91	20.59	21.62	23.37
78.0	2.93	3.44	4.16	29.32	23.89	19.13	21.24	19.09	16.05
79.0	4.16	4.97	6.07	11.67	10.50	9.23	10.64	9.60	8.42
80.0	6.65	7.69	9.00	5.97	5.65	5.28	5.54	5.25	4.92
82.0	13.41	14.39	15.58	2.32	2.42	2.50	2.17	2.29	2.38
83.5	18.20	19.05	20.04	1.52	1.64	1.76	1.42	1.56	1.70
84.0	19.66	20.46	21.37	1.36	1.48	1.60	1.27	1.41	1.56
87.0	27.19	27.77	28.47	0.83	0.93	1.03	0.79	0.91	1.03
88.5	30.30	30.82	31.42	0.69	0.79	0.87	0.66	0.78	0.88
97.0	43.29	43.55	43.87	0.36	0.41	0.46	0.34	0.41	0.48
113.0	57.78	57.64	58.03	0.18	0.22	0.25	0.17	0.22	0.27
126.0	64.96	65.48	65.20	0.13	0.15	0.18	0.12	0.16	0.19
140.0	71.07	70.93	72.88	0.10	0.11	0.14	0.08	0.12	0.15
155.0	76.48	77.79	77.05	0.07	0.10	0.11	0.06	0.10	0.11
190.0	84.34	85.10	85.54	0.05	0.07	0.08	0.04	0.07	0.09
420.0	94.27	87.74	85.78	0.00	0.04	0.05	0.01	0.04	0.09
675.0	96.48	91.48	93.16	0.02	0.04	0.06	0.01	0.07	0.12
825.0	88.82	88.93	92.43	0.02	0.05	0.07	0.00	0.09	0.15
1150.0	75.49	76.88	77.86	0.01	0.07	0.10	0.03	0.15	0.20
1200.0	76.14	75.33	75.30	0.01	0.07	0.09	0.04	0.17	0.23
1250.0	80.24	78.71	77.04	0.03	0.05	0.09	0.04	0.15	0.21
1300.0	95.17	83.17	85.58	0.01	0.08	0.11	0.07	0.19	0.26
1400.0	68.38	70.27	69.29	0.00	0.09	0.12	0.07	0.20	0.26
1500.0	81.16	84.43	78.76	0.00	0.10	0.13	0.09	0.23	0.29
1525.0	104.18	86.59	90.29	0.02	0.08	0.11	0.08	0.22	0.28
1625.0	66.89	68.90	70.50	0.01	0.09	0.12	0.09	0.24	0.31
1750.0	77.32	77.54	76.47	0.02	0.09	0.14	0.10	0.25	0.34
1800.0	63.97	62.45	59.97	0.02	0.12	0.17	0.18	0.37	0.53
1825.0	60.61	59.38	58.05	0.02	0.14	0.20	0.26	0.53	0.73
1900.0	61.75	61.77	60.78	0.21	0.46	0.57	0.92	0.71	0.76
2000.0	66.99	67.32	66.63	0.14	0.22	0.27	0.14	0.30	0.42
2025.0	69.27	69.19	71.79	0.06	0.16	0.21	0.14	0.31	0.44
2125.0	55.49	55.05	54.01	0.03	0.15	0.20	0.14	0.31	0.46
2275.0	57.88	57.92	59.14	0.00	0.13	0.19	0.15	0.31	0.45
2325.0	50.85	51.38	50.16	0.05	0.17	0.22	0.14	0.31	0.48
2500.0	52.90	52.82	54.78	0.05	0.18	0.25	0.17	0.33	0.49
2525.0	53.21	53.37	52.20	0.08	0.20	0.28	0.16	0.34	0.51
2675.0	57.22	56.63	57.23	0.06	0.21	0.31	0.20	0.38	0.54
2775.0	45.07	45.19	43.82	0.16	0.38	0.54	0.31	0.53	0.70
2925.0	52.29	61.02	48.91	2.72	1.93	1.99	1.76	2.11	1.97
3000.0	45.10	43.67	42.86	0.48	0.56	0.69	1.04	0.92	0.98
3150.0	44.53	43.52	46.33	0.19	0.32	0.42	0.31	0.51	0.61
3300.0	45.31	44.34	41.20	0.14	0.31	0.42	0.25	0.49	0.63
3450.0	37.23	37.13	36.55	0.29	0.43	0.48	0.24	0.50	0.63
3750.0	31.48	32.23	34.82	0.22	0.42	0.49	0.37	0.74	1.05
3800.0	39.00	39.56	40.23	0.23	0.41	0.56	0.39	0.68	1.04
4000.0	29.11	27.66	26.78	0.26	0.46	0.59	0.34	0.71	1.15



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



REV. OR

SXBP-72+

140215

Page 1 of 2

# Band Pass Filter

**SXPB-72+**

## Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@ -40°C	@ +25°C	@ +85°C
68.0	102.14	99.74	96.68
68.5	94.96	92.99	90.56
69.0	88.20	86.81	84.97
69.5	82.84	81.77	80.37
70.0	78.73	77.93	76.90
70.5	75.57	74.91	74.27
71.0	73.24	72.72	72.21
71.5	71.40	71.11	70.69
72.0	70.04	69.89	69.62
72.5	69.01	68.91	68.69
73.0	68.36	68.40	68.22
73.5	67.93	67.92	67.94
74.0	67.81	67.80	67.75
74.5	67.84	68.01	68.12
75.0	68.22	68.52	69.03
75.5	69.03	69.51	70.47
76.0	70.53	71.45	72.92









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS




REV. OR  
SXPB-72+  
140215  
Page 2 of 2

## Typical Performance Curves



## Typical Performance Curves




# Case Style



HF

HF1139

## Outline Dimensions



## PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .015$ "; 3 Pl.  $\pm .01$ "

### Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
[minicircuits.com](http://minicircuits.com)

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)


RF/IF MICROWAVE COMPONENTS

HF1139 Rev.: P (06/08/19) M175802 File: HF1139.doc  
This document and its contents are the property of Mini-Circuits.

Sheet 1 of 1

# Tape & Reel Packaging TR-F5

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

## THIRD ANGLE PROJECTION




## REVISI

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION

FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



## NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS:  $.025 \pm .002$ ". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## UNLESS OTHERWISE SPECIFIED

## INITIALS

## DATE

DIMENSIONS ARE IN INCHES

DRAWN DK (RAVON) 29 NOV 05

TOLERANCES ON:

CHECKED RZ (RAVON) 29 NOV 05

2 PL DECIMALS  $\pm$ 


APPROVED HH (RAVON) 29 NOV 05

3 PL DECIMALS  $\pm .005$ ANGLES  $\pm$ FRACTIONS  $\pm$ 

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95




Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235


PL, cr, HF1139, SCLF, TB-368

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-230	OR
FILE:	98PL230	SCALE: 4:1	SHEET: 1 OF 1

# Evaluation Board and Circuit



TB-368



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



## Environmental Specifications

## ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215