

Low Pass Filter

50Ω DC to 380 MHz

Maximum Ratings

Operating Temperature -40°C to 85°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W Max.

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

INPUT 1

OUTPUT 8

GROUND 2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	gr
.040	.660	.200	.470	.055	.060	
1.02	16.76	5.08	11.94	1.40	1.52	

Note: Please refer to case style drawing for details


Demo Board MCL P/N: TB-368

Suggested PCB Layout (PL-230)



NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-




Features

- high rejection
- sharp cut-off
- shielded package
- aqueous washable
- low cost

Applications

- defense communications
- receivers / transmitters
- harmonic rejection

SXLP-380+



Generic photo used for illustration purposes only
CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)		VSWR (:1)	
		(Loss > 20dB)	(Loss > 35dB)	Passband Typ.	Stopband Typ.
DC - 380	440	580 - 750	750 - 2200	1.3	18

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
1.0	0.02	0.01	52.50	1.0	2.38
10.0	0.05	0.01	42.94	10.0	2.34
50.0	0.08	0.01	33.85	20.0	2.30
100.0	0.12	0.01	32.54	50.0	2.27
300.0	0.28	0.01	27.42	70.0	2.29
380.0	0.47	0.02	36.10	100.0	2.30
410.0	0.74	0.09	11.33	120.0	2.33
420.0	1.15	0.19	7.78	140.0	2.35
440.0	3.25	0.42	3.44	160.0	2.39
460.0	6.77	0.49	1.55	180.0	2.42
500.0	15.18	0.45	0.54	200.0	2.46
580.0	29.49	0.42	0.28	220.0	2.51
750.0	54.77	2.27	0.19	240.0	2.58
900.0	67.61	2.84	0.16	280.0	2.76
1000.0	67.09	2.24	0.13	300.0	2.87
1200.0	71.02	2.58	0.12	340.0	3.18
1500.0	68.08	4.29	0.10	380.0	3.85
2000.0	66.96	6.58	0.14	400.0	4.51
2100.0	64.85	4.98	0.16	420.0	5.16
2200.0	64.12	5.39	0.18	440.0	5.06



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Low Pass Filter

SXLP-380+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	0.01	0.02	0.03	57.38	54.62	52.48	56.21	53.14	51.25
10	0.03	0.05	0.06	44.89	42.09	40.76	44.58	41.99	40.82
50	0.07	0.11	0.13	33.58	33.39	33.25	34.11	34.58	35.09
100	0.11	0.16	0.18	31.99	33.92	35.21	35.54	39.92	45.57
200	0.20	0.28	0.31	22.43	22.12	21.93	22.16	21.86	21.69
300	0.26	0.36	0.41	29.53	31.58	33.57	29.77	31.64	33.39
380	0.44	0.57	0.64	20.18	20.34	20.45	20.28	20.64	20.97
410	0.62	0.82	0.94	16.96	16.02	15.26	18.08	17.22	16.45
420	0.95	1.20	1.37	11.51	10.88	10.36	11.94	11.40	10.90
440	2.76	3.17	3.47	4.79	4.58	4.38	4.87	4.73	4.55
460	6.32	6.80	7.16	1.91	1.91	1.87	1.91	1.96	1.96
500	15.00	15.42	15.74	0.53	0.59	0.62	0.48	0.59	0.65
580	30.02	30.35	30.58	0.22	0.27	0.30	0.16	0.27	0.32
600	33.37	33.69	33.93	0.20	0.25	0.28	0.13	0.24	0.29
700	49.32	49.70	49.85	0.14	0.18	0.21	0.06	0.17	0.23
750	57.84	58.21	58.34	0.11	0.16	0.20	0.04	0.16	0.22
800	69.70	70.12	70.26	0.10	0.16	0.19	0.02	0.15	0.21
900	72.42	72.19	72.95	0.09	0.14	0.18	0.01	0.15	0.22
1000	71.04	70.94	71.39	0.08	0.14	0.19	0.00	0.15	0.22
1100	73.85	76.48	73.77	0.09	0.15	0.19	0.00	0.16	0.23
1200	78.09	79.58	78.95	0.09	0.16	0.20	0.00	0.16	0.25
1300	84.95	84.03	86.28	0.10	0.17	0.22	0.00	0.18	0.27
1400	95.04	93.35	86.86	0.11	0.19	0.24	0.00	0.19	0.28
1500	85.68	82.15	85.98	0.12	0.20	0.25	0.01	0.21	0.31
1600	80.85	81.86	79.44	0.13	0.21	0.27	0.01	0.21	0.32
1700	75.69	77.12	75.38	0.14	0.22	0.28	0.02	0.23	0.34
1800	70.58	71.89	76.81	0.15	0.24	0.30	0.03	0.25	0.36
1900	72.31	70.55	69.93	0.17	0.26	0.31	0.04	0.27	0.38
2000	74.25	69.96	70.00	0.18	0.27	0.33	0.05	0.28	0.40
2100	59.37	65.21	63.09	0.19	0.29	0.34	0.06	0.29	0.41
2200	61.89	62.42	63.47	0.21	0.30	0.36	0.06	0.31	0.43
2300	53.64	59.33	52.50	0.21	0.31	0.38	0.06	0.32	0.45
2400	51.79	55.44	56.88	0.22	0.33	0.38	0.08	0.33	0.45
2500	53.86	56.64	57.12	0.23	0.34	0.41	0.07	0.34	0.47
2600	53.08	58.66	59.84	0.22	0.34	0.41	0.09	0.35	0.47
2700	53.92	53.89	54.60	0.24	0.35	0.41	0.07	0.36	0.50
2800	46.46	52.19	59.66	0.24	0.37	0.44	0.10	0.37	0.51
2900	50.75	49.58	48.06	0.24	0.37	0.45	0.09	0.40	0.54
3000	42.42	46.89	43.91	0.31	0.40	0.47	0.13	0.42	0.60
3100	43.98	41.18	43.21	0.31	0.44	0.55	0.10	0.43	0.60
3200	40.49	44.36	39.89	0.31	0.42	0.50	0.18	0.45	0.68
3300	42.22	43.90	43.40	0.35	0.45	0.57	0.10	0.46	0.63
3400	40.77	41.03	45.53	0.26	0.46	0.55	0.12	0.48	0.73
3500	39.52	37.85	38.52	0.37	0.52	0.67	0.22	0.52	0.74
3600	40.75	36.32	39.18	0.51	0.58	0.81	0.19	0.55	0.74
3700	37.40	36.87	40.60	0.48	0.65	0.83	0.21	0.61	0.83
3800	34.90	35.75	35.43	0.54	0.73	1.02	0.20	0.68	0.96
3900	35.48	34.78	35.91	0.71	0.89	1.11	0.34	0.70	1.03
4000	35.35	36.64	38.89	0.72	1.08	1.83	0.30	0.83	1.11
4100	29.66	37.16	25.65	1.16	2.58	4.75	0.68	0.94	1.27
4200	23.93	20.86	21.62	5.87	4.18	3.59	0.67	1.30	1.66
4300	18.08	24.46	28.60	4.31	2.87	1.95	1.02	1.29	1.69
4400	23.84	24.34	22.93	1.33	1.50	1.89	1.05	1.60	2.29
4500	20.72	22.10	24.44	1.13	1.48	1.49	1.28	2.20	3.44

REV. X2
SXLP-380+
101124
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SXLP-380+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
1	2.04	1.99	2.07
10	2.11	2.09	2.13
20	2.16	2.16	2.17
30	2.15	2.15	2.16
40	2.15	2.15	2.16
50	2.15	2.15	2.16
60	2.16	2.16	2.16
70	2.16	2.16	2.17
80	2.17	2.16	2.17
90	2.18	2.17	2.18
100	2.18	2.18	2.19
110	2.19	2.19	2.20
120	2.21	2.20	2.21
130	2.22	2.22	2.22
140	2.23	2.23	2.23
150	2.25	2.24	2.25
160	2.26	2.26	2.26
170	2.28	2.27	2.28
180	2.30	2.29	2.29
190	2.31	2.31	2.31
200	2.34	2.33	2.34
210	2.36	2.35	2.36
220	2.38	2.38	2.39
230	2.41	2.41	2.41
240	2.44	2.44	2.45
250	2.48	2.48	2.49
260	2.52	2.52	2.53
270	2.57	2.57	2.58
280	2.63	2.63	2.64
290	2.68	2.68	2.69
300	2.74	2.74	2.75
310	2.81	2.81	2.82
320	2.88	2.88	2.89
330	2.95	2.96	2.97
340	3.03	3.03	3.05
350	3.10	3.10	3.11
360	3.25	3.27	3.28
370	3.41	3.44	3.46
380	3.61	3.64	3.67
390	3.89	3.92	3.97
400	4.22	4.28	4.33
410	4.73	4.78	4.84
420	5.20	5.23	5.26
430	5.50	5.46	5.44
440	5.43	5.32	5.25
450	4.97	4.82	4.72
460	4.21	4.09	4.00
470	3.83	3.72	3.65
480	3.35	3.26	3.19
490	2.88	2.81	2.76
500	2.50	2.45	2.41
600	1.13	1.09	1.10
700	0.75	0.70	0.71
800	3.09	1.30	5.31

REV. X2
SXLP-380+
101124
Page 2 of 2




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE





Typical Performance Curves




REV. X2
SXLP-380+
101124
Page 2 of 2

Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ± .005

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-230

REV:

OR

FILE:

98PL230


SCALE:

4:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215