

50Ω Wideband 10 MHz to 10 GHz



CASE STYLE: GU1414-2

The Big Deal

- Extremely Wideband 10 GHz
- Miniature SMT (0.15" x 0.15")

Product Overview

The TCBT-14R+ surface mount bias tee provides outstanding application versatility, covering an ultra-wide frequency range of 10 MHz to 10 GHz with excellent isolation performance over the band. Its miniature package and surface mount are space-efficient and practical for automated pick and place operation. Designed to handle 30 dBm of RF power and 200 mA input current, the TCBT-14R+ is ideal for many communications and testing applications including biasing of amplifiers and MMICs, laser diodes and active antennas.

Key Features






Feature	Advantages
Wideband	The TCBT-14R+ achieves wide 10 MHz – 10 GHz frequency range to serve a large host of applications.
Low Insertion Loss	0.6 dB typ. insertion loss enables highly efficient signal amplification with minimal impact on gain.
Excellent VSWR	Well-matched for 50Ω systems at 1.25:1 typ. VSWR.
Miniature Size	Its miniature footprint (0.15" x 0.15") makes the TCBT-14R+ a high-performing space-saver in surface mount assemblies.
Aqueous Washable	The TCBT-14R+ features a unique open casing style which allows easy washing without trapping water.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Performance Charts

TCBT-14R+



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount

Bias-Tee

TCBT-14R+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (RF port to RF&DC port) (dB)					VSWR (:1)					ISOLATION (RF port to DC port) (RF&DC port to DC port) (dB)	
	+25°C		0mA			+25°C		0mA			+25°C & 0mA	
	0mA	200mA	-40°C	+25°C	+85°C	0mA	200mA	-40°C	+25°C	+85°C	RF-DC	RF&DC-DC
10.0	0.42	0.10	0.13	0.42	0.02	1.19	1.18	1.75	1.19	1.51	36.38	35.97
50.0	0.21	0.05	0.05	0.21	0.04	1.03	1.03	1.03	1.03	1.03	67.83	76.42
100.0	0.05	0.05	0.04	0.05	0.06	1.03	1.03	1.02	1.03	1.02	65.56	66.99
500.0	0.07	0.07	0.05	0.07	0.08	1.03	1.03	1.03	1.03	1.03	60.34	56.95
1000.0	0.09	0.09	0.07	0.09	0.12	1.02	1.02	1.02	1.02	1.03	51.24	48.05
2050.0	0.14	0.14	0.11	0.14	0.19	1.02	1.02	1.02	1.02	1.03	37.50	36.11
3100.0	0.19	0.19	0.13	0.19	0.25	1.08	1.07	1.08	1.08	1.09	31.08	29.64
4000.0	0.24	0.24	0.19	0.24	0.32	1.07	1.07	1.09	1.07	1.05	29.31	27.43
5050.0	0.33	0.33	0.28	0.33	0.43	1.04	1.04	1.04	1.04	1.06	26.34	24.91
6100.0	0.44	0.44	0.39	0.44	0.55	1.04	1.04	1.09	1.04	1.05	20.43	19.27
7000.0	0.66	0.67	0.60	0.66	0.78	1.09	1.09	1.04	1.09	1.16	16.60	15.87
8050.0	0.86	0.88	0.72	0.86	1.00	1.09	1.09	1.15	1.09	1.04	17.92	17.69
9100.0	0.92	0.93	0.92	0.92	0.98	1.23	1.23	1.34	1.23	1.21	19.03	18.34
9400.0	0.94	0.95	0.93	0.94	0.99	1.29	1.29	1.35	1.29	1.26	18.86	18.17
10000.0	0.98	0.98	0.91	0.98	1.08	1.45	1.46	1.41	1.45	1.44	17.61	17.20



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

TCBT-14R+


4/3/2013

Page 1 of 1

Surface Mount Bias-Tee

TCBT-14R+

Typical Performance Curves



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. OR

TCBT-14R+

4/3/2013

Page 1 of 1


Case Style

GU

Outline Dimensions

GU1414-2

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
GU1414-2	.150 (3.81)	.150 (3.81)	.14 (3.56)	.025 (.64)	.100 (2.54)	.043 (1.09)	.030 (.76)	.050 (1.27)	.087 (2.21)	.193 (4.90)	.066 (1.68)

CASE #	M	N	P	Q	R	WT.GRAMS
GU1414-2	.031 (.79)	-	.083 (2.11)	.027 (.69)	.013 (.33)	.06

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination finish: 3-5 μ inch Gold over 120-240 μ inch Nickel Plate. All models (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350168, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site:



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVIEWS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M167305	NEW RELEASE	04/18/18	ITG	IG

SUGGESTED MOUNTING CONFIGURATION FOR
GU1414-2 CASE STYLE, "04BT03" PIN CONNECTION



CAPACITOR C1: .010 uF, 0603 SIZE

NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020 ± 0.0015 ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS \pm

3 PL DECIMALS $\pm .005$

ANGLES \pm

FRACTIONS \pm



Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, 04BT03, GU1414-2, TCBT, TB-268

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-146A	OR
FILE: 98PL146A	SCALE: 10:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



TB-268



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®



Environmental Specifications

ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215