



Mini-Circuits

SURFACE MOUNT


Bias Tee

TCBT-14R+

50Ω Wideband 10 MHz to 10 GHz

THE BIG DEAL

- Wideband, 10 MHz to 10 GHz
- Low Insertion Loss, 0.6 dB Typ.
- Excellent VSWR, 1.25:1 Typ.
- Miniature Surface Mount 0.15x0.15"
- Aqueous Washable
- Protected by US Patent 8,644,029



Generic photo used for illustration purposes only

CASE STYLE: GU1414-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Biasing Amplifiers
- Biasing of Laser Diodes
- Biasing of Active Antennas

PRODUCT OVERVIEW

The TCBT-14R+ surface mount bias tee provides outstanding application versatility, covering an ultra-wide frequency range of 10 MHz to 10 GHz with excellent isolation performance over the band. Its miniature package and surface mount are space-efficient and practical for automated pick and place operation. Designed to handle +30 dBm of RF power and 200 mA input current, the TCBT-14R+ is ideal for many communications and testing applications including biasing of amplifiers and MMICs, laser diodes and active antennas.

KEY FEATURES

Feature	Advantages
Wideband	The TCBT-14R+ achieves wide 10 MHz to 10 GHz frequency range to serve a large host of applications.
Low Insertion Loss	0.6 dB typ. insertion loss enables highly efficient signal amplification with minimal impact on gain.
Excellent VSWR	Well-matched for 50Ω systems at 1.25:1 typ. VSWR.
Miniature Size	Its miniature footprint (0.15x0.15") makes the TCBT-14R+ a high-performing space-saver in surface mount assemblies.
Aqueous Washable	The TCBT-14R+ features a unique open casing style which allows easy washing without trapping water.





Mini-Circuits

SURFACE MOUNT

Bias Tee

TCBT-14R+

50Ω Wideband 10 MHz to 10 GHz

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		10000	MHz
Insertion Loss	10-10000	0.05	0.6	1.6	dB
Isolation ¹	10-10000	15	33		dB
VSWR	10-10000	1.02	1.25	1.7	:1
DC Resistance, DC to RF and DC Port	10-10000		1.0		Ohms


1. Isolation between DC to RF & DC 14 dB/min at 6-10 GHz.

ABSOLUTE MAXIMUM RATINGS

Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
RF Power	+30 dBm max.
Voltage at DC Port	+25 V max.
Input Current	200 mA

Permanent damage may occur if any of these limits are exceeded.

FUNCTIONAL SCHEMATIC





Bias Tee

50Ω Wideband 10 MHz to 10 GHz

RF	1
RF & DC	2
DC	4
NOT USED	3

Figure 1 illustrates the dimensions and nomenclature of the test specimen. The diagrams show the specimen's geometry, including dimensions A, B, C, D, E, F, G, H, and J, and locations 1, 2, 3, and 4. The legend indicates that hatched areas denote metallization and cross-hatched areas denote solder mask.

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

A	B	C	D	E	F	G	H
0.150	0.150	0.140	0.025	0.100	0.043	0.030	0.050
3.81	3.81	3.56	0.64	2.54	1.09	0.76	1.27
J	K	L	M	P	Q	R	wt
0.087	0.193	0.066	0.031	0.083	0.027	0.013	grams
2.21	4.90	1.68	0.79	2.11	0.69	0.33	0.06



SURFACE MOUNT

Bias Tee






TCBT-14R+

Mini-Circuits

50Ω Wideband 10 MHz to 10 GHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)		Isolation 0 mA	
		RF	RF & DC	RF-DC	RF & DC - DC
10	0.42	1.19	1.42	36.38	35.97
50	0.21	1.03	1.03	67.83	76.42
100	0.05	1.03	1.02	65.56	66.99
500	0.07	1.03	1.02	60.34	56.95
1000	0.09	1.02	1.02	51.24	48.05
2050	0.14	1.02	1.03	37.50	36.11
3100	0.19	1.08	1.08	31.08	29.64
4000	0.24	1.07	1.07	29.31	27.43
5050	0.33	1.04	1.03	26.34	24.91
6100	0.44	1.04	1.01	20.43	19.27
7000	0.66	1.09	1.07	16.60	15.87
8050	0.86	1.09	1.15	17.92	17.69
9100	0.92	1.23	1.22	19.03	18.34
9400	0.94	1.29	1.27	18.86	18.17
10000	0.98	1.45	1.41	17.61	17.20








NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits


Typical Performance Data

FREQUENCY	INSERTION LOSS (RF port to RF&DC port) (dB)					VSWR (:1)					ISOLATION (RF port to DC port) (RF&DC port to DC port) (dB)	
	+25°C		0mA			+25°C		0mA			+25°C & 0mA	
	0mA	200mA	-40°C	+25°C	+85°C	0mA	200mA	-40°C	+25°C	+85°C	RF-DC	RF&DC-DC
(MHz)												
10.0	0.42	0.10	0.13	0.42	0.02	1.19	1.18	1.75	1.19	1.51	36.38	35.97
50.0	0.21	0.05	0.05	0.21	0.04	1.03	1.03	1.03	1.03	1.03	67.83	76.42
100.0	0.05	0.05	0.04	0.05	0.06	1.03	1.03	1.02	1.03	1.02	65.56	66.99
500.0	0.07	0.07	0.05	0.07	0.08	1.03	1.03	1.03	1.03	1.03	60.34	56.95
1000.0	0.09	0.09	0.07	0.09	0.12	1.02	1.02	1.02	1.02	1.03	51.24	48.05
2050.0	0.14	0.14	0.11	0.14	0.19	1.02	1.02	1.02	1.02	1.03	37.50	36.11
3100.0	0.19	0.19	0.13	0.19	0.25	1.08	1.07	1.08	1.08	1.09	31.08	29.64
4000.0	0.24	0.24	0.19	0.24	0.32	1.07	1.07	1.09	1.07	1.05	29.31	27.43
5050.0	0.33	0.33	0.28	0.33	0.43	1.04	1.04	1.04	1.04	1.06	26.34	24.91
6100.0	0.44	0.44	0.39	0.44	0.55	1.04	1.04	1.09	1.04	1.05	20.43	19.27
7000.0	0.66	0.67	0.60	0.66	0.78	1.09	1.09	1.04	1.09	1.16	16.60	15.87
8050.0	0.86	0.88	0.72	0.86	1.00	1.09	1.09	1.15	1.09	1.04	17.92	17.69
9100.0	0.92	0.93	0.92	0.92	0.98	1.23	1.23	1.34	1.23	1.21	19.03	18.34
9400.0	0.94	0.95	0.93	0.94	0.99	1.29	1.29	1.35	1.29	1.26	18.86	18.17
10000.0	0.98	0.98	0.91	0.98	1.08	1.45	1.46	1.41	1.45	1.44	17.61	17.20


*Typical Performance Curves***Insertion Loss @ +25°C****Insertion Loss @ 0mA****VSWR @ +25°C****VSWR @ 0mA****Isolation @ +25°C & 0mA**

Outline Dimensions

GU1414-2



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
GU1414-2	.150 (3.81)	.150 (3.81)	.14 (3.56)	.025 (.64)	.100 (2.54)	.043 (1.09)	.030 (.76)	.050 (1.27)	.087 (2.21)	.193 (4.90)	.066 (1.68)

CASE #	M	N	P	Q	R	WT.GRAMS
GU1414-2	.031 (.79)	-	.083 (2.11)	.027 (.69)	.013 (.33)	.06

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination finish: 3-5µinch Gold over 120-240 µinch Nickel Plate. All models (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F102

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M167305	NEW RELEASE	04/18/18	ITG	IG

SUGGESTED MOUNTING CONFIGURATION FOR
GU1414-2 CASE STYLE, "04BT03" PIN CONNECTION



CAPACITOR C1: .010 μ F, 0603 SIZE

NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020 ± 0.0015 ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG
TOLERANCES ON:	CHECKED	GF
2 PL DECIMALS $\pm$	APPROVED	IG
3 PL DECIMALS $\pm$.005		
ANGLES $\pm$		
FRACTIONS $\pm$		



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, 04BT03, GU1414-2, TCBT, TB-268

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-146A	OR
FILE:	98PL146A	SCALE:	10:1
SHEET:	1	OF	1

Evaluation Board and Circuit



TB-268



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215