

Surface Mount  **RF Transformer**

50Ω 20 to 4500 MHz

TCM4-452X+



Generic photo used for illustration purposes only

CASE STYLE: DB1627

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

 Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Features

- wide bandwidth 20 to 4500 MHz
- balanced transmission line
- good return loss
- aqueous washable


Applications

- PCS
- wideband push-pull amplifiers
- cellular

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio (secondary/primary)			4		
Frequency Range		20	—	4500	MHz
Insertion Loss	20 - 4500	—	1.5	3.0	dB
Amplitude Unbalance	20 - 4500	—	0.5	—	dB
Phase Unbalance	20 - 4500	—	5	—	Degree

Electrical Schematic



Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.4W
DC Current	30mA

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number
PRIMARY DOT	3
PRIMARY	2
SECONDARY DOT	4
SECONDARY	6
GND	2, 5
NOT USED	1

Product Marking




Config. H




TCM4-452X+


Outline Drawing



PCB Land Pattern



Demo Board MCL P/N: TB-697+ Suggested PCB Layout (PL-381)







- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. 0402 SIZE CHIP COMPONENT FOOTPRINT IS SHOWN FOR REFERENCE. FOR COMPONENT VALUE REFER TO TB-697+.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Dimensions (inch/mm)

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K	wt	
.028	.065	.190	.030	grams	
0.71	1.65	4.83	0.76	0.15	

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Input R. Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
10.0	1.54	15.59	0.04	0.06
500.0	1.44	16.30	0.02	2.83
1000.0	1.45	12.89	0.03	4.85
1500.0	1.55	10.82	0.01	6.26
2000.0	1.60	10.63	0.17	6.46
2500.0	1.57	12.23	0.19	5.36
3000.0	1.54	15.11	0.22	4.87
3500.0	1.58	17.73	0.61	2.79
4000.0	1.73	21.68	0.85	0.04
4500.0	1.82	33.66	0.89	0.58



Additional Notes





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
10.0	1.54	15.59	0.04	0.06
30.0	1.49	16.57	0.03	0.22
50.0	1.49	16.62	0.02	0.36
70.0	1.50	16.73	0.02	0.49
90.0	1.49	16.79	0.02	0.62
100.0	1.49	16.83	0.02	0.65
200.0	1.50	16.95	0.03	1.21
300.0	1.48	16.92	0.01	1.77
400.0	1.46	16.72	0.01	2.30
500.0	1.44	16.30	0.02	2.83
600.0	1.44	15.66	0.02	3.24
700.0	1.43	14.95	0.01	3.64
800.0	1.43	14.23	0.01	4.04
900.0	1.44	13.55	0.02	4.45
1000.0	1.45	12.89	0.03	4.85
1100.0	1.47	12.30	0.04	5.20
1200.0	1.49	11.81	0.04	5.54
1300.0	1.51	11.40	0.04	5.75
1400.0	1.53	11.06	0.03	6.01
1500.0	1.55	10.82	0.01	6.26
1600.0	1.57	10.63	0.02	6.47
1700.0	1.58	10.52	0.05	6.64
1800.0	1.59	10.48	0.08	6.71
1900.0	1.59	10.53	0.13	6.71
2000.0	1.60	10.63	0.17	6.46
2100.0	1.59	10.80	0.22	6.21
2200.0	1.59	11.03	0.23	5.84
2300.0	1.58	11.37	0.22	5.67
2400.0	1.58	11.77	0.20	5.54
2500.0	1.57	12.23	0.19	5.36
2600.0	1.56	12.74	0.19	4.94
2700.0	1.55	13.32	0.17	4.76
2800.0	1.55	13.92	0.15	4.85
2900.0	1.54	14.52	0.17	4.91
3000.0	1.54	15.11	0.22	4.87
3100.0	1.54	15.69	0.28	4.67
3200.0	1.54	16.24	0.34	4.26
3300.0	1.54	16.69	0.42	3.85
3400.0	1.56	17.24	0.51	3.36
3500.0	1.58	17.73	0.61	2.79
3600.0	1.60	18.30	0.71	2.20
3700.0	1.64	19.02	0.79	1.55
3800.0	1.67	19.77	0.82	1.02
3900.0	1.70	20.62	0.85	0.42
4000.0	1.73	21.68	0.85	0.04
4100.0	1.76	23.33	0.89	0.20
4200.0	1.79	25.85	0.91	0.04
4300.0	1.81	29.34	0.92	0.15
4400.0	1.82	33.11	0.91	0.34
4500.0	1.82	33.66	0.89	0.58


Typical Performance Data



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3Pl. ± .005

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M138571	NEW RELEASE	10/02/12	GF	DJ

SUGGESTED MOUNTING CONFIGURATION FOR DB1627 CASE STYLE, "06TH02" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 3. 0402 SIZE CHIP COMPONENT FOOTPRINT IS SHOWN FOR REFERENCE. FOR COMPONENT VALUE REFER TO TB-697+.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF	09/28/12
	CHECKED	IL	10/02/12
	APPROVED	DJ	10/02/12



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 06TH02, DB1627, TB-697+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-381	REV: OR
FILE: 98PL381	SCALE: 10:1	SHEET: 1 OF 1	


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215