



top hat
SURFACE MOUNT
RF Transformer

TCM2-43X+

50Ω 10 to 4000 MHz

FEATURES

- Wide bandwidth 10 to 4000 MHz
- Balanced transmission line
- Excellent return loss
- Aqueous washable

APPLICATIONS

- PCS
- Wideband push-pull amplifiers
- Cellular



Generic photo used for illustration purposes only

CASE STYLE: DB1627


+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter | Frequency (MHz) | Min. | Typ. | Max. | Units |
|-------------------------------------|-----------------|------|------|------|--------|
| Impedance Ratio (secondary/primary) | | | 2 | | Ohm |
| Frequency Range | | 10 | | 4000 | MHz |
| Insertion Loss | 10-4000 | — | 1.3 | 3.0 | dB |
| Amplitude Unbalance | 10-4000 | — | 0.5 | — | dB |
| Phase Unbalance | 10-4000 | — | 7 | — | Degree |

ELECTRICAL SCHEMATIC




MAXIMUM RATINGS

| Parameter | Ratings |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Power | 0.4 W |
| DC Current | 30 mA |

Permanent damage may occur if any of these limits are exceeded.

CONFIGURATION K



REV. B
ECO-013812
TCM2-43X+
DJ/CP/AM
220620





top hat
SURFACE MOUNT
RF Transformer

TCM2-43X+

Mini-Circuits


50Ω 10 to 4000 MHz

PIN CONNECTIONS

| | |
|---------------|-----|
| PRIMARY DOT | 3 |
| PRIMARY | 1,2 |
| SECONDARY DOT | 6 |
| SECONDARY | 4 |
| GND | 1,2 |
| NOT USED | 5 |

PRODUCT MARKING: GJ

DEMOBOARD MCL P/N: TB-TCM2-43X+
SUGGESTED PCB LAYOUT (PL-380)




| COMPONENT | SIZE |
|-----------|------|
| C1, C2 | 0402 |


- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.020 \pm .0015$ "; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-676+.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

OUTLINE DRAWING



PCB Land Pattern



OUTLINE DIMENSIONS (Inches/mm)

| A | B | C | D | E | F |
|------|------|------|------|-------|------|
| .160 | .150 | .160 | .050 | .040 | .025 |
| 4.06 | 3.81 | 4.06 | 1.27 | 1.02 | 0.64 |
| G | H | J | K | wt | |
| .028 | .065 | .190 | .030 | grams | |
| 0.71 | 1.65 | 4.83 | 0.76 | 0.15 | |

TAPE & REEL INFORMATION: F47






top hat
SURFACE MOUNT
RF Transformer

TCM2-43X+

50Ω 10 to 4000 MHz

TYPICAL PERFORMANCE DATA

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) | Amplitude Unbalance (dB) | Phase Unbalance (deg) |
|-----------------|---------------------|------------------|--------------------------|-----------------------|
| 10 | 1.88 | 15.46 | 0.08 | 0.74 |
| 100 | 1.76 | 15.22 | 0.03 | 1.07 |
| 500 | 1.61 | 14.98 | 0.24 | 4.40 |
| 1000 | 1.35 | 15.87 | 0.32 | 5.96 |
| 1500 | 1.17 | 17.86 | 0.09 | 6.73 |
| 2000 | 1.09 | 21.30 | 0.23 | 7.01 |
| 2500 | 1.11 | 24.93 | 0.52 | 7.71 |
| 3000 | 1.17 | 25.06 | 0.82 | 6.95 |
| 3500 | 1.26 | 23.10 | 0.79 | 5.04 |
| 4000 | 1.55 | 16.24 | 0.81 | 3.16 |



- NOTES
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



RF Transformer


TCM2-43X+

Typical Performance Data


| FREQUENCY (MHz) | AVERAGE INSERTION LOSS (dB) | INPUT RETURN LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (deg.) |
|--------------------|--------------------------------------|---------------------------------|--------------------------------|------------------------------|
| 10.0 | 1.88 | 15.46 | 0.08 | 0.74 |
| 30.0 | 1.78 | 15.47 | 0.04 | 0.31 |
| 50.0 | 1.76 | 15.41 | 0.03 | 0.42 |
| 70.0 | 1.76 | 15.32 | 0.03 | 0.67 |
| 90.0 | 1.76 | 15.25 | 0.03 | 0.94 |
| 100.0 | 1.76 | 15.22 | 0.03 | 1.07 |
| 200.0 | 1.75 | 15.12 | 0.06 | 2.17 |
| 300.0 | 1.72 | 15.07 | 0.12 | 3.15 |
| 400.0 | 1.67 | 14.99 | 0.18 | 3.88 |
| 500.0 | 1.61 | 14.98 | 0.24 | 4.40 |
| 600.0 | 1.56 | 15.10 | 0.28 | 4.80 |
| 700.0 | 1.50 | 15.24 | 0.31 | 5.16 |
| 800.0 | 1.44 | 15.41 | 0.33 | 5.46 |
| 900.0 | 1.39 | 15.63 | 0.34 | 5.73 |
| 1000.0 | 1.35 | 15.87 | 0.32 | 5.96 |
| 1100.0 | 1.30 | 16.19 | 0.30 | 6.13 |
| 1200.0 | 1.26 | 16.53 | 0.26 | 6.28 |
| 1300.0 | 1.23 | 16.87 | 0.22 | 6.44 |
| 1400.0 | 1.19 | 17.36 | 0.16 | 6.60 |
| 1500.0 | 1.17 | 17.86 | 0.09 | 6.73 |
| 1600.0 | 1.14 | 18.45 | 0.06 | 6.78 |
| 1700.0 | 1.12 | 19.03 | 0.08 | 6.80 |
| 1800.0 | 1.11 | 19.62 | 0.11 | 6.85 |
| 1900.0 | 1.10 | 20.40 | 0.17 | 6.89 |
| 2000.0 | 1.09 | 21.30 | 0.23 | 7.01 |
| 2100.0 | 1.09 | 22.29 | 0.28 | 7.08 |
| 2200.0 | 1.10 | 23.36 | 0.32 | 7.16 |
| 2300.0 | 1.10 | 24.06 | 0.35 | 7.33 |
| 2400.0 | 1.11 | 25.08 | 0.43 | 7.53 |
| 2500.0 | 1.11 | 24.93 | 0.52 | 7.71 |
| 2600.0 | 1.12 | 25.24 | 0.60 | 7.74 |
| 2700.0 | 1.14 | 25.59 | 0.67 | 7.71 |
| 2800.0 | 1.15 | 25.75 | 0.72 | 7.56 |
| 2900.0 | 1.16 | 25.36 | 0.78 | 7.32 |
| 3000.0 | 1.17 | 25.06 | 0.82 | 6.95 |
| 3100.0 | 1.19 | 24.89 | 0.84 | 6.44 |
| 3200.0 | 1.20 | 24.74 | 0.84 | 6.01 |
| 3300.0 | 1.21 | 24.43 | 0.80 | 5.61 |
| 3400.0 | 1.23 | 24.09 | 0.80 | 5.25 |
| 3500.0 | 1.26 | 23.10 | 0.79 | 5.04 |
| 3600.0 | 1.30 | 22.31 | 0.78 | 4.71 |
| 3700.0 | 1.34 | 20.50 | 0.77 | 4.38 |
| 3800.0 | 1.40 | 18.85 | 0.77 | 4.03 |
| 3900.0 | 1.47 | 17.47 | 0.79 | 3.76 |
| 4000.0 | 1.55 | 16.24 | 0.81 | 3.16 |

Typical Performance Data


Average Insertion Loss




Input Return Loss




Amplitude Unbalance




Phase Unbalance



Outline Dimensions



PCB Land Pattern



| CASE # | A | B | C | D | E | F | G | H | J | K | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB1627 | .160 (4.06) | .150 (3.81) | .160 (4.06) | .050 (1.27) | .040 (1.02) | .025 (0.64) | .028 (0.71) | .065 (1.65) | .190 (4.83) | .030 (0.76) | .15 |


Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note |
|----------------|-------------------------|-------------------|---------------------------|
| 12 | 8 | 13 | 1000, 2000 |
| | | 7 | 20, 50, 100, 200, 500 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------|----------|----|------|
| OR | M138367 | NEW RELEASE | 08/15/12 | AV | DJ |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION
FOR DB1627 CASE STYLE, "06TK02" PIN CODE



| COMPONENT | SIZE |
|-----------|------|
| C1, C2 | 0402 |

- NOTES:**
- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-676+.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|--|----------|-------------|
| DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± | DRAWN | AV 08/13/12 |
| | CHECKED | IL 08/15/12 |
| | APPROVED | DJ 08/15/12 |

 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235



PL, 06TK02, DB1627, TB-676+

 Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|-------|------------|-------------|---------------|
| A | 15542 | 98-PL-380 | OR |
| FILE: | 98PL380 | SCALE: 10:1 | SHEET: 1 OF 1 |

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |