Surface Mount

RF Transformer

TRC1-1K122-75+

75Ω 20 to 1250 MHz 1:1 Ratio

The Big Deal

- Low insertion loss, 0.9 dB typ.
- Good return loss, 23 dB typ.
- Low unbalance, 0.2 dB, 4°
- Power handling up to 2.0W



CASE STYLE: GU2644

Product Overview

The TRC1-1K122-75+ is a 75Ω surface mount transmission line transformer with a 1:1 secondary/primary impedance ratio covering the 20 to 1250 MHz band, meeting bandwidth requirements for DOCSIS® 3.1 compliant systems and equipment, among other applications. This model handles RF input power up to 2W and provides low insertion loss, good return loss and low unbalance. Measuring only 0.12 x 0.17 x 0.13”, the unit features core and wire construction mounted on a 4-pad plastic base, ideal for dense PCB layouts.

Key Features

Feature	Advantages
Wideband, 20 to 1250 MHz	TRC1-1K122-75+ supports a variety of applications including CATV and DOCSIS 3.1 systems and equipment.
Low insertion loss, 0.9 dB	Enables excellent signal power transmission from input to output.
Good return loss, 23 dB typ.	Excellent matching for 75Ω systems with minimal signal reflection.
Low unbalance, 0.2 dB, 4°	Low unbalance can improve a system’s electromagnetic compatibility by rejecting unwanted common-mode noise.
Small footprint, 0.12 x 0.17”	Accommodates tight space requirements for dense PCB layouts.

Surface Mount

RF Transformer

TRC1-1K122-75+

75Ω 20 to 1250 MHz 1:1 Ratio

Features

- wideband, 20 to 1250 MHz
- balanced transmission line
- good return loss, 23 dB typ.
- excellent amplitude unbalance, 0.2 dB typ. and phase unbalance, 4 deg typ.
- plastic base with leads
- aqueous washable

Applications

- balanced to unbalanced transformation
- push-pull amplifiers
- PCS/DCS
- MMDS
- DOCSIS 3.1



Generic photo used for illustration purposes only

CASE STYLE: GU2644

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio			1		
Frequency Range		20	—	1250	MHz
Insertion Loss (Average)	20 - 1000 1000 - 1250	— —	0.9 0.68	1.4 1.0	dB
Amplitude Unbalance	20 - 1250	—	0.2	1.0	dB
Phase Unbalance	20 - 1250	—	4	10	Degree
Input Return Loss	20 - 1250	14	23	—	dB
Input Power	20 - 1250	—	—	2.0	Watt

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
DC Current	300mA

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


Function	Pin Number
PRIMARY DOT (INPUT)	1
PRIMARY (GND)	2
SECONDARY DOT (OUTPUT)	3
SECONDARY (OUTPUT)	4

Config. K



Mini-Circuits®
www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Outline Drawing




Outline Dimensions (inch / mm)


A	B	C	D	E	F	G
.117	.170	.130	.100	.102	.035	.040
2.97	4.32	3.30	2.54	2.59	0.89	1.02

H	J	K	L	M	N	wt
.039	.124	.047	.007	0.098	.145	grams
0.99	3.15	1.19	0.18	2.49	3.68	0.10

Typical Performance Data

Frequency (MHz)	Insertion Loss (Avg.) (dB)	Input R. Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
20.00	0.98	17.13	0.06	0.20
75.00	0.93	20.94	0.08	0.73
100.00	0.92	21.69	0.09	0.91
350.00	0.85	25.15	0.12	2.65
550.00	0.80	26.82	0.09	3.78
700.00	0.75	27.12	0.06	4.39
800.00	0.72	26.63	0.03	4.66
900.00	0.68	25.76	0.02	4.93
1100.00	0.61	23.67	0.11	5.12
1250.00	0.56	22.24	0.20	5.18





Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

RF Transformer TRC1-1K122-75+


Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
5	1.35	9.54	0.05	0.27
9	1.16	13.61	0.05	0.02
10	1.15	14.21	0.05	0.04
20	1.07	17.13	0.06	0.21
30	1.01	18.42	0.07	0.32
40	0.96	19.24	0.07	0.44
45	0.95	19.56	0.08	0.46
50	0.93	19.86	0.08	0.50
75	0.89	20.94	0.08	0.73
100	0.87	21.69	0.09	0.91
125	0.85	22.05	0.09	1.20
150	0.85	22.82	0.10	1.35
250	0.82	24.06	0.11	2.02
350	0.79	25.15	0.12	2.65
450	0.77	26.08	0.11	3.25
550	0.75	26.82	0.09	3.78
575	0.75	26.95	0.09	3.88
600	0.74	27.03	0.09	4.01
625	0.73	27.08	0.08	4.13
650	0.73	27.10	0.07	4.23
700	0.72	27.12	0.06	4.39
750	0.71	26.97	0.04	4.57
800	0.70	26.63	0.03	4.66
850	0.70	26.23	0.01	4.85
900	0.69	25.76	0.02	4.93
950	0.68	25.32	0.04	4.99
975	0.68	25.08	0.05	5.06
1000	0.68	24.80	0.06	5.08
1025	0.68	24.51	0.07	5.10
1050	0.67	24.25	0.09	5.13
1100	0.67	23.67	0.11	5.12
1150	0.66	23.24	0.14	5.18
1175	0.66	23.00	0.15	5.16
1200	0.66	22.76	0.17	5.19
1225	0.66	22.47	0.18	5.22
1250	0.66	22.24	0.20	5.18
1350	0.66	21.37	0.27	5.19
1400	0.65	20.97	0.30	5.16
1450	0.65	20.59	0.34	5.16
1500	0.65	20.21	0.38	5.14


RF Transformer TRC1-1K122-75+

Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance




Phase Unbalance




Case Style GU

Outline Dimensions GU2644



PCB Land Pattern



Suggested Layout
Tolerance to be within ±.002

Wires shown are for reference only.

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
GU2644	.117 (2.97)	.170 (4.32)	.130 (3.30)	.100 (2.54)	.102 (2.59)	.035 (.89)	.040 (1.02)	.039 (.99)	.124 (3.15)	.047 (1.19)	.007 (.018)	.098 (2.49)	.145 (3.68)	.10


Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

Notes:
1. Case material: Plastic Base.
2. Termination finish: Tin Plate.


Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles
GU1604, GU1804, GU2644, TT1618-2

Applicable Case Styles
MZ4532C, NM1812C, NM1812C-1, NM1812C-2, NM1812C-3, NM1812C-5, NM1812C-6, NM3237 NM1812C-9

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.